



DEWALT 54V XR FLEXVOLT 32mm SDS-Plus Rotary Hammer – Bare Unit

DCH417NT-XJ



- Brushless motor offers incredible efficiency and increased power delivery
- Category-leading high speed drilling performance at more than 74 holes (18mm Ø x 80mm) per charge
- Perform & Protect: best-in-class vibration at 6.3m/s², minimising user fatigue
- Ideal for drilling anchors and fixing holes into concrete, brick and masonry from 4mm to 32mm
- Quick release SDS-Plus toolholder and keyless chuck supplied for easy switching between hammer / rotary hammer and rotary only applications
- Rotation stop mode for light chiselling in plaster, tiles and render and impact stop mode for rotary only drilling in wood and metal
- Bright white LED with delay feature improves visibility
- An anti rotation system detects a loss of tool control, and reacts by instantly cutting the power
- Wireless tool control transmitter which allows the tool to be wirelessly paired with another wtc device, such as a dust extractor, for automatic activation and shut down
- Tool Connect ready (tag is NOT included) provides the option for jobsite connectivity for inventory management

Description:

The DEWALT 54V XR FLEXVOLT Brushless 3 Mode Cordless SDS+ Hammer Drill has been engineered to be a category leading drill delivering high speed drilling performance at more than 74 holes (18mm Ø x 80mm) per charge. This innovative drill is part of the 54V XR FLEXVOLT platform offering unrivalled enhanced runtime and performance. The brushless motor offers incredible efficiency and increased power delivery, resulting in less wear and increased longevity of the tool. The drill features rotation stop mode for light chiselling in plaster, tiles and render and impact stop mode for rotary only drilling in wood and metal. Carrying the Perform & Protect shield, offering the best-in-class vibration at 6.3m/s² minimising user fatigue and anti-rotation system which detects a loss of tool control and reacts instantly by cutting power. The wireless tool control technology provides users with increased control and convenience, as well as a cleaner, less harmful working environment. Practical and efficient, WTC enables the tool to be wirelessly paired with another wireless tool control device, such as a dust extractor, for automatic activation and shut down delivering increased runtime, efficiency and productivity.

What we like – Cordless 54V XR FLEXVOLT system delivers corded performance. Wireless Tool Control technology offers greater connectivity and convenience saving time and effort.

Supplied With:

- 1 x Multi-position side handle
- 1 x Deep TSTAK kit box
- 1 x Quick release SDS-Plus toolholder
- 1 x Quick release 13mm 3 jaw chuck

Specifications	
Battery	XR Lithium-Ion
Voltage	54 V
Max. Drilling Capacity (Core bit)	127 mm
Max. Drilling Capacity (Concrete)	32 mm
Max. Drilling Capacity (Wood)	32 mm
Max. Drilling Capacity (Metal)	13 mm
Impact Energy	4.5 J
No Load Speed	0-725 rpm
Hand/Arm Vibration - Hammer drilling into concrete	6.3 m/s ²
Weight	4.1 kg