



$A = 2.54 * \frac{n^p}{2} + 0.40 \pm 0.35$   
 $B = 2.54 * \frac{n^p}{2} - 2.54 \pm 0.20$   
 Pin Number = 2 ~ 80

**Technical Data**  
 Material:  
 Contact material: Brass  
 Plating: Gold Flash  
 Insulator material: Black polyester UL94V-0  
 Standard: PBT+30%G.F

**Electrical:**  
 Current rating: 3amps/contact max.  
 Contact resistance:  $\leq 20m\Omega$  /contact  
 Insulation resistance:  $\geq 1000M\Omega$  at V=100V  
 Withstanding voltage: 550V AC/minute

**Mechanical:**  
 Soldering temperature: +220°C, 4s max  
 UNSPECIFIED TOLERANCE:  $\pm 0.20$

APPROVALS		DATE	DRAWING NO.		SHEET	
DRAWN	G.M.Chen	2015/7/17	DW254W-22-XX-85		SHEET 1 OF 1	
CHECKED			CONNECTION		PROJ.	
APPROVALS			PART NO.		SCALE: 1:1	
			UNIT: mm		DRAWING NO.	
			ANGLE		PROJ.	
			±2'			
TOLERANCES ARE			30~40 ±	±0.30		
			10~30	±0.20		
			5~10	±0.15		
			~5	±0.10		
ECN NO.	REV.	DATE.	DESCRIPTION.			
	A		NEW			

**DEALON 德之隆**  
 ELECTRONICS CO.,LTD