

Rubber hose for use with Propane/Butane cutting and welding and allied processes. Suitable for Liquid Petroleum Gas (LPG), Methylacetylene-propadiene (MPS) gas, Compressed Natural Gas (CNG).

- Inner tube: Synthetic rubber resistant to LPG and Propane/Butane gases
- Reinforcement: High tensile synthetic textile.
- External cover: Orange synthetic rubber resistant to abrasion and weather
- **NON RETURN VALVE in the outlet**
- Temperature: -20°C / +60°C
- Safety factor: 3 : 1
- Marking: In compliance with the below mentioned standard.
- Workpressure: 20 bar
- Bursting pressure: 60 bar
- **Standards: ISO 3821 (hose) EN 1256 (hose assembly)**

Art. Nr.	Ø int × Ø ext	Inlet - Outlet	Coil
849113	6 × 13 mm	G 3/8LH - G 3/8LH NRV	5 m
849114	6 × 13 mm	G 3/8LH - G 3/8LH NRV	10 m
849117	8 × 15 mm	G 3/8LH - G 3/8LH NRV	10 m
849119	10 × 17 mm	G 3/8LH - G 3/8LH NRV	5 m
849120	10 × 17 mm	G 3/8LH - G 3/8LH NRV	10 m
849121	10 × 17 mm	G 3/8LH - G 3/8LH NRV	20 m

According to standards the rubber hoses do not expire. It's reasonable to replace them periodically according to their wear and the common sense.