

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **5016471100**  
**Status:** **Active**  
**Overview:** iGrid Wire-to-Board Dual-Row System  
**Description:** 2.00mm Pitch, iGrid Female Crimp Terminal, Tin (Sn) Plating, 22-26 AWG, Bag

**Documents:**

<a href="#">3D Model (PDF)</a>	<a href="#">Application Specification 5016460000-A00 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Application Specification 5016460000-A01 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 5016479200-200 (PDF)</a>
<a href="#">Product Specification 5016461001-PS-001 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-501646-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



Series image - Reference only

**General**

Product Family	Crimp Terminals
Series	501647
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	iGrid Wire-to-Board Dual-Row System
Packaging Alternative	5016471000 (Reel)
Product Name	iGrid
UPC	822350087292

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	76.000/mg
Packaging Type	Bag
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.95-1.50mm
Wire Size AWG	22, 24, 26
Wire Size mm <sup>2</sup>	0.126-0.34

**Electrical**

Current - Maximum per Contact	2.0A
Voltage - Maximum	250V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification	5016460000-A00, 5016460000-A01
Crimp Specification	5016470000-CS-000
Packaging Specification	5016479200-200
Product Specification	5016461001-PS-001, PS-501646-001-001
Sales Drawing	5016470000-SD-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

501647 Series

**Use With**

iGrid Receptacle Housing 501646

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to-Motor Terminals PremiumGrade Hand Crimp Tool for iGrid Female Terminals, 22-26 AWG and 0.30-0.20mm <sup>2</sup> Wire	638131500
--	-----------

This document was generated on 02/07/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[501647-1100](#)