

# PESD5V0U2BT

# Ultra low capacitance bidirectional double ESD protection diode

Rev. 01 — 27 March 2007

**Product data sheet** 

### 1. Product profile

### 1.1 General description

Ultra low capacitance bidirectional double ElectroStatic Discharge (ESD) protection diode in a SOT23 (TO-236AB) small Surface-Mounted Device (SMD) plastic package designed to protect two data lines from the damage caused by ESD.

#### 1.2 Features

- Bidirectional ESD protection of two lines Ultra low leakage current: I<sub>RM</sub> = 5 nA
- Ultra low diode capacitance: C<sub>d</sub> = 2.9 pF ESD protection of up to 10 kV
- IEC 61000-4-2; level 4 (ESD)

### 1.3 Applications

- Computers and peripherals
- Audio and video equipment
- Cellular handsets and accessories
- 10/100/1000 Ethernet
- Local Area Network (LAN) equipment
- Communication systems
- Portable electronics
- Subscriber Identity Module (SIM) card protection
- FireWire
- High-speed data lines

#### 1.4 Quick reference data

Table 1. Quick reference data

 $T_{amb}$  = 25 °C unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Per diode						
$V_{RWM}$	reverse standoff voltage		-	-	5	V
C <sub>d</sub>	diode capacitance	$f = 1 MHz; V_R = 0 V$	-	2.9	3.5	pF



#### **Pinning information** 2.

Table 2 Pinning

Filling		
Description	Simplified outline	Symbol
cathode 1		
cathode 2		1
common cathode	1 2	2 006aaa155
	Description cathode 1 cathode 2	Description Simplified outline cathode 1 cathode 2

#### **Ordering information** 3.

**Ordering information** Table 3.

Type number	Package			
	Name	Description	Version	
PESD5V0U2BT	-	plastic surface-mounted package; 3 leads	SOT23	

### **Marking**

Table 4. **Marking codes** 

Type number	Marking code <sup>[1]</sup>
PESD5V0U2BT	1U*

[1] \* = -: made in Hong Kong

\* = p: made in Hong Kong

\* = t: made in Malaysia

\* = W: made in China

### 5. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
Per device					
Tj	junction temperature		-	150	°C
T <sub>amb</sub>	ambient temperature		-65	+150	°C
T <sub>stg</sub>	storage temperature		-65	+150	°C


Table 6. ESD maximum ratings

Symbol	Parameter	Conditions		Min	Max	Unit
Per diode						
V <sub>ESD</sub>	electrostatic discharge voltage	IEC 61000-4-2 (contact discharge)	[1][2]	-	10	kV
		MIL-STD-883 (human body model)		-	8	kV

<sup>[1]</sup> Device stressed with ten non-repetitive ESD pulses.

Table 7. ESD standards compliance

Standard	Conditions
Per diode	
IEC 61000-4-2; level 4 (ESD)	> 15 kV (air); > 8 kV (contact)
MIL-STD-883; class 3 (human body model)	> 4 kV



<sup>[2]</sup> Measured from pin 1 to pin 2.

### 6. Characteristics

Table 8. Characteristics

 $T_{amb}$  = 25 °C unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Per diode						
$V_{RWM}$	reverse standoff voltage		-	-	5	V
I <sub>RM</sub>	reverse leakage current	$V_{RWM} = 5 V$	-	5	100	nA
$V_{BR}$	breakdown voltage	$I_R = 5 \text{ mA}$	5.5	7	9.5	V
C <sub>d</sub>	diode capacitance	f = 1 MHz				
		$V_R = 0 V$	-	2.9	3.5	pF
		$V_R = 5 V$	-	1.9	-	pF
r <sub>dif</sub>	differential resistance	$I_R = 1 \text{ mA}$	-	-	100	Ω




Fig 2. Diode capacitance as a function of reverse voltage; typical values






Fig 3. V-I characteristics for a bidirectional ESD protection diode



### 7. Application information

The PESD5V0U2BT is designed for the bidirectional protection of two signal lines from the damage caused by ESD pulses. The PESD5V0U2BT may be used on lines where the signal polarities are either positive or negative with respect to ground.




#### Circuit board layout and protection device placement

Circuit board layout is critical for the suppression of ESD, Electrical Fast Transient (EFT) and surge transients. The following guidelines are recommended:

- 1. Place the PESD5V0U2BT as close to the input terminal or connector as possible.
- 2. The path length between the PESD5V0U2BT and the protected line should be minimized.
- 3. Keep parallel signal paths to a minimum.
- 4. Avoid running protected conductors in parallel with unprotected conductors.
- 5. Minimize all Printed-Circuit Board (PCB) conductive loops including power and ground loops.
- 6. Minimize the length of the transient return path to ground.
- 7. Avoid using shared transient return paths to a common ground point.
- 8. Ground planes should be used whenever possible. For multilayer PCBs, use ground vias.

### 8. Package outline



### 9. Packing information


Table 9. Packing methods

The indicated -xxx are the last three digits of the 12NC ordering code.[1]

Type number	Package	Description	Packing	Packing quantity	
			3000	10000	
PESD5V0U2BT	SOT23	4 mm pitch, 8 mm tape and reel	-215	-235	

[1] For further information and the availability of packing methods, see Section 13.

### 10. Soldering



# PESD5V0U2BT

Ultra low capacitance bidirectional double ESD protection diode

### 11. Revision history

### Table 10. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
PESD5V0U2BT_1	20070327	Product data sheet	-	-

### 12. Legal information

#### 12.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <a href="http://www.nexperia.com">http://www.nexperia.com</a>.

#### 12.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

### 12.3 Disclaimers

**General** — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — Nexperia products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or

malfunction of a Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia accepts no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nexperia.com/profile/terms">http://www.nexperia.com/profile/terms</a>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by Nexperia. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

#### 12.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

#### 13. Contact information

For additional information, please visit: http://www.nexperia.com

For sales office addresses, send an email to: <a href="mailto:salesaddresses@nexperia.com">salesaddresses@nexperia.com</a>

### **Nexperia**

# PESD5V0U2BT

Ultra low capacitance bidirectional double ESD protection diode

### 14. Contents

1	Product profile
1.1	General description
1.2	Features
1.3	Applications 1
1.4	Quick reference data
2	Pinning information
3	Ordering information
4	Marking
5	Limiting values
6	Characteristics4
7	Application information 6
8	Package outline
9	Packing information 7
10	Soldering 8
11	Revision history
12	Legal information
12.1	Data sheet status
12.2	Definitions
12.3	Disclaimers
12.4	Trademarks
13	Contact information
4.4	Contents

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nexperia:

PESD5V0U2BT,215