

PRODUCT SPECIFICATION

TITLE :	UNIVERSAL SERIAL BUS
	MICRO - USB CONNECTORS

TABLE OF CONTENTS

- 1.0 SCOPE
- 2.0 PRODUCT DESCRIPTION
 - 2.1 DESIGN AND CONSTRUCTION
 - 2.2 MATERIAL AND PLATING
- 3.0 APPLICABLE DOCUMENTS
 - 3.1 RATING
 - 3.2 PERFORMANCE AND TEST DESCRIPTION
 - 3.3 TEST REQUIREMENTS AND PROCEDURES
- 4.0 TEST SEQUENCE
- 5.0 REFLOW CONDITION
- 6.0 PACKAGING

REVISION:	ECR/ECN INFORMATION:	TITLE:			SHEET No.
Α	EC No: SH2014-0449	MICPO	USB CONNECTO	DC	1 of 7
A	DATE: 2014/04/24	WIICKO-	1 01 7		
DOCUMEN	T NUMBER:	CREATED / REVISED BY:	CHECKED BY:	<u>APPR</u>	OVED BY:
PS-105133-001		XQZHANG	XQZHANG	A	YIN

TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A4](V.1).DOC

molex®

PRODUCT SPECIFICATION

1.0 SCOPE

This product specification defines the mechanical, electrical and environmental performance requirements and test methods for Micro-USB connector series products.

2.0 PRODUCT DESCRIPTION

2.1 Design and Construction

Construction and physical dimensions shall be specified on the applicable sales drawing. Connector consists of a metal shell, a plastic housing, and 5 terminals.

Solder components shall meet Lead-Free soldering requirements and the connectors shall be RoHS Compliant.

2.2 Materials and Plating

Refer to respective Molex sales drawings for information on materials, plating and marking.

3.0 APPLICABLE DOCUMENTS

In the event of conflict between the requirements of this specification and the sales drawing, the sales drawing shall take precedence. In the event of conflict between the requirements of the specification and the referenced documents, this specification shall take precedence.

EIA-STANDARD-364: ELECTRICAL CONNECTOR/SOCKET TEST PROCEDURES INCLUDING ENVIRONMENTAL CLASSIFICATIONS

3.1 Rating

Item	Standard
Rated Voltage (Max.)	30V AC (rms)
Rated Current (Max.)	Signal (Pins 2,3,4): 1.0A Power (Pins 1,5): 1.8 A
Operating Temperature Range	-30°C ~ +85°C (Including Terminal Temperature Rise)
Shipping and Storage Temperature Range	-40°C ~ +85°C
Ambient Temperature (Ta):	25°C ± 2°C

3.2 Performance and Test Description

The connectors shall be designed to meet the electrical, mechanical and environmental performance requirements specified in Para. 3.3

REVISION:	ECR/ECN INFORMATION:	TITLE:			SHEET No.
Α	EC No: SH2014-0449	MICRO-	USB CONNECTO	RS	2 of 7
^	DATE: 2014/04/24	WIIOICO-	2017		
DOCUMEN	T NUMBER:	CREATED / REVISED BY:	CHECKED BY:	<u>APPR</u>	OVED BY:
PS-105133-001		XQZHANG XQZHANG		Δ	YIN

TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A4](V.1).DOC

$\widehat{\text{molex}}^{\circ}$

PRODUCT SPECIFICATION

3.3 Test Requirements and Procedures

3.3.1 Electrical Performances

Item	Requirement	Test Condition
Low Level Contact Resistance (initial)	30mΩ Max.	Mated plugs, measure by dry circuit, 20mV DC maximum, open circuit 100mA maximum. Except wire conductor resistance. EIA-364-23
Insulation Resistance (initial)	1000MΩ Min.	Mated plugs, apply 100V DC for 1 minute between adjacent terminal or ground. EIA-364-21
Dielectric Withstanding Voltage	No Breakdown	Mated plugs, apply 100V AC (rms) at 60Hz for 1 minute between adjacent terminal or ground. EIA-364-20
Temperature Rise	30°C Max.	Mated plugs and measure the temperature rise of contact when the maximum DC rated current is passed EIA-364-70
Contact Capacitance	2pF Max.	Measured between adjacent circuits of unmated connectors at 1kHz. EIA-364-30

3.3.2 Mechanical Performances

Item	Requi	irement	Test Condition
Mating / un- mating force (initial)	Mating force	35N (3.57kgf) Max.	Mating / un-mating at a rate of 12.5mm
	Un-mating force	8N (0.82kgf) Min. 25N (2.58kgf) Max.	per minute. EIA-364-13
	Contact Resistance	Δ R = 10mΩ Max.	Material (superior to do 000 position
	Mating force	35N (3.57kgf) Max.	Mated / un-mated up to 10,000 cycles repeatedly at maximum rate of 500
Durability	Un-mating force	8N (0.82kgf) Min. 25N (2.58kgf) Max.	cycles per hour. (When manually operated, mating speed should be below 200 cycles per hour.) EIA-364-09
	Appearance	No breakdown	EIA-304-09

REVISION:	ECR/ECN INFORMATION:	TITLE:			SHEET No.
Α	EC No: SH2014-0449	MICRO-	USB CONNECTO	RS	3 of 7
^	DATE: 2014/04/24	MICKO-COB CONNECTORS	3 01 7		
DOCUMENT NUMBER:		CREATED / REVISED BY: CHECKED BY: APPR		OVED BY:	
PS-105133-001		XQZHANG XQZHANG		YIN	
			TEMPLATE FILENAME	: PRODUCT SPE	CISIZE A41(V.1).DOC



PRODUCT SPECIFICATION

3.3.3 Environmental Performances

Item	Requir	ement	Test Condition
	Appearance	No Damage	Mate plugs and subject to the following vibration conditions:
Vibration	Contact Resistance	Δ R =10mΩ Max.	Random Vibration 3 mutually perpendicularly. 10~2000Hz, 0.02G2/Hz
	Discontinuity	1 microsecond Max.	20 minutes per plane EIA-364-28
	Appearance	No damage	Mate plugs and subject to the following shock conditions, 3 shocks shall be applied along 3
Mechanical Shock	Contact Resistance	ΔR =10mΩ Max.	mutually perpendicular axes, passing DC 100mA current during the test. (Total of 18 shocks) Test Pulse: Half Sine
	Discontinuity	1 microsecond Max.	Peak Value: 30G Duration: 11 ms EIA-364-27
	Appearance	No damage	Mate plugs and expose to 105±2°C
Temperature Life (Heat	Contact Resistance	Δ R =10mΩ Max.	for 250 hours, Upon completion of the exposure period, the test specimens shall be conditioned at
Resistance)	Insulation Resistance	100 MΩ Min.	ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed
	Dielectric Strength	No Breakdown	EIA-364-17B
	Appearance	There shall be no remarkable corrosion	Mate connectors and expose to humidity in 7 cycles 7 clause. Upon
Cyclic Humidity	Contact Resistance	ΔR =10mΩ Max.	completion of the exposure period, the test specimens shall be conditioned at ambient room
	Dielectric Strength	No breakdown	conditions for 1 to 2 hours, after which the specified measurements shall be performed.
	Insulation Resistance	100 MΩ Min.	EIA-364-31 method III

			TEMPLATE FILENAME	: PRODUCT SPE	C[SIZE A4](V.1).DOC
PS-105133-001		XQZHANG XQZHANG A		YIN	
DOCUMEN	T NUMBER:	CREATED / REVISED BY: CHECKED BY: APPRO		OVED BY:	
^	DATE: 2014/04/24	WIIOICO-C	4017		
Α	EC No: SH2014-0449	MICRO-I	JSB CONNECTO	RS	4 of 7
REVISION:	ECR/ECN INFORMATION:	TITLE:			SHEET No.



PRODUCT SPECIFICATION

Item	Requir	rement	Test Condition		
	Appearance	No Damage	Mate plugs and subject to the flowing conditions for 10 cycles, Upon completion of the exposure period, the test specimens shall be		
Thermal shock	Contact resistance	ΔR =10mΩ Max.	conditioned at ambient room conditions for 1 to 2 hours, after		
(Temperature cycling)	Dielectric Strength	No breakdown	which the specified measurements shall be performed. 1 cycle		
	Insulation Resistance	100 MΩ Min.	a) -55 ± 3°C 30 minutes. b) +85 ± 2°C 30 minutes. EIA-364-32C		
Salt spray	Appearance	By visual inspection without noticeable rust.	Mate plugs and expose to the following salt mist conditions. Upon completion of the exposure period, salt deposits shall be removed by a gentle wash or dip in running water, after which the specified		
	Contact Resistance $\Delta R = 10 \text{m}\Omega$ Max.		measurements shall be performed NaCl solution Concentration: 5 ± 1% Spray time: 48 ± 4 hours Ambient Temperature: 35 ± 2°C EIA-364-26		
Solder-ability (not for black nickel plating)	Solder Wetting	95% of immersed area must show no voids or pin holes	Dip solder-tails in flux then immerse in solder bath at 245 ± 5°C up to 0.5mm from the bottom of the housing for 4 ~ 5 seconds (EIA-364-52 Category 2)		
Resistance to soldering heat	Without any deformation of case or excessive looseness of the terminals (pins). Electrical characteristics shall be satisfied.		For procedures other than specified below, refer to IEC PUB. 68-2-20. Test Tb Method 1A or 2 Solder bath method: Solder temperature: 255 +5/-0°C Immersion time: 10 ± 1 second Thickness of PCB: 1.6 mm Solder iron method: Solder temperature: 350 ± 10°C		
	No any damage afte	er reflow	Immersion time: 3 ± 1 second However, excessive pressure shall not be applied to the terminal Reference reflow condition at Para. 5.0		

REVISION:	ECR/ECN INFORMATION:	TITLE:			SHEET No.	
Α	EC No: SH2014-0449	MICRO-I	USB CONNECTO	RS	5 of 7	
_	DATE: 2014/04/24	WICKO-03B CONNECTORS 9				
DOCUMEN	T NUMBER:	CREATED / REVISED BY: CHECKED BY: APP		<u>APPR</u> (OVED BY:	
PS-105133-001		XQZHANG XQZHANG		Δ	YIN	
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A4](V.1).DOC						

molex®

PRODUCT SPECIFICATION

4.0 TEST SEQUENCE

All samples have to be soldered on PCB and reflow twice before measuring and testing.


	Item	Α	В	С	D	Е	F	G	Н
1	Contact Resistance	1, 4	2, 5	1, 7	1, 3	1, 3			
2	Insulation Resistance			3, 8					
3	Dielectric Strength			4, 9					
4	Contact capacitance			2					
5	Durability		3						
6	Vibration	3							
7	Mechanical Shock	2							
8	Temperature Life					2			
9	Humidity			6					
10	Thermal shock			5					
11	Salt spray				2				
12	Temperature Rise						1		
13	Mating / un- mating force		1, 4						
14	Solder-ability							1	
15	Resistance to soldering heat								1
	Number of sample	5	5	5	5	5	5	5	5

TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A4](V.1).DOC							
PS-105133-001		XQZHANG	XQZHANG	AYIN			
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:			
^	DATE: 2014/04/24	WITOTO-	0 01 7				
Α	EC No: SH2014-0449	MICRO-USB CONNECTORS			6 of 7		
REVISION:	ECR/ECN INFORMATION:	TITLE:			SHEET No.		

molex®

PRODUCT SPECIFICATION

5.0 REFLOW CONDITION



TEMPERATURE CONDITION GRAPH

6.0 PACKAGING

Parts shall be packaged to protect against damage during handling, transit and storage. Receptacles will be supplied in tape and reel.

REVISION:	ECR/ECN INFORMATION:	TITLE:			SHEET No.	
Α	EC No: SH2014-0449	MICRO-USB CONNECTORS			7 of 7	
	DATE: 2014/04/24					
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:		
PS-105133-001		XQZHANG	XQZHANG	AYIN		
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A4](V.1).DOC						