
DESCRIPTION: POWER - VERTICAL - FEMALE - MACHINED



SPECIFICATIONS:

CONTACT INSERTION FORCE:

CONTACT SEPARATION FORCE:

MECHANICAL:

MATERIALS:

CONTACTS:

INSULATOR:

HARDWARE:


SHELL:

ELECTRICAL:INSULATION RESISTANCE:DIELECTRIC WITHSTANDING VOLTAGE:WORKING VOLTAGE:OPERATING TEMPERATURE:POWER CONTACT RESISTANCE:POWER CONTACT AMPERAGE:


5 GOhms MIN. 1000 VAC FOR 1 MIN 250V -55°C TO +125°C 2.0 mOhms MAX. SEE P/N KEY

4.5 Kg MAX. 0.3 Kg MIN.

COPPER ALLOY, GOLD FLASH PBT UL94V-0 RATED 230°C PROCESS TEMP. NICKEL PLATED STEEL NICKEL PLATED BRASS



SEE SHEET 2 FOR CONTACT DIMENSION DETAILS



0 = 40 AMP POWER // STANDARD PCB TAILS 1 = 40 AMP POWER // 2.22mm PCB TAILS 2 = 20 AMP POWER // STANDARD PCB TAILS

0 = NO HARDWARE -

- = 0.098" CN PCB SIDE
- 2 = 0.236" CN PCB SIDE
- 3 = 0.236" CN MATING SIDE
- 4 = 0.237" BOARDLOCK PCB SIDE
- 5 = 0.224" BOARDLOCK PCB SIDE

1 = GOLD FLASH -



