



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Staff Mfg & Process Dvl Engineer		
Company Unique ID	TE Connectivity	Response Date	2018-04-03	Contact Email	dave.benfer@te.com				
Contact Phone Number	+1-717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1337771-1	Amount	36829.88	Version	-	Identity			
Manufacturer Item Name	50 OHM COAX BNC STR PLUG STR P	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s)								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	COAXIAL CABLE RG58C/U LEONI				1.0	9385.0	mg	
Material	2	Inner Conductor				1.0	1137.5	mg	
Substance	3	Copper	Supplier	7440-50-8	100.0	1.0	1137.5	mg	
Material	2	Tape				1.0	80.0	mg	
Substance	3	Poly(oxy-1,2-ethanedioxy carbonyl-1,4-phenylene carbonyl)	Supplier	25038-59-9	100.0	1.0	80.0	mg	
Material	2	Outer Shield				1.0	3512.5	mg	
Substance	3	Copper	Supplier	7440-50-8	100.0	1.0	3512.5	mg	
Material	2	Jacket				1.0	3345.0	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	99.15	1.0	3316.5675	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.85	1.0	28.4325	mg	
Material	2	Insulation				1.0	1310.0	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	100.0	1.0	1310.0	mg	
Sub-Item	1	STRAIN RELIEF (BLACK) PLYM				2.0	3000.0	mg	
Material	2	small boot				2.0	3000.0	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	50.0	2.0	1500.0	mg	
Substance	3	Limestone	Supplier	1317-65-3	27.5	2.0	825.0	mg	
Substance	3	Soybean oil, epoxidized	Supplier	8013-07-8	1.99	2.0	59.7	mg	
Substance	3	Calcium hydroxide (Ca(OH)2)	Supplier	1305-62-0	0.01	2.0	0.3	mg	
Substance	3	1,2-Benzenedicarboxylic acid, 1,2-diisodecyl ester	Phthalates (DINP, DIDP, DNOP)	26761-40-0	20.5	2.0	615.0	mg	

Sub-Item	1	BNC Str Plg Hex 50Ohm Silver P				2.0	10722.44	mg	
Material	2	Contact - Brass				2.0	199.973506	mg	
Substance	3	Zinc	Supplier	7440-66-6	38.7	2.0	77.38975	mg	
Substance	3	Iron	Supplier	7439-89-6	0.49	2.0	0.97987	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 0217	1.0	2.0	1.99974	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.01999735	mg	
Substance	3	Copper	Supplier	7440-50-8	57.8	2.0	115.58469	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	2.0	0.39995	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	1.8	2.0	3.59952	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Material	2	Ferrule - Brass				2.0	999.9747544	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.08	2.0	0.79998	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.01	2.0	0.09999748	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.09999748	mg	
Substance	3	Zinc	Supplier	7440-66-6	36.25	2.0	362.49085	mg	
Substance	3	Copper	Supplier	7440-50-8	63.5	2.0	634.98397	mg	
Substance	3	Iron	Supplier	7439-89-6	0.15	2.0	1.49996	mg	
Material	2	Washer 1 - Brass				2.0	469.9645452	mg	
Substance	3	Iron	Supplier	7439-89-6	0.15	2.0	0.70495	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.01	2.0	0.04699645	mg	
Substance	3	Copper	Supplier	7440-50-8	63.5	2.0	298.42749	mg	
Substance	3	Zinc	Supplier	7440-66-6	36.25	2.0	170.36215	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.04699645	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.08	2.0	0.37597	mg	
Material	2	Insulation - PTFE				2.0	499.9873772	mg	
Substance	3	Ethene, 1,1,2,2- tetrafluoro- homopolymer	Supplier	9002-84-0	100.0	2.0	499.98738	mg	
Material	2	Body - Brass				2.0	4100.0466072	mg	
Substance	3	Copper	Supplier	7440-50-8	57.8	2.0	2369.82694	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 0217	1.0	2.0	41.00047	mg	
Substance	3	Iron	Supplier	7439-89-6	0.49	2.0	20.09023	mg	
Substance	3	Zinc	Supplier	7440-66-6	38.7	2.0	1586.71804	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.41	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	2.0	8.20009	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	1.8	2.0	73.80084	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Material	2	Shell - Silver Plating				2.0	0.6433464	mg	
Substance	3	Silver	Supplier	7440-22-4	98.5	2.0	0.6337	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	2.0	0.0096502	mg	
Material	2	Washer 2 - Silver Plating				2.0	0.536122	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	2.0	0.00804183	mg	
Substance	3	Silver	Supplier	7440-22-4	98.5	2.0	0.52808	mg	
Material	2	Washer 2 - Brass				2.0	250.0473008	mg	
Substance	3	Iron	Supplier	7439-89-6	0.49	2.0	1.22523	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	2.0	0.50009	mg	
Substance	3	Copper	Supplier	7440-50-8	57.8	2.0	144.52734	mg	
Substance	3	Zinc	Supplier	7440-66-6	38.7	2.0	96.76831	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 0217	1.0	2.0	2.50047	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.02500473	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	1.8	2.0	4.50085	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Material	2	Spring - Steel				2.0	199.973506	mg	
Substance	3	Nickel	Nickel	7440-02-0	11.0	2.0	21.99709	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.08	2.0	0.15998	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.0	2.0	1.99974	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.03	2.0	0.05999205	mg	
Substance	3	Chromium	Supplier	7440-47-3	19.0	2.0	37.99497	mg	
Substance	3	Iron	Supplier	7439-89-6	66.85	2.0	133.68229	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	2.0	0.0799894	mg	
Substance	3	Manganese	Supplier	7439-96-5	2.0	2.0	3.99947	mg	
Material	2	Contact - Silver plating				2.0	0.4288976	mg	
Substance	3	Silver	Supplier	7440-22-4	98.5	2.0	0.42246	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	2.0	0.00643346	mg	
Material	2	Washer 1 - Silver Plating				2.0	0.3216732	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	2.0	0.0048251	mg	
Substance	3	Silver	Supplier	7440-22-4	98.5	2.0	0.31685	mg	
Material	2	Shell - Brass				2.0	3899.9658768	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	1.8	2.0	70.19939	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	3	Zinc	Supplier	7440-66-6	38.7	2.0	1509.28679	mg	
Substance	3	Copper	Supplier	7440-50-8	57.8	2.0	2254.18028	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.39	mg	
Substance	3	Iron	Supplier	7439-89-6	0.49	2.0	19.10983	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	2.0	7.79993	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0217	1.0	2.0	38.99966	mg	
Material	2	Gasket - Silicon Rubber				2.0	100.0403652	mg	
Substance	3	Siloxanes and Silicones, di-Me, Me vinyl, vinyl group-terminated	Supplier	68083-18-1	77.5	2.0	77.53128	mg	
Substance	3	Siloxanes and Silicones, di-Me, hydroxy-terminated	Supplier	70131-67-8	1.0	2.0	1.0004	mg	
Substance	3	Silica	Supplier	7631-86-9	21.5	2.0	21.50868	mg	
Material	2	Ferrule - Silver Plating				2.0	0.3216732	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	2.0	0.0048251	mg	
Substance	3	Silver	Supplier	7440-22-4	98.5	2.0	0.31685	mg	
Material	2	Body - Silver Plating				2.0	0.2144488	mg	
Substance	3	Silver	Supplier	7440-22-4	98.5	2.0	0.21123	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	2.0	0.00321673	mg	