



Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14	14	19	
Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	14-b	19-a	
Contact arrangement	IEC 60130-9 ¹⁾	yes		no		yes		no		yes				
Rated voltage ²⁾	IEC 60664-1	300 V (100 V)		300 V (63 V)		100 V (32 V)		300 V (63 V)		100 V (32 V)		150 V (32 V)		
Rated voltage	UL 1977	250V								60V				
Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (1500 V)		1200 V (800 V)		1500 V (1500 V)		1200 V (800 V)						
Pollution degree ²⁾	IEC 60664-1	1 (2)												
Installation category	IEC 60664-1	I												
Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600												
Current rating	IEC 60512-5-2 UL 1977	10A/+40°C			7A/+40°C						3A/+40°C			
Insulation resistance	IEC 60512-3-1	>10 ¹⁰ Ohm ³⁾												
Contact resistance	IEC 60512-2-1	<5mOhm												
Climatic category	IEC 60668-1	40 / 100 / 56												
Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F												
IP degree	IEC 60529	IP 40												
Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N	50N	60N	
mechanical operation	IEC 60512-9-1	Silver ≥500 mating cycles / Gold ≥1000 mating cycles												
housing material		brass and / or zinc die cast, nickel plated or thermoplast												
dielectric material		thermoplastic												
contacts		silver or gold plated												
termination technique		solder												
wire gauge		≤0,5mm ² / 20 AWG						≤0,35mm ² / 22 AWG						
flamability		UL 94 V0												
locking system		metal screw coupling; tightening torque 0,7 - 1,5 Nm												

Gewicht (errechnet) / Calc WT: 0,029 kg	Zul. Abw./Tolerances:
Prüfmaß / Testdimension	ISO 2768-c
Teileindex / Partindexnumber:	DIN / ISO 13715
Bagatelle change: 23.02.2021 MCARLE	

Gez. Drawn	02.12.2020
Gepr. Released	MCARLE
Checked	10.02.2021
	MBERTSCH

Maßstab / Scale: 2:1	A3	
CUSTOMER DRAWING		
Female cable connector PG9, cable diameter 6-8mm		

01	202000083	08.12.2020	MCARLE
Index	Änderung / Description	Datum / Date	Name

Amphenol Tuchel Industrial GmbH	
----------------------------------------	--

M	DA	T	3XXX	002+020+028	Blatt / Sheet
					1
Ers. f. / Replacement for:					1 Bl.

	19 (19-a)	Ag	T 3691 002 U
		Au	T 3691 028 U
	14 (14-b)	Ag	T 3671 002 U
		Au	T 3671 028 U
	14 (14-a)	Ag	T 3651 020 U
		Au	T 3651 002 U
	12 (12-a)	Ag	T 3636 020 U
		Au	T 3636 002 U
	8 (08-a)	Ag	T 3505 002 U
		Au	T 3505 028 U
	7 (07-b)	Ag	T 3485 002 U
		Au	T 3485 028 U
	7 (07-a)	Ag	T 3476 002 U
		Au	T 3476 028 U
	6 (6-a)	Ag	T 3401 002 U
		Au	T 3401 028 U
	5 (05-b)	Ag	T 3361 020 U
		Au	T 3357 028 U
	5 (05-a)	Ag	T 3361 002 U
		Au	T 3361 028 U
	4 (04-a)	Ag	T 3301 002 U
		Au	T 3301 028 U
	3 (03-a)	Ag	T 3261 002 U
		Au	T 3261 028 U
	2 (Pin 1+3)	Ag	T 3201 002 U
		Au	T 3201 028 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. DIN EN 61076-2-106)	contact plating	Part number

Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

FAI2020-004404

NXM-V05