

DATASHEET

6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER 4N2X Series 4N3X Series H11AX Series








Features:

- 4N2X series: 4N25, 4N26, 4N27, 4N28
- 4N3X series: 4N35, 4N36, 4N37, 4N38
- H11AX series: H11A1, H11A2, H11A3, H11A4, H11A5
- High isolation voltage between input and output (Viso=5000 V rms)
- Creepage distance >7.62 mm
- Operating temperature up to +110°C
- Compact dual-in-line package
- •The product itself will remain within RoHS compliant version
- •Compliance with EU REACH
- UL and cUL approved(No. E214129)
- VDE approved (No. 132249)
- SEMKO approved
- NEMKO approval
- · DEMKO approval
- FIMKO approval
- CQC approved

Schematic



Pin Configuration

- 1. Anode
- 2. Cathode
- 3. No Connection
- 4. Emitter
- 5. Collector
- 6. Base

Description

The 4N2X, 4N3X, H11AX series of devices each consist of an infrared emitting diode optically coupled to a phototransistor.

They are packaged in a 6-pin DIP package and available in wide-lead spacing and SMD option.

Applications

- Power supply regulators
- Digital logic inputs
- Microprocessor inputs



Absolute Maximum Ratings (Ta=25℃)

	Parameter	Symbol	Rating	Unit
	Forward current	I _F	60	mA
	Peak forward current (t = 10µs)	I _{FM}	1	А
Input	Reverse voltage	V_R	6	V
	Power dissipation (T _A = 25°C)	P _D —	100	mW
	Derating factor (above 100°C)	FD	3.8	mW/°C
	Collector-Emitter voltage	V_{CEO}	80	V
	Collector-Base voltage	V_{CBO}	80	V
Outrout	Emitter-Collector voltage	V_{ECO}	7	V
Output	Emitter-Base voltage	V _{EBO}	7	V
	Power dissipation (T _A = 25°C)	р —	150	mW
	Derating factor (above 100°C)	P _C —	9.0	mW/°C
Total Power Dissipation		P _{TOT} 200		mW
Isolation Voltage*1		V _{ISO}	5000	V rms
Operating Temperature		T_OPR	-55 to 110	°C
Storage Temperature		T _{STG}	T _{STG} -55 to 125	
Soldering Temperature* ²		T _{SOL}	260	°C

Notes:

^{*1} AC for 1 minute, R.H.= $40 \sim 60\%$ R.H. In this test, pins 1, 2 & 3 are shorted together, and pins 4, 5 & 6 are shorted together.

^{*2} For 10 seconds



Electro-Optical Characteristics (Ta=25 $^{\circ}$ C unless specified otherwise)

Input

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Forward voltage	V_{F}	-	1.2	1.5	V	I _F = 10mA
Reverse current	I_R	-	-	10	μΑ	$V_R = 6V$
Input capacitance	C_in	-	30	-	pF	V = 0, f = 1MHz

Output

Parameter		Symbol	Min	Тур.	Max.	Unit	Condition
Collector-Base dark current		I_{CBO}	-	-	20	nA	V _{CB} = 10V
Collector- Emitter dark current	4N2X H11AX	- loso -	-	-	50	nA	V _{CE} = 10V, IF=0mA
	4N3X	- I _{CEO} -	-	-	50	11/ (V _{CE} = 60V, IF=0mA
	Collector-Emitter breakdown voltage		80		-	V	I _c =1mA
	Collector-Base breakdown voltage		80	-		V	I _C =0.1mA
Emitter-Collector breakdown voltage		BV _{ECO}	7	-	-	V	I _E =0.1mA
Emitter-Base breakdown voltage		BV _{EBO}	7	-	-	V	I _E =0.1mA
Collector-Emitter capacitance		C_CE	-	8	-	pF	VCE=0V, f=1MHz

^{*} Typical values at T_a = 25°C



Transfer Characteristics

Parameter		Symbol	Min	Тур.	Max.	Unit	Condition
	4N35, 4N36, 4N37	CTR .	100	-	-	- - - %	$I_F = \pm 10 \text{mA}, V_{CE} = 10 \text{V}$
	H11A1		50	-	-		
Current Transfer	H11A5		30	-	-		
ratio	4N25, 4N26, 4N38, H11A2, H11A3		20	-	-		
	4N27, 4N28, H11A4	-	10	-	-		
	4N25, 4N26, 4N27, 4N28		-	-	0.5		$I_F = 50 \text{mA}, I_c = 2 \text{mA}$
Collector- Emitter	4N35, 4N36, 4N37	•	-	-	0.3	- V	$I_F = 10 \text{mA}, I_c = 0.5 \text{mA}$
saturation voltage	H11A1,H11A2, H11A3,H11A4, H11A5	V _{CE(sat)}	-	-	0.4		
	4N38		-	-	1.0		$I_F = 20$ mA, $I_c = 4$ mA
Isolation resistance		R _{IO}	10 ¹¹	-	-	Ω	V _{IO} = 500Vdc
Input-output	capacitance	C_{IO}		0.2	-	pF	$V_{IO} = 0$, $f = 1MHz$
4N25, 4N26, 4N27, 4N28, H11A1,H11A2, H11A3,H11A4, Turn-on time H11A5		Ton	31	3	10	μs	V_{CC} = 10V, I_F = 10mA, R_L = 100 Ω See Fig. 11
	4N35, 4N36, 4N37, 4N38		-	10	12		V_{CC} = 10V, I_C = 2mA, R_L = 100 Ω , See Fig. 11
Turn-off time	4N25, 4N26, 4N27, 4N28, H11A1,H11A2, H11A3,H11A4, H11A5	Toff .	-	3	10	μs	V_{CC} = 10V, I_F = 10mA, R_L = 100 Ω See Fig. 11
	4N35, 4N36, 4N37, 4N38		-	9	12		$V_{CC} = 10V$, $I_C = 2mA$, $R_L = 100\Omega$, See Fig. 11

^{*} Typical values at T_a = 25°C



Typical Electro-Optical Characteristics Curves








Figure 2. Current Tranfer Ratio vs Forward Current Normalized Current Transfer Ratio, CTR 0.8 0.6 0.4 V_{CE}=5 V 0.2 Normalized to I_=10 mA 0.0 Forward Current, I (mA)

















Figure 11. Switching Time Test Circuit & Waveforms



Order Information

Part Number

4NXXY(Z)-V or H11AXY(Z)-V

Note

XX = Part no. for 4NXX series (25, 26, 27, 28, 35, 36, 37 or 38)

X = Part no. for H11AX series (1, 2, 3, 4, or 5)

Y = Lead form option (S, S1, M or none)

Z = Tape and reel option (TA, TB or none).


V = VDE safety (optional)


Option	Description	Packing quantity	
None	Standard DIP-6	65 units per tube	
М	Wide lead bend (0.4 inch spacing)	65 units per tube	
S (TA)	Surface mount lead form + TA tape & reel option	1000 units per reel	
S (TB)	Surface mount lead form + TB tape & reel option	1000 units per reel	
S1 (TA)	Surface mount lead form (low profile) + TA tape & reel option	1000 units per reel	
S1 (TB)	Surface mount lead form (low profile) + TB tape & reel option	1000 units per reel	




Package Dimension (Dimensions in mm)


Standard DIP Type









Option M Type













Option S Type









Option S1 Type











Recommended pad layout for surface mount leadform



Notes

Suggested pad dimension is just for reference only. Please modify the pad dimension based on individual need.

Device Marking




Notes

EL	denotes Everlight
4N35	denotes Device Number
Υ	denotes 1 digit Year code
WW	denotes 2 digit Week code
V	denotes VDE (optional)



Tape & Reel Packing Specifications


Option TA





Direction of feed from reel


Option TB





Direction of feed from reel

Tape dimensions



Dimension No.	Α	В	Do	D1	E	F
Dimension (mm)	10.8±0.1	7.55±0.1	1.5±0.1	1.5+0.1/-0	1.75±0.1	7.5±0.1
Dimension No.	Ро	P1	P2	t	w	К
Dimension (mm)	4.0±0.15	12±0.1	2.0±0.1	0.35±0.03	16.0±0.2	4.5±0.1




Reference: IPC/JEDEC J-STD-020D

Precautions for Use

1. Soldering Condition

1.1 (A) Maximum Body Case Temperature Profile for evaluation of Reflow Profile



Note:

Preheat

150 °C Temperature min (T_{smin}) Temperature max (T_{smax}) 200°C

Time $(T_{smin} \text{ to } T_{smax}) (t_s)$ 60-120 seconds 3 °C/second max Average ramp-up rate (T_{smax} to T_p)

Liquidus Temperature (T_L) 217 °C Time above Liquidus Temperature (t L) 60-100 sec

Peak Temperature (T_P) 260°C

Time within 5 °C of Actual Peak Temperature: T_P - 5°C 30 s

Ramp- Down Rate from Peak Temperature 6°C /second max.

Time 25°C to peak temperature 8 minutes max.

Reflow times 3 times



DISCLAIMER

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 3. When using this product, please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 4. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without the specific consent of EVERLIGHT.
- 5. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.
- 6. Statements regarding the suitability of products for certain types of applications are based on Everlight's knowledge of typical requirements that are often placed on Everlight products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Everlight's terms and conditions of purchase, including but not limited to the warranty expressed therein.