

# SATA III M.2 Solid State Drive M.2 SSD 820S

Transcend's ultra-compact SATA III 6Gb/s M.2 SSD 820S addresses the high-performance needs and strict size limitations of small form factor devices, best suited for Ultrabooks and thin, light notebooks. Boasting high-quality flash chips and enhanced firmware algorithms, Transcend's M.2 SSD 820S delivers optimal reliability.




### Perfect for your Ultrabook

Measured at just 80mm in length, the M.2 SSD 820S makes for an easy upgrade to your computer, taking up little space while giving it a much needed energy boost.



Superior transfer speeds

Transcend's M.2 SSD 820S reaches incredible read and write speeds of up to 550MB/s and 500MB/s. When used as a cache, the M.2 SSD 820S provides 1.5 times faster boot time than conventional hard drives.



Store more in less space

The M.2 form factor enables expansion and integration of functions onto a single form factor module solution. M.2 SSDs include a smaller form factor but with larger capacities than that of mSATA and half-slim SSDs.





# SATA III M.2 Solid State Drive M.2 SSD 820S

### Features

- · Space-saving M.2 Type 2280 form factor
- Up to 550 MB/s read; 500 MB/s write
- · 3D NAND flash memory
- RAID engine and LDPC coding for data integrity; DDR3 DRAM cache for short access times
- Supports DevSleep ultra low power state, S.M.A.R.T., TRIM, and NCQ commands

# Transcend SSD

Transcend SSD Scope is advanced, user-friendly software that makes it easy to ensure your Transcend SSD remains healthy, and continues to run fast and error-free by determining the condition and optimizing the performance of your drive.

SSD Scope Software

### Specifications

| specifications                          |  |  |  |
|---|--|--|--|
| Appearance                              |  |  |  |
| Dimensions (Max.)                       | 80.0 mm x 22.0 mm x 3.58 mm (3.15" x 0.87" x 0.14" |  |  |
| Weight (Max.)                           | 9 g (0.32 oz)                                      |  |  |
| Interface                               |  |  |  |
| Bus Interface                           | SATA III 6Gb/s                                     |  |  |
| Storage                                 |  |  |  |
| Flash Type                              | 3D NAND flash                                      |  |  |
| Capacity                                | 120 GB/240 GB/480 GB/960 GB                        |  |  |
| Operating Environmen                    | t  |  |  |
| Operating Temperature                   | 0°C (32°F) ~ 70°C (158°F)                          |  |  |
| Operating Voltage                       | 3.3V±5%  |  |  |
| Performance                             |  |  |  |
| Sequential Read/Write                   | Read: 550 MB/s                                     |  |  |
| (CrystalDiskMark, max.)                 | Write: 500 MB/s                                    |  |  |
| 4K Random Read/Write<br>(IOmeter, max.) | Read: 70,000 IOPS                                  |  |  |
|   | Write: 75,000 IOPS                                 |  |  |
| Mean Time Between Failures<br>(MTBF)    | 1,000,000 hour(s)                                  |  |  |
| Terabytes Written (Max.)                | 320 TB   |  |  |
| Drive Writes Per Day<br>(DWPD)          | 0.3 (3 yrs)  |  |  |

#### Note

Speed may vary due to host hardware, software, usage, and storage capacity.

#### Warranty

| Certificate | CE/FCC/BSMI                 |
|-------------|-----------------------------|
| Warranty    | Three-year Limited Warranty |

## Ordering Information

| TS120GMTS820S |
|---------------|
| TS240GMTS820S |
| TS480GMTS820S |
| TS960GMTS820S |
|               |

Product specifications are subject to change without notice. Pictures shown may differ from actual products. When used as a storage capacity unit, one terabyte (TB) = one trillion bytes. Total accessible capacity varies depending on operating environment.



| SATA III M.2 SSDs<br>Comparison                  |   |   | TIME TO A CONTRACT OF A CONTRACT | Titlents<br>Summing                                       |  |
|--|---|---|--|---|--|
|  | SATA III 6Gb/s<br>M.2 SSD 420S                            | SATA III 6Gb/s<br>M.2 SSD 430S                            | SATA III 6Gb/s<br>M.2 SSD 820S   | SATA III 6Gb/s<br>M.2 SSD 830S                            |  |
| Appearance                                       |   |   |  |   |  |
| Dimensions (Max.)                                | 42.0 mm x 22.0 mm<br>x 3.88 mm<br>(1.65" x 0.87" x 0.15") | 42.0 mm x 22.0 mm<br>x 3.58 mm<br>(1.65" x 0.87" x 0.14") | 80.0 mm x 22.0 mm<br>x 3.58 mm<br>(3.15" x 0.87" x 0.14")  | 80.0 mm x 22.0 mm<br>x 3.58 mm<br>(3.15" x 0.87" x 0.14") |  |
| Weight (Max.)                                    | 5 g (0.18 oz)   | 5 g (0.18 oz)   | 9 g (0.32 oz)  | 9 g (0.32 oz)   |  |
| Storage  |   |   |  |   |  |
| Flash Type                                       | 3D NAND flash   |   |  |   |  |
| Capacity   | 120GB ~ 240GB   | 128GB ~ 512GB   | 120GB ~ 960GB  | 128GB ~ 1TB   |  |
| Operating Environment                            |   |   |  |   |  |
| Operating Temperature                            | 0°C (32°F) ~ 70°C (158°F)                                 |   |  |   |  |
|  |   |   |  |   |  |
| Performance                                      |   |   |  |   |  |
| Sequential Read/Write<br>(ATTO, max.)            | Read: 520 MB/s<br>Write: 480 MB/s                         | Read: 560 MB/s<br>Write: 500 MB/s                         | -  | Read: 560 MB/s<br>Write: 520 MB/s                         |  |
| Sequential Read/Write<br>(CrystalDiskMark, max.) | Read: 500 MB/s<br>Write: 500 MB/s                         | Read: 560 MB/s<br>Write: 500 MB/s                         | Read: 550 MB/s<br>Write: 500 MB/s  | Read: 560 MB/s<br>Write: 500 MB/s                         |  |
| 4K Random Read/Write<br>(IOmeter, max.)          | Read: 40,000 IOPS<br>Write: 75,000 IOPS                   | Read: 80,000 IOPS<br>Write: 85,000 IOPS                   | Read: 70,000 IOPS<br>Write: 75,000 IOPS  | Read: 85,000 IOPS<br>Write: 85,000 IOPS                   |  |
| Mean Time Between Failures<br>(MTBF)             | 1,000,000 hour(s)   |   |  |   |  |
| Terabytes Written (Max.)                         | 80 TB   | 280 TB  | 320 TB   | 560 TB  |  |
| Drive Writes Per Day (DWPD)                      | 0.3 (3 yrs)   | 0.3 (5 yrs)   | 0.3 (3 yrs)  | 0.3 (5 yrs)   |  |
|  |   |   |  |   |  |
| Warranty   |   |   |  |   |  |
| Warranty   | Three-year Limited<br>Warranty                            | Five-year Limited<br>Warranty                             | Three-year Limited<br>Warranty   | Five-year Limited<br>Warranty                             |  |
| Taskasla   |   |   |  |   |  |
| Technology                                       |   |   |  |   |  |
| TRIM & NCQ Command                               |   | ✓   | ~  |   |  |
| S.M.A.R.T.                                       | -   | ✓   | ~  |   |  |
| DDR3 DRAM Cache                                  |   | ✓   | -  | <u> </u>  |  |
| Advanced Garbage Collection                      | ✓   | ✓   |  | <pre></pre>   |  |
| DevSleep Mode                                    | <u> </u>  | <u> </u>  | <u> </u>   | ✓<br>✓  |  |
|  | <br>  | ~<br>~  | ~<br>~   | ~<br>~  |  |
| LDPC Coding                                      | ¥   | ~   | ~  | *   |  |

 $\ensuremath{^*\!\text{Speed}}$  may vary due to host hardware, software, usage, and storage capacity.