
Resistors

Precision Metal Film Resistors

PR series

- Low cost precision resistors
- Tolerances down to ±0.1%
- TCR down to 15ppm/°C





All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

Electrical Data

		PR4	PR5
Power rating at 70°C	watts	0.25	0.5
Resistance range	ohms		а — 1М
Limiting element voltage	volts	250	350
TCR (20°C to 70°C)	ppm/°C	≤240K: 15, 25, 50	>240K: 25, 50
Resistance tolerance	%	≤500K: 0.1, 0.25, 0.5, 1	
Standard values		E24	, E96
Thermal impedance	°C/watt	140	112
Ambient temperature range	°C	-55 to	

Physical Data

Dimensions (mm) & Weight (g)										
Туре	L Max	D Max	f min	d nom	PC mounting centres	Min. bend radius	Wt. nom]=
PR4 PR5	6.2 9.0	2.5 3.6	21 19.6	0.6 0.8	10.2 12.7	0.6	0.3	u a	Ď <u> </u>	Ļ

Construction

The resistance element is a precisely controlled thin film of metal alloy sputtered on to a high purity ceramic core, protected by a moisture-resistant, high dielectric strength coating applied so that terminations remain completely clear.

This permits a well defined body length (clean lead to clean lead dimension L).

Terminations

Material	Hot tin dipped copper wire
Strength	The terminations meet the requirements of
	IEC 68.2.21
Solderability	The terminations meet the requirements of
	IEC 115-1, Clause 4.17.3.2

Marking

25ppm/°C resistors are colour coded with 5 bands. The other grades have an additional 6th band indicating TCR which is orange for 15ppm/°C and red for 50ppm/°C.

Solvent Resistance

The body protection and marking are resistant to all normal industrial cleaning solvents suitable for printed circuits.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

BI Technologies IRC Welwyn



PR series

Performance Data

		Maximum
Load: 1000 hours at 70°C	ΔR %	0.5
Derating from rated power at 70°C		zero at 155°C
Short term overload	ΔR %	0.25
Climatic	ΔR %	0.5
Climatic category		55/125/56
Long term damp heat	ΔR %	0.5
Temperature rapid change	ΔR %	0.25
Resistance to solder heat	ΔR %	0.25
Vibration and bump	ΔR %	0.1
Insulation resistance	ohms	> 1G
Voltage proof	volts	PR4: 500 min, PR5: 700 min


Packaging

All PR resistors are supplied tape packed ready for loading on to automatic sequencing and insertion machines.

Component wires will not protrude beyond the outside edge of the tapes.

Alternative packaging available by request.

Lead formed resistors can also be supplied. Standard options of Lancet, Radial and Goalpost forming are available.



Body location $f_1 - f_2 \le 1.4 \text{ mm}$

Ordering Procedure

Example: PR4 with TCR of 15ppm/ $^\circ C$ at 10 kilohms and 0.1% tolerance in an ammo pack box of 5000 pieces -

Туре					<u>PR4Y</u> – <u>101</u>	<u> </u>
2	15 ppm/ °C 25 ppm/ °C					
C t	50 ppm/°C					
Value	(use IEC6	2 code))			
Tolera	ance (use	IEC62 c	ode)			_
B 0.	.1% D	0.5%				
C 0.	.25% F	1%				
Packi	na ——					
	Ĭ	PR4	5000/box	Olevalent		
Ι	Ammo	PR5	2500/box	Standard		

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

www.ttelectronics.com/resistors