


5 V low clamping single line bidirectional ESD protection



ST0201 package



Product status link

ESD051-1BF4

Features

- · Low clamping voltage:
 - 11 V (IEC 61000-4-2 contact discharge at 30 ns)
- · Bidirectional diode
- Low leakage current
- ST0201 package
- Complies with the following standards: IEC 61000-4-2 level 4 (exceeds level 4)
 - ±30 kV (air discharge)
 - ±30 kV (contact discharge)

Application

Where transient over voltage protection in ESD sensitive equipment is required, such as:

- · Smartphones, mobile phones and accessories
- · Tablet, PC, netbooks and notebooks
- · Portable multimedia devices and accessories
- · Digital cameras and camcorders
- · Communication and highly integrated systems

Description

The ESD051-1BF4 is a bidirectional single line TVS diode designed to protect the power line against EOS and ESD transients.

The device is ideal for applications where board space saving is required.



1 Characteristics

Table 1. Absolute maximum ratings (T_{amb} = 25 °C)

Symbol		Value	Unit	
V	Peak pulse voltage	IEC 61000-4-2 contact discharge	±30	kV
V_{pp}		IEC 61000-4-2 air discharge	±30	K.V
P _{pp}	Peak pulse power (8/20 µs)		110	W
I _{pp}	Peak pulse current (8/20 µs)		10	Α
Tj	Operating junction temperature range		-55 to 150	
T _{stg}	Storage junction tempera	-65 to 150	°C	
T _L	Maximum lead temperatu	260		

Figure 1. Electrical characteristics (definitions)

Symbol Parameter V_{BR} Breakdown voltage V_{CL} Clamping voltage I_{RM} Leakage current @V_{RM} V_{RM} = Stand-off voltage Peak pulse current = I_{PP} $R_{\scriptscriptstyle D}$ Dynamic resistance = = Breakdown current I_R




Table 2. Electrical characteristics (values) (T_{amb} = 25° C)

Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
V _{RM}	Reverse working voltage				5	V
V _{BR}	Breakdown voltage	I _R = 1 mA	5.8			V
I _{RM}	Leakage current	V _{RM} = 5 V			70	nA
V _{CL}	Clamping voltage	IEC 61000-4-2, 8 kV contact measured at 30 ns		11		V
R _D	Dynamic resistance, pulse duration 100 ns ⁽¹⁾			0.145		Ω
C _{LINE}	Line capacitance	V _{LINE} = 0 V, F = 1 MHz, V _{OSC} = 30 mV		45		pF

^{1.} More information are available in ST application note: AN4022

DS12643 - Rev 3 page 2/10



1.1 Characteristics (curves)


Figure 2. Variation of leakage current versus junction temperature

I_R(n A)

V_R = V_{RM} = 5 V

T_J (°C)

125 50 75 100 125 150




5 V/div


5 V/div


5 V/div

5 V/div

6 V_{0.} Peak clamping voltage expose at 30 ns of V_{0.} clamping voltage at 100 ns of V_{0.} clamping vo







DS12643 - Rev 3 page 3/10



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 ST0201 package information

Figure 8. ST0201 package outline





Table 3. ST0201 package mechanical data

	Dimensions						
Ref.	Millimeters			Inches			
	Min.	Тур.	Max.	Min.	Тур.	Max.	
Α	0.280	0.300	0.320	0.0110	0.0118	0.0126	
b	0.125	0.140	0.155	0.0049	0.0055	0.0061	
D	0.570	0.600	0.630	0.0224	0.0236	0.0248	
D1		0.350			0.0138		
Е	0.270	0.300	0.330	0.0106	0.0118	0.0130	
E1	0.175	0.190	0.205	0.0069	0.0075	0.0081	
fD	0.040	0.055	0.070	0.0015	0.0021	0.0028	
fE	0.040	0.055	0.070	0.0115	0.0021	0.0028	

DS12643 - Rev 3 page 4/10




Figure 9. Marking



Note: Marking can be rotated by 90° or 180° to differentiate assembly location.

Figure 10. Tape and reel specification




DS12643 - Rev 3 page 5/10



3 Recommendation on PCB assembly

3.1 Footprint


Figure 11. Footprint in mm



3.2 Stencil opening design

- 1. Recommended design reference
 - a. Stencil opening dimensions: 75 μm

Figure 12. Stencil opening recommendations



DS12643 - Rev 3 page 6/10



3.3 Solder paste

- 1. Halide-free flux qualification ROL0 according to ANSI/J-STD-004.
- 2. "No clean" solder paste is recommended.
- 3. Offers a high tack force to resist component movement during high speed.
- 4. Use solder paste with fine particles: powder particle size 20-48 μm.

3.4 Placement

- Manual positioning is not recommended.
- 2. It is recommended to use the lead recognition capabilities of the placement system, not the outline centering
- 3. Standard tolerance of ±0.05 mm is recommended.
- 4. 1.0 N placement force is recommended. Too much placement force can lead to squeezed out solder paste and cause solder joints to short. Too low placement force can lead to insufficient contact between package and solder paste that could cause open solder joints or badly centered packages.
- 5. To improve the package placement accuracy, a bottom side optical control should be performed with a high resolution tool.
- For assembly, a perfect supporting of the PCB (all the more on flexible PCB) is recommended during solder paste printing, pick and place and reflow soldering by using optimized tools.


3.5 PCB design preference

- 1. To control the solder paste amount, the closed via is recommended instead of open vias.
- 2. The position of tracks and open vias in the solder area should be well balanced. A symmetrical layout is recommended, to avoid any tilt phenomena caused by asymmetrical solder paste due to solder flow away.

3.6 Reflow profile

Note:

Figure 13. ST ECOPACK® recommended soldering reflow profile for PCB mounting



Minimize air convection currents in the reflow oven to avoid component movement. Maximum soldering profile corresponds to the latest IPC/JEDEC J-STD-020.

DS12643 - Rev 3 page 7/10



4 Ordering information

Figure 14. Ordering information scheme




Table 4. Ordering information

Order code	Marking	Weight	Base qty.	Delivery mode
ESD051-1F4	5	0.12 mg	15000	Tape and reel

DS12643 - Rev 3 page 8/10



Revision history

Table 5. Document revision history

Date	Revision	Changes
04-Jul-2018	1	First issue.
15-May-2019	2	Updated Table 2.
03-Jun-2019	3	Updated Table 2 and Figure 6.

DS12643 - Rev 3 page 9/10



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics - All rights reserved

DS12643 - Rev 3 page 10/10