

MCP2221

USB 2.0 to I²C/UART Protocol Converter with GPIO

Features

Universal Serial Bus (USB)

- Supports Full-Speed USB (12 Mb/s)
- Implements USB Protocol Composite Device:
 - Communication Device Class (CDC) for USB-to-UART Conversion
 - Human Interface Device (HID) for I²C Device Control and Configuration
- 128-Byte Buffer to Handle Data Throughput at Any Supported UART Baud Rate:
 - 64-Byte Transmit
 - 64-Byte Receive
- Human Interface Device (HID) for Both I²C Communication and Control: 64-Byte Buffer to Handle Data Throughput at
 - Any I²C Baud Rate
- Fully-Configurable VID and PID Assignments and String Descriptors
- Bus-Powered or Self-Powered
- USB 2.0-Compliant: TID# 40001594

USB Driver and Software Support

- Enumerates as a Composite USB Device (CDC and HID) Using Standard Drivers for Virtual Com Port (VCP) on the Following Windows[®] Operating Systems: XP[®] (SP3), Vista[®], 7, 8 and 8.1
- Configuration Utility for Establishing a Custom Boot-Up Configuration
- I²C/SMBus Terminal
- Windows DLL

CDC and Universal Asynchronous Receiver/Transmitter (UART) Options

- Communications Device Class (CDC) for the USB-to-UART Option
- Responds to SET LINE CODING Commands to Dynamically Change Baud Rates
- Supports Baud Rates: 300-115200
- · UART Tx and Rx Pins Only
- Serial Number Used During the CDC Enumeration Can Be Enabled by Using the Microchip-Provided Configuration Utility or by Calling the Proper API from the Support Libraries for this Device

I²C/SMBus

- The Device Runs as an I²C Master. The Data to Write/Read on the I²C Bus is Conveyed by the USB Interface
- I²C Master
 - Up to 400 kHz Clock Rate
 - Supports 7-Bit or 10-Bit Addressable Devices; 10-Bit Addressable Devices are Supported through the PC Host Library
 - Supports Block Reads/Writes of up to 65,535 Bytes
- · SMBus Master
 - Supports All of the SMBus Transfers
 - SMBus Functionality Is Achieved through a Combination of Chip and Support Library Processing
 - Up to 400 kHz Clock Rate

General-Purpose Input/Output (GPIO) Pins

- Four General-Purpose Input/Output Pins
- All GP Pins Can Be Assigned to Other Functionalities


Other Functionalities

- UART Activity LED Outputs (UTx and URx)
- SSPND Output Pin
- USBCFG Output Pin (Indicates When the Enumeration Has Completed)
- Three ADC Inputs
- · One DAC with Two Possible Output Options
- Clock Reference Output: 12 MHz or Other Configurable Values
- External Interrupt Edge Detection


Other

- Operating Voltage: 3.0 to 5.5V
- Electrostatic Discharge (ESD) Protection: > 4 kV Human Body Model (HBM)
- Industrial (I) Operating Temperature: -40°C to +85°C
- Automotive AEC-Q100 Qualified

Package Types



Block Diagram



1.0 FUNCTIONAL DESCRIPTION

The MCP2221 is a USB-to-UART serial converter that enables USB connectivity in applications that have UART and/or I^2C interfaces. The device reduces external components by integrating the USB termination resistors and the oscillator needed for USB operation. The MCP2221 has four GP pins for miscellaneous functionalities (including GPIO, USBCFG, SSPND, Clock Output, ADC, DAC and interrupt detector).

See Table 1-1 and **Section 1.7 "Pin Mux Module**" for details about the pin functions.

Pin Name	PDIP, SOIC, SSOP	QFN	Pin Type	Standard Function	AI	ternate Functions
GP0	2	1	I/O	General purpose I/O or alternate function pin	SSPND (OUT) LED_URx (OUT)	Signals when the host has entered Suspend mode UART Rx LED activity output (factory default)
GP1	3	2	I/O	General purpose I/O or alternate function pin	CLKR (OUT) ADC1 (IN) LED_UTX (OUT) IOC (IN)	Clock Reference Output ADC Channel 1
RST	4	3	Ι	Reset input (with internal pull-up)	N/A	
URx	5	4	Ι	UART Rx pin (input)	N/A	
UTx	6	5	0	UART Tx pin (output)	N/A	
GP2	7	6	I/O	General purpose I/O or alternate function pin	USBCFG (OUT) ADC2 (IN) DAC1 (OUT)	USB device configured status (factory default) ADC Channel 2 DAC Output 1
GP3	8	7	I/O	General purpose I/O or alternate function pin	LED_I2C (OUT) ADC3 (IN) DAC2 (OUT)	USB-I ² C traffic indicator (factory default) ADC Channel 3 DAC Output 2
SDA	9	8	I/O	I ² C Data line	N/A	
SCL	10	9	I/O	I ² C Clock line	N/A	
VUSB	11	10	USB	USB Power pin (internally connected to 3.3V) Should be locally bypassed with a high-quality ceramic capacitor		
D-	12	11	USB	USB D-		
D+	13	12	USB	USB D+		
Vss	14	13	Р	Ground		
NC	—	14 15	—	Not Connected		
Vdd	1	16	Р	Power		
EP		17		Exposed Thermal Pad (EP) Do not electrically connect.		

 TABLE 1-1:
 PINOUT DESCRIPTION

1.1 Supported Operating Systems

The following operating systems are supported:

- Windows[®] XP (SP3), Vista, 7, 8 and 8.1
- Linux $^{\ensuremath{\mathbb{R}}}$ any distribution with support for CDC and HID classes
- Mac $OS^{\mathbb{R}}$ all versions beginning with 10.7

1.1.1 ENUMERATION

The MCP2221 enumerates as a composite USB device after Power-on Reset (POR). The device enumerates as both a Human Interface Device (HID) for I^2C , GPIO control, and as CDC for the USB-to-UART converter.

1.1.1.1 USB HID

The MCP2221 enumerates as an HID, so the device can be configured, while the I^2C and GPIO can be controlled. A DLL package, with example applications and tools, is supplied by Microchip on the device web page on the Microchip web site, www.microchip.com.

1.1.1.2 USB CDC

The CDC enumeration implements the USB-to-UART data translation.

1.2 Bus-Matrix Module

The Bus-Matrix module is the heart of the MCP2221. All other modules are tied together and controlled via the Bus-Matrix module. This module manages the data transfers between the USB and the UART, the I^2C Master module, as well as the command requests generated by the USB host controller and commands for controlling the function of the UART, GPIO, ADC, DAC and Clock Output.

1.2.1 UART

The control module interfaces to the UART and USB modules.

1.2.2 ACCESSING THE DEVICE

The MCP2221 can be accessed for reading and writing via USB host commands. The device cannot be accessed or controlled via the UART interface.

1.3 UART Interface

The MCP2221 UART interface consists of the Tx and Rx data signals.

The UART is configurable for several baud rates. The available baud rates are listed in Table 1-2.

1.3.1 GET/SET LINE CODING

The GET_LINE_CODING and SET_LINE_CODING commands are used to read and set the UART parameters while in operation. For example, terminal applications (e.g., Putty, RealTerm, Hyperterminal, etc.) send the SET_LINE_COMMAND when connecting to the port. The MCP2221 responds by setting the baud rate only.

The other parameters (Data Bits, Parity, Stop Bits) remain unchanged.

Note:	MCP2221 supports only eight Data bits,
	no Parity, and one Stop bit.

1.3.1.1 Rounding Errors

Primary baud rate settings (with associated rounding errors) are shown in Table 1-2.

If baud rates other than the ones shown in the table are used, the error percentage can be calculated using Equation 1-1 to find the actual baud rate.

TABLE 1-2:	UART PRIMARY BAUD
	RATES

Desired Rate	Actual rate	% Error
300	300	0.00%
1200	1200	0.00%
2400	2400	0.00%
4800	4800	0.00%
9600	9600	0.00%
19200	19200	0.00%
38400	38339	0.16%
57600	57692	0.16%
115200	115385	0.16%

EQUATION 1-1: SOLVING FOR ACTUAL BAUD RATE

 $ActualRate = \frac{12MHz}{int(x)}$

Where: $x = \frac{12MHz}{DesiredBaud}$

1.3.2 CUSTOM BAUD RATES

Custom baud rates are configured by sending the SET_LINE_CODING USB command. See Section 2.0 "USB Enumeration Process" for more information.

1.4 Device Configuration

The MCP2221 keeps all the essential device configuration settings stored in Flash memory.

Device configuration settings affect the way the MCP2221 behaves at run time.

The settings are stored into the Flash memory on the device. Some of the settings are also copied into SRAM at Power-Up/Reset.

These device configuration settings reside in the following two distinct areas of Flash memory:

Chip Settings

The Chip Settings area stores the key MCP2221 parameters – USB parameters, ADC/DAC reference voltage choice, start-up DAC value, Clock Reference output (CLKR) frequency and duty cycle values.

GP Settings

The GP Settings area stores the GP designation settings. For GP settings that are assigned to GPIO output operation, output values (logic 1 or 0) are also specified.

Even though the MCP2221 places a partial copy of the Chip Settings in SRAM, the following Chip Settings always reside in Flash:

- USB Manufacturer/Product and Serial Number descriptors
- · USB VID and PID pair
- USB options (e.g., the requested amount of current that is presented to the USB host during the USB enumeration process)

1.4.1 POWER-UP RESET DEVICE CONFIGURATION BEHAVIOR


At Power-up Reset, the MCP2221 configures the device options (GP designation, special function pins parameters and USB enumeration options) according to the Flash settings. Then, the Flash Chip Settings and GP Settings are loaded into SRAM to allow for their temporary modification at run time.

Chip Settings of the Device Configuration Flash are copied partially into SRAM. Only the run-time-modifiable parameters are copied into SRAM.

GP Settings of the Device Configuration Flash (GP settings area) are copied entirely into the SRAM. By copying the GP settings completely into SRAM, the user is allowed to completely change the GP designation at run time.

The SRAM copy of the settings can be altered at run time in order to change certain device behavior, e.g., GP designation (the GPs can be re-assigned for a different type of operation than the one assigned at Power-up) and special parameters (DAC value, ADC/DAC voltage references, Clock output value).

FIGURE 1-1: CHIP SETTINGS RUN TIME MANAGEMENT



The SRAM settings (GP and partial Chip Settings) can be modified through USB HID commands and they will have an effect on the following device features:

- GP pin designation (switch between GPIO, dedicated or special functions modes)
- GPIO direction and output value (only for GPIO outputs) – for the GPs assigned to work in GPIO mode
- Clock Output duty cycle and value if GP1 is assigned for CLKR mode (Clock Reference output mode), by modifying the SRAM settings, the clock frequency and duty cycle can be changed at run time
- DAC value and voltage reference used the DAC value setting as well as the voltage reference used for it are stored in SRAM settings and they can be changed at run time. Through this mechanism, at run time the user can change the DAC value, as well as the voltage reference.
- ADC voltage reference value the voltage reference used for ADC conversions can be changed by altering its corresponding SRAM setting
- Interrupt-on-change (IOC) detector settings if GP1 is assigned for IOC mode, the SRAM settings are used for setting up the triggers used for external interrupt detection (positive or negative edge detection, or both)

1.4.2 CHIP SETTINGS MAP

The Chip Settings area resides in Flash memory and is copied into SRAM at run time. Not all of the device's settings can be altered at run time. All the fields in the Flash settings can be altered by the user.

Byte Index	Register Name	Comments
0	CHIPSETTING0	Controls the USB CDC serial number enumeration, default state for the GP LED designation, default state for GP dedicated-function pins and chip settings protection level
1	CHIPSETTING1	Default clock output divider and duty cycle
2	CHIPSETTING2	DAC reference options and default DAC value
3	CHIPSETTING3	ADC reference and interrupt detection settings
4	USBVIDL	USB VID lower byte
5	USBVIDH	USB VID higher byte
6	USBPIDL	USB PID lower value
7	USBPIDH	USB PID higher byte
8	USBPWRATTR	USB power attributes
9	USBREQCRT	USB required current
10	PASS0	Password byte 0
11	PASS1	Password byte 1
12	PASS2	Password byte 2
13	PASS3	Password byte 3
14	PASS4	Password byte 4
15	PASS5	Password byte 5
16	PASS6	Password byte 6
17	PASS7	Password byte 7

TABLE 1-3: CHIP SETTINGS MAP

R/W-0	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-0	R/W-0
CDCSNEN	LEDURXINST	LEDUTXINST	LEDI2CINST	SSPNDINST	USBCFGINST	CHIPPROT1	CHIPPROT0
bit 7							bit 0
Legend:							
R = Readat	R = Readable bit		bit	•	nented bit, read	as '0'	
-n = Value at POR		'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown
bit 7		SB CDC Serial		-			
		Serial Number DC Serial Num		-	ault)		
bit 6		LED UART RX					
	1 = LED UART Rx is inactive high and active low (factory default)						
	0 = LED UART Rx is inactive low and active high						
bit 5	LEDUTXINST: LED UART Tx Inactive State						
		T Tx is inactive	•		default)		
		T Tx is inactive		high			
bit 4	_	LED I ² C Inactiv		(footom / dofouit	N		
	 1 = LED I²C is inactive high and active low (factory default) 0 = LED I²C is inactive low and active high 						
bit 3		SSPND Inactive	0				
	1 = SSPND is	inactive high a	nd active low (factory default))		
	0 = SSPND is	inactive low an	d active high				
bit 2		USBCFG Inac					
		is inactive high			lt)		
h:+ 4 0		is inactive low a	0				
bit 1-0	11 =Reserved	:0>: Chip Settin	gs Protection I	Levei			
	10 =Permaner	ntly locked					
	01 =Password						
	00 =Chip settir	ngs unprotected	l (factory defau	ult)			

REGISTER 1-1: CHIPSETTING0 REGISTER

REGISTER 1-2:	CHIPSETTING1 REGISTER

R/W-0	R/W-0	R/W-0	R/W-1	R/W-0	R/W-0	R/W-1	R/W-0
_		_	CLKDC1	CLKDC0	CLKDIV2	CLKDIV1	CLKDIV0
bit 7				ł			bit 0
Logondu							
Legend: R = Readabl	a hit	W = Writable	b.it		monted hit rea	d aa '0'	
				-	mented bit, rea		
-n = Value at	PUR	'1' = Bit is set		'0' = Bit is cle	eared	x = Bit is unk	nown
bit 7-5	Reserved: S	Set to '0'					
bit 4-3	CLKDC<1:0>: Clock-Out Duty Cycle						
	10 =Duty cy (factor) 01 =Duty cy	rcle 50% (50% (ry default) rcle 25% (25% (of 1 clock period of 1 clock period of 1 clock period of 1 clock period	is logic '1' and is logic '1' and	50% of 1 clock	period is logic	ʻ0 ')
bit 2-0	CLKDIV<2:	0>: Clock-Out E	Divider Output				
	110 =750 kł 101 =1.5 MI 100 =3 MHz 011 =6 MHz 010 =12 MH	Iz clock output					

REGISTER 1-3: CHIPSETTING2 REGISTER

R/W-1	R/W-0	R/W-0	R/W-0	R/W-1	R/W-0	R/W-0	R/W-0
DACVRM1	DACVRM0	DACREF	DACVAL4	DACVAL3	DACVAL2	DACVAL1	DACVAL0
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit	, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-6	DACVRM<1:0>: DAC Internal Voltage Reference (DAC VRM) Selection 11 =VRM voltage is 4.096V (only if VDD is above this voltage) 10 =VRM voltage is 2.048V (factory default) 01 =VRM voltage is 1.024V 00 =VRM is off
bit 5	DACREF: DAC Reference Output Selection
bit 4-0	 1 = DAC reference output is DAC VRM voltage selection 0 = DAC reference output is VDD (factory default) DACVAL<4:0>: Initial DAC Output Value
	·

REGISTER 1-4: CHIPSETTING3	
----------------------------	--

Legend: R = Readable bit W = Writable bit U = Unimplemented bit, read as '0' on = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown Dit 7 Reserved: Set to '0' Dit 6 INTDETFEEN: Interrupt Falling Edge Detect Enable 1 = Interrupt detector will trigger when a falling edge is detected (factory default) 0 = Falling edges will not trigger the detector Dit 5 INTDETREEN: Interrupt Rising Edge Detect Enable 1 = Interrupt detector will trigger when a rising edge is detected (factory default) 0 = Rising edges will not trigger the detector Dit 4-3 ADCVRM ADCVRM 1.0> 1 = VRM voltage is 4.096V (only if VDD is above this voltage) 1 = VRM voltage is 1.024V (factory default) 0 = VRM voltage is 1.024V (factory default) 0 = VRM is off Dit 2 ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD	R/W-0	R/W-1	R/W-1	R/W-0	R/W-1	R/W-1	R/W-0	R/W-0				
Legend: R = Readable bit W = Writable bit U = Unimplemented bit, read as '0' in = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown bit 7 Reserved: Set to '0' bit 6 INTDETFEEN: Interrupt Falling Edge Detect Enable 1 = Interrupt detector will trigger when a falling edge is detected (factory default) 0 = Falling edges will not trigger the detector bit 5 INTDETREEN: Interrupt Rising Edge Detect Enable 1 = Interrupt detector will trigger when a rising edge is detected (factory default) 0 = Rising edges will not trigger the detector bit 4-3 ADCVRM ADCVRM ADCV Internal Voltage Reference (ADC VRM) Selection 11 = VRM voltage is 4.096V (only if VDD is above this voltage) 10 = VRM voltage is 1.024V (factory default) 00 = VRM voltage is 1.024V (factory default) 00 = VRM is off bit 2 ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD	_	INTDETFEEN	INTDETREEN	ADCVRM1	ADCVRM0	ADCREF	_					
R = Readable bit W = Writable bit U = Unimplemented bit, read as '0' on = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown bit 7 Reserved: Set to '0' bit 6 INTDETFEEN: Interrupt Falling Edge Detect Enable 1 = Interrupt detector will trigger when a falling edge is detected (factory default) 0 = Falling edges will not trigger the detector 0 bit 5 INTDETREEN: Interrupt Rising Edge Detect Enable 1 = Interrupt detector will trigger when a rising edge is detected (factory default) 0 = Rising edges will not trigger the detector bit 4-3 ADCVRM<1:0>: ADC Internal Voltage Reference (ADC VRM) Selection 11 = VRM voltage is 4.096V (only if VDD is above this voltage) 10 = VRM voltage is 1.024V (factory default) 00 = VRM is off bit 2 ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD	bit 7		1					bit 0				
R = Readable bit W = Writable bit U = Unimplemented bit, read as '0' on = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown bit 7 Reserved: Set to '0' bit 6 INTDETFEEN: Interrupt Falling Edge Detect Enable 1 = Interrupt detector will trigger when a falling edge is detected (factory default) 0 = Falling edges will not trigger the detector 0 bit 5 INTDETREEN: Interrupt Rising Edge Detect Enable 1 = Interrupt detector will trigger when a rising edge is detected (factory default) 0 = Rising edges will not trigger the detector bit 4-3 ADCVRM<1:0>: ADC Internal Voltage Reference (ADC VRM) Selection 11 = VRM voltage is 4.096V (only if VDD is above this voltage) 10 = VRM voltage is 1.024V (factory default) 00 = VRM is off bit 2 ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD												
in = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown bit 7 Reserved: Set to '0' bit 6 INTDETFEEN: Interrupt Falling Edge Detect Enable 1 = Interrupt detector will trigger when a falling edge is detected (factory default) 0 = Falling edges will not trigger the detector bit 5 INTDETREEN: Interrupt Rising Edge Detect Enable 1 = Interrupt detector will trigger when a rising edge is detected (factory default) 0 = Rising edges will not trigger the detector bit 4-3 ADCVRM<1:0>: ADC Internal Voltage Reference (ADC VRM) Selection 11 = VRM voltage is 4.096V (only if VDD is above this voltage) 10 = VRM voltage is 1.024V (factory default) 00 = VRM is off bit 2 ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD	Legend:											
 Applier of the second state of the se	R = Readab	le bit	W = Writable bi	t	U = Unimple	mented bit, rea	ad as '0'					
 INTDETFEEN: Interrupt Falling Edge Detect Enable Interrupt detector will trigger when a falling edge is detected (factory default) 0 = Falling edges will not trigger the detector INTDETREEN: Interrupt Rising Edge Detect Enable Interrupt detector will trigger when a rising edge is detected (factory default) Rising edges will not trigger the detector INTDETREEN: Interrupt Rising Edge Detect Enable Interrupt detector will trigger when a rising edge is detected (factory default) Rising edges will not trigger the detector ADCVRM<1:0>: ADC Internal Voltage Reference (ADC VRM) Selection INTUBETREEN: ADC Internal Voltage Reference (ADC VRM) Selection INTUBETREEN: a to trigger is 4.096V (only if VDD is above this voltage) VRM voltage is 2.048V INTUBETREEN: ADC Reference Output Selection ADCREF: ADC Reference Output Selection ADC reference output is ADC VRM voltage selection (factory default) ADC reference output is VDD 	-n = Value a	t POR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown				
 1 = Interrupt detector will trigger when a falling edge is detected (factory default) 0 = Falling edges will not trigger the detector bit 5 INTDETREEN: Interrupt Rising Edge Detect Enable 1 = Interrupt detector will trigger when a rising edge is detected (factory default) 0 = Rising edges will not trigger the detector bit 4-3 ADCVRM<1:0>: ADC Internal Voltage Reference (ADC VRM) Selection 11 =VRM voltage is 4.096V (only if VDD is above this voltage) 10 =VRM voltage is 2.048V 01 =VRM voltage is 1.024V (factory default) 00 = VRM is off bit 2 ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD 	bit 7	Reserved: Set	t to '0'									
 1 = Interrupt detector will trigger when a falling edge is detected (factory default) 0 = Falling edges will not trigger the detector bit 5 INTDETREEN: Interrupt Rising Edge Detect Enable 1 = Interrupt detector will trigger when a rising edge is detected (factory default) 0 = Rising edges will not trigger the detector bit 4-3 ADCVRM<1:0>: ADC Internal Voltage Reference (ADC VRM) Selection 11 =VRM voltage is 4.096V (only if VDD is above this voltage) 10 =VRM voltage is 2.048V 01 =VRM voltage is 1.024V (factory default) 00 = VRM is off bit 2 ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD 	bit 6	INTDETFEEN:	Interrupt Falling	Edge Detect	Enable							
bit 5 INTDETREEN: Interrupt Rising Edge Detect Enable 1 = Interrupt detector will trigger when a rising edge is detected (factory default) 0 = Rising edges will not trigger the detector bit 4-3 ADCVRM<1:0>: ADC Internal Voltage Reference (ADC VRM) Selection 11 =VRM voltage is 4.096V (only if VDD is above this voltage) 10 =VRM voltage is 2.048V 01 =VRM voltage is 1.024V (factory default) 00 = VRM is off bit 2 ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD												
 1 = Interrupt detector will trigger when a rising edge is detected (factory default) 0 = Rising edges will not trigger the detector ADCVRM<1:0>: ADC Internal Voltage Reference (ADC VRM) Selection 11 =VRM voltage is 4.096V (only if VDD is above this voltage) 10 =VRM voltage is 2.048V 01 =VRM voltage is 1.024V (factory default) 00 = VRM is off ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD 												
 0 = Rising edges will not trigger the detector add CVRM<1:0>: ADC Internal Voltage Reference (ADC VRM) Selection 11 =VRM voltage is 4.096V (only if VDD is above this voltage) 10 =VRM voltage is 2.048V 01 =VRM voltage is 1.024V (factory default) 00 = VRM is off bit 2 ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD 	bit 5	INTDETREEN	Interrupt Rising	Edge Detect	Enable							
 11 =VRM voltage is 4.096V (only if VDD is above this voltage) 10 =VRM voltage is 2.048V 01 =VRM voltage is 1.024V (factory default) 00 = VRM is off ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD 						ected (factory d	lefault)					
 10 =VRM voltage is 2.048V 01 =VRM voltage is 1.024V (factory default) 00 = VRM is off ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD 	bit 4-3	ADCVRM<1:0	>: ADC Internal \	/oltage Refere	ence (ADC VR	M) Selection						
01 =VRM voltage is 1.024V (factory default) 00 = VRM is off Doit 2 ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD		11 =VRM volta	ige is 4.096V (on	ly if VDD is ab	ove this voltag	le)						
 00 = VRM is off ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD 												
bit 2 ADCREF: ADC Reference Output Selection 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD												
 1 = ADC reference output is ADC VRM voltage selection (factory default) 0 = ADC reference output is VDD 	hit 2			ut Selection								
0 = ADC reference output is VDD					ae selection (f	actory default)						
· ·			•		30 001001011 (1							
	bit 1-0											

REGISTER 1-5: USBVIDL REGISTER

R/W-1	R/W-1	R/W-0	R/W-1	R/W-1	R/W-0	R/W-0	R/W-0
USBVIDL7	USBVIDL6	USBVIDL5	USBVIDL4	USBVIDL3	USBVIDL2	USBVIDL1	USBVIDL0
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	d as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-0 USBVIDL<7:0>: USB VID Lower Byte (factory default: 0xD8(hex))

REGISTER 1-6: USBVIDH REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-1	R/W-0	R/W-0
USBVIDH7	USBVIDH6	USBVIDH5	USBVIDH4	USBVIDH3	USBVIDH2	USBVIDH1	USBVIDH0
bit 7			•			•	bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit,	, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-0 USBVIDH<7:0>: USB VID Higher Byte (factory default: 0x04(hex))

REGISTER 1-7: USBPIDL REGISTER

R/W-1	R/W-1	R/W-0	R/W-1	R/W-1	R/W-1	R/W-0	R/W-1
USBPIDL7	USBPIDL6	USBPIDL5	USBPIDL4	USBPIDL3	USBPIDL2	USBPIDL1	USBPIDL0
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, rea	d as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-0 USBPIDL<7:0>: USB PID Lower Byte (factory default: 0xDD(hex))

REGISTER 1-8: USBPIDH REGISTER

| R/W-0 |
|----------|----------|----------|----------|----------|----------|----------|----------|
| USBPIDH7 | USBPIDH6 | USBPIDH5 | USBPIDH4 | USBPIDH3 | USBPIDH2 | USBPIDH1 | USBPIDH0 |
| bit 7 | | | • | | | • | bit 0 |

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'	
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-0 USBPIDH<7:0>: USB PID Higher Byte (factory default: 0x00(hex))

REGISTER 1-9: USBPWRATTR REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
	SELFPWR	REMWKUP	—	—	—	—	—
bit 7							bit 0

Legend:				
R = Readable bit	W = Writable bit	U = Unimplemented bit	U = Unimplemented bit, read as '0'	
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

bit 7	Reserved: Reserved – set to '1' (factory default)
bit 6	SELFPWR: USB Self-Powered Attribute
	 1 = Chip will enumerate on the USB bus as being self-powered 0 = Chip will enumerate on the USB bus as being USB-bus powered (factory default)
bit 5	REMWKUP: USB Remote Wake-Up Capability
	 1 = Chip will enumerate on the USB bus as being able to wake-up the USB host 0 = Chip will enumerate as not being capable of remote wake-up of the USB host (factory default)
bit 4-0	Reserved: Set all bits to '0' (factory default)

REGISTER 1-10: USBREQCRT REGISTER

R/W-0	R/W-0	R/W-1	R/W-1	R/W-0	R/W-0	R/W-1	R/W-0
USBRE-	USBRE-	USBRE-	USBRE-	USBRE-	USBRE-	USBRE-	USBRE-
QCRT7	QCRT6	QCRT5	QCRT4	QCRT3	QCRT2	QCRT1	QCRT0
bit 7 bit 0							
Legend:							
R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'		l as '0'					
-n = Value at POR '1' = Bit is set '0' =		'0' = Bit is clea	ared	x = Bit is unk	nown		

bit 7-0 USBREQCRT<7:0>: USB Bus-Powered Required Current Amount (in units of 2 mA) Factory default is 50 (decimal); the USB enumeration interprets this value as a current requirement of 100 mA.

REGISTER 1-11: PASS0 – PASS7 REGISTER

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| PASSx7 | PASSx6 | PASSx5 | PASSx4 | PASSx3 | PASSx2 | PASSx1 | PASSx0 |
| bit 7 | | | | | | | bit 0 |

Legend:				
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

bit 7-0 **PASSx<7:0>:** Password Byte X Value (factory default is 0)

1.4.3 GP SETTINGS MAP

The GP Settings area resides in Flash memory and is copied into SRAM at run time. The user can alter both the Flash and the SRAM GP settings. Any modification in the SRAM copy of the GP settings will have an immediate effect. The GP pins designation changes according to the new content of the SRAM settings. The Flash variant of the settings will affect the Power-Up behavior of the GP pins.

TABLE 1-4:GP SETTINGS MAP

Byte Index	Register Name	Comments
0	GPSETTING0	GP0 pin designation and GPIO default output value, when GP is set for GPIO output operation
1	GPSETTING1	GP1 pin designation and GPIO default output value, when GP is set for GPIO output operation
2	GPSETTING2	GP2 pin designation and GPIO default output value, when GP is set for GPIO output operation
3	GPSETTING3	GP3 pin designation and GPIO default output value, when GP is set for GPIO output operation

REGISTER 1-12: GPSETTING0 REGISTER

R/W-0	R/W-0	R/W-0	R/W-1	R/W-0	R/W-0	R/W-1	R/W-0
	—	—	GPIOOUTVAL	GPIODIR	GPDES2	GPDES1	GPDES0
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'	
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-5 Re	eserved: Set to '0'
------------	---------------------

bit 4	GPIOOUTVAL: GPIO Output Value (valid only when GP0 is set for GPIO output operation)

1 = Default output value is logic '1' (factory default)

- 0 = Default output value is logic '0'
- bit 3 **GPIODIR:** GPIO Direction (input or output; valid only when GP0 is set for GPIO operation) 1 = GPIO Input
 - 0 = GPIO Output (factory default)

bit 2-0 **GPDES<2:0>:** GP0 Designation

- 111 =Reserved
 - 110 =Reserved
 - 101 =Reserved
 - 100 =Reserved
 - 011 =Reserved
 - 010 =Alternate function 0 (LED UART Rx LEDURX) (factory default)
 - 001 =Dedicated function operation (SSPND)
 - 000 =GPIO operation (GPIO0)

REGISTER 1-13: GPSETTING1 REGISTER

R/W-0	R/W-0	R/W-0	R/W-1	R/W-0	R/W-0	R/W-1	R/W-1
_	_	_	GPIOOUTVAL	GPIODIR	GPDES2	GPDES1	GPDES0
bit 7							bit C
Logondu							
Legend: R = Readable	hit	W = Writable	bit	LI = Unimplei	mented bit, rea	d as '0'	
-n = Value at		'1' = Bit is se		'0' = Bit is cle	,	x = Bit is unk	nown
bit 7-5	Reserved: S	Set to '0'					
bit 4	1 = Default		but Value (valid onl logic '1' (factory d	-	s set for GPIO	output operatio	on)
bit 3		PIO Direction	(input or output; va	alid only when	GP1 is set for	GPIO operatio	n)
	0 = GPIO O	utput (factory	default)				
bit 2-0	111 =Reserv 110 =Reserv 101 =Reserv 100 =Alterna 011 =Alterna 010 =Alterna 001 =Dedica	ved ved ate function 2 (ate function 1 (ate function 0 (Interrupt detector) LED UART Tx – L ADC1) peration (Clock Ou	EDUTX) (facto	ory default)		

REGISTER 1-14: GPSETTING2 REGISTER

R/W-0	R/W-0	R/W-0	R/W-1	R/W-0	R/W-0	R/W-0	R/W-1		
_	_	_	GPIOOUTVAL	GPIODIR	GPDES2	GPDES1	GPDES0		
bit 7	l .						bit 0		
Legend:									
R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'									
-n = Value a	t POR	'1' = Bit is se	t	'0' = Bit is cle	eared	x = Bit is unki	nown		
bit 7-5	Reserved:	Set to '0'							
bit 4	GPIOOUTV	AL: GPIO Out	out Value (valid onl	y when GP2 is	s set for GPIO	output operatio	on)		
	1 = Default	output value is	logic '1' (factory d	efault)					
	0 = Default	output value is	logic '0'						
bit 3	GPIODIR: (GPIO Direction	(input or output; va	alid only when	GP2 is set for	GPIO operatio	n)		
	1 = GPIO II	nput							
	0 = GPIO (Dutput (factory	default)						
bit 2-0	GPDES<2:0	0>: GP2 Desigi	nation						
	111 =Reser	rved							
	110 =Reser								
	101 =Reserved								
		100 =Reserved							
	100 =Rese								
	100 =Reser 011 =Altern	ate function 1 (,						
	100 =Reser 011 =Altern 010 =Altern	ate function 1 (ate function 0 (,	6) (factory defa	ault)				

REGISTER 1-15: GPSETTING3 REGISTER

R/W-0	R/W-0	R/W-0	R/W-1	R/W-0	R/W-0	R/W-0	R/W-1
_	_	_	GPIOOUTVAL	GPIODIR	GPDES2	GPDES1	GPDES0
bit 7	1					•	bit 0
Legend:							
R = Readable	e bit	W = Writable	bit	U = Unimpler	mented bit, rea	d as '0'	
-n = Value at	POR	'1' = Bit is se	t	'0' = Bit is cle	ared	x = Bit is unk	nown
bit 7-5	Reserved: S	Set to '0'					
bit 4	GPIOOUTV	AL: GPIO Out	out Value (valid on	ly when GP3 is	s set for GPIO	output operatio	on)
	1 = Default	output value is	logic '1' (factory d	lefault)			
	0 = Default	output value is	logic '0'				
bit 3	GPIODIR: G	PIO Direction	(input or output; va	alid only when	GP3 is set for	GPIO operatio	n)
	1 = GPIO In						
	0 = GPIO O	utput (factory	default)				
bit 2-0	GPDES<2:0	: GP3 Desigi	nation				
	111 =Reser						
	110 =Reser						
	101 =Reser 100 =Reser						
		ate function 1 (
		ate function 0 (,				
		,	peration (LEDI2C)	(factory defau	lt)		
	000 =GPIO	operation (GP	103)	-			

1.5 USB Module (HID, CDC and Transceiver Modules)

The USB HID and CDC modules in the MCP2221 are full-speed USB 2.0-compliant.

- Composite device (CDC + HID):
 - CDC: USB-to-UART Communications
 - HID: I²C Transactions, GPIO Control, Configuration and Miscellaneous Operations (ADC, DAC, Clock Output)
- 128-byte buffer to handle data throughput at any UART Baud Rate:
 - 64-Byte Transmit
 - 64-Byte Receive
- Fully Configurable VID and PID Assignments and Descriptors (stored on-chip)
- · Bus-Powered or Self-Powered

1.5.1 DESCRIPTORS

During configuration, the supplied PC interface stores the descriptors in the MCP2221.

1.5.2 SUSPEND AND RESUME

The USB Suspend and Resume signals are supported for power management of the MCP2221. The device enters Suspend mode when Suspend Signaling is detected on the bus.

The MCP2221 exits Suspend mode when any of the following events occur:

- · Resume Signaling is detected or generated
- A USB Reset signal is detected
- A device Reset occurs

1.6 USB Transceiver

The MCP2221 has a built-in USB 2.0 full-speed transceiver internally connected to the USB module.

The USB transceiver obtains power from the VUSB pin, which is internally connected to the 3.3V regulator. The best electrical signal quality is obtained when VUSB is locally bypassed with a high-quality ceramic capacitor.

1.6.1 INTERNAL PULL-UP RESISTORS

The MCP2221 devices have built-in pull-up resistors designed to meet the requirements for full-speed USB.

1.6.2 MCP2221 POWER OPTIONS

The following are the main power options for the MCP2221:

• USB Bus-Powered (5V)


· 3.3V Self-Powered

1.6.2.1 Internal Power Supply Details

MCP2221 offers various options for power supply. To meet the required USB signaling levels, the MCP2221 incorporates an internal LDO that is used solely by the USB transceiver to present the correct D+/D- voltage levels.

Figure 1-2 shows the internal connections of the USB transceiver LDO in relation to the VDD power supply rail. The output of the USB transceiver LDO is tied to the VUSB line. A capacitor connected to the VUSB pin is required if the USB transceiver LDO provides the 3.3V supply to the transceiver.






The provided VDD voltage has a direct influence on the voltage levels present on the GPIO and UART Tx/Rx pins. When VDD is 5V, all of these pins will have a logical '1' around 5V with the variations specified in **Section 4.1 "DC Characteristics"**.

For applications that require a 3.3V logical '1' level, VDD must be connected to a power supply providing the 3.3V voltage. In this case, the internal USB transceiver LDO cannot provide the required 3.3V power. It is necessary to also connect the VUSB pin of the MCP2221 to the 3.3V power supply rail. This way, the USB transceiver is powered up directly from the 3.3V power supply.

1.6.2.2 USB Bus-Powered (5V)

In Bus Power Only mode, all power for the application is drawn from the USB (Figure 1-3). This is effectively the simplest power method for the device.





In order to meet the inrush current requirements of the USB 2.0 specifications, the total effective capacitance appearing across VBUs and ground must be no more than 10 μ F. If it is more than 10 μ F, some kind of inrush limiting is required. For more details on Inrush Current Limiting, search for that subject in the latest "Universal Serial Bus Specification".

According to the USB 2.0 specification, all USB devices must also support a Low-Power Suspend mode. In the USB Suspend mode, devices must consume no more than 500 μ A (or 2.5 mA for high-powered devices that are remote wake-up capable) from the 5V VBUS line of the USB cable.

The host signals the USB device to enter Suspend mode by stopping all USB traffic to that device for more than 3 ms.


The USB bus provides a 5V voltage. However, the USB transceiver requires 3.3V for the signaling (on D+ and D- lines).

During USB Suspend mode, the D+ or D- pull-up resistor must remain active, which will consume some of the allowed suspend current budget (500 μ A/2.5 mA). The VUSB pin requires an external bypass capacitor with a value between 0.22 and 0.47 μ F (ceramic cap).

Figure 1-4 shows a circuit where MCP2221's internal LDO is used to provide 3.3V to the USB transceiver. The voltage on the VDD affects the voltage levels onto the UART and GPIO pins. With VDD at 5V, these pins will have a logic '1' of 5V with the variations specified in **Section 4.1 "DC Characteristics"**.

FIGURE 1-4:

TYPICAL POWER SUPPLY OPTION USING THE 5V PROVIDED BY THE USB



1.6.2.3 3.3V Self-Powered

Typically, many embedded applications are using 3.3V power supplies. When such option is available in the target system, MCP2221 can be powered-up from the existing 3.3V power supply rail. The typical connections for MCP2221 are shown in Figure 1-5.


In this example, MCP2221 has both VDD and VUSB lines tied to the 3.3V rail. These tied connections disable the internal USB transceiver LDO of the MCP2221 to regulate the power supply on the VUSB pin. Another consequence is that the '1' logical level on the GPIO pins will be at the 3.3V level, in accordance with the variations specified in Section 4.1 "DC Characteristics".

1.6.2.4 Remote Wake-Up Capability

The MCP2221 offers a mechanism for triggering a remote wake-up event for the USB host. The remote wake-up trigger works only with the external interrupt detector.

In order to use this capability, GP1 must be designated for interrupt detection operation. Before the USB host goes into Sleep/Standby, the interrupt detector must be set up for detecting positive edges, negative edges or both; also, the detector flag must be cleared. After these conditions are met, the USB host can go into Sleep/Standby mode and it will be awakened whenever an external signal on GP1 triggers the interrupt detector.

FIGURE 1-5: USING AN EXTERNALLY PROVIDED 3.3V POWER SUPPLY



1.7 Pin Mux Module

The Pin Mux module offers multiple functionalities for the GP pins.

1.7.1 CONFIGURABLE PIN FUNCTIONS

The pins can be configured as:

- GPIO individually configurable general-purpose input or output
- SSPND USB Suspend state
- USBCFG indicates USB configuration status
- LED_URX indicates UART receive traffic (when seen from the MCP2221)
- LED_UTX indicates UART transmit traffic (when seen from the MCP2221)
- LED_I2C indicates I²C traffic
- ADC1/2/3 analog inputs connected to the internal 10-bit ADC
- DAC1/2 analog outputs connected to the same 5-bit DAC
- CLKR digital clock output (the nominal value is 12 MHz, but other values are possible)
- · IOC external interrupt detector

1.7.1.1 GPIO Pin Function

When the GPIO pin function is enabled for a given GP(n) pin, it will operate as a digital input or an output pin. When configured as a digital output, its value is controlled through the USB HID commands. When configured as a digital input, its logic value is read using USB HID commands.

1.7.1.2 SSPND Pin Function

The SSPND pin (if enabled) reflects the USB state (Suspend/Resume). The pin is active low (factory-default setting; see the CHIPSETTING0 register for more details) when the Suspend state has been issued by the USB host. Likewise, the pin drives high after the Resume state is achieved.

This pin allows the application to go into Low Power mode when USB communication is suspended and switches to a full active state when USB activity is resumed.

1.7.1.3 USBCFG Pin Function

The USBCFG pin (if enabled) starts out low (factory default setting; see the CHIPSETTING0 register for more details) during Power-Up or after Reset and goes high after the device successfully configures to the USB. The pin will go low when in Suspend mode and high when the USB resumes.

1.7.1.4 LED_URX

The "Rx" in this pin name refers to the UART of the MCP2221. The LED_URX pin is an indicator of UART Rx characters being received.

This pin will pulse low or high (depending on the chip configuration settings; see the CHIPSETTING0 register for more details) for a period of time (a few milliseconds). This allows the application to provide a visual indication of the UART Rx traffic.

1.7.1.5 LED_UTX

The "Tx" in this pin name refers to the UART of the MCP2221. The LED_UTX pin is an indicator of UART Tx characters being transmitted.

This pin will pulse low or high (depending on the chip configuration settings; see the CHIPSETTING0 register for more details) for a period of time (a few milliseconds). This allows the application to provide a visual indication of the UART Tx traffic.

1.7.1.6 LED_I2C

The "I2C" in this pin name refers to the I²C module in the MCP2221. The LED_I2C pin is an indicator of I²C activity.

This pin will pulse low or high (depending on the chip configuration settings; see the CHIPSETTING0 register for details) for a period of time (a few milliseconds). This allows the application to provide a visual indication of the l^2C traffic.

1.7.1.7 ADC1/2/3

When GP1/2/3 are configured for ADC operation, they will work as analog input pins and they are tied to the first three channels of the 10-bit ADC in the MCP2221.

1.7.1.8 DAC1/2

When GP2/3 are configured for DAC operation, they will work as analog output pins and they are tied to the output of the MCP2221's 5-bit DAC.

GP Designation Bits <2:0>	Assignment	GP0	GP1	GP2	GP3
000	GPIO	GPIO	GPIO	GPIO	GPIO
001	DEDICATED_FUNC	SSPND	CLK OUT	USBCFG	LED_I2C
010	ALT_FUNC_0	LED_URX	ADC1	ADC2	ADC3
011	ALT_FUNC_1	—	LED_UTX	DAC1	DAC2
100	ALT_FUNC_2	_	IOC		_

TABLE 1-5: GP DESIGNATION TABLE

1.8 GPIO/ADC/DAC Module

This module communicates with the USB HID sub-module through the Bus Matrix module. It allows the manipulation of GPIOs, retrieving the ADC data and setting the DAC value.

1.8.1 GPIO

When the GPs are configured for GPIO operation, those configured GPs can be used as digital inputs or outputs.

When working as outputs, the GPs output logic levels (logic 0 or 1).

1.8.1.1 VRM

The ADC and DAC sub-modules each have a voltage reference module (VRM). Each VRM can be configured (at Power-Up and run time) to output one of the four voltage choices available.

The $\mathsf{V}\mathsf{R}\mathsf{M}$ can provide the following voltages as a reference:

- VDD the VRM output is exactly the voltage present at the VDD pin of the MCP2221. It can take any value from 3.3 to 5V.
- 1.024V the VRM output of 1.024V is obtained from an internal voltage reference
- 2.048V the VRM output of 2.048V is obtained from an internal voltage reference
- 4.096V the VRM output of 4.096V is obtained from an internal voltage reference. If the VDD is lower than 4.096V, the VRM output will have the value of VDD.


1.8.2 ADC CONVERTER

The ADC converter is producing 10-bit values and it uses its own VRM module.

It features three external channels (connected to GP1/2/3 if configured for ADC operation).

The sampling rate of the ADC is around 1000 sps.

FIGURE 1-6: ADC SUB-MODULE DETAILS




1.8.3 DAC CONVERTER

The DAC is 5-bit wide, has a single analog output and it uses its own VRM module.

The DAC output voltage can be routed to GP2/3 (if GP2/3 are configured for DAC operation).

If the GP2 and GP3 are configured for DAC operation, they will present the same analog voltage value because they are connected to the same DAC output.

FIGURE 1-7: DAC SUB-MODULE DETAILS



1.9 CLKR

When GP1 is configured for clock output operation, the GP1 pin will act as a digital output, providing a clock signal derived from the device's internal clock. The clock's nominal frequency is $12 \text{ MHz} \pm 0.25\%$. Other clock values and duty cycles are possible by setting different values that are associated with this mode of operation.

1.10 IOC

When GP1 is configured for interrupt-on-change (IOC) operation, GP1 acts as a digital input that is sensitive to positive and negative edges. Depending on the settings associated with this mode of operation, the GP1 can detect positive, negative or both edges.

1.11 RESET/POR

1.11.1 RESET PIN

The \overrightarrow{RST} pin provides a method for triggering an external Reset of the device. A Reset is generated by holding the pin low. These devices have a noise filter in the Reset path, which detects and ignores small pulses.

1.11.2 POR

A POR pulse is generated on-chip whenever VDD rises above a certain threshold. This allows the device to start in the initialized state when VDD is adequate for operation.

To take advantage of the POR circuitry, tie the $\overline{\text{RST}}$ pin to VDD through a resistor $(1 - 10 \text{ k}\Omega)$. This will eliminate external RC components usually needed to create a POR delay.

When the device starts normal operation (i.e., exits the Reset condition), device operating parameters (voltage, frequency, temperature, etc.) must be met to ensure operation. If these conditions are not achieved, the device must be held in Reset until the operating conditions are met.

1.12 Internal Oscillator

The MCP2221 features an internal oscillator that provides a 12 MHz clock, which is needed for the USB modules (HID and CDC).

Full-speed USB is nominally 12 Mb/s. The clock signal's accuracy is over temp (2,500 ppm maximum).

The internal clock of the MCP2221 is fed into the CLKR module to provide a clock signal outside of the device.

GP1 can be configured as a clock output pin providing a 12 MHz clock to the rest of the system. Other clock and duty-cycle values are possible by using different settings for this module.

1.13 I²C Master Module

The I^2C Master module is responsible for the I^2C traffic generation. The module is controlled through the USB HID, through the Bus Matrix module.

The I^2C module only implements the functionality of an I^2C /SMBus Master.

1.13.1 I²C/SMBUS MASTER

The I^2C Master initiates all the I^2C /SMBus transactions (being read or write operations) on the bus.

The I²C/SMBus Master module has the following capabilities:

- sending/receiving data at a multitude of bit rates, up to 400 kbps
- 7-bit Addressing mode
- single data transfers of up to 65,535 bytes
- clock-stretching (it allows the slower I²C Slaves to communicate)

All the user data to be sent/transmitted over the I²C bus is conveyed to the USB host only through the USB HID interface.

1.14 Bus Matrix Module

The Bus Matrix module manages the communication between various functional modules, such as: USB (HID and CDC), I^2 C, UART, GPIO/ADC/DAC, Config, IOC, CLKR, Pin Mux.

1.15 Config Module

The Config module is in charge of the storage of the device settings and also of their management (loading/modifying/access protection). The module uses non-volatile memory for storing the Power-Up device settings.

At Power-Up, the module loads the settings from the non-volatile storage area into an SRAM location (volatile settings). These settings represent the device's configuration, along with other key parameters (e.g., string descriptors, VID/PID, etc.). After the settings are loaded in SRAM (volatile settings), they can be changed through the USB HID interface.

The user can read/modify/change either settings (nonvolatile or volatile) through the same interface (USB HID).

The Config module contains the relevant Power-Up settings that are used by the MCP2221. A few examples of settings are: USB descriptors, GP settings, ADC, DAC, CLKR.

2.0 USB ENUMERATION PROCESS

The MCP2221 implements the CDC class to support the USB-to-UART protocol converter functionality. Using USB-to-UART (CDC class) adapters with personal computers running the Windows operating system (OS) requires some consideration because of the way the Windows OS responds to their connection.

When a USB-to-UART (CDC class) adapter is connected to the USB port of the PC, Windows searches for a driver. After a suitable driver is found, the system creates an entry in the registry. The entry stores relevant information about the USB-to-UART adapter, its driver and the associated COM port.

The COM port and its number are legacy-type adapters, which are still supported by Windows OS. Historically, the COM ports in a computer are part of the computer's motherboard and are assigned a different index number. With the advent of USB-to-UART adapters, the Windows OS kept the COM port concept and extended it to support the USB adapters.

Whenever a USB-to-UART adapter is first connected to a PC, the system searches the registry for an entry that is suitable for the connected adapter. If one is not found, the system asks for a suitable driver. If this step is completed, it creates a registry entry, and assigns a COM port number, as well. Then, whenever the USB-to-UART adapter is connected to that PC, the system checks the registry entry, loads the specified driver and assigns the given COM port number (as found in the registry entry).

During the enumeration process, the device can specify a serial number. If it does, this number is stored in the registry entry and it is used to assign the same COM port number to the adapter in question, no matter which USB port the adapter is connected to.

USB-to-UART adapters have the option to not present a serial number during USB enumeration. In this case, the operating system would not be able to differentiate between two identical devices, if neither is providing its serial number. Each time one of these two devices (with no serial number provided during enumeration) is connected to the same USB port, they will have the same COM port number assigned.

Both functionalities (with or without serial numbers) are very useful for different applications.

When the serial number is provided, an adapter using the MCP2221 solution receives the same COM port number from a Windows machine, no matter which USB port they are connected to. The case with no serial number is useful for test/validation of products using the MCP2221. The fact that all the tested boards are not supplying a serial number will force Windows to assign them the same COM port number (but only if connected to the same USB port).

The MCP2221 is factory-set to not use a serial number. Later in the process, if a customer wants the benefits provided by using a serial number, the Configuration Utility from Microchip can be used to enable the MCP2221 to enumerate its serial number as well.

The MCP2221 comes with a uniquely-provided serial number to be used during the USB enumeration process; however, this can be changed by the user in the Configuration Utility.

The serial number enumeration enable/disable can be changed, as well, using the Configuration Utility.

All the USB-related settings mentioned above are part of the Device Configuration (Chip Settings area) and they reside only in Flash. When the Chip Settings area (1st area) is being copied into the SRAM (at Power-Up), the USB settings are skipped (not copied into SRAM).

3.0 USB HID COMMUNICATION

Except for the USB CDC and UART modules, all the other modules in the MCP2221 use USB HID protocol for communication.

The USB HID protocol uses 64-byte reports.

A typical command exchange starts with a 64-byte packet that is written by the USB Host (i.e., the PC). Afterward, the USB Host reads the response from the device as a 64-byte packet.

3.1 USB HID Commands/Responses

3.1.1 STATUS/SET PARAMETERS

This command offers many options for this device. It is used to poll for the status of the device. It is also used to establish certain I^2C bus parameters/conditions.

Byte Index	Function Description	Value	Effect
0	_	0x10	Status/Set Parameters - command code
1	Don't care	Any value	
2	Cancel current I ² C/SMBus transfer (sub-command)	0x10	When this value is put in this field, the device will cancel the current $l^2C/SMBus$ transfer and will attempt to free the l^2C bus. This command is very useful since it can cancel a transfer and free the bus. An example would be when trying to communicate with a device using a wrong address. This will cause a time-out to occur. This time-out situation can be read using the "Status/Set Parameter" and the cancellation of the $l^2C/SMBus$ transfer can be achieved by this sub-command.
		Any other value	No effect.
3	Set I ² C/SMBus communication speed (sub-command)	0x20	When this value is put in this field, the device will take the next command field and interpret it as the system clock divider that will give the I ² C/SMBus communication clock.
		Any other value	No effect.
4	The I ² C/SMBus system clock divider that will be used to establish the communication speed		The value in this field is being taken into consideration only when the Byte Index 3 contains the code for establishing a new communication speed. In all the other cases, this field's value won't matter.
5-63	Don't care	Any value	

TABLE 3-1: COMMAND STRUCTURE

3.1.1.1 Responses

TABLE 3-2: RESPONSE 1 STRUCTURE

Byte Index	Function Description	Value	Effect
0	—	0x10	Status/Set Parameters - command code echo
1		0x00	Command completed successfully
2	Cancel transfer	0x00	No special operation (i.e., Cancel current I ² C/SMBus transfer)
		0x10	The current I ² C/SMBus transfer was marked for cancellation. The actual I ² C/SMBus transfer cancellatior and bus release will need some time (a few hundred microseconds, depending on the communication speed initially chosen for the canceled transfer)
		0x11	The I ² C engine (inside MCP2221) was already in Idle mode. The cancellation command had no effect.
3		0x00	No Set I ² C/SMBus communication speed was issued.
		0x20	The new I ² C/SMBus communication speed is now considered.
		0x21	The I ² C/SMBus communication speed was not set (e.g., I ² C transfer in progress).
4		The divider value given at the same index in the command field	Only in the case when the code for establishing a new communication speed is given at Byte Index 3.
F 7	Denit com	0x00	When the communication speed is not being set.
5-7	Don't care Internal I ² C state machine state	Any value	
8	value		
9	Lower byte (16-bit value) of the requested I ² C transfer length	_	
10	Higher byte (16-bit value) of the requested I ² C transfer length	—	
11	Lower byte (16-bit value) of the already transferred (through I ² C) number of bytes	—	
12	Higher byte (16-bit value) of the already transferred (through I ² C) number of bytes	—	
13	Internal I ² C data buffer counter	—	
14	Current I ² C communication speed divider value		
15	Current I ² C timeout value		
16	Lower byte (16-bit value) of the I ² C address being used		
17	Higher byte (16-bit value) of the I ² C address being used	_	
18-21	Don't care	Any value	
22	SCL line value – as read from the pin	_	

Byte Index	Function Description	Value	Effect
23	SDA line value – as read from the pin		
24	Interrupt edge detector state	0 or 1	
25	I ² C Read pending value	0, 1 or 2	This field is used by the USB host to know if the MCP2221 still has to read from a slave device.
26-45	Don't care	Any value	
46	MCP2221 Hardware Revision Major ('A')		
47	MCP2221 Hardware Revision Minor ('6')	—	
48	MCP2221 Firmware Revision Major ('1')	—	
49	MCP2221 Firmware Revision Minor ('1')		
50-55	ADC Data (16-bit) values		3 x (16-bit) little-endian ADC channel values (CH0 LSB, CH0 MSB, CH1 LSB, CH1 MSB, CH2 LSB, CH2 MSB).
56-63	Don't care	Any value	

TABLE 3-2: RESPONSE 1 STRUCTURE (CONTINUED)

3.1.2 READ FLASH DATA

This command is used to read various important data structures and strings that are stored in Flash memory on the MCP2221.

Byte Index	Function Description	Value	Effect
0	_	0xB0	Read Flash Data – command code
1	Read Flash Data Sub-code. The value in this field will instruct	0x00	Read Chip Settings - it will read the MCP2221 flash settings
	the MCP2221 on what Flash data to be read.	0x01	Read GP Settings - it will read the MCP2221 flash GP settings
		0x02	Read USB Manufacturer Descriptor String – reads the USB Manufacturer String Descriptor used during the USB enumeration
		0x03	Read USB Product Descriptor String – reads the USB Product String Descriptor used during the USB enumeration
		0x04	Read USB Serial Number Descriptor String – reads the USB Serial Number String Descriptor that is used during USB enumeration. This serial number can be changed by the user through a specific USB HID com- mand.
		0x05	Read Chip Factory Serial Number – reads the factory-set serial number. This serial number cannot be changed.
		Any other value	No meaning. The device will reply with a code for an unsupported command at Byte Index 1 in the Response report.
2-63	Reserved	0x00	

TABLE 3-3: COMMAND STRUCTURE

3.1.2.1 Responses

TABLE 3-4: RESPONSE STRUCTURE

Byte Index	Function Description	Value	Effect
0	_	0xB0	Read Flash Data - command code
1	—	0x00	Command completed successfully
		0x01	Command not supported
2	Data structure length or Don't care	—	
3-63	Data or Don't care		Depends on the issued sub-command or the returned code at Byte Index 1

Byte Index	Function Description	Value	Effect
0	—	0xB0	Read Flash Data - command code echo
1	—	0x00	Command completed successfully
2	Structure length	—	
3	Don't care	—	
4	Bit 7: CDC Serial Number Enumeration Enable	1	The USB serial number will be used during the USB enumeration of the CDC interface.
		0	No serial number descriptor will be presented during the USB enumeration.
	Bit 6: Initial value for LEDUARTRX pin option	_	This value represents the logic level signaled when no UART Rx activity takes places. When the UART Rx (of the MCP2221) is receiving data, the LEDUARTRX pin will take the negated value of this bit.
	Bit 5: Initial value for LEDUARTTX pin option	_	This value represents the logic level signaled when no UART Tx transmission takes place. When the UART Tx (of the MCP2221) is sending data, the LEDUARTTX pin will take the negated value of this bit.
	Bit 4: Initial value for LEDI2C pin option	-	This value represents the logic level signaled when no I^2C traffic occurs. When the I^2C traffic is active, the LEDI2C pin (if enabled) will take the negated value of this bit.
	Bit 3: Initial value for SSPND pin option	_	This value represents the logic level signaled when the device is not in Suspend mode. Upon entering Suspend mode, the SSPND pin (if enabled) will take the negated value of this bit.
	Bit 2: Initial value for USBCFG pin option	_	This value represents the logic level signaled when the device is not USB configured. When the device will be USB configured, the USBCFG pin (if enabled) will take the negated value of this bit.
	Bits 1-0: Chip configuration security	11-10	Permanently locked
	option	01	Password-protected
		0.0	Unsecured
5	Bits 7-5	Don't care	
	Bits 4-0: Clock Output divider value	_	If the GP pin (exposing the clock output) is enabled for clock output operation, the divider value will be used on the 48 MHz USB internal clock and its divided output will be sent to this pin.
6	Bits 7-6: DAC Reference voltage option	11	Reference voltage is 4.096V (only if VDD is above this voltage)
		10	Reference voltage is 2.048V
		01	Reference voltage is 1.024V
		00	Reference voltage is off (this is useful for the case in which the DAC uses other reference than VRM DAC; e.g., VDD)
	Bit 5: DAC reference option	1	DAC reference is VRM DAC voltage
		0	DAC reference is VDD
	Bits 4-0: Power-Up DAC value	_	

TABLE 3-5: RESPONSE STRUCTURE – READ CHIP SETTINGS SUB-COMMAND

TABLE 3-5: RESPONSE STRUCTURE – READ CHIP SETTINGS SUB-COMMAND (CONTINUED)

Byte Index	Function Description	Value	Effect
7	Bit 7	Don't care	
	Bit 6: Interrupt detection – negative edge		If set, the interrupt detection flag will be set when a negative edge occurs.
	Bit 5: Interrupt detection – positive edge		If set, the interrupt detection flag will be set when a positive edge occurs.
	Bit 4-3: ADC Reference Voltage	11	Reference voltage is 4.096V (only if VDD is above this voltage)
		10	Reference voltage is 2.048V
		01	Reference voltage is 1.024V
		0.0	Reference voltage is off (this is useful for the case in which the ADC uses other reference than VRM ADC; e.g., VDD)
	Bit 2	1	DAC reference is VDD DAC voltage
		0	DAC reference is VRM
	Bit 1	Don't care	
	Bit 0	Don't care	
8	Lower byte of the 16-bit USB VID value	_	
9	Higher byte of the 16-bit USB VID value		
10	Lower byte of the 16-bit USB PID value		
11	Higher byte of the 16-bit USB PID value	_	
12	USB power attributes ⁽¹⁾	—	This value will be used by the MCP2221's USB Configuration Descriptor (power attributes value) during the USB enumeration.
13	USB requested number of mA(s) ⁽¹⁾	_	The requested mA value during the USB enumeration will represent the value at this index multiplied by 2.
14-63	Don't care	_	

Note 1: Please consult the USB 2.0 specification for details on the correct values for power and attributes

Byte ndex	Function Description	Value	Effect			
0	_	0xB0	Read Flash Data - command code echo			
1		0x00	Command completed successfully			
2			Structure length			
3	_	Don't care				
4	GP0 Power-Up Settings					
	Bit 7-5:	Don't care				
	Bit 4: GPIO Output value	_	When GP0 is set as an output GPIO, this value will be present at the GP0 pin at Power-Up/Reset.			
	Bit 3: GPIO Direction	1	GPIO Input mode			
	(Input/Output) – Works only when GP0 is set for GPIO operation	0	GPIO Output mode			
	Bit 2-0: GP0 Designation	111-011	Don't care			
		010	Alternate function 0 (LED UART RX)			
		001	Dedicated function operation (SSPND)			
		000	GPIO operation			
5	GP1 Power-Up Settings					
	Bits7-5:	Don't care				
	Bit 4: GPIO Output value	_	When GP1 is set as an output GPIO, this value will be present at the GP1 pin at Power-Up/Reset.			
	Bit 3: GPIO Direction	1	GPIO Input mode			
	(Input/Output) – Works only when GP0 is set for GPIO operation	0	GPIO Output mode			
	Bit 2-0: GP1 Designation	111-101	Don't care			
		001	Dedicated function operation (Clock Output)			
		100	Alternate function 2 (Interrupt Detection)			
		011	Alternate function 1 (LED UART TX)			
		010	Alternate function 0 (ADC1)			
		000	GPIO operation			
6	GP2 Power-Up Settings					
	Bits7-5:	Don't care				
	Bit 4: GPIO Output value		When GP2 is set as an output GPIO, this value will be present at the GP2 pin at Power-Up/Reset.			
	Bit 3: GPIO Direction	1	GPIO Input mode			
	(Input/Output) – Works only when GP2 is set for GPIO operation	0	GPIO Output mode			
	Bit 2-0: GP1 Designation	111-100	Don't care			
		011	Alternate function 1 (DAC1)			
		010	Alternate function 0 (ADC2)			
		001	Dedicated function operation (USB)			
		000	GPIO operation			

TABLE 3-6: RESPONSE STRUCTURE – READ GP SETTINGS SUB-COMMAND

TABLE 3-6: RESPONSE STRUCTURE – READ GP SETTINGS SUB-COMMAND (CONTINUED)

Byte Index	Function Description	Value	Effect
7	GP3 Power-Up Settings		
	Bits7-5:	Don't	
		care	
	Bit 4: GPIO Output value		When GP3 is set as an output GPIO, this value will be present at the GP3 pin at Power-Up/Reset.
	Bit 3: GPIO Direction	1	GPIO Input mode
	(Input/Output) – Works only when GP3 is set for GPIO operation	0	GPIO Output mode
	Bit 2-0: GP1 Designation	111-100	Don't care
		011	Alternate function 1 (DAC2)
		010	Alternate function 0 (ADC3)
		001	Dedicated function operation (LED I2C)
		000	GPIO operation
8-63		Don't	
		care	

TABLE 3-7:RESPONSE STRUCTURE – READ USB MANUFACTURER DESCRIPTOR STRING
SUB-COMMAND

Byte Index	Value	Effect
0	0xB0	Read Flash Data - command code echo
1	0x00	Command completed successfully
2	(2)	Number of bytes + 2 in the provided USB Manufacturer Descriptor String. The actual String starts at Byte Index 4.
3	0x03	The value at this index must always be 0x03.
4 + 2 x Unicode_char_number + 0 ⁽¹⁾	_	Lower byte of the 16-bit Unicode character.
4 + 2 x Unicode_char_number + 1 ⁽¹⁾		Higher byte of the 16-bit Unicode character.
(4 + 2 x Unicode_char_number + 2) - 63 ⁽¹⁾		Don't care. Only if the USB string descriptor is less than 60-bytes long in total.

Note 1: "Unicode_char_number" value starts from 0 to a maximum of 30 (included).

2: The value at Byte Index 2 must be 2 + 2 x (number of Unicode characters in the string).

TABLE 3-8:RESPONSE STRUCTURE – READ USB PRODUCT DESCRIPTOR STRING
SUB-COMMAND

Byte Index	Value	Effect
0	0xB0	Read Flash Data - command code echo
1	0x00	Command completed successfully
2	(2)	Number of bytes + 2 in the provided USB Product Descriptor String. The actual String starts at Byte Index 4.
3	0x03	The value at this index must always be 0x03
4 + 2 x Unicode_char_number + 0 ⁽¹⁾	_	Lower byte of the 16-bit Unicode character.
4 + 2 x Unicode_char_number + 1 ⁽¹⁾	_	Higher byte of the 16-bit Unicode character.
(4 + 2 x Unicode_char_number + 2) - 63 ⁽¹⁾		Don't care. Only if the USB string descriptor is less than 60-bytes long (in total).

Note 1: "Unicode_char_number" value starts from 0 to a maximum of 30 (included).

2: The value at Byte Index 2 must be 2 + 2 x (number of Unicode characters in the string).

TABLE 3-9: RESPONSE STRUCTURE – READ USB SERIAL NUMBER DESCRIPTOR STRING SUB-COMMAND

Byte Index	Value	Effect
0	0xB0	Read Flash Data - command code echo
1	0x00	Command completed successfully
2	(2)	The number of bytes + 2 in the provided USB Serial Number Descriptor String. The actual String starts at Byte Index 4
3	0x03	The value at this index must always be 0x03
4 + 2 x Unicode_char_number + 0 ⁽¹⁾		Lower byte of the 16-bit Unicode character
4 + 2 x Unicode_char_number + 1 ⁽¹⁾		Higher byte of the 16-bit Unicode character
(4 + 2 x Unicode_char_number + 2) - 63 ⁽¹⁾		Don't care. Only if the USB string descriptor is less than 60-bytes long in total.

Note 1: "Unicode_char_number" value starts from 0 to a maximum of 30 (included).

2: The value at Byte Index 2 must be 2 + 2 x (number of Unicode characters in the string).

TABLE 3-10:RESPONSE STRUCTURE – READ CHIP FACTORY SERIAL NUMBER
SUB-COMMAND⁽¹⁾

Byte Index	Value	Effect
0	0xB0	Read Flash Data - command code echo
1	0x00	Command completed successfully
2		Structure length
3	Don't	
	care	
4 - (4 + Structure length - 1)	—	Structure data – Factory Serial Number String
(4 + Structure length) - 63	Don't	
	care	

Note 1: The Chip Serial Number is typically 8 bytes in length.

3.1.3 WRITE FLASH DATA

This command is used to write various important data structures and strings into the Flash memory of the device.

TABLE 3-11:	COMMAND STRUCTURE
IADLE J-II.	

Byte Index	Function Description	Value	Effect
0		0xB1	Write Flash Data - command code
1	Write Flash Data Sub-code. The value in this field will instruct the	0x00	Write Chip Settings - it will write the MCP2221 flash settings
	MCP2221 about the particular Flash settings to be altered.	0x01	Write GP Settings - it will write the MCP2221 flash GP settings
		0x02	Write USB Manufacturer Descriptor String – writes the USB Manufacturer String Descriptor used during the USB enumeration
		0x03	Write USB Product Descriptor String – writes the USB Product String Descriptor used during the USB enumeration
		0x04	Write USB Serial Number Descriptor String- writes the USB Serial Number String Descriptor used during the USB enumeration
		Any other value	No meaning. The device will reply with a code for an unsupported command at Byte Index 1 in the response report.
2-63	Data to be written	_	Data format depends on the Write Flash Data Sub- code (at Byte Index 1).

Byte Index	Function Description	Value	Effect
0	_	0xB1	Write Flash Data - command code
1		0x00	Write Chip Settings - it will write the MCP2221 flash device settings
2	Bit 7: CDC Serial Number Enumeration Enable.	1	The USB serial number will be used during the USB enumeration of the CDC interface.
		0	No serial number descriptor will be presented during the USB enumeration.
	Bit 6: Initial value for LEDUARTRX pin option	_	This value represents the logic level signaled when no UART RX activity takes places. When the UART RX (of the MCP2221) is receiving data, the LEDUARTRX pin will take the negated value of this bit.
	Bit 5: Initial value for LEDUARTTX pin option	_	This value represents the logic level signaled when no UART TX transmission takes place. When the UART TX (of the MCP2221) is sending data, the LEDUARTTX pin will take the negated value of this bit.
	Bit 4: Initial value for LEDI2C pin option	—	This value represents the logic level signaled when no I^2C traffic occurs. When I^2C traffic is active, the LEDI2C pin (if enabled) will take the negated value of this bit.
	Bit 3: Initial value for SSPND pin option	—	This value represents the logic level signaled when the device is not in Suspend mode. Upon entering Suspend mode, the SSPND pin (if enabled) will take the negated value of this bit.
	Bit 2: Initial value for USBCFG pin option	—	This value represents the logic level signaled when the device is not USB configured. When the device will be USB-configured, the USBCFG pin (if enabled) will take the negated value of this bit.
	Bit 1-0: Chip Configuration Security Option	11-10	Permanently locked
		01	Password-protected
		00	Unsecured
3	Bit 7-5	Don't care	
	Bit 4-0: Clock Output divider value	—	If the GP pin (exposing the clock output) is enabled for clock output operation, the divider value will be used on the 48 MHz USB internal clock and its divided output will be sent to this pin.
4	Bit 7-6: DAC Reference voltage option	11	Reference voltage is 4.096V (only if VDD is above this voltage)
		10	Reference voltage is 2.048V
		01	Reference voltage is 1.024V
		00	Reference voltage is off (this is useful for the case in which the DAC uses other reference than VRM DAC, i.e., VDD)
	Bit 5: DAC reference option	1	DAC reference is VDD
		0	DAC reference is VRM DAC voltage
	Bit 4-0: Power-Up DAC value		

TABLE 3-12: SUB-COMMAND STRUCTURE – WRITE CHIP SETTINGS SUB-COMMAND

Byte Index	Function Description	Value	Effect
5	Bit 7	Don't care	
	Bit 6: Interrupt detection – negative edge	—	If set, the interrupt detection flag will be set when a negative edge occurs.
	Bit 5: Interrupt detection – positive edge	—	If set, the interrupt detection flag will be set when a positive edge occurs.
	Bit 4-3: ADC Reference Voltage	11	Reference voltage is 4.096V (only if VDD is above this voltage).
		10	Reference voltage is 2.048V
		01	Reference voltage is 1.024V
		00	Reference voltage is off (this is useful for the case in which the ADC uses other reference than VRM ADC; e.g., VDD)
	Bit 2: ADC Reference Option	1	ADC reference voltage is VRM ADC
		0	ADC reference voltage is VDD
	Bit 1	Don't care	
	Bit 0	Don't care	
6	Lower byte of the 16-bit USB VID value.	—	
7	Higher byte of the 16-bit USB VID value.	—	
8	Lower byte of the 16-bit USB PID value.	_	
9	Higher byte of the 16-bit USB PID value.	—	
10	USB power attributes	_	This value will be used by the MCP2221's USB Configuration Descriptor (power attributes value) during the USB enumeration.
11	USB requested number of mA(s)	_	The requested mA value during the USB enumeration will represent the value at this index multiplied by 2.
12-19	8-bytes password (for Flash modifications protection)	_	
20-63	—	Don't care	

TABLE 3-12: SUB-COMMAND STRUCTURE – WRITE CHIP SETTINGS SUB-COMMAND

Byte ndex	Function Description	Value	Effect				
0		0xB1	Write Flash Data - command code				
1	_	0x01	Write GP Settings – it will write the MCP2221 flash GP settings				
2	GP0 Power-Up Settings						
	Bit 7-5:	Don't care					
	Bit 4: GPIO Output value	—	When GP0 is set as an output GPIO, this value will be present at the GP0 pin at Power-up Reset.				
	Bit 3: GPIO Direction	1	GPIO Input mode				
	(Input/Output) – Works only when GP0 is set for GPIO operation.	0	GPIO Output mode				
	Bit 2-0: GP0 Designation	111-011	Don't care				
		010	Dedicated function operation (SSPND)				
		001	Alternate function 0 (LED UART RX)				
		000	GPIO operation				
3	GP1 Power-Up Settings						
	Bit 7-5:	Don't care					
	Bit 4: GPIO Output value		When GP1 is set as an output GPIO, this value will be present at the GP1 pin at Power-up Reset.				
	Bit 3: GPIO Direction	1	GPIO Input mode				
	(Input/Output) – Works only when GP1 is set for GPIO operation.	0	GPIO Output mode				
	Bit 2-0: GP1 Designation	111-101	Don't care				
		100	Alternate function 2 (Interrupt Detection)				
		011	Alternate function1 (LED UART TX)				
		010	Alternate function 0 (ADC1)				
		001	Dedicated function operation (Clock Output)				
		000	GPIO operation				
4	GP2 Power-Up Settings						
	Bit 7-5:	Don't care					
	Bit 4: GPIO Output value		When GP2 is set as an output GPIO, this value will be present at the GP2 pin at Power-up Reset.				
	Bit 3: GPIO Direction (Input/Output) – Works only when GP2 is set for GPIO operation.	1	GPIO Input mode				
		0	GPIO Output mode				
	Bit 2-0: GP2 Designation	111-100	Don't care				
		011	Alternate function1 (DAC1)				
		010	Alternate function 0 (ADC2)				
		001	Dedicated function operation (Clock Output)				
		000	GPIO operation				

TABLE 3-13: SUB-COMMAND STRUCTURE – WRITE GP SETTINGS SUB-COMMAND (CONTINUED)

Byte Index	Function Description	Value	Effect
5	GP3 Power-Up Settings		
	Bit 7-5:	Don't care	
	Bit 4: GPIO Output value		When GP3 is set as an output GPIO, this value will be present at the GP2 pin at Power-up Reset.
	Bit 3: GPIO Direction (Input/Output) – Works only when GP3 is set for GPIO operation.	1	GPIO Input mode
		0	GPIO Output mode
	Bit 2-0: GP3 Designation	111-100	Don't care
		011	Alternate function 1 (DAC2)
		010	Alternate function 0 (ADC3)
		001	Dedicated function operation (LED I2C)
		000	GPIO operation
6-63		Don't care	

TABLE 3-14: SUB-COMMAND STRUCTURE – WRITE USB MANUFACTURER DESCRIPTOR STRING SUB-COMMAND

Byte Index	Value	Effect
0	0xB1	Write Flash Data - command code
1	0x02	Write USB Manufacturer Descriptor String – writes the USB Manufacturer String Descriptor used during the USB enumeration
2	(2)	Number of bytes + 2 in the provided USB Serial Number Descriptor String
3	0x03	The value at this index must always be 0x03.
4 + 2 x Unicode_char_number + 0 ⁽¹⁾	_	Lower byte of the 16-bit Unicode character.
4 + 2 x Unicode_char_number + 1 ⁽¹⁾	_	Higher byte of the 16-bit Unicode character.

Note 1: "Unicode_char_number" value starts from 0 to a maximum of 30 (included).

2: The value at Byte Index 2 must be 2 + 2 x (number of Unicode characters in the string).

TABLE 3-15:SUB-COMMAND STRUCTURE – WRITE USB PRODUCT DESCRIPTOR
STRING SUB-COMMAND

Byte Index	Value	Effect
0	0xB1	Write Flash Data - command code
1	0x03	Write USB Product Descriptor String – writes the USB Product String Descriptor used during the USB enumeration
2	(2)	Number of bytes + 2 in the provided USB Serial Number Descriptor String. The actual String starts at Byte Index 4.
3	0x03	The value at this index must always be 0x03.
4 + 2 x Unicode_char_number + 0 ⁽¹⁾	_	Lower byte of the 16-bit Unicode character
4 + 2 x Unicode_char_number + 1 ⁽¹⁾	_	Higher byte of the 16-bit Unicode character

Note 1: "Unicode_char_number" value starts from 0 to a maximum of 30 (included).

2: The value at Byte Index 2 must be 2 + 2 x (number of Unicode characters in the string).

TABLE 3-16: SUB-COMMAND STRUCTURE – WRITE USB SERIAL NUMBER DESCRIPTOR STRING SUB-COMMAND

Byte Index	Value	Effect
0	0xB1	Write Flash Data - command code
1	0x04	Write USB Serial Number Descriptor String – writes the USB Serial Number String Descriptor used during the USB enumeration
2	(2)	Number of bytes + 2 in the provided USB Serial Number Descriptor String. The actual String starts at Byte Index 4
3	0x03	The value at this index must always be 0x03.
4 + 2 x Unicode_char_number + 0 ⁽¹⁾	_	Lower byte of the 16-bit Unicode character
4 + 2 x Unicode_char_number + 1 ⁽¹⁾	—	Higher byte of the 16-bit Unicode character

Note 1: "Unicode_char_number" value starts from 0 to a maximum of 30 (included).

2: The value at Byte Index 2 must be 2 + 2 x (number of Unicode characters in the string).

3.1.3.1 Responses

TABLE 3-17:RESPONSE STRUCTURE – READ CHIP FACTORY SERIAL NUMBER
SUB-COMMAND

Byte Index	Value	Effect	
0	0xB1 Write Flash Data - command code		
1	0x00	Command completed successfully	
	0x02	Command not supported	
	0x03	Command not allowed	
2-63	Don't care		

3.1.4 SEND FLASH ACCESS PASSWORD

This command is used to send a user-supplied password that will be compared to the one stored in the device's Flash when Flash updates (Chip/GP configuration, USB strings) are required and the Flash data is password-protected.

In the case where no protection mechanism is in place or the Flash data has been permanently locked, this command has no meaning.

TABLE 3-18:COMMAND STRUCTURE

Byte Index	Value	Effect
0	0xB2	Send Flash Access Password - command code
1	Don't	
	care	
2	_	Password byte 1
3		Password byte 2
4	_	Password byte 3
5		Password byte 4
6		Password byte 5
7	_	Password byte 6
8	_	Password byte 7
9	_	Password byte 8
10-63	_	Don't care

3.1.4.1 Responses

TABLE 3-19: RESPONSE 1 STRUCTURE

Byte Index	Value	Effect
0	0xB2	Send Flash Access Password - command code echo
1	0x00	Command completed successfully
	0x03	Command not allowed (when the number of failed Flash updates has been reached, no password will be accepted)
2-63	Don't	
	care	

3.1.5 I²C WRITE DATA

This command is used to write user-given data to the I^2C Slave device (the speed is specified by the STATUS/SET Parameters command).

The command will have the following effects:

- The I²C engine will send the START condition.
- The selected I²C slave address is sent next and the I²C engine will wait for the slave to send an acknowledge bit.
- The user data follows next and the I²C engine awaits for the acknowledge bit from the slave.
- If the requested length is more than 60 bytes, subsequent user bytes will be sent on the bus.
- When the user data length (being sent on the bus) reaches the requested length, the I²C engine will send the STOP condition on the bus.

Value	Effect
0x90	I ² C Write Data - command code
Low Byte	Requested I ² C transfer length – 16-bit value – low byte
High Byte	Requested I ² C transfer length – 16-bit value – high byte
	8-bit value representing the I ² C slave address to communicate with (even – address to write, odd – address to read) (Note 2)
—	User data to be sent to the selected I ² C slave device
	0x90 Low Byte High Byte I ² C Slave

TABLE 3-20: COMMAND STRUCTURE⁽¹⁾

Note 1: When the requested transfer length is more than 60 bytes, subsequent I²C Write Data commands will transport the reminder of the user data (till the requested length).

2: The I²C slave address is represented on 8 bits, with even values for writes and odd for reads. To get the 8-bit address value out of a 7-bit address, the 7-bit value needs to be shifted left by 1 position. For write operations use the shifted value, while for reads add 1 to the shifted value.

3.1.5.1 Responses

TABLE 3-21: RESPONSE 1 STRUCTURE

Byte Index	Value	Effect
0	0x90	I ² C Write Data - command code echo
1	0x00	Command completed successfully
	0x01	I ² C Engine is busy (command not completed)
2	—	Internal I^2C Engine state (at the moment the command was issued) – useful for monitoring the status of the I^2C Engine
3-63	Don't	
	care	

3.1.6 I²C WRITE DATA REPEATED-START

This command is used to write user-given data to the I^2C Slave device (the speed is specified by the <code>STATUS/SET Parameters command</code>).

The command will have the following effects:

- The I²C engine will send the Repeated-START condition.
- The selected I²C slave address is sent next and the I²C engine will wait for the slave to send an acknowledge bit.

TABLE 3-22: COMMAND STRUCTURE ⁽¹⁾

- The user data follows next and the I²C engine waits for the acknowledge bit from the slave.
- If the requested length is more than 60 bytes, subsequent user bytes will be sent on the bus.
- When the user data length (being sent on the bus) reaches the requested length, the I²C engine will send the STOP condition on the bus.

Byte Index	Value	Effect
0	0x92	I ² C Write Data Repeated-START - command code (cl2C_CMD_RSTART_WRDATA7)
1	Low Byte	Requested I ² C transfer length – 16-bit value – low byte
2	High Byte	Requested I ² C transfer length – 16-bit value – high byte
3	I ² C Slave Address	8-bit value representing the I ² C slave address to communicate with (even – address to write, odd – address to read) (Note 2)
4-63		User data to be sent to the selected I ² C slave device
Note 1: When the requested transfer length is more than 60 bytes, subsequent I ² C Write Data Repeated-START		

commands will transport the reminder of the user data (till the requested length).
 2: The I²C slave address is represented on 8 bits, with even values for writes and odd for reads. To get the

2: The PC slave address is represented on 8 bits, with even values for writes and odd for reads. To get the 8-bit address value out of a 7-bit address, the 7-bit value needs to be shifted left by 1 position. For write operations use the shifted value, while for reads add 1 to the shifted value.

3.1.6.1 Responses

TABLE 3-23: RESPONSE 1 STRUCTURE

Byte Index	Value	Effect
0	0x92	I ² C Write Data Repeated-START - command code echo (cl2C_CMD_RSTART_WRDATA7)
1	0x00	Command completed successfully
	0x01	I ² C Engine is busy (command not completed)
2	—	Internal I^2C Engine state (at the moment the command was issued) – useful for monitoring the status of the I^2C Engine
3-63	Don't	
	care	

3.1.7 I²C WRITE DATA NO STOP

This command is used to write user-given data to the I^2C Slave device (the speed is specified by the STATUS/SET Parameters command).

The command will have the following effects:

- The I²C engine will send the START condition.
- The selected I²C slave address is sent next and the I²C engine will wait for the slave to send an acknowledge bit.

TABLE 3-24: COMMAND STRUCTURE ⁽¹⁾

- The user data follows next and the I²C engine waits for the acknowledge bit from the slave.
- If the requested length is more than 60 bytes, subsequent user bytes will be sent on the bus.
- When the user data length (being sent on the bus) reaches the requested length, the I²C engine will <u>not</u> send the STOP condition on the bus.

Byte Index	Value	Effect
0	0x94	I ² C Write Data No STOP - command code
1	Low Byte	Requested I ² C transfer length – 16-bit value – low byte
2	High Byte	Requested I ² C transfer length – 16-bit value – high byte
3		8-bit value representing the I^2C slave address to communicate with (even – address to write, odd – address to read) (Note 2)
4-63	—	User data to be sent to the selected I ² C slave device

Note 1: When the requested transfer length is more than 60 bytes, subsequent I²C Write Data No STOP commands will transport the reminder of the user data (till the requested length).

2: The I²C slave address is represented on 8 bits, with even values for writes and odd for reads. To get the 8-bit address value out of a 7-bit address, the 7-bit value needs to be shifted left by 1 position. For write operations use the shifted value, while for reads add 1 to the shifted value.

3.1.7.1 Responses

TABLE 3-25: RESPONSE 1 STRUCTURE

Byte Index	Value	Effect
0	0x94	I ² C Write Data No STOP - command code echo
1	0x00	Command completed successfully
	0x01	I ² C Engine is busy (command not completed)
2	_	Internal I^2C Engine state (at the moment the command was issued) – useful for monitoring the status of the I^2C Engine
3-63	Don't	
	care	

3.1.8 I²C READ DATA

This command is used to read user-given data to the I^2C Slave device (the speed is specified by the <code>STATUS/SET Parameters command</code>).

The command will have the following effects:

- The I²C engine will send the START condition.
- The selected I²C slave address is sent next and the I²C engine will wait for the slave to send an acknowledge bit.

TABLE 3-26: COMMAND STRUCTURE

- The user data is read next and the I²C engine sends the acknowledge bit to the slave.
- If the requested length is more than 60 bytes, subsequent user bytes will be read from the l²C slave on the bus.
- When the user data length (being sent on the bus) reaches the requested length, the I²C engine will send the STOP condition on the bus.

Byte Index	Value	Effect
0	0x91	I ² C Read Data – command code
1	Low Byte	Requested I ² C transfer length – 16-bit value – low byte
2	High Byte	Requested I ² C transfer length – 16-bit value – high byte
3		8-bit value representing the I ² C slave address to communicate with (even – address to write, odd – address to read) (Note 1)
4-63	Don't	
	care	
Note 1. The l^2C slave address is represented on 8 bits with even values for writes and odd for reads. To get the		

Note 1: The I²C slave address is represented on 8 bits, with even values for writes and odd for reads. To get the 8-bit address value out of a 7-bit address, the 7-bit value needs to be shifted left by 1 position. For write operations use the shifted value, while for reads add 1 to the shifted value.

3.1.8.1 Responses

TABLE 3-27: RESPONSE 1 STRUCTURE

Byte Index	Value	Effect
0	0x91	I ² C Read Data – command code echo
1	0x00	Command completed successfully
	0x01	I ² C Engine is busy (command not completed)
2	—	Internal I ² C Engine state (at the moment the command was issued) – useful for monitoring the I ² C Engine's status
3-63	Don't	
	care	

3.1.9 I²C READ DATA REPEATED-START

This command is used to read user-given data to the I^2C Slave device (the speed is specified by the <code>STATUS/SET Parameters command</code>).

The command will have the following effect:

- The I²C engine will send the Repeated-START condition.
- The selected I²C slave address is sent next and the I²C engine will wait for the slave to send an acknowledge bit.

TABLE 3-28: COMMAND STRUCTURE

- The user data is read next and the I²C engine sends the acknowledge bit to the slave.
- If the requested length is more than 60 bytes, subsequent user bytes will be read from the I²C slave on the bus.
- When the user data length (being sent on the bus) reaches the requested length, the I²C engine will send the STOP condition on the bus.

Byte Index	Value	Effect
0	0x93	I ² C Read Data Repeated-START - command code
1	Low Byte	Requested I ² C transfer length – 16-bit value – low byte
2	High Byte	Requested I ² C transfer length – 16-bit value – high byte
3	I ² C Slave Address	8-bit value representing the I ² C slave address to communicate with (even – address to write, odd – address to read) (Note 1)
4-63	Don't	
	care	

Note 1: The I²C slave address is represented on 8 bits, with even values for writes and odd for reads. To get the 8-bit address value out of a 7-bit address, the 7-bit value needs to be shifted left by 1 position. For write operations use the shifted value, while for reads add 1 to the shifted value.

3.1.9.1 Responses

TABLE 3-29:RESPONSE 1 STRUCTURE

Byte Index	Value	Effect
0	0x93	I ² C Read Data Repeated-START - command code echo
1	0x00	Command completed successfully
	0x01	I ² C Engine is busy (command not completed)
2		Internal I^2C Engine state (at the moment the command was issued) – useful for monitoring the status of the I^2C Engine
3-63	Don't	
	care	

3.1.10 I²C READ DATA – GET I²C DATA

This command is used to read back the data from the $\ensuremath{\mathsf{I}}^2\ensuremath{\mathsf{C}}$ Slave device.

TABLE 3-30: COMMAND STRUCTURE

Byte Index	Value	Effect
0	0x40	I ² C Read Data - Get I ² C Data - command code
1-63	Don't care	

3.1.10.1 Responses

TABLE 3-31: RESPONSE 1 STRUCTURE

Byte Index	Value	Effect	
0	0x40	I ² C Read Data - Get I ² C Data - command code echo	
1	0x00	Command completed successfully	
	0x41	Error reading the I ² C slave data from the I ² C engine	
2	—	Internal I ² C Engine state (at the moment the command was issued) – useful for monitoring the I ² C Engine's status	
3	0-60	The number of read-back data bytes to follow in this packet: from 0 to a maximum of 60 bytes of ead-back bytes	
	127	This value is signaled when an error has occurred and the following data should not be taken into account	
4-63	_	User Data or Don't care	

3.1.11 SET GPIO OUTPUT VALUES

This command is used to change the GPIO output value for those GP pins assigned for GPIO operation (GPIO outputs).

Byte Index	Function Description	Value	Effect
0		0x50	Set GPIO Output Values - command code
1		Don't care	
2	Alter GP0 output	0x00	Do not modify GP0 output (if GP0 is set as GPIO output)
	(enable/disable)	Any other value	The next byte (index 3) will be the value used to set GP0 output (only if GP0 is set for GPIO output)
3	GP0 output value	0x00	GP0 (if set up for GPIO output operation) will take a logical value of '0'
		Any other value	GP0 (if set up for GPIO output operation) will take a logical value of '1'
4	Alter GP0 pin direction	0x00	Leave the GP0 GPIO designation as is (input or output)
	(enable/disable)	Any other value	The next byte (index 5) will be the value used to set GP0's pin direction (only if GP0 is set for GPIO operation)
5	GP0 pin direction	0x00	Set GP0 GPIO as output
	(input or output)	Any other value	GP0 (if set up for GPIO operation) will be set as a digital input
6	Alter GP1 output	0x00	Do not modify GP1 output (if GP1 is set as GPIO output)
	(enable/disable)	Any other value	The next byte (index 7) will be the value used to set GP1 output (only if GP1 is set for GPIO output)
7	GP1 output value	0x00	GP1 (if set up for GPIO output operation) will take a logical value of '0'
		Any other value	GP1 (if set up for GPIO output operation) will take a logical value of '1'
8	Alter GP1 pin direction	0x00	Leave the GP1 GPIO designation as is (input or output)
	(enable/disable)	Any other value	The next byte (index 9) will be the value used to set GP1's pin direction (only if GP1 is set for GPIO operation)
9	GP1 pin direction	0x00	Set GP1 GPIO as output
	(input or output)	Any other value	GP1 (if set up for GPIO operation) will be set as a digital input
10	Alter GP2 output	0x00	Do not modify GP2 output (if GP2 is set as GPIO output)
	(enable/disable)	Any other value	The next byte (index 11) will be the value used to set GP2 output (only if GP2 is set for GPIO output)
11	GP2 output value	0x00	The GP2 (if GP2 is set up for GPIO output operation) will take a logical value of '0'
		Any other value	GP2 (if GP2 is set up for GPIO output operation) will take a logical value of '1'
12	Alter GP2 pin direction	0x00	Leave the GP2 GPIO designation as is (input or output)
	(enable/disable)	Any other value	The next byte (index 13) will be the value used to set GP2's pin direction (only if GP2 is set for GPIO operation)
13	GP2 pin direction	0x00	Set GP2 GPIO as output
	(input or output)	Any other value	GP2 (if set up for GPIO operation) will be set as a digital input
14	Alter GP3 output	0x00	Do not modify GP3 output (if GP3 is set as GPIO output)
	(enable/disable)	Any other value	The next byte (index 11) will be the value used to set GP3 output (only if GP3 is set for GPIO output)

TABLE 3-32: COMMAND STRUCTURE

© 2014-2017 Microchip Technology Inc.

TABLE 3-32:	COMMAND STRUCTURE (CONTINUED)
--------------------	-------------------------------

Byte Index	Function Description	Value	Effect
15	GP3 output value	0x00	GP3 (if set up for GPIO output operation) will take a logical value of '0'.
		Any other value	GP3 (if set up for GPIO output operation) will take a logical value of '1'
16	Alter GP3 pin direction	0x00	Leave the GP3 GPIO designation as is (input or output)
	(enable/disable)	Any other value	The next byte (index 17) will be the value used to set GP3's pin direction (only if GP3 is set for GPIO operation)
17	GP3 pin direction	0x00	Set GP3 GPIO as output
	(input or output)	Any other value	GP3 (if set up for GPIO operation) will be set as a digital input
18-63	Reserved	0x00	

3.1.11.1 Responses

TABLE 3-33: RESPONSE 1 STRUCTURE

Byte Index	Function Description	Value	Effect
0	_	0x50	Set GPIO Output Values - command code
1	_	0x00	Command completed successfully
2	Alter GP0 output	0xEE	If GP0 is not set for GPIO operation
	(enable/disable) status	Any other value	If GP0 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
3	GP0 output value status	0xEE	If GP0 is not set for GPIO operation
		Any other value	If GP0 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
4	Alter GP0 pin direction	0xEE	If GP0 is not set for GPIO operation
	(enable/disable)	Any other value	If GP0 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
5	GP1 pin direction	0xEE	If GP1 is not set for GPIO operation
	(input or output)	Any other value	If GP1 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
6	Alter GP1 output	0xEE	If GP1 is not set for GPIO operation
	(enable/disable) status	Any other value	If GP1 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
7	GP1 output value status	0xEE	If GP1 is not set for GPIO operation
		Any other value	If GP1 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
8	Alter GP1 pin direction	0xEE	If GP1 is not set for GPIO operation
	(enable/disable)	Any other value	If the GP1 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
9	GP1 pin direction	0xEE	If GP1 is not set for GPIO operation
	(input or output)	Any other value	If GP1 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
10	Alter GP2 output	0xEE	If GP2 is not set for GPIO operation
	(enable/disable) status	Any other value	If GP2 is already set for GPIO operation, the value will be copied from the same byte index in the command structure

TABLE 3-33 :	RESPONSE 1 STRUCTURE ((CONTINUED)

Byte Index	Function Description	Value	Effect
11	GP2 output value status	0xEE	If GP2 is not set for GPIO operation
		Any other value	If GP2 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
12	Alter GP2 pin direction	0xEE	If GP2 is not set for GPIO operation
	(enable/disable)	Any other value	If GP2 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
13	GP2 pin direction	0xEE	If GP2 is not set for GPIO operation
	(input or output)	Any other value	If GP2 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
14	Alter GP3 output	0xEE	If GP3 is not set for GPIO operation
	(enable/disable) status	Any other value	If GP3 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
15	GP3 output value status	0xEE	If GP3 is not set for GPIO operation
		Any other value	If GP3 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
16	Alter GP3 pin direction	0xEE	If GP3 is not set for GPIO operation
	(enable/disable)	Any other value	If GP3 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
17	GP3 pin direction	0xEE	If GP3 is not set for GPIO operation
	(input or output)	Any other value	If GP3 is already set for GPIO operation, the value will be copied from the same byte index in the command structure
18-63		Don't care	

3.1.12 GET GPIO VALUES

This command is used to retrieve the GPIO direction and pin value for those GP pins assigned for GPIO operation (GPIO inputs or outputs).

TABLE 3-34: COMMAND STRUCTURE

Byte Index	Value	Effect			
0	0x51	Get GPIO Values - command code			
1-63	Don't				
	care				

3.1.12.1 Responses

TABLE 3-35: RESPONSE 1 STRUCTURE

Byte Index	Function Description	Value	Effect
0	_	0x51	Get GPIO Values - command code
1	_	0x00	Command completed successfully
2	GP0 pin value	0xEE	If GP0 is not set for GPIO operation
		Other values (0x00 or 0x01)	If GP0 is already set for GPIO operation, the value represents the GP0 logic pin value
3	GP0 direction	0xEF	If GP0 is not set for GPIO operation
	value	Other values (0x00 or 0x01)	If GP0 is already set for GPIO operation, the value represents the GP0 pin designation (0x00 for output and 0x01 for input)
4	GP1 pin value	0xEE	If GP1 is not set for GPIO operation
		Other values (0x00 or 0x01)	If GP1 is already set for GPIO operation, the value represents the GP1 logic pin value
5	GP1 direction	0xEF	If GP1 is not set for GPIO operation
	value	Other values (0x00 or 0x01)	If GP1 is already set for GPIO operation, the value represents the GP1 pin designation (0x00 for output and 0x01 for input)
6	GP2 pin value	0xEE	If GP2 is not set for GPIO operation
		Other values (0x00 or 0x01)	If GP2 is already set for GPIO operation, the value represents the GP2 logic pin value
7	GP2 direction	0xEF	If GP2 is not set for GPIO operation
	value	Other values (0x00 or 0x01)	If GP2 is already set for GPIO operation, the value represents the GP2 pin designation (0x00 for output and 0x01 for input)
8	GP3 pin value	0xEE	If GP3 is not set for GPIO operation
		Other values (0x00 or 0x01)	If GP3 is already set for GPIO operation, the value represents the GP3 logic pin value
9	GP3 direction	0xEF	If GP3 is not set for GPIO operation
	value	Other values (0x00 or 0x01)	If GP3 is already set for GPIO operation, the value represents the GP3 pin designation (0x00 for output and 0x01 for input)
10-63		Don't care	

3.1.13 SET SRAM SETTINGS

This command is used to alter various run time chip-settings. The altered settings reside in SRAM memory and they won't affect the chip's Power-up Reset default settings. These altered settings will be active till the next chip Power-up Reset.

Byte Index	Function Description	Value	Effect			
0	_	0x60	Set SRAM settings - command code			
1	_	Don't care				
2	Clock Output Divider value - this allows the user to modify the clock output value on the fly, at run-time					
	Bit 7: Enable loading of a	1	The 4-0 bits will be loaded into the clock divider			
	new clock divider	0	Clock divider value won't be altered			
	Bit 6-5	Don't care				
	Bit 4-3: Duty cycle	00	0% duty cycle			
		01	25% duty cycle			
		10	50% duty cycle			
		11	75% duty cycle			
	Bit 2-0: Clock divider value	_				
3	DAC Voltage Reference -	- this allows	the user to modify the DAC reference voltage			
	Bit 7: Enable loading of a new DAC reference	1	Bits 2-0 will be used for DAC reference voltage selection			
		0	DAC reference will remain unaltered			
	Bit 6-3	Don't care				
	Bit 2-1: DAC VRM voltage	11	VRM voltage is 4.096V (only if VDD is higher than this value)			
	selection. These bits are used to change the DAC VRM voltage	10	VRM voltage is 2.048V			
		01	VRM voltage is 1.024V			
		00	VRM voltage is off			
	Bit 0: This bit is used to change the DAC	1	DAC voltage reference is the internal DAC voltage reference module (DAC VRM)			
	reference voltage	0	DAC voltage reference is VDD			
4	Set DAC output value					
	Bit 7: Enable loading of a new DAC value	1	Bits 4-0 will be used for DAC reference voltage selection			
		0	The current DAC value will remain unaltered			
	Bit 6-5	Don't care				
	Bit 4-0: The new DAC value					

Byte ndex	Function Description	Value	Effect		
5	ADC Voltage Reference -	- this allows	the user to modify the ADC reference voltage		
	Bit 7: Enable loading of a	1	Bits 2-0 will be used for ADC reference voltage selection		
	new ADC reference	0	ADC reference will remain unaltered		
	Bit 6-3	Don't care			
	Bit 2-1: These bits are	11	VRM voltage is 4.096V (only if VDD is higher than this value)		
	used to change the DAC	10	VRM voltage is 2.048V		
		01	VRM voltage is 1.024V		
		00	VRM voltage is off		
	Bit 0: This bit is used to change the DAC	1	VDD ADC voltage reference is the internal ADC voltage reference module (ADC VRM)		
	reference voltage	0	ADC voltage reference is V _{DD}		
6	Setup the interrupt detection module to detect		anism and clear the detection flag – useful for preparing the interrupt rrupt condition		
	Bit 7: Enable the	1	The interrupt detection settings and flag will change		
	modification of the interrupt detection conditions	0	The interrupt detection settings and flag will remain unchanged		
	Bit 6-5	Don't care			
	Bit 4		Enable the modification of the positive edge detection		
	Bit 3: The new value for	1	Interrupt detection will trigger on positive edges		
	the positive edge detector	0	Interrupt detection will not trigger on positive edges		
	Bit 2		Enable the modification of the negative edge detection		
	Bit 1: The new value for	1	Interrupt detection will trigger on negative edges		
	the negative edge detector	0	Interrupt detection will not trigger on negative edges		
	Bit 0: Clear the interrupt	1	Clear the interrupt detection flag		
	detection flag	0	Leave the interrupt detection flag as is		
7	Alter GPIO configuration: alters the current GP	1	Alter the GP designation. The values from Byte Index 8 will be used to load a new set of values into the SRAM GP settings.		
	designation	0	Do not alter the current GP designation		
8	GP0 settings				
	Bit 7-5	Don't care			
	Bit 4: GPIO Output value	—	When GP0 is set as an output GPIO, this value will be present at the GP0 pin		
	Bit 3: GPIO Direction	1	GPIO Input mode		
	(Input/Output) – Works only when GP0 is set for GPIO operation	0	GPIO Output mode		
	Bit 2-0: GP0 Designation	111-011	Don't care		
		010	Alternate function 0 (LED UART RX)		
			Dedicated function operation (SSPND)		
		001	Dedicated function operation (SSPND)		

TABLE 3-36: COMMAND STRUCTURE (CONTINUED)

Byte ndex	Function Description	Value	Effect					
9	GP1 settings		·					
	Bit 7-5	Don't care						
	Bit 4: GPIO Output value	_	When GP1 is set as an output GPIO, this value will be present at the GP1 pin					
	Bit 3: GPIO Direction	1	GPIO Input mode					
	(Input/Output) – Works only when GP1 is set for GPIO operation	0	GPIO Output mode					
	Bit 2-0: GP0 Designation	111-101	Don't care					
		100	Alternate function 2 (Interrupt Detection)					
		011	Alternate function 1 (LED UART TX)					
		010	Alternate function 0 (ADC1)					
		001	Dedicated function operation (Clock Output)					
		000	GPIO operation					
10	GP2 settings							
	Bit 7-5	Don't care						
	Bit 4: GPIO Output value		When GP2 is set as an output GPIO, this value will be present at the GP2 pin					
	Bit 3: GPIO Direction	1	GPIO Input mode					
	(Input/Output) – Works only when GP2 is set for GPIO operation	0	GPIO Output mode					
	Bit 2-0: GP2 Designation	111-100	Don't care					
		011	Alternate function 1 (DAC1)					
		010	Alternate function 0 (ADC2)					
		001	Dedicated function operation (USBCFG)					
		000	GPIO operation					
11	GP3 settings							
	Bit 7-5	Don't care						
	Bit 4: GPIO Output value	_	When GP3 is set as an output GPIO, this value will be present at the GP3 pin					
	Bit 3: GPIO Direction	1	GPIO Input mode					
	(Input/Output) – Works only when GP3 is set for GPIO operation	0	GPIO Output mode					
	Bit 2-0: GP3 Designation	111-100	Don't care					
		011	Alternate function 1 (DAC2)					
		010	Alternate function 0 (ADC3)					
		001	Dedicated function operation (LED I2C)					
		000	GPIO operation					
2-63	Reserved	0x00						

TA

MCP2221

3.1.13.1 Responses

TABLE 3-37: RESPONSE 1 STRUCTURE

Byte Index	Value	Effect	
0	0x60	Set SRAM Settings - command code echo	
1	0x00	Command completed successfully	
2-63	Don't		
	care		

3.1.14 GET SRAM SETTINGS

This command is used to retrieve the run time Chip and GP settings.

TABLE 3-38: COMMAND STRUCTURE

Byte Index	Value	Effect	
0	0x61	Get SRAM Settings - command code echo	
1-63	0x00	Command completed successfully	

3.1.14.1 Responses

TABLE 3-39: RESPONSE 1 STRUCTURE

Byte Index	Function Description	Value	Effect
0		0x61	Get SRAM Settings - command code echo
1		0x00	Command completed successfully
2	Length in bytes of the SRAM Chip-settings area.	_	
3	Length in bytes of the SRAM GP settings area.	_	
4	Bit 7: CDC Serial Number Enumeration Enable	1	The USB serial number will be used during the USB enumeration of the CDC interface
		0	No serial number descriptor will be presented during the USB enumeration
	Bit 6: Initial value for LEDUARTRX pin option	—	This value represents the logic level signaled when no UART RX activity takes places. When the UART RX (of the MCP2221) is receiving data, the LEDUARTRX pin will take the negated value of this bit.
	Bit 5: Initial value for LEDUARTTX pin option.	—	This value represents the logic level signaled when no UART TX transmission takes place. When the UART TX (of the MCP2221) is sending data, the LEDUARTTX pin will take the negated value of this bit.
	Bit 4: Initial value for LEDI2C pin option		This value represents the logic level signaled when no I^2C traffic occurs. When I^2C traffic is active, the LEDI2C pin (if enabled) will take the negated value of this bit.
	Bit 3: Initial value for SSPND pin option	_	This value represents the logic level signaled when the device is not in Suspend mode. Upon entering Suspend mode, the SSPND pin (if enabled) will take the negated value of this bit.
	Bit 2: Initial value for USBCFG pin option		This value represents the logic level signaled when the device is not USB configured. When the device will be USB-configured, the USBCFG pin (if enabled) will take the negated value of this bit.
	Bit 1-0: Chip configuration security	10	Permanently locked
	option	01	Password-protected
		00	Unsecured

TABLE 3-39: RESPONSE 1 STRUCTURE (CONTINUED)

Byte Index	Function Description	Value	Effect
5	Bit 7-5	Don't care	
	Bit 4-0: Clock Output divider value		If the GP pin (exposing the clock output) is enabled for clock output operation, the divider value will be used on the 48 MHz USB internal clock and its divided output will be sent to this pin. (Bits 4-3 for duty cycle and bits 2-0 for the clock divider.)
6	Bit 7-6: DAC Reference voltage option	11	Reference voltage is 4.096V
		10	Reference voltage is 2.048V
		01	Reference voltage is 1.024V
		00	Reference voltage is off (this is useful for the case in which the DAC uses other reference than VRM DAC; e.g., VDD)
	Bit 5: DAC reference option	1	DAC reference is VRM DAC voltage
	[[0	DAC reference is VDD
	Bit 4-0: Power-Up DAC value	_	
7	Bit 7	Don't care	
	Bit 6: Interrupt detection – negative edge		If set, the interrupt detection flag will be set when a negative edge occurs
	Bit 5: Interrupt detection – positive edge		If set, the interrupt detection flag will be set when a positive edge occurs
	Bit 4-3: ADC Reference Voltage	11	Reference voltage is 4.096V (only if VDD is above this voltage)
		10	Reference voltage is 2.048V
		01	Reference voltage is 1.024V
		00	Reference voltage is off (this is useful for the case in which the ADC uses other reference than VRM DAC; e.g., VDD)
	Bit 2: ADC Reference Option	1	ADC reference is VRM ADC
		0	ADC reference is VDD
	Bit 1	Don't care	
	Bit 2	Don't care	
8	Lower byte of the 16-bit USB VID value	_	
9	Higher byte of the 16-bit USB VID value	—	
10	Lower byte of the 16-bit USB PID value		
11	Higher byte of the 16-bit USB PID value	_	
12	USB power attributes	_	This value will be used by the MCP2221's USB Configuration Descriptor (power attributes value) during the USB enumeration
13	USB requested number of mA(s)		The requested mA value during the USB enumeration will represent the value at this index multiplied by 2
14	Current supplied-password byte 1	_	
15	Current supplied-password byte 2	_	
16	Current supplied-password byte 3	_	

Byte Index	Function Description	Value	Effect
17	Current supplied-password byte 4	_	
18	Current supplied-password byte 5	_	
19	Current supplied-password byte 6	_	
20	Current supplied-password byte 7	_	
21	Current supplied-password byte 8	_	
22	GP0 settings		
	Bit 7-5	Don't care	
	Bit 4: GPIO Output value	-	When the GP0 is set as an output GPIO, this value will be present at the GP0 pin
	Bit 3: GPIO Direction (Input/Output) -	1	GPIO Input mode
	Works only when GP0 is set for GPIO operation	0	GPIO Output mode
	Bit 2-0: GP0 Designation	111-011	Don't care
		010	Alternate function 0 (LED UART RX)
		001	Dedicated function operation (SSPND)
		000	GPIO operation
23	GP1 settings		
	Bit 7-5	Don't care	
	Bit 4: GPIO Output value	_	When the GP1 is set as an output GPIO, this value will be present at the GP1 pin
	Bit 3: GPIO Direction (Input/Output) -	1	GPIO Input mode
	Works only when GP1 is set for GPIO operation	0	GPIO Output mode
	Bit 2-0: GP1 Designation	111-101	Don't care
		100	Alternate function 2 (Interrupt Detection)
		011	Alternate function 1 (LED UART TX)
		010	Alternate function 0 (ADC1)
		001	Dedicated function operation (Clock Output)
		000	GPIO operation
24	GP2 settings		1
	Bit 7-5	Don't care	
	Bit 4: GPIO Output value	_	When the GP2 is set as an output GPIO, this value will be present at the GP2 pin
	Bit 3: GPIO Direction (Input/Output) -	1	GPIO Input mode
	Works only when GP2 is set for GPIO operation	0	GPIO Output mode
	Bit 2-0: GP2 Designation	111-100	Don't care
		011	Alternate function 1 (DAC1)
		010	Alternate function 0 (ADC2)
		001	Dedicated function operation (USBCFG)
		000	GPIO operation

TABLE 3-39: RESPONSE 1 STRUCTURE (CONTINUED)

TABLE 3-39: RESPONSE 1 STRUCTURE (CONTINUED)

Byte Index	Function Description	Value	Effect
25	GP3 settings		
	Bit 7-5	Don't	
		care	
	Bit 4: GPIO Output value	_	When the GP3 is set as an output GPIO, this value will
			be present at the GP3 pin
	Bit 3: GPIO Direction (Input/Output) -	1	GPIO Input mode
	Works only when GP3 is set for GPIO operation	0	GPIO Output mode
	Bit 2-0: GP3 Designation	111-100	Don't care
		011	Alternate function 1 (DAC2)
		010	Alternate function 0 (ADC3)
		001	Dedicated function operation (LED I2C)
		000	GPIO operation
26-63	_	Don't	
		care	

3.1.15 RESET CHIP

This command is used to force a Reset of the MCP2221 device. This command is useful when the Flash memory is updated with new data. The MCP2221 would need to be re-enumerated to see the new data.

Note:	This command is the only command that			
	does not expect a response.			

TABLE 3-40: COMMAND STRUCTURE

Byte Index	Value	Effect
0	0x70	Reset Chip - command code
1	0xAB	
2	0xCD	
3	0xEF	
4-63	0x00	Reserved

NOTES:

4.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings ^{(†)(1)}

Ambient temperature under bias	–40°C to +85°C
Storage temperature	–65°C to +150°C
Voltage on VDD with respect to Vss	–0.3V to +6.0V
Voltage on RST with respect to Vss	–0.3V to +9.0V
Voltage on VUSB pin with respect to VSS	–0.3V to +4.0V
Voltage on D+ and D- pins with respect to Vss	–0.3V to (VusB + 0.3V)
Voltage on all other pins with respect to Vss	–0.3V to (VDD + 0.3V)
Total power dissipation ⁽²⁾	800 mW
Maximum current out of Vss pin	
Maximum current into VDD pin	
Clamp current, Ік (VPIN < 0 or VPIN > VDD)	± 20 mA
Maximum output current sunk by any I/O pin	
Maximum output current sourced by any I/O pin	25 mA
Maximum current sunk by all ports	90 mA
Maximum current sourced by all ports	
† NOTICE: Stresses above those listed under "Absolute Maximum Ratings" may cause	permanent damage to the

† NOTICE: Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operation listings of this specification is not implied. Exposure above maximum rating conditions for extended periods may affect device reliability.

Note 1: VUSB must always be \leq VDD + 0.3V.

2: Power dissipation is calculated as follows: PDIS = VDD x {IDD $-\sum$ IOH} + \sum {(VDD - VOH) x IOH} + \sum (VOL x IOL).

4.1 DC CHARACTERISTICS

DC Characteristics			Operating Conditions (unless otherwise indicated): $3.0V \le V_{DD} \le 5.5V$ at $-40^{\circ}C \le T_{A} \le +85^{\circ}C$ (I-Temp)								
Param. No.	Characteristic	Sym.	Min.	Тур.	Max.	Units	Conditions				
D001	Supply Voltage	Vdd	3.0	_	5.5	V					
	POR Release Voltage	VPOR	_	1.6	—	V					
	POR Rearm Voltage	_		0.8	_	V					
D003	VDD Rise Rate to Ensure POR	SVDD	0.05	-	_	V/ms	Design guidance only Not tested				
D004	Supply Current	IDD	_	_	—						
	VDD = 3.0V		_	10	12	mA	Fosc = 12 MHz,				
	VDD = 5.0V		_	13	15	mA	(330 nF on VUSB)				
D005	Standby Current	IDDS	—	46	_	μA					
	Input Low-Voltage										
D031	Schmitt Trigger (URX)	VIL	—	—	0.2 Vdd	V	$3.0V \le V \text{DD} \le 5.5 \text{V}$				
	TTL (GP pins)		_	-	0.8		$4.5V \le V \text{DD} \le 5.5V$				
	Input High-Voltage										
D041	Schmitt Trigger (URX)	Vih	0.8 Vdd	_	Vdd	V	$3.0V \le VDD \le 5.5V$				
	TTL (GP pins)		2.0	-	Vdd		$4.5V \le V \text{DD} \le 5.5V$				
	Input Leakage Current										
D060	GP, URX	lı∟		±50	±100	nA	$Vss \le VPIN \le VDD,$ pin at Hi-Z				
	Output Low-Voltage										
D080	GP, UTX	Vol	—	_	0.6	V	IOL = 8.0 mA, VDD = 5.0V				
			_	—	0.6		IOL = 6.0 mA, VDD = 3.3V				
	Output High-Voltage										
D090	GP, UTX	Voн	Vdd - 0.7	_	_	V	IOH = -3.5 mA, VDD = 5.0V				
			Vdd - 0.7	_	_		Іон = -3.0 mA, VDD = 3.3V				
	Capacitive Loading Spec	s on Out	put Pins								
D102	GPIO	Сю		_	50	pF	Note 1				

Note 1: Characterized only, not 100% tested.




TABLE 4-1: USB MODULE SPECIFICATIONS

D	C Characteristics		$\begin{array}{l} \textbf{Operating Conditions (unless otherwise indicated):} \\ 3.0V \leq \mbox{ VDD} \leq \mbox{ 5.5V at } -40^{\circ}C \leq \mbox{ Ta} \leq \mbox{ +85}^{\circ}C \mbox{ (I-Temp)} \end{array}$							
Param. No.	Characteristic	Sym.	Min.	Тур.	Max.	Units	Conditions			
D313	USB Voltage	VUSB	3.0	_	3.6	V	Voltage on the VUSB pin must be in this range for proper USB operation			
D314	Input Leakage on Pin	lıL	—	-	±1	μA	$Vss \le VPIN \le VDD$ pin at high impedance			
D315	Input Low Voltage for USB Buffer	VILUSB	_	—	0.8	V	For VUSB range			
D316	Input High Voltage for USB Buffer	VIHUSB	2.0	—		V	For VUSB range			
D318	Differential Input Sensitivity	VDIFS	—	_	0.2	V	The difference between D+ and D- must exceed this value while VCM is met			
D319	Differential Common Mode Range	Vсм	0.8	—	2.5	V				
D320	Driver Output Impedance ⁽¹⁾	Ζουτ	28	—	44	W				
D321	Voltage Output Low	Vol	0.0	_	0.3	V	1.5 k Ω load connected to 3.6V			
D322	Voltage Output High	Voн	2.8	_	3.6	V	1.5 k Ω load connected to ground			

Note 1: The D+ and D- signal lines have been built-in impedance matching resistors. No external resistors, capacitors or magnetic components are necessary on the D+/D- signal paths between the MCP2221 family device and the USB cable.

TABLE 4-2: A/D CONVERTER (ADC) CHARACTERISTICS

Standard Operating Conditions (unless otherwise stated)

Operatin	Operating temperature lested at +25°C								
Param No.	Characteristic	Sym.	Min.	Тур.	Max.	Units	Conditions		
AD01	Resolution	NR	_	_	10	bit			
	Recommended Impedance of Analog Voltage Source	ZAIN			10	1	Can go higher if external 0.01µF capaci- tor is present on input pin.		

TABLE 4-3: DIGITAL-TO-ANALOG CONVERTER (DAC) SPECIFICATIONS

Operating Conditions: 3.0V < VDD < 5.5V, -40°C < TA < +85°C (unless otherwise stated).									
Param No.	Characteristic	Sym.	Min.	Тур.	Max.	Units	Comments		
DAC01*	Step Size	CLSB	_	VDD/32	_	V			
DAC02*	Absolute Accuracy	CACC	_	_	± 1/2	LSb			
DAC03*	Unit Resistor Value (R)	CR	_	5K		Ω			
DAC04*	Settling Time ⁽¹⁾	Сѕт		_	10	μS			

* These parameters are characterized but not tested.

Note 1: Settling time measured while DACVAL<4:0> transitions from '0000' to '1111'.

TABLE 4-4: THERMAL CONSIDERATIONS

	Standard Operating Conditions (unless otherwise stated) Operating temperature: $-40^{\circ}C \le TA \le +85^{\circ}C$ (I-Temp)								
Param. No.	Characteristic	Sym.	Тур.	Units	Conditions				
TH01	Thermal Resistance Junction	θја	70	°C/W	14-pin PDIP package				
	to Ambient		95.3	°C/W	14-pin SOIC package				
			100	°C/W	14-pin TSSOP package				
			45.7	°C/W	16-pin QFN 4 x 4 mm package				
TH02	Thermal Resistance Junction	θJC	32	°C/W	14-pin PDIP package				
	to Case		31	°C/W	14-pin SOIC package				
			24.4	°C/W	14-pin TSSOP package				
			6.3	°C/W	16-pin QFN 4 x 4 mm package				
TH03	Maximum Junction Temperature	Тјмах	+150	°C					
TH04	Power Dissipation	PD		W	PD = PINTERNAL + PI/O				
TH05	Internal Power Dissipation	PINTERNAL	—	W	PINTERNAL = IDD x VDD ⁽¹⁾				
TH06	I/O Power Dissipation	Pı/o		W	$PI/O = \Sigma(IOL \times VOL) + \Sigma(IOH \times (VDD - VOH))$				
TH07	Derated Power	Pder		W	Pder = PDmax (Tj – Ta)/θja ^(2, 3)				

Note 1: IDD is the current to run the device alone without driving any load on the output pins.

2: TA = Ambient Temperature.

3: T_J = Junction Temperature.

4.2 AC Characteristics

4.2.1 TIMING PARAMETER SYMBOLOGY

The timing parameter symbols have been created in one of the following formats:

1. TppS2	ppS	2. TppS				
Т						
F	Frequency	Т	Time			
Е	Error					
Lowercas	e letters (pp) and their meanings:					
рр						
io	Input or Output pin	osc	Oscillator			
rx	Receive	tx	Transmit			
bitclk	RX/TX BITCLK	RST	Reset			
drt	Device Reset Timer					
Uppercas	e letters and their meanings:					
S						
F	Fall	Р	Period			
Н	High	R	Rise			
1	Invalid (high-impedance)	V	Valid			
L	Low	Z	High-impedance			


4.2.2 TIMING CONDITIONS

The operating temperature and voltage specified in Table 4-5 apply to all timing specifications, unless otherwise noted. Figure 4-2 specifies the load conditions for the timing specifications.

TABLE 4-5: TEMPERATURE AND VOLTAGE SPECIFICATIONS – AC

	Standard Operating Conditions (unless otherwise stated)
AC CHARACTERISTICS	Operating temperature -40°C \leq TA \leq +85°C
AC CHARACTERISTICS	Operating voltage VDD range as described in DC spec,
	Section 4.1 "DC Characteristics".

FIGURE 4-2: LOAD CONDITIONS FOR DEVICE TIMING SPECIFICATIONS



4.2.3 TIMING DIAGRAMS AND SPECIFICATIONS

TABLE 4-6: RESET, OSCILLATOR START-UP TIMER AND POWER-UP TIMER PARAMETERS

Standard Operating Conditions (unless otherwise stated) Operating Temperature: $-40^{\circ}C \le TA \le +85^{\circ}C$									
Param No.CharacteristicSym.Min.Typ.†Max.UnitsConditions									
30	RST Pulse Width (low)	Trst	2	_	_	μs			
31	Power-Up timer	TPWRT	40	65	140	ms			
32	Oscillator Start-Up Time	Tost	_	1024	_	Тоѕт			


* These parameters are characterized but not tested.

⁺ Data in the "Typ." column is at 5V, +25°C, unless otherwise stated. These parameters are for design guidance only and are not tested.

5.0 **PACKAGING INFORMATION**




14-Lead PDIP (300 mil)



14-Lead Plastic Dual In-Line (P) – 300 mil Body [PDIP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units			
Din	nension Limits	MIN	NOM	MAX
Number of Pins	N		14	
Pitch	e		.100 BSC	
Top to Seating Plane	А	-	-	.210
Molded Package Thickness	A2	.115	.130	.195
Base to Seating Plane	A1	.015	-	—
Shoulder to Shoulder Width	E	.290	.310	.325
Molded Package Width	E1	.240	.250	.280
Overall Length	D	.735	.750	.775
Tip to Seating Plane	L	.115	.130	.150
Lead Thickness	С	.008	.010	.015
Upper Lead Width	b1	.045	.060	.070
Lower Lead Width	b	.014	.018	.022
Overall Row Spacing §	eB	-	-	.430

Notes:


1. Pin 1 visual index feature may vary, but must be located with the hatched area.

2. § Significant Characteristic.


3. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed .010" per side.


Dimensioning and tolerancing per ASME Y14.5M.
 BSC: Basic Dimension. Theoretically exact value shown without tolerances.


Microchip Technology Drawing C04-005B



Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging









VIEW A-A

Microchip Technology Drawing No. C04-065C Sheet 1 of 2

14-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging





VIEW C

	MILLIMETERS				
Dimension Lin	nits	MIN	NOM	MAX	
Number of Pins	N		14		
Pitch	е		1.27 BSC		
Overall Height	A	-	-	1.75	
Molded Package Thickness	A2	1.25	-	-	
Standoff §	A1	0.10	-	0.25	
Overall Width	E		6.00 BSC		
Molded Package Width	E1	3.90 BSC			
Overall Length	D	8.65 BSC			
Chamfer (Optional)	h	0.25	-	0.50	
Foot Length	L	0.40	-	1.27	
Footprint	L1		1.04 REF		
Lead Angle	Θ	0°	-	-	
Foot Angle	φ	0°	-	8°	
Lead Thickness	С	0.10	-	0.25	
Lead Width	b	0.31	-	0.51	
Mold Draft Angle Top	α	5°	-	15°	
Mold Draft Angle Bottom	β	5°	-	15°	


Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. § Significant Characteristic
- 3. Dimension D does not include mold flash, protrusions or gate burrs, which shall not exceed 0.15 mm per end. Dimension E1 does not include interlead flash or protrusion, which shall not exceed 0.25 mm per side.
- Dimensioning and tolerancing per ASME Y14.5M BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.
- 5. Datums A & B to be determined at Datum H.

Microchip Technology Drawing No. C04-065C Sheet 2 of 2

14-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	Units	N	S	
Dimension	Limits	MIN	NOM	MAX
Contact Pitch	E 1.27 BSC			
Contact Pad Spacing	С		5.40	
Contact Pad Width	Х			0.60
Contact Pad Length	Y			1.50
Distance Between Pads	Gx	0.67		
Distance Between Pads	G	3.90		

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2065A

14-Lead Plastic Thin Shrink Small Outline (ST) - 4.4 mm Body [TSSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging






Microchip Technology Drawing C04-087C Sheet 1 of 2

14-Lead Plastic Thin Shrink Small Outline (ST) - 4.4 mm Body [TSSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS			
Dimension Limits		MIN	NOM	MAX	
Number of Pins	N	14			
Pitch	е	0.65 BSC			
Overall Height	A	1.20			
Molded Package Thickness	A2	0.80	1.00	1.05	
Standoff	A1	0.05	-	0.15	
Overall Width	E	6.40 BSC			
Molded Package Width	E1	4.30 4.40 4.50			
Molded Package Length	D	4.90	5.00	5.10	
Foot Length	L	0.45	0.60	0.75	
Footprint	(L1)	1.00 REF			
Foot Angle	φ	0°	-	8°	
Lead Thickness	С	0.09	-	0.20	
Lead Width	b	0.19	-	0.30	

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15mm per side.


3. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing No. C04-087C Sheet 2 of 2

14-Lead Plastic Thin Shrink Small Outline (ST) - 4.4 mm Body [TSSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN


	Units	MILLIMETERS		
Dimensior	n Limits	MIN	NOM	MAX
Contact Pitch	E	0.65 BSC		
Contact Pad Spacing	C1		5.90	
Contact Pad Width (X14)	X1			0.45
Contact Pad Length (X14)	Y1			1.45
Distance Between Pads	G	0.20		

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2087A



16-Lead Plastic Quad Flat, No Lead Package (ML) - 4x4x0.9mm Body [QFN]

http://www.microchip.com/packaging


For the most current package drawings, please see the Microchip Packaging Specification located at

Microchip Technology Drawing C04-127D Sheet 1 of 2

Note:

16-Lead Plastic Quad Flat, No Lead Package (ML) - 4x4x0.9mm Body [QFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS			
Dimension Limits		MIN	NOM	MAX	
Number of Pins	Ν	16			
Pitch	е	0.65 BSC			
Overall Height	Α	0.80 0.90 1.00			
Standoff	A1	0.00 0.02 0.05			
Contact Thickness	A3	0.20 REF			
Overall Width	E	4.00 BSC			
Exposed Pad Width	E2	2.50 2.65 2.80			
Overall Length	D	4.00 BSC			
Exposed Pad Length	D2	2.50	2.65	2.80	
Contact Width	b	0.25	0.30	0.35	
Contact Length	L	0.30 0.40 0.50			
Contact-to-Exposed Pad	K	0.20			

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Package is saw singulated


3. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-127D Sheet 2 of 2

16-Lead Plastic Quad Flat, No Lead Package (ML) - 4x4x0.9mm Body [QFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS			
Dimension Limits		MIN	NOM	MAX	
Contact Pitch	E	0.65 BSC			
Optional Center Pad Width	W2			2.50	
Optional Center Pad Length	T2			2.50	
Contact Pad Spacing	C1		4.00		
Contact Pad Spacing	C2		4.00		
Contact Pad Width (X28)	X1			0.35	
Contact Pad Length (X28)	Y1			0.80	
Distance Between Pads	G	0.30			

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2127A

NOTES:

APPENDIX A: REVISION HISTORY

Revision C (June 2017)

The following is the list of modifications:

- Added Table 4-2 and Table 4-3.
- Minor typographical edits.

Revision B (February 2015)

• Updated bit settings in Registers 1-1 to 1-7, Register 1-10 and Registers 1-12, 1-13, 1-14, 1-15.

Revision A (May 2014)

Original Release of this Document.

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip sales office.

PART NO.	I ⁽¹⁾ ¥ <u>/XX</u>	Exa	amples:	
Device Tape an Optic	nd Reel Temperature Package on Range	a)	MCP2221- I/P:	Industrial temperature, 14LD PDIP Package
Device:	MCP2221: USB-to-I ² C/UART Protocol Converter	a)	MCP2221- I/SL:	Industrial temperature, 14LD SOIC Package
Device.	MCP2221T: USB-to-1 ² C/UART Protocol Converter (Tape and Reel)	b)	MCP2221T- I/SL:	Tape and Reel, Industrial temperature, 14LD SOIC Package
Temperature Range:	I = -40° C to $+85^{\circ}$ C (Industrial)	a)	MCP2221- I/ST:	Industrial temperature, 14LD TSSOP Package
Package:	ML = Plastic Quad Flat, No Lead Package – 4x4x0.9 mm Body (QFN), 16-Lead	b)	MCP2221T- I/ST:	Tape and Reel, Industrial temperature, 14LD TSSOP Package
	P = Plastic Dual In Line, 300 mil. Body (PDIP), 14-Lead SL = Plastic Small Outline – Narrow, 3.90 mm Body	a)	MCP2221- I/ML:	Industrial temperature, 16LD 4x4 QFN Package
	(SOIC), 14-Lead ST = Plastic Thin Shrink Small Outline – 4.4 mm Body (TSSOP), 14-Lead	b)	MCP2221T- I/ML:	Tape and Reel, Industrial temperature, 16LD 4x4 QFN Package
This identifi package. C	teel identifier only appears in the catalog part number description. ier is used for ordering purposes and is not printed on the device heck with your Microchip Sales Office for package availability with d Reel option.			

NOTES:

Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Friday, May 10, 2002Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTA-TIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.

QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

Trademarks

The Microchip name and logo, the Microchip logo, AnyRate, dsPIC, FlashFlex, flexPWR, Heldo, JukeBlox, KeeLoq, KeeLoq logo, Kleer, LANCheck, LINK MD, MediaLB, MOST, MOST logo, MPLAB, OptoLyzer, PIC, PICSTART, PIC32 logo, RightTouch, SpyNIC, SST, SST Logo, SuperFlash and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

ClockWorks, The Embedded Control Solutions Company, ETHERSYNCH, Hyper Speed Control, HyperLight Load, IntelliMOS, mTouch, Precision Edge, and QUIET-WIRE are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BodyCom, chipKIT, chipKIT logo, CodeGuard, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, MiWi, motorBench, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PureSilicon, RightTouch logo, REAL ICE, Ripple Blocker, Serial Quad I/O, SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

GestIC is a registered trademarks of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2014-2017, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

ISBN: 978-1-5224-1791-0



Worldwide Sales and Service

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270

Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078

ASIA/PACIFIC

Asia Pacific Office Suites 3707-14, 37th Floor Tower 6, The Gateway Harbour City, Kowloon

Hong Kong Tel: 852-2943-5100 Fax: 852-2401-3431

Australia - Sydney Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

China - Beijing Tel: 86-10-8569-7000 Fax: 86-10-8528-2104

China - Chengdu Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Chongqing Tel: 86-23-8980-9588 Fax: 86-23-8980-9500

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115 Fax: 86-571-8792-8116

China - Hong Kong SAR Tel: 852-2943-5100

Fax: 852-2401-3431 China - Nanjing Tel: 86-25-8473-2460 Fax: 86-25-8473-2470

China - Qingdao Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

China - Shanghai Tel: 86-21-3326-8000 Fax: 86-21-3326-8021

China - Shenyang Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

China - Shenzhen Tel: 86-755-8864-2200 Fax: 86-755-8203-1760

China - Wuhan Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

China - Xian Tel: 86-29-8833-7252 Fax: 86-29-8833-7256 ASIA/PACIFIC China - Xiamen

Tel: 86-592-2388138 Fax: 86-592-2388130

China - Zhuhai Tel: 86-756-3210040 Fax: 86-756-3210049

India - Bangalore Tel: 91-80-3090-4444 Fax: 91-80-3090-4123

India - New Delhi Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-3019-1500

Japan - Osaka Tel: 81-6-6152-7160 Fax: 81-6-6152-9310

Japan - Tokyo Tel: 81-3-6880- 3770 Fax: 81-3-6880-3771

Korea - Daegu Tel: 82-53-744-4301 Fax: 82-53-744-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur Tel: 60-3-6201-9857 Fax: 60-3-6201-9859

Malaysia - Penang Tel: 60-4-227-8870 Fax: 60-4-227-4068

Philippines - Manila Tel: 63-2-634-9065 Fax: 63-2-634-9069

Singapore Tel: 65-6334-8870 Fax: 65-6334-8850

Taiwan - Hsin Chu Tel: 886-3-5778-366 Fax: 886-3-5770-955

Taiwan - Kaohsiung Tel: 886-7-213-7830

Taiwan - Taipei Tel: 886-2-2508-8600 Fax: 886-2-2508-0102

Thailand - Bangkok Tel: 66-2-694-1351 Fax: 66-2-694-1350

EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

Finland - Espoo Tel: 358-9-4520-820

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

France - Saint Cloud Tel: 33-1-30-60-70-00

Germany - Garching Tel: 49-8931-9700 **Germany - Haan** Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-67-3636

Germany - Karlsruhe Tel: 49-721-625370

Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Ra'anana Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7289-7561

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Gothenberg Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microchip:

MCP2221T-I/ST MCP2221-I/ST MCP2221-I/SL MCP2221-I/P MCP2221-I/ML