


DA1206C121R-10



UNCONTROLLED DOCUMENT

PHYSICAL DIMENSIONS:


A	3.20 [.126]	+ 0.200 [.008]
B	1.60 [.063]	+ 0.200 [.008]
C	0.80 [.031]	+ 0.200 [.008]
D	0.40 [.016]	+ 0.150 [.006]
D1	0.30 [.012]	+ 0.200 [.008]
E	0.80 [.031]	+ 0.100 [.004]




ELECTRICAL CHARACTERISTICS:		
Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	120	
Minimum	90	
Maximum	150	0.2
LINE TO LINE INSULATION RESISTANCE		300 mA
>100 MΩ AT 75 VOLTS.		



LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.762 (0.030) to this dimension)



DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
C	UPDATE COMPANY LOGO ADD ROHS	05/20/09	JRK	PROJECT/PART NUMBER:	DA1206C121R-10	REV	C
B	D1 dim chgd from 0.008 ±0.004 to 0.012 ± 0.008. UPDATE COMPANY LOGO	10/30/07	JRK	SCALE:	NTS	PART TYPE:	CO-FIRE
A	ORIGINAL DRAFT	03/30/04	TMB	DATE:	03/30/04	DRAWN BY:	TMB
REV	DESCRIPTION	DATE	INT	GAD #	DA1206C121R-10-C	TOOL #	-
						SHEET:	
						2 of 2	

