

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0039000073](#)  
**Status:** **Active**  
**Overview:** Mini-Fit Jr. Power Connectors  
**Description:** Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 18-24 AWG, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 55560001-PK-000 (PDF)</a>
<a href="#">Product Specification 55560008-TS-000 (PDF)</a>	<a href="#">Test Summary 55560010-TS-000 (PDF)</a>
<a href="#">Product Specification PS-5556-001-001 (PDF)</a>	<a href="#">Test Summary TS-5556-002-001 (PDF)</a>
<a href="#">Product Specification PS-5556-002-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 55560001-AS-000 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	5556
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Jr. Power Connectors</a>
Packaging Alternative	<a href="#">39000074 (Loose)</a>
Product Name	Mini-Fit
UPC	800753825178

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.130/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Engineering Number	5556GS4
--------------------	---------

**Reference - Drawing Numbers**

Application Specification	55560001-AS-000
Packaging Specification	55560001-PK-000
Product Specification	55560008-TS-000, PS-5556-001-001, PS-5556-002-001
Sales Drawing	SD-5556-006-001
Test Summary	55560010-TS-000, TS-5556-002-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5556 Series](#)

**Use With**

Mini-Fit Jr. Receptacle Housing [5557](#)  
 <br>Mini-Fit BMI Slide and Lock Panel  
 Mount [44516](#) <br>Mini-Fit BMI Panel Mount  
 Receptacle Housing<br> [42474](#) , [43760](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool	<a href="#">11030044</a>
FineAdjust Applicator	<a href="#">2037026300</a>
for Mini-Fit Double Crimp Applications Using Two 22 AWG Wires	
Hand Crimp Tool	<a href="#">638190901</a>
for Mini-Fit Jr. Male	

and Female Crimp  
 Terminals, 18-24  
 AWG  
 FineAdjust Applicator [639015600](#)  
 for Insulation OD  
 1.90-2.30mm - 18-24  
 AWG  
 FineAdjust Applicator [639023900](#)  
 for Insulation OD  
 1.40-1.70mm - 18-24  
 AWG  
 FineAdjust Applicator [639024800](#)  
 for Insulation OD  
 2.50-2.95mm  
 Optimized for 18  
 AWG Only  
 FineAdjust Applicator [639024900](#)  
 for Insulation OD  
 2.30-2.60mm - 18-24  
 AWG  
 FineAdjust Applicator [639047800](#)  
 for Insulation OD  
 2.50-2.95mm, 18-24  
 AWG  
 FineAdjust Applicator [639048000](#)  
 for Insulation OD  
 1.65-2.05mm, 18-24  
 AWG  
 T2 Terminator [639115600](#)  
 for insulation OD  
 1.90-2.30mm - 18-24  
 AWG  
 T2 Terminator [639123900](#)  
 for insulation OD  
 1.40-1.70mm - 18-24  
 AWG  
 T2 Terminator [639124800](#)  
 for insulation OD  
 2.50-2.95mm  
 optimized for 18  
 AWG only  
 T2 Terminator [639124900](#)  
 for insulation OD  
 2.30-2.60mm - 18-24  
 AWG  
 T2 Terminator [639147800](#)  
 for Mini-Fit Crimp  
 Terminals, 18-24  
 AWG with Large  
 Insulation ODs  
 T2 Terminator [639148000](#)  
 for Mini-Fit Crimp  
 Terminals, 18-24  
 AWG with Smaller  
 Insulation ODs

This document was generated on 08/06/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**