

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0987881201](#)
Status: **Active**
Overview: NSCC - New Standard Casing Contact
Description: 1.50mm Pitch NSCC, Wire-to-Wire, Receptacle Housing, Gray, 10 Circuits

Documents:

[Drawing \(PDF\)](#) [Application Specification AS-98788-003-FR \(PDF\)](#)
[Application Specification AS-98788-002-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-98788-003-001 \(PDF\)](#)

General

Product Family	Crimp Housings
Series	98788
Application	Power, Wire-to-Wire
Application Tooling Part Link	63812-1200
Application Tooling Part Link	63813-5700
Application Tooling Part Link	63813-7400
Overview	NSCC - New Standard Casing Contact
Product Name	NSCC
UPC	822348791620

Physical

Circuits (maximum)	10
Circuits Detail	10x1.5mm male terminal
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Resin	Polyester
Net Weight	9.590/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.25mm
Pitch - Termination Interface	6.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	N/A

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	19201EV10M1
--------------------	-------------

Reference - Drawing Numbers

Application Specification	AS-98788-002-001, AS-98788-003-001, AS-98788-003-FR
Sales Drawing	SD-98788-006



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[98788](#) Series

Mates With

[98789-1201](#)

Use With

Sicma 1.5 and 2.8mm Female Terminals for Single Wire Seal from FCI