

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1053091104](#)  
**Status:** **Active**  
**Overview:** [Nano-Fit Power Connectors](#)  
**Description:** Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 4 Circuits, with Kinked Pins, Tin (Sn) Plating, Black, Glow-Wire Capable, Tray

**Documents:**

|                                                                  |                                                                   |
|------------------------------------------------------------------|-------------------------------------------------------------------|
| <a href="#">3D Model</a>                                         | <a href="#">Product Specification PS-105300-100-001 (PDF)</a>     |
| <a href="#">3D Model (PDF)</a>                                   | <a href="#">Application Specification AS-105300-100-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                    | <a href="#">Packaging Specification PK-105309-300-000 (PDF)</a>   |
| <a href="#">Product Specification 1053001000-PS-CH-000 (PDF)</a> | <a href="#">Test Summary 1053001000-TS-000 (PDF)</a>              |
| <a href="#">Product Specification 1053001000-PS-ES-000 (PDF)</a> | <a href="#">Datasheet (PDF)</a>                                   |
| <a href="#">Product Specification 1053001000-PS-JP-000 (PDF)</a> | <a href="#">Symbol Footprint Data SYM-105309-XX04-001 (PDF)</a>   |
| <a href="#">Product Specification 1053001000-PS-SK-000 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>              |

**Agency Certification**


|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                       |                                           |
|-----------------------|-------------------------------------------|
| Product Family        | PCB Headers                               |
| Series                | <a href="#">105309</a>                    |
| Application           | Power, Wire-to-Board                      |
| Overview              | <a href="#">Nano-Fit Power Connectors</a> |
| Packaging Alternative | <a href="#">1053093504</a>                |
| Product Name          | Nano-Fit                                  |
| UPC                   | 887191937380                              |

**Physical**

|                                |                        |
|--------------------------------|------------------------|
| Breakaway                      | No                     |
| Circuits (Loaded)              | 4                      |
| Circuits (maximum)             | 4                      |
| Color - Resin                  | Black                  |
| Durability (mating cycles max) | 25                     |
| Flammability                   | 94V-0                  |
| Glow-Wire Capable              | Yes                    |
| Guide to Mating Part           | No                     |
| Keying to Mating Part          | Yes                    |
| Lock to Mating Part            | Yes                    |
| Material - Metal               | Brass                  |
| Material - Plating Mating      | Tin                    |
| Material - Plating Termination | Tin                    |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 0.470/g                |
| Number of Rows                 | 1                      |
| Orientation                    | Vertical               |
| PC Tail Length                 | 3.20mm                 |
| PCB Locator                    | Yes                    |
| PCB Retention                  | Yes                    |
| PCB Thickness - Recommended    | 1.60mm, 2.40mm         |
| Packaging Type                 | Tray                   |
| Pitch - Mating Interface       | 2.50mm                 |
| Pitch - Termination Interface  | 2.50mm                 |
| Plating min - Mating           | 1.524µm                |
| Plating min - Termination      | 1.524µm                |
| Polarized to Mating Part       | Yes                    |
| Polarized to PCB               | Yes                    |



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[105309](#) Series

**Mates With**

Nano-Fit Receptacle Housing [1053071204](#) .  
Nano-Fit Cable Assembly [145130](#)

|                                    |                                                                                                                 |
|------------------------------------|-----------------------------------------------------------------------------------------------------------------|
| Shrouded                           | Yes                                                                                                             |
| Stackable                          | No                                                                                                              |
| Surface Mount Compatible (SMC)     | No                                                                                                              |
| Temperature Range - Operating      | -40° to +105°C                                                                                                  |
| Termination Interface: Style       | Through Hole                                                                                                    |
| <b>Electrical</b>                  |                                                                                                                 |
| Current - Maximum per Contact      | 8.0A                                                                                                            |
| Voltage - Maximum                  | 250V AC (RMS)/DC                                                                                                |
| <b>Material Info</b>               |                                                                                                                 |
| <b>Reference - Drawing Numbers</b> |                                                                                                                 |
| Application Specification          | AS-105300-100-001                                                                                               |
| Packaging Specification            | PK-105309-300-000                                                                                               |
| Product Specification              | 1053001000-PS-CH-000, 1053001000-PS-ES-000,<br>1053001000-PS-JP-000, 1053001000-PS-SK-000,<br>PS-105300-100-001 |
| Sales Drawing                      | SD-105309-100-000                                                                                               |
| Symbol/Footprint Data              | SYM-105309-XX04-001                                                                                             |
| Test Summary                       | 1053001000-TS-000                                                                                               |

This document was generated on 09/02/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[105309-1104](#)