



# SAFETY DATA SHEET

Machineable Glass Ceramic

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

**Product name** : Machineable Glass Ceramic  
**Product code** : MA800  
**Product description** : Not available.  
**Product type** : Solid.  
**Other means of identification** : Not available.

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Not applicable.

### 1.3 Details of the supplier of the safety data sheet

Goodfellow Cambridge Ltd.  
Ermine Business Park, Huntingdon, England PE29 6WR  
Email: [info@goodfellow.com](mailto:info@goodfellow.com)  
Telephone: 0800 731 4653 (UK) or +44 1480 424 800  
Fax: 0800 328 7689 (UK) or +44 1480 424 900

**e-mail address of person responsible for this SDS** : [sds@goodfellow.com](mailto:sds@goodfellow.com)

### 1.4 Emergency telephone number

#### Emergency phone:

**Telephone number** : +01-813-248-0585

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

**Product definition** : Mixture

#### Classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Not classified.

The product is not classified as hazardous according to Regulation (EC) 1272/2008 as amended.

**Ingredients of unknown toxicity** : 93 percent of the mixture consists of component(s) of unknown acute oral toxicity  
93 percent of the mixture consists of component(s) of unknown acute dermal toxicity  
93 percent of the mixture consists of component(s) of unknown acute inhalation toxicity

## SECTION 2: Hazards identification

**Ingredients of unknown ecotoxicity** : Contains 83% of components with unknown hazards to the aquatic environment

See Section 11 for more detailed information on health effects and symptoms.

### 2.2 Label elements

**Signal word** : No signal word.

**Hazard statements** : No known significant effects or critical hazards.

#### Precautionary statements

**Prevention** : Not applicable.

**Response** : Not applicable.

**Storage** : Not applicable.

**Disposal** : Not applicable.

**Supplemental label elements** : Safety data sheet available on request.

**Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles** : Not applicable.

#### Special packaging requirements

**Containers to be fitted with child-resistant fastenings** : Not applicable.

**Tactile warning of danger** : Not applicable.

### 2.3 Other hazards

**Product meets the criteria for PBT or vPvB according to Regulation (EC) No. 1907/2006, Annex XIII** : This mixture does not contain any substances that are assessed to be a PBT or a vPvB.

**Other hazards which do not result in classification** : None known.

## SECTION 3: Composition/information on ingredients

**3.2 Mixtures** : Mixture

Product/ingredient name	Identifiers	%	Regulation (EC) No. 1272/2008 [CLP]	Type
Fluoride	CAS: 16984-48-8	≤5	Not classified.	[2]

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs, vPvBs or Substances of equivalent concern, or have been assigned a workplace exposure limit and hence require reporting in this section.

#### Type

[1] Substance classified with a health or environmental hazard

[2] Substance with a workplace exposure limit

[3] Product meets the criteria for PBT or vPvB according to Regulation (EC) No. 1907/2006, Annex XIII

[4] Substance meets the criteria for vPvB according to Regulation (EC) No. 1907/2006, Annex XIII

[5] Substance of equivalent concern

[6] Additional disclosure due to company policy

Occupational exposure limits, if available, are listed in Section 8.

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur.
- Skin contact** : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur.
- Ingestion** : Wash out mouth with water. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training.

### 4.2 Most important symptoms and effects, both acute and delayed

#### Over-exposure signs/symptoms

- Eye contact** : No specific data.
- Inhalation** : No specific data.
- Skin contact** : No specific data.
- Ingestion** : No specific data.

### 4.3 Indication of any immediate medical attention and special treatment needed

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.

### 5.2 Special hazards arising from the substance or mixture

- Hazards from the substance or mixture** : No specific fire or explosion hazard.
- Hazardous combustion products** : Decomposition products may include the following materials:  
halogenated compounds  
metal oxide/oxides

### 5.3 Advice for firefighters

- Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.
- Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilt material. Put on appropriate personal protective equipment.
- For emergency responders** : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

- 6.2 Environmental precautions** : Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

### 6.3 Methods and material for containment and cleaning up

- Small spill** : Move containers from spill area. Vacuum or sweep up material and place in a designated, labelled waste container. Dispose of via a licensed waste disposal contractor.
- Large spill** : Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Vacuum or sweep up material and place in a designated, labelled waste container. Dispose of via a licensed waste disposal contractor.

- 6.4 Reference to other sections** : See Section 1 for emergency contact information.  
See Section 8 for information on appropriate personal protective equipment.  
See Section 13 for additional waste treatment information.

## SECTION 7: Handling and storage

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

### 7.1 Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8).
- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

### 7.2 Conditions for safe storage, including any incompatibilities

Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabelled containers. Use appropriate containment to avoid environmental contamination. See Section 10 for incompatible materials before handling or use.

### 7.3 Specific end use(s)

- Recommendations** : Not available.
- Industrial sector specific solutions** : Not available.

## SECTION 8: Exposure controls/personal protection

The information in this section contains generic advice and guidance. Information is provided based on typical anticipated uses of the product. Additional measures might be required for bulk handling or other uses that could significantly increase worker exposure or environmental releases.

### 8.1 Control parameters

#### Occupational exposure limits

Product/ingredient name	Exposure limit values
Fluoride	<b>EH40/2005 WELs (United Kingdom (UK), 8/2007).</b> TWA: 2.5 mg/m <sup>3</sup> , (as F) 8 hours.

**Recommended monitoring procedures** : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to monitoring standards, such as the following: European Standard EN 689 (Workplace atmospheres - Guidance for the assessment of exposure by inhalation to chemical agents for comparison with limit values and measurement strategy) European Standard EN 14042 (Workplace atmospheres - Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents) European Standard EN 482 (Workplace atmospheres - General requirements for the performance of procedures for the measurement of chemical agents) Reference to national guidance documents for methods for the determination of hazardous substances will also be required.

#### DNELs/DMELs

No DNELs/DMELs available.

#### PNECs

No PNECs available

### 8.2 Exposure controls

**Appropriate engineering controls** : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

#### Individual protection measures

**Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

**Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.

#### Skin protection

**Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

**Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

Machineable Glass Ceramic

## SECTION 8: Exposure controls/personal protection

**Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

#### Appearance

**Physical state** : Solid.  
**Colour** : Not available.  
**Odour** : Not available.  
**Odour threshold** : Not available.  
**pH** : Not available.  
**Melting point/freezing point** : Not available.  
**Initial boiling point and boiling range** : Not available.  
**Flash point** : Not applicable.  
**Evaporation rate** : Not available.  
**Flammability (solid, gas)** : Not available.  
**Upper/lower flammability or explosive limits** : Not applicable.  
**Vapour pressure** : Not available.  
**Vapour density** : Not applicable.  
**Relative density** : Not available.  
**Solubility(ies)** : Not available.  
**Partition coefficient: n-octanol/ water** : Not applicable.  
**Auto-ignition temperature** : Not applicable.  
**Decomposition temperature** : Not available.  
**Viscosity** : Not applicable.  
**Explosive properties** : Not available.  
**Oxidising properties** : Not available.

### 9.2 Other information

**Solubility in water** : Not available.

No additional information.

## SECTION 10: Stability and reactivity

**10.1 Reactivity** : No specific test data related to reactivity available for this product or its ingredients.

**10.2 Chemical stability** : The product is stable.

**10.3 Possibility of hazardous reactions** : Under normal conditions of storage and use, hazardous reactions will not occur.

**10.4 Conditions to avoid** : No specific data.

**10.5 Incompatible materials** : No specific data.

**10.6 Hazardous decomposition products** : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity

**Conclusion/Summary** : Not available.

#### Acute toxicity estimates

Not available.

#### Irritation/Corrosion

**Conclusion/Summary** : Not available.

#### Sensitisation

**Conclusion/Summary** : Not available.

#### Mutagenicity

**Conclusion/Summary** : Not available.

#### Carcinogenicity

**Conclusion/Summary** : Not available.

#### Reproductive toxicity

**Conclusion/Summary** : Not available.

#### Teratogenicity

**Conclusion/Summary** : Not available.

#### Specific target organ toxicity (single exposure)

Not available.

#### Specific target organ toxicity (repeated exposure)

Not available.

#### Aspiration hazard

Not available.

**Information on likely routes of exposure** : Not available.

#### Potential acute health effects

**Eye contact** : No known significant effects or critical hazards.

**Inhalation** : No known significant effects or critical hazards.

**Skin contact** : No known significant effects or critical hazards.

**Ingestion** : No known significant effects or critical hazards.

#### Symptoms related to the physical, chemical and toxicological characteristics

**Eye contact** : No specific data.

**Inhalation** : No specific data.

**Skin contact** : No specific data.

**Ingestion** : No specific data.

#### Delayed and immediate effects as well as chronic effects from short and long-term exposure

##### Short term exposure

**Potential immediate effects** : Not available.

**Potential delayed effects** : Not available.

##### Long term exposure

**Potential immediate effects** : Not available.

**Potential delayed effects** : Not available.

##### Potential chronic health effects

## SECTION 11: Toxicological information

Not available.

<b>Conclusion/Summary</b>	: Not available.
<b>General</b>	: No known significant effects or critical hazards.
<b>Carcinogenicity</b>	: No known significant effects or critical hazards.
<b>Mutagenicity</b>	: No known significant effects or critical hazards.
<b>Teratogenicity</b>	: No known significant effects or critical hazards.
<b>Developmental effects</b>	: No known significant effects or critical hazards.
<b>Fertility effects</b>	: No known significant effects or critical hazards.

**Other information** : Not available.

## SECTION 12: Ecological information

### 12.1 Toxicity

**Conclusion/Summary** : Not available.

### 12.2 Persistence and degradability

**Conclusion/Summary** : Not available.

### 12.3 Bioaccumulative potential

Not available.

### 12.4 Mobility in soil

**Soil/water partition coefficient ( $K_{oc}$ )** : Not available.

**Mobility** : Not available.

### 12.5 Results of PBT and vPvB assessment

This mixture does not contain any substances that are assessed to be a PBT or a vPvB.

**12.6 Other adverse effects** : No known significant effects or critical hazards.

## SECTION 13: Disposal considerations

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

### 13.1 Waste treatment methods

#### Product

**Methods of disposal** : The generation of waste should be avoided or minimised wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction.

**Hazardous waste** : Within the present knowledge of the supplier, this product is not regarded as hazardous waste, as defined by EU Directive 2008/98/EC.

#### Packaging

**Methods of disposal** : The generation of waste should be avoided or minimised wherever possible. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible.



Machineable Glass Ceramic

## SECTION 13: Disposal considerations

**Special precautions** : This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers.

## SECTION 14: Transport information

	ADR/RID	ADN	IMDG	IATA
14.1 UN number	Not available.	Not available.	Not available.	Not available.
14.2 UN proper shipping name	Not available.	Not available.	Not available.	Not available.
14.3 Transport hazard class(es)	Not available.	Not available.	Not available.	Not available.
14.4 Packing group	-	-	-	-
14.5 Environmental hazards	No.	No.	No.	No.
Additional information	-	-	-	-

**14.6 Special precautions for user** : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

**14.7 Transport in bulk according to IMO instruments** : Not available.

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

#### EU Regulation (EC) No. 1907/2006 (REACH)

##### Annex XIV - List of substances subject to authorisation

###### Annex XIV

None of the components are listed.

###### Substances of very high concern

None of the components are listed.

**Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles** : Not applicable.

#### Other EU regulations

**Europe inventory** : Not determined.

**Black List Chemicals (76/464/EEC)** :

**Industrial emissions (integrated pollution prevention and control) - Air** : Listed

**Ozone depleting substances (1005/2009/EU)**

**Ozone depleting substances (1005/2009/EU)**

## SECTION 15: Regulatory information

Not listed.

### Prior Informed Consent (PIC) (649/2012/EU)

Not listed.

### Seveso Directive

This product is not controlled under the Seveso Directive.

### International regulations

#### Chemical Weapon Convention List Schedules I, II & III Chemicals

Not listed.

#### Montreal Protocol

Not listed.

#### Stockholm Convention on Persistent Organic Pollutants

Not listed.

#### UNECE Aarhus Protocol on POPs and Heavy Metals

Not listed.

### International lists

#### National inventory

<b>Australia</b>	: Not determined.
<b>Canada</b>	: All components are listed or exempted.
<b>China</b>	: All components are listed or exempted.
<b>Japan</b>	: <b>Japan inventory (CSCL)</b> : Not determined. <b>Japan inventory (ISHL)</b> : Not determined.
<b>Malaysia</b>	: Not determined
<b>New Zealand</b>	: All components are listed or exempted.
<b>Philippines</b>	: All components are listed or exempted.
<b>Republic of Korea</b>	: Not determined.
<b>Taiwan</b>	: Not determined.
<b>Turkey</b>	: Not determined.
<b>United States</b>	: Not determined.

**15.2 Chemical safety assessment** : This product contains substances for which Chemical Safety Assessments are still required.

## SECTION 16: Other information

✔ Indicates information that has changed from previously issued version.

**Abbreviations and acronyms** : ATE = Acute Toxicity Estimate  
CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]  
DMEL = Derived Minimal Effect Level  
DNEL = Derived No Effect Level  
EUH statement = CLP-specific Hazard statement  
PBT = Persistent, Bioaccumulative and Toxic  
PNEC = Predicted No Effect Concentration  
RRN = REACH Registration Number  
vPvB = Very Persistent and Very Bioaccumulative

### Procedure used to derive the classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Classification	Justification
Not classified.	

### Full text of abbreviated H statements

Machineable Glass Ceramic

## SECTION 16: Other information

Not applicable.

### [Full text of classifications \[CLP/GHS\]](#)

Not applicable.

**Date of printing** : 17/02/2022

**Date of issue/ Date of revision** : 16/02/2022

**Date of previous issue** : 07/12/2019

**Version** : 0.06

### [Notice to reader](#)

Further information.

License granted to make unlimited paper copies for internal use only.

This datasheet has been compiled for guidance in connection with products sourced from and supplied by Metals & Materials Limited only, including all subsidiary companies (Goodfellow Cambridge Limited, Goodfellow SARM, Goodfellow GmbH, Goodfellow Corporation and Goodfellow (Shanghai) Trading Co., Ltd., subsequently referred to as "Goodfellow") and must not be used in connection with any non-Goodfellow supplied products. In accepting receipt of this datasheet with no material purchase from Goodfellow, you agree to absolve Goodfellow entirely and waive any legal rights or remedy against Goodfellow arising from such unauthorised use

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. It is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. Employers should use this information only as a supplement to other information gathered by them and should make independent judgement of the suitability of this information to ensure proper use of the product and to protect the health and safety of their employees and the end-user(s) of the product.

Goodfellow supplies this information without warranty and any use of the product not in conformance with this Material Safety Data Sheet or in combination with any other product or process is the responsibility of the user. The Company does not represent any guarantee of the properties of the product or any suitability of the product for a given application.

Goodfellow shall not be held liable for any damage resulting from handling or from contact with the product. See [www.goodfellow.com](http://www.goodfellow.com) or [www.goodfellowusa.com](http://www.goodfellowusa.com) for additional terms and conditions of sale.