



| | | | | | | | | | |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------|---------------------------|----------------------|--------------------------------|----------------------|----------------------------------|----------------------|-------------------------------------------------------------------------------|
| Form Type | Distribute | Version | 2.0 | Ref | IPC 1752A | Sectionals | Material Info | Subsectionals | D, A |
| Supplier Information | | | | | | | | | |
| Company Name | TE Connectivity | Request Document ID | | Contact Name | Benfer, David W | Contact Title | Staff Mfg & Process Dvl Engineer | | |
| Company Unique ID | TE Connectivity | Response Date | 2018-04-03 | Contact Email | dave.benfer@te.com | | | | |
| Contact Phone Number | +1-717-986-3725 | | | | | | | | |
| Legal Statement | | | | | | | | | |
| Supplier Acceptance | true | | | | | | | | |
| Legal Statement | | | | | | | | | |
| The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers. | | | | | | | | | |
| Product | | | | | | | | | |
| Manufacturer Item number | 1337771-4 | Amount | 64984.88 | Version | - | Identity | | | |
| Manufacturer Item Name | 50 OHM COAX BNC STR PLUG STR P | Weight Uom | mg | Mfr Site | | Authority | | | |
| Date | | UOM | Each | | | | | | |
| EURoHS-0508 | Product(s) meets EU RoHS requirements by application of the selected exemption(s) | | | | | | | | |
| ChinaRoHS-0508 | Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products | | | | | | | | |
| EUREACH-0117 | REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH | | | | | | | | |
| Complex Article Description | REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed | | | | | | | | |
| Product Disclosure | | | | | | | | | |
| Sub-Item/Material/Substance | Level | Name | Substance Category | Substance CAS | Substance Concentration | Quantity | Mass per Unit | UOM | Exemption |
| Sub-Item | 1 | BNC Str Plg Hex 50Ohm Silver P | | | | 2.0 | 10722.44 | mg | |
| Material | 2 | Ferrule - Silver Plating | | | | 2.0 | 0.3216732 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 1.5 | 2.0 | 0.0048251 | mg | |
| Substance | 3 | Silver | Supplier | 7440-22-4 | 98.5 | 2.0 | 0.31685 | mg | |
| Material | 2 | Contact - Brass | | | | 2.0 | 199.973506 | mg | |
| Substance | 3 | Zinc | Supplier | 7440-66-6 | 38.7 | 2.0 | 77.38975 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 0.49 | 2.0 | 0.97987 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-0217 | 1.0 | 2.0 | 1.99974 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 2.0 | 0.01999735 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 57.8 | 2.0 | 115.58469 | mg | |
| Substance | 3 | Aluminum | Supplier | 7429-90-5 | 0.2 | 2.0 | 0.39995 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 1.8 | 2.0 | 3.59952 | mg | 6(c) Lead as an alloying element in copper containing up to 4% lead by weight |
| Material | 2 | Washer 2 - Silver Plating | | | | 2.0 | 0.536122 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 1.5 | 2.0 | 0.00804183 | mg | |
| Substance | 3 | Silver | Supplier | 7440-22-4 | 98.5 | 2.0 | 0.52808 | mg | |
| Material | 2 | Insulation - PTFE | | | | 2.0 | 499.9873772 | mg | |
| Substance | 3 | Ethene, 1,1,2,2-tetrafluoro-, homopolymer | Supplier | 9002-84-0 | 100.0 | 2.0 | 499.98738 | mg | |
| Material | 2 | Washer 1 - Silver Plating | | | | 2.0 | 0.3216732 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 1.5 | 2.0 | 0.0048251 | mg | |
| Substance | 3 | Silver | Supplier | 7440-22-4 | 98.5 | 2.0 | 0.31685 | mg | |
| Material | 2 | Washer 1 - Brass | | | | 2.0 | 469.9645452 | mg | |

| | | | | | | | | | |
|-----------|---|--------------------------------------------|---------------------|---------------|-------|-----|--------------|----|-------------------------------------------------------------------------------|
| Substance | 3 | Iron | Supplier | 7439-89-6 | 0.15 | 2.0 | 0.70495 | mg | |
| Substance | 3 | Phosphorus | Supplier | 7723-14-0 | 0.01 | 2.0 | 0.04699645 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 63.5 | 2.0 | 298.42749 | mg | |
| Substance | 3 | Zinc | Supplier | 7440-66-6 | 36.25 | 2.0 | 170.36215 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 2.0 | 0.04699645 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.08 | 2.0 | 0.37597 | mg | |
| Material | 2 | Washer 2 - Brass | | | | 2.0 | 250.0473008 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 0.49 | 2.0 | 1.22523 | mg | |
| Substance | 3 | Aluminum | Supplier | 7429-90-5 | 0.2 | 2.0 | 0.50009 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 57.8 | 2.0 | 144.52734 | mg | |
| Substance | 3 | Zinc | Supplier | 7440-66-6 | 38.7 | 2.0 | 96.76831 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-0217 | 1.0 | 2.0 | 2.50047 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 2.0 | 0.02500473 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 1.8 | 2.0 | 4.50085 | mg | 6(c) Lead as an alloying element in copper containing up to 4% lead by weight |
| Material | 2 | Spring - Steel | | | | 2.0 | 199.973506 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 11.0 | 2.0 | 21.99709 | mg | |
| Substance | 3 | Carbon | Supplier | 7440-44-0 | 0.08 | 2.0 | 0.15998 | mg | |
| Substance | 3 | Silicon | Supplier | 7440-21-3 | 1.0 | 2.0 | 1.99974 | mg | |
| Substance | 3 | Sulfur | Supplier | 7704-34-9 | 0.03 | 2.0 | 0.05999205 | mg | |
| Substance | 3 | Chromium | Supplier | 7440-47-3 | 19.0 | 2.0 | 37.99497 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 66.85 | 2.0 | 133.68229 | mg | |
| Substance | 3 | Phosphorus | Supplier | 7723-14-0 | 0.04 | 2.0 | 0.0799894 | mg | |
| Substance | 3 | Manganese | Supplier | 7439-96-5 | 2.0 | 2.0 | 3.99947 | mg | |
| Material | 2 | Shell - Silver Plating | | | | 2.0 | 0.6433464 | mg | |
| Substance | 3 | Silver | Supplier | 7440-22-4 | 98.5 | 2.0 | 0.6337 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 1.5 | 2.0 | 0.0096502 | mg | |
| Material | 2 | Shell - Brass | | | | 2.0 | 3899.9658768 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 1.8 | 2.0 | 70.19939 | mg | 6(c) Lead as an alloying element in copper containing up to 4% lead by weight |
| Substance | 3 | Zinc | Supplier | 7440-66-6 | 38.7 | 2.0 | 1509.28679 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 57.8 | 2.0 | 2254.18028 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 2.0 | 0.39 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 0.49 | 2.0 | 19.10983 | mg | |
| Substance | 3 | Aluminum | Supplier | 7429-90-5 | 0.2 | 2.0 | 7.79993 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-0217 | 1.0 | 2.0 | 38.99966 | mg | |
| Material | 2 | Body - Brass | | | | 2.0 | 4100.0466072 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 57.8 | 2.0 | 2369.82694 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-0217 | 1.0 | 2.0 | 41.00047 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 0.49 | 2.0 | 20.09023 | mg | |
| Substance | 3 | Zinc | Supplier | 7440-66-6 | 38.7 | 2.0 | 1586.71804 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 2.0 | 0.41 | mg | |
| Substance | 3 | Aluminum | Supplier | 7429-90-5 | 0.2 | 2.0 | 8.20009 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 1.8 | 2.0 | 73.80084 | mg | 6(c) Lead as an alloying element in copper containing up to 4% lead by weight |
| Material | 2 | Contact - Silver plating | | | | 2.0 | 0.4288976 | mg | |
| Substance | 3 | Silver | Supplier | 7440-22-4 | 98.5 | 2.0 | 0.42246 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 1.5 | 2.0 | 0.00643346 | mg | |
| Material | 2 | Body - Silver Plating | | | | 2.0 | 0.2144488 | mg | |
| Substance | 3 | Silver | Supplier | 7440-22-4 | 98.5 | 2.0 | 0.21123 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 1.5 | 2.0 | 0.00321673 | mg | |
| Material | 2 | Gasket - Silicon Rubber | | | | 2.0 | 100.0403652 | mg | |

| | | | | | | | | | |
|-----------|---|------------------------------------------------------------------|-------------------------------|------------|-------|-----|-------------|----|--|
| Substance | 3 | Siloxanes and Silicones, di-Me, Me vinyl, vinyl group-terminated | Supplier | 68083-18-1 | 77.5 | 2.0 | 77.53128 | mg | |
| Substance | 3 | Siloxanes and Silicones, di-Me, hydroxy-terminated | Supplier | 70131-67-8 | 1.0 | 2.0 | 1.0004 | mg | |
| Substance | 3 | Silica | Supplier | 7631-86-9 | 21.5 | 2.0 | 21.50868 | mg | |
| Material | 2 | Ferrule - Brass | | | | 2.0 | 999.9747544 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.08 | 2.0 | 0.79998 | mg | |
| Substance | 3 | Phosphorus | Supplier | 7723-14-0 | 0.01 | 2.0 | 0.09999748 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 2.0 | 0.09999748 | mg | |
| Substance | 3 | Zinc | Supplier | 7440-66-6 | 36.25 | 2.0 | 362.49085 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 63.5 | 2.0 | 634.98397 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 0.15 | 2.0 | 1.49996 | mg | |
| Sub-Item | 1 | STRAIN RELIEF (BLACK) PLYM | | | | 2.0 | 3000.0 | mg | |
| Material | 2 | small boot | | | | 2.0 | 3000.0 | mg | |
| Substance | 3 | Ethene, chloro-, homopolymer | Supplier | 9002-86-2 | 50.0 | 2.0 | 1500.0 | mg | |
| Substance | 3 | Limestone | Supplier | 1317-65-3 | 27.5 | 2.0 | 825.0 | mg | |
| Substance | 3 | Soybean oil, epoxidized | Supplier | 8013-07-8 | 1.99 | 2.0 | 59.7 | mg | |
| Substance | 3 | Calcium hydroxide (Ca(OH)2) | Supplier | 1305-62-0 | 0.01 | 2.0 | 0.3 | mg | |
| Substance | 3 | 1,2-Benzenedicarboxylic acid, 1,2-diisodecyl ester | Phthalates (DINP, DIDP, DNOP) | 26761-40-0 | 20.5 | 2.0 | 615.0 | mg | |
| Sub-Item | 1 | COAXIAL CABLE RG58C/U LEONI | | | | 1.0 | 37540.0 | mg | |
| Material | 2 | Jacket | | | | 1.0 | 13380.0 | mg | |
| Substance | 3 | Ethene, chloro-, homopolymer | Supplier | 9002-86-2 | 99.15 | 1.0 | 13266.27 | mg | |
| Substance | 3 | Carbon black | Supplier | 1333-86-4 | 0.85 | 1.0 | 113.73 | mg | |
| Material | 2 | Outer Shield | | | | 1.0 | 14050.0 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 100.0 | 1.0 | 14050.0 | mg | |
| Material | 2 | Tape | | | | 1.0 | 320.0 | mg | |
| Substance | 3 | Poly(oxy-1,2-ethanediyl oxy carbonyl-1,4-phenylene carbonyl) | Supplier | 25038-59-9 | 100.0 | 1.0 | 320.0 | mg | |
| Material | 2 | Inner Conductor | | | | 1.0 | 4550.0 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 100.0 | 1.0 | 4550.0 | mg | |
| Material | 2 | Insulation | | | | 1.0 | 5240.0 | mg | |
| Substance | 3 | Ethene, homopolymer | Supplier | 9002-88-4 | 100.0 | 1.0 | 5240.0 | mg | |