

Power line chokes

Current-compensated E core double chokes 250 V AC, 0.3 ... 1.8 A, 3.3 ... 100 mH, +40 °C

 Series/Type:
 B82731T

 Date:
 July 2012

© EPCOS AG 2015. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.



B82731T

Power line chokes

Current-compensated E core double chokes

Rated voltage 250 V AC Rated current 0.3 ... 1.8 A Rated inductance 3.3 ... 100 mH

Construction

- Current-compensated double choke
- Closed E ferrite core
- Closed PET coil former with 4 sections (UL 94 V-0)
- Without encapsulation
- 4-section winding
- Clearances > 2.5 mm, creepage distances > 3 mm

Features

- High resonance frequency due to 2-section winding
- High pulse strength
- Low whirring noise
- Approx. 2% stray inductance for symmetrical interference suppression
- Suitable for wave soldering
- Design complies with EN 60938-2 (VDE 0565-2) and UL 1283
- RoHS-compatible

Applications

- Suppression of common-mode interferences
- Electronic ballasts for lamps
- Switch-mode power supplies for consumer electronics

Terminals

- Pins 0.64 × 0.64 (mm)
- Lead spacing 10 × 10 (mm)

Marking

Manufacturer, rated current, rated inductance, approvals, pin 1 marking, ordering code, date of manufacture (YYWW), production place

Delivery mode

Blister tray in cardboard box





怂TDK


Power line chokes


Current-compensated E core double chokes

Dimensional drawing and pin configuration










IND0359-Z-E

Tolerances to ISO 2768-C unless otherwise noted. Dimensions in mm



ø1.45±0.05



Recommended hole arrangement (view in mounting direction) IND0361-L-E



B82731T



Power line chokes

Current-compensated E core double chokes

Technical data and measuring conditions

Rated voltage V _R	250 V AC (50/60 Hz)
Test voltage V _{test}	1500 V AC, 2 s (line/line)
Rated temperature T _R	+40 °C
Rated current I _R	Referred to 50 Hz and rated temperature
Rated inductance L _R	Measured with Agilent 4284A at 10 kHz, 0.1 mA, +20 °C Inductance is specified per winding.
Inductance tolerance	−30/+50% at +20 °C
Inductance decrease $\Delta L/L_0$	< 10% at DC magnetic bias with I _R , +20 $^\circ$ C
Stray inductance L _{stray,typ}	Measured with Agilent 4284A at 10 kHz, 5 mA, +20 °C, typical values
DC resistance R _{typ}	Measured at +20 °C, typical values, specified per win- ding
Solderability (lead-free)	Sn96.5Ag3.0Cu0.5: +(245 ±5) °C, (3 ±0.3) s Wetting of soldering area ≥ 95% (to IEC 60068-2-20, test Ta)
Resistance to soldering heat (wave soldering)	+(260 ±5) °C, (10 ±1) s (to IEC 60068-2-20, test Tb)
Climatic category	40/125/56 (to IEC 60068-1)
Storage conditions (packaged)	–25 °C … +40 °C, ≤ 75% RH
Weight	Approx. 15 g
Approvals	EN 60938-2, UL 1283

⇔TDK

Power line chokes

Current-compensated E core double chokes

I _R	L _R	L _{stray,typ}	R _{typ}	Ordering code	Approvals	
A	mH	μH	mΩ		à	71
0.30	100	2000	6600	B82731T2301A020	×	×
0.35	68	1300	4400	B82731T2351A020	×	×
0.45	47	950	2800	B82731T2451A020	×	×
0.55	39	800	2200	B82731T2551A020	×	×
0.65	27	550	1600	B82731T2651A020	×	×
0.8	15	300	950	B82731T2801A020	×	×
1.0	10	200	630	B82731T2102A020	×	×
1.3	6.8	140	370	B82731T2132A020	×	×
1.8	3.3	65	200	B82731T2182A020	×	×


Characteristics and ordering codes

× = approval granted


Sample kit available. Ordering code: B82731X002 For more information refer to chapter "Sample kits".

Impedance |Z| versus frequency f

measured with windings in parallel at +20 °C typical values



Current derating I_{op}/I_R versus ambient temperature T_A



B82731T

Cautions and warnings

Current-compensated ring core double chokes

- Please note the recommendations in our Inductors data book (latest edition) and in the data sheets.
 - Particular attention should be paid to the derating curves given there. Derating must be applied in case the ambient temperature in the application exceeds the rated temperature of the component.
 - Ensure the operation temperature (which is the sum of the ambient temperature and the temperature rise caused by losses / self-heating) of the component in the application does not exceed the maximum value specified in the climatic category.
 - The soldering conditions should also be observed. Temperatures quoted in relation to wave soldering refer to the pin, not the housing.
- If the components are to be washed varnished it is necessary to check whether the washing varnish agent that is used has a negative effect on the wire insulation, any plastics that are used, or on glued joints. In particular, it is possible for washing varnish agent residues to have a negative effect in the long-term on wire insulation.

Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g. ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.

- The following points must be observed if the components are potted in customer applications:
 - Many potting materials shrink as they harden. They therefore exert a pressure on the plastic housing or core. This pressure can have a deleterious effect on electrical properties, and in extreme cases can damage the core or plastic housing mechanically.
 - It is necessary to check whether the potting material used attacks or destroys the wire insulation, plastics or glue.
 - The effect of the potting material can change the high-frequency behaviour of the components.
- Ferrites are sensitive to direct impact. This can cause the core material to flake, or lead to breakage of the core.
- Even for customer-specific products, conclusive validation of the component in the circuit can only be carried out by the customer.



The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.

We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

- 6. Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.
- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EPCOS / TDK:

<u>B82731T2102A20</u> <u>B82731T2132A20</u> <u>B82731T2182A20</u> <u>B82731T2801A20</u> <u>B82731T2301A20</u> <u>B82731T2351A20</u> B82731T2451A20 B82731T2551A20 B82731T2651A20