

Emparro Power Supply 3-PHASE

IN: 360 - 500VAC OUT: 24-28V/5ADC


INPUT: 3 × 324...572 V AC / 450...745 V DC

OUTPUT: 24...28 V DC

Current: 5 A

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Input

Input voltage	3 × 324...572 V AC/450...745 V DC
Input current	0.45 A (3 × 360 V AC)
Inrush current after 1 ms	max. 9.5 A
Power factor	0.61 (3 × 400 V AC)
Frequency	50...60 Hz
Input fuse (internal)	3 × 6.3 A (T)

General data

Standards	EN 60950-1, EN 61204-3, EN 55011 B, EN 61000-3-2, SEMI F47
Relative humidity	5...95 %, no condensation
Efficiency	92.5 % (3 × 400 V AC); 91.8 % (3 × 480 V AC)
Dimensions H × W × D	143×50×143 mm
Mounting method	DIN-rail mountable TH35 (EN 60715)
Temperature range	-40...+70 °C, ...+70 °C derating (storage temperature -40...+85 °C)

Output

Output voltage	24 V DC (SELV), ±1 %; 24...28 V adjustable
Power Boost	I _{out} N × 150 % (min. 5 s)
Output current	3.7 A (70 °C); 5.0 A (60 °C); 6.0 A (45 °C)
Mains failure bridging time	min. 25 ms (3 × 360 V AC); 5 A (24 V DC)
Ripple	max. 20 mV _{rms}
Spikes	max. 50 mV p-p
Unit protection	short circuit and overload protected, permanently by 20 % (to 45 °C)
LED display	LED (green): OK; LED (red): overload, overheating or short-circuit
Parallel usage/serial usage	max. 3 units

Commercial data

country of origin	CH
customs tariff number	85044090
EAN	4048879538534
minimum order quantity	1