

M8 PCB Adapter 4pol Pcod. female



Image is for illustration purposes only. Please refer to product description.

Part number	21 02 341 2419
Specification	M8 PCB Adapter 4pol Pcod. female
HARTING eCatalogue	https://b2b.harting.com/21023412419

Identification

Category	Connectors
Series	Circular connectors M8
Element	PCB connector
Specification	Straight

Version

Termination method	Reflow soldering termination (THR)
Gender	Female
Shielding	Shielded
Number of contacts	4
Coding	P-coding
Details	Order housings separately
Pack contents	25 pieces in a carton box

Technical characteristics

Rated current	4 A
Rated voltage	60 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Insulation resistance	>10 ⁸ Ω



Pushing Performance

Technical characteristics

Contact resistance	≤10 mΩ
Ambient temperature	-40 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 61076-2-114
----------------	-----------------

Commercial data

Packaging size	25
Net weight	6 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27460201 PCB connector (board connector)