

Vishay Siliconix

Improved Quad CMOS Analog Switches

DESCRIPTION

The DG211B, DG212B analog switches are highly improved versions of the industry-standard DG211, DG212. These devices are fabricated in Vishay Siliconix' proprietary silicon gate CMOS process, resulting in lower on-resistance, lower leakage, higher speed, and lower power consumption.

These quad single-pole single-throw switches are designed for a wide variety of applications in telecommunications, instrumentation, process control, computer peripherals, etc. An improved charge injection compensation design minimizes switching transients. The DG211B and DG212B can handle up to \pm 22 V, and have an improved continuous current rating of 30 mA. An epitaxial layer prevents latchup.

All devices feature true bi-directional performance in the on condition, and will block signals to the supply levels in the off condition.

The DG211B is a normally closed switch and the DG212B is a normally open switch. (see Truth Table.)

FEATURES

- ± 22 V supply voltage rating
- TTL and CMOS compatible logic
- Low on-resistance $R_{DS(on)}$: 50 Ω
- Low leakage I_{D(on)}: 20 pA
- Single supply operation possible
- Extended temperature range
- Fast switching t_{ON}: 120 ns
- Low charge injection Q: 1 pC


BENEFITS

- · Wide analog signal range
- Simple logic interface
- Higher accuracy
- Minimum transients
- Reduced power consumption
- Superior to DG211, DG212
- Space savings (TSSOP)

APPLICATIONS

- Industrial instrumentation
- Test equipment
- Communications systems
- Disk drives
- Computer peripherals
- Portable instruments
- · Sample-and-hold circuits

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION



TRUTH TABLE					
Logic	DG211B	DG212B			
0	ON	OFF			
1	OFF	ON			

 $\begin{array}{l} \text{Logic "0"} \leq 0.8 \ \text{V} \\ \text{Logic "1"} \geq 2.4 \ \text{V} \end{array}$

* Pb containing terminations are not RoHS compliant, exemptions may apply.



Vishay Siliconix



ORDERING INFORMATION						
Temp. Range	Package	Standard Part Number	Lead (Pb)-free Part Number			
	16-Pin Plastic DIP	DG211BDJ	DG211BDJ-E3			
		DG212BDJ	DG212BDJ-E3			
- 40 °C to 85 °C	16-Pin Narrow SOIC	DG211BDY DG211BDY-T1	DG211BDY-E3 DG211BDY-T1-E3			
	10-Fill Nation SOIC	DG212BDY DG212BDY-T1	DG212BDY-E3 DG212BDY-T1-E3			
	16-Pin TSSOP	DG211BDQ DG211BDQ-T1	DG211BDQ-E3 DG211BDQ-T1-E3			
		DG212BDQ DG212BDQ-T1	DG212BDQ-E3 DG212BDQ-T1-E3			

ABSOLUTE MAXIMUM RATINGS (T _A = 25 °C, unless otherwise noted)						
Parameter		Limit	Unit			
Voltages Referenced, V+ to V-		44				
GND		25 V				
Digital Inputs ^a , V _S , V _D		(V-) - 2 to (V+) + 2 or 30 mA, whichever occurs first	`			
Current (Any terminal)		30	mA			
Peak Current, S or D (Pulsed at 1	ns, 10 % duty cycle max.)	100				
Storage Temperature		- 65 to 125	°C			
Power Dissipation (Package) ^b	16-Pin Plastic DIP ^c	470	mW			
	16-Pin Narrow SOIC and TSSOP ^d	640	mvv			

Notes:


a. Signals on S_X , D_X , or IN_X exceeding V+ or V- will be clamped by internal diodes. Limit forward diode current to maximum current ratings.

b. All leads welded or soldered to PC board.

c. Derate 6.5 mW/°C above 75 °C.

d. Derate 7.6 mW/°C above 75 °C.

SCHEMATIC DIAGRAM (Typical Channel)







DG211B, DG212B Vishay Siliconix

SPECIFICATIONS							
		Test Conditions Unless Otherwise Specified		D Suffix - 40 °C to 85 °C			
Parameter	Symbol	V+ = 15 V, V- = - 15 V V _L = 5 V, V _{IN} = 2.4 V, 0.8 V ^e	Temp. ^a	Min. ^b	Typ. ^c	Max. ^b	Uni
Analog Switch				•	•	•	
Analog Signal Range ^d	V _{ANALOG}		Full	- 15		15	V
Drain-Source On-Resistance	R _{DS(on)}	V _D = ± 10 V, I _S = 1 mA	Room Full		45	85 100	Ω
R _{DS(on)} Match	$\Delta R_{DS(on)}$		Room		2		
Source Off Leakage Current	I _{S(off)}	$V_{S} = \pm 14 \text{ V}, V_{D} = \pm 14 \text{ V}$	Room Full	- 0.5 - 5	± 0.01	0.5 5	
Drain Off Leakage Current	I _{D(off)}	$V_{D} = \pm 14 \text{ V}, V_{S} = \pm 14 \text{ V}$	Room Full	- 0.5 - 5	± 0.01	0.5 5	nA
Drain On Leakage Current	I _{D(on)}	$V_{S} = V_{D} = \pm 14 V$	Room Full	- 0.5 - 10	± 0.02	0.5 10	
Digital Control							
Input Voltage High	V _{INH}		Full	2.4			v
Input Voltage Low	V _{INL}		Full			0.8	v
Input Current	I _{INH} or I _{INL}	V _{INH} or V _{INL}	Full	- 1		1	μA
Input Capacitance	C _{IN}		Room		5		pF
Dynamic Characteristics							
Turn-On Time	t _{ON}	V _S = 10 V	Room			300	ns
Turn-Off Time	t _{OFF}	see figure 2	Room			200	113
Charge Injection	Q	${\sf C}_{\sf L}$ = 1000 pF, ${\sf V}_{\sf gen}$ = 0 V, ${\sf R}_{\sf gen}$ = 0 Ω	Room		1		pC
Source-Off Capacitance	C _{S(off)}	V _S = 0 V, f = 1 MHz	Room		5		
Drain-Off Capacitance	C _{D(off)}	$v_{\rm S} = 0$ v, $i = 1$ with z	Room		5		pF
Channel-On Capacitance	C _{D(on)}	$V_D = V_S = 0 V$, f = 1 MHz	Room		16		
Off Isolation	OIRR	$C_{L} = 15 \text{ pF}, \text{ R}_{L} = 50 \Omega,$	Room		90		dB
Channel-to-Channel Crosstalk	X _{TALK}	$V_{S} = 1 V_{RMS}$, f = 100 kHz	Room		95		uL
Power Supply							
Positive Supply Current	l+	V _{IN} = 0 or 5 V	Room Full			10 50	
Negative Supply Current	I-	V IN = 0 01 0 V	Room Full	- 10 - 50			μA
Logic Supply Current	ΙL		Room Full			10 50	
Power Supply Range for Continuous Operation	V _{OP}		Full	± 4.5		± 22	V

Vishay Siliconix



SPECIFICATIONS (for Single Supply)							
		Test Conditions Unless Otherwise Specified		D Suffix - 40 °C to 85 °C			
Parameter	Symbol	$V_{+} = 12 V, V_{-} = 0 V$ $V_{L} = 5 V, V_{IN} = 2.4 V, 0.8 V^{e}$	Temp. ^a	Min. ^b	Typ. ^c	Max. ^b	Unit
Analog Switch							
Analog Signal Range ^d	V _{ANALOG}		Full	0		12	V
Drain-Source On-Resistance	R _{DS(on)}	$V_{D} = 3 V, 8 V, I_{S} = 1 mA$	Room Full		90	160 200	Ω
Dynamic Characteristics							
Turn-On Time	t _{ON}	V _S = 8 V	Room			300	
Turn-Off Time	t _{OFF}	see figure 1	Room			200	ns
Charge Injection	Q	C_L = 1 nF, V_{gen} = 6 V, R_{gen} = 0 Ω	Room		4		рС
Power Supply		· · ·					
Positive Supply Current	l+		Room Full			10 50	
Negative Supply Current	I-	$V_{IN} = 0 \text{ or } 5 \text{ V}$	Room Full	- 10 - 50			μA
Logic Supply Current	١L		Room Full			10 50	
Power Supply Range for Continuous Operation	V _{OP}		Full	+ 4.5		+ 25	V

Notes:

a. Room = 25 $\,^{\circ}$ C, Full = as determined by the operating temperature suffix.

b. The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this data sheet.


c. Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.

d. Guaranteed by design, not subject to production test.

e. V_{IN} = input voltage to perform proper function.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


TYPICAL CHARACTERISTICS ($T_A = 25 \text{ °C}$, unless otherwise noted)








Vishay Siliconix

TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)











Leakage Currents vs. Analog Voltage





Q_S, Q_D - Charge Injection vs. Analog Voltage




Vishay Siliconix

TEST CIRCUITS










Figure 3. Off Isolation







Figure 4. Channel-to-Channel Crosstalk





 ΔV_O = measured voltage error due to charge injection The charge injection in coulombs is Q = C_L x ΔV_O

Figure 5. Charge Injection







APPLICATIONS





Figure 6. Sample-and-Hold





Document Number: 70040 S11-0179-Rev. J, 07-Feb-11

Vishay Siliconix



APPLICATIONS




Figure 8. A Precision Amplifier with Digitally Programable Input and Gains


Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <u>www.vishay.com/ppg?70040</u>.




Package Information Vishay Siliconix

SOIC (NARROW): 16-LEAD


JEDEC Part Number: MS-012









PDIP: 16-LEAD








	MILLIN	IETERS	INC	HES	
Dim	Min	Max	Min	Max	
Α	3.81	5.08	0.150	0.200	
A ₁	0.38	1.27	0.015	0.050	
В	0.38	0.51	0.015	0.020	
B ₁	0.89	1.65	0.035	0.065	
С	0.20	0.30	0.008	0.012	
D	18.93	21.33	0.745	0.840	
Е	7.62	8.26	0.300	0.325	
E ₁	5.59	7.11	0.220	0.280	
e ₁	2.29	2.79	0.090	0.110	
e _A	7.37	7.87	0.290	0.310	
L	2.79	3.81	0.110	0.150	
Q 1	1.27	2.03	0.050	0.080	
S	0.38	1.52	.015	0.060	
ECN: S-03946—Rev. D, 09-Jul-01 DWG: 5482					




Package Information

Vishay Siliconix

TSSOP: 16-LEAD






	DIMENSIONS IN MILLIMETERS					
Symbols	Min	Nom	Max			
A	-	1.10	1.20			
A1	0.05	0.10	0.15			
A2	-	1.00	1.05			
В	0.22	0.28	0.38			
С	-	0.127	-			
D	4.90	5.00	5.10			
E	6.10	6.40	6.70			
E1	4.30	4.40	4.50			
е	-	0.65	-			
L	0.50	0.60	0.70			
L1	0.90	1.00	1.10			
у	-	-	0.10			
θ1	0°	3°	6°			
ECN: S-61920-Rev. D, 23-Oct-06 DWG: 5624						



PAD Pattern

Vishay Siliconix

RECOMMENDED MINIMUM PAD FOR TSSOP-16



Recommended Minimum Pads Dimensions in inches (mm)


Revision: 02-Sep-11

Application Note 826

Vishay Siliconix



RECOMMENDED MINIMUM PADS FOR SO-16



Recommended Minimum Pads Dimensions in Inches/(mm)

Return to Index

www.vishay.com 24



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.