



Fuse-link, high speed, 12 A, AC 240 V, DC 150 V, 200 kA, BS88, 9 x 47 mm, aR, BS



Part no. **12AMP 240V AC BS88 FUSE**  
 Catalog No. **12LCT**

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	12
Rated voltage			AC 240 V DC 150 V
Construction size			BS88
Size			9 x 47 mm
Utilization category			aR
Breaking Capacity		kA	200
usable for size/applications			DC common bus, DC drives, power converters/rectifiers and reduced voltage starters
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-4 IEC 60269-4
Optional accessories			fuse-holder BH-0111

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	12
Rated voltage		V	240
Voltage type			AC/DC
Rated switching capacity		kA	200
Utilization category			aR (accompanied semiconductor protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

### Additional product information (links)

Product datasheet (web)	<a href="http://www.cooperindustries.com/content/public/en/bussmann/electrical/products/high_speed_/british/bs_88_240v.html">http://www.cooperindustries.com/content/public/en/bussmann/electrical/products/high_speed_/british/bs_88_240v.html</a>
-------------------------	---