

SEE SHEET 2 FOR CONTACT DIMENSION DETAILS

SPECIFICATIONS:

ELECTRICAL:

INSULATION RESISTANCE: DIELECTRIC WITHSTANDING VOLTAGE: WORKING VOLTAGE: OPERATING TEMPERATURE: POWER CONTACT RESISTANCE: SIGNAL CONTACT RESISTANCE: POWER CONTACT AMPERAGE: SIGNAL CONTACT AMPERAGE:

MECHANICAL:

CONTACT INSERTION FORCE: CONTACT SEPARATION FORCE:


MATERIALS:

CONTACTS: INSULATOR:

SHELL: HARDWARE: 5 GOhms MIN. 1000 VAC FOR 1 MIN 250V -55°C TO +125°C 2.0 mOhms MAX. 10 mOhms MAX. SEE P/N KEY 5 AMPS

4.5 Kg MAX. 0.3 Kg MIN.

COPPER ALLOY, GOLD FLASH PBT UL94V-0 RATED 230°C PROCESS TEMP. NICKEL PLATED STEEL NICKEL PLATED BRASS



ROHS COMPLIANT DO NOT SCALE FROM DRAWING UNITS = inches [mm] DRAWN: SCALE: SHEET OF REV THESE DRAWINGS AND SPECIFICATIONS ARE NorComp M. SIGMON THE PROPERTY OF NorComp AND SHALL NOT NTS 4 1 3 BE REPRODUCED, COPIED OR USED AS THE DWG NO. DATE: BASIS FOR THE MANUFACTURE OR SALE OF 681M9W4103LYYY 07/19/2013 APPARATUS WITHOUT WRITTEN PERMISSION.

