

PRODUCT-DETAILS

TY125-40-100

CABLE TIE 30LB 5.5IN NATURAL NYL



General Information

Extended Product Type	TY125-40-100
Product ID	7TAG054360R0125
EAN	5414363060543
Catalog Description	CABLE TIE 30LB 5.5IN NATURAL NYL
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 141.48mm (5.57 Inches), Width of 3.556mm (0.140 Inches), Thickness of 1.17mm (0.046 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), UL Recognized Tensile Strength Rating of 135 Newtons (30 Pounds), 100 Pack

Ordering

E-Number (Finland)	1370040
EAN	5414363060543
UPC	786210918099

Dimensions

Product Net Width	0.14 in 3.556 mm
Product Net Depth / Length	5.57 in 141.48 mm

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	5 in 127 mm
Package Level 1 Height	1.7 in 43 mm
Package Level 1 Depth / Length	9 in 229 mm
Package Level 2 Units	1000 piece
Package Level 2 Width	13.25 in 337 mm
Package Level 2 Height	10.5 in 267 mm
Package Level 2 Depth / Length	17 in 432 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	1.25 in 31.75 mm
Color	Natural
Effective Date	19930820
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	CATAMOUNT FASTENING PRODUCTS
Product Type	General Purpose
Standards	UL E49405
Tensile Strength	40 lb 180 N
Thickness	0.046 in 1.17 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY125-40-100
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY125-40-100

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

