High Isolation Gate Drive Transformers

PH9400.XXXNL and PH9400.XXXANL - SMT











Sidecar package with 12mm creepage

Up to 5000Vrms gate to drive isolation

1000Vrms continuous isolation between windings

Up to 8W of Driver Power

Patented: US Patent 9,646,755

Electrical Specifications @ 25°C - Operating Temperature -40°C to +125°C										
Part Number	Turns Ratio	ET (1-4) (V * μsec MAX)	Core Loss Factor K1	Primary Inductance (1-4) (mH +/-35%)	Leakage Inductance Drive to Gate (µH MAX)	Parasitic Capacitance Drive to Gate (pF MAX)	DCR Drive (1-4) (Ω MAX)	(5-6) (7-8) (Ω MAX)	Hi-Pot	
									Drive-Gate (Vrms)	Gate-Gate (Vrms)
PH9400.XXXNL - Basic Insulation 600Vrms continuous isolation										
PH9400.111NL	1:1:1	315	0.67	4.5	5.0	60	1.8	2.5	4000	1500
PH9400.566NL	5:6:6	315	0.67	4.5	3.5	60	1.8	3.0	4000	1500
PH9400.122NL	1:2:2	250	0.84	2.88	3.5	60	1.5	4.2	4000	1500
PH9400.655NL	6:5:5	375	0.56	6.48	5.3	60	2.2	2.5	4000	1500
PH9400.211NL	2:1:1	375	0.56	6.48	8.0	60	2.2	1.6	4000	1500
PH9400.XXXANL - Reinforced Insulation 1000Vrms continuous isolation										
PH9400.111ANL	1:1:1	160	1.32	1.21	2.5	45	0.9	0.9	5000	2000
PH9400.566ANL	5:6:6	155	1.36	1.12	3.0	45	0.9	1.0	5000	2000
PH9400.233ANL	2:3:3	125	1.68	0.72	2.0	45	0.7	1.0	5000	2000
PH9400.655ANL	6:5:5	185	1.14	1.62	3.0	45	1.0	0.9	5000	2000
PH9400.211ANL	2:1:1	185	1.14	1.62	3.5	45	1.0	0.55	5000	2000

Notes:

- The max ET is calculated to limit the core loss and temperature rise at 100KHz based on a bipolar flux swing of 2100Ga Peak. This value needs to be derated for higher frequencies using the temperature rise calculation.
- 2. The temperature rise of the component is calculated based on the total core loss and copper loss:
 - A. To calculate total copper loss (W), use the following formula: Copper Loss (W) = Irms² * (DCR_Drive + (# of Gates) * DCR_Gates)
 - B. To calculate total core loss (W), use the following formula: Core Loss (W) = 5.1E-10 * (Frequency in kHz)^{1,42} * (K1 * ET)^{2,5} Where ET = (V * Duty Cycle) / Frequency
 - C. To calculate temperature rise, use the following formula: Temperature Rise (°C) = 71 * (Core Loss(W) + Copper Loss (W))
- Continuous isolation voltage confirmed by 125°C/1000hrs accelerated aging with the bias voltage applied between gate and drive windings.

- ANL versions, which use triple insulated wire on both the drive and gate windings, are compliant with IEC 60950, IEC 61558, IEC 61010 & IEC 60601 for reinforced insulation.
 - NL versions, which use triple insulated wire on just the drive winding, comply with basic insulation requirements.
- 12mm package creepage distance satisfies IEC60950-1 & IEC61558-1/-2-16 reinforced insulation requirements for working voltage to 600Vrms max, OVC II, Pollution Degree 2 and altitude up to 2000m.
- 6. Unless otherwise specified, all testing is made at 100kHz, 0.1VAC.
- Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the part number (i.e. PH9400.111NL becomes PH9400.111NLT). Pulse complies to industry standard tape and reel specification EIA481.


High Isolation Gate Drive Transformers

PH9400.XXXNL and PH9400.XXXANL - SMT




Mechanicals Schematics


PH9400.XXXNL and PH9400.XXXANL



PA9400.XXXNL



PA9400.XXXANL



 Weight
 2.5 grams

 Tape & Reel
 150/Reel

 Tray
 80/tray

Dimension: Inches

Unless otherwise specified, all tolerances are $\pm \frac{.010}{0.75}$

For More Information

Pulse Worldwide Headquarters

15255 Innovation Drive Ste 100 San Diego, CA 92128 U.S.A.

Pulse Europe

Pulse Electronics GmbH Am Rottland 12 58540 Meinerzhagen Germany

Pulse China Headquarters

Pulse Electronics (ShenZhen) CO., LTD D708, Shenzhen Academy of Aerospace Technology, The 10th Keji South Road, Nanshan District, Shenzhen, P.R. China 518057

Pulse North China

Room 2704/2705 Super Ocean Finance Ctr. 2067 Yan An Road West Shanghai 200336 China

Pulse South Asia

3 Fraser Street 0428 DUO Tower Singapore 189352

Pulse North Asia

1F., No.111 Xiyuan Road Zhongli District Taoyuan City 32057 Taiwan (R.O.C)

Tel: 858 674 8100 Fax: 858 674 8262 Tel: 49 2354 777 100 Fax: 49 2354 777 168 Tel: 86 755 33966678 Fax: 86 755 33966700

Tel: 86 21 62787060 Fax: 86 2162786973 Tel: 65 6287 8998 Fax: 65 6280 0080 Tel: 886 3 4356768 Fax: 886 3 4356820

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2020. Pulse Electronics, Inc. All rights reserved.