LL103A, LL103B, LL103C

Vishay Semiconductors

Small Signal Schottky Diode

- Integrated against static protection ring discharge
- Low capacitance
- Low leakage current
- Low forward voltage drop
- AEC-Q101 qualified
- · Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- HF-detector
- Protection circuit
- Small battery charger
- AC/DC / DC/DC converters

PARTS TABLE						
PART	TYPE DIFFERENTIATION	ORDERING CODE	CIRCUIT CONFIGURATION	REMARKS		
LL103A	V _R = 40 V	LL103A-GS08 or LL103A-GS18	Single	Tape and reel		
LL103B	V _R = 30 V	LL103B-GS08 or LL103B-GS18	Single	Tape and reel		
LL103C	V _R = 20 V	LL103C-GS08 or LL103C-GS18	Single	Tape and reel		

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	VALUE	UNIT		
		LL103A	V _R	40	V		
Reverse voltage		LL103B	V _R	30	V		
		LL103C	V _R	20	V		
Forward continuous current			I _{FAV}	200	mA		
Peak forward surge current	t_p = 300 µs, square pulse		I _{FSM}	15	А		
Power dissipation			P _{tot}	400	mW		

THERMAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT		
Thermal resistance junction to ambient air	On PC board 50 mm x 50 mm x 1.6 mm	R _{thJA}	250	K/W		
Junction temperature		Тj	125	°C		
Storage temperature range		T _{stg}	-65 to +150	°C		

For technical questions within your region: DiodesAmericas@vishav.com, DiodesAsia@vishav.com, DiodesEurope@vishav.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000





RoHS COMPLIANT



www.vishay.com

DESIGN SUPPORT TOOLS click logo to get started



MECHANICAL DATA

Case: MiniMELF (SOD-80)

Weight: approx. 31 mg

Cathode band color: black

Packaging codes/options:

GS18/10K per 13" reel (8 mm tape), 10K/box GS08/2.5K per 7" reel (8 mm tape), 12.5K/box

Rev. 1.8, 01-Jun-17



LL103A, LL103B, LL103C

Vishay Semiconductors

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
	I _R = 50 μA	LL103A	V _(BR)	40			V
Reverse breakdown voltage		LL103B	V _(BR)	30			V
		LL103C	V _(BR)	20			V
	V _R = 30 V	LL103A	I _R			5	μA
Leakage current	V _R = 20 V	LL103B	I _R			5	μA
	V _R =10 V	LL103C	I _R			5	μA
	I _F = 20 mA		VF			370	mV
Forward voltage drop	I _F = 200 mA		V _F			600	mV
Diode capacitance	$V_R = 0 V$, f = 1 MHz		CD		50		pF
Reverse recovery time	$I_F = I_R = 50 \text{ mA to } 200 \text{ mA},$ recover to 0.1 I_R		t _{rr}		10		ns

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Forward Current vs. Forward Voltage




Fig. 2 - Forward Current vs. Forward Voltage




Fig. 3 - Reverse Current vs. Junction Temperature




Fig. 4 - Diode Capacitance vs. Reverse Voltage

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



LL103A, LL103B, LL103C

Vishay Semiconductors





Fig. 5 - Typical Non-Repetitive Forward Surge Current vs. Pulse Width

PACKAGE DIMENSIONS in millimeters (inches): MiniMELF (SOD-80)



Rev. 1.8, 01-Jun-17 Document Number: 85630 3 For technical questions within your region: DiodesAmericas@vishav.com, DiodesAsia@vishav.com, DiodesEurope@vishav.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

LL103B-GS08 LL103A-GS08 LL103C-GS08 LL103A-GS18 LL103B-GS18 LL103C-GS18