

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild guestions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



August 2014

FDP39N20 / FDPF39N20 N-Channel UniFETTM MOSFET 200 V, 39 A, 66 m Ω

Features

- $R_{DS(on)}$ = 66 m Ω (Max.) @ V_{GS} = 10 V, I_D = 19.5 A
- Low Gate Charge (Typ. 38 nC)
- Low C_{rss} (Typ. 57 pF)
- 100% Avalanche Tested

Applications

- PDP TV
- Lighting
- · Uninterruptible Power Supply
- · AC-DC Power Supply

Description

UniFETTM MOSFET is Fairchild Semiconductor's high voltage MOSFET family based on planar stripe and DMOS technology. This MOSFET is tailored to reduce on-state resistance, and to provide better switching performance and higher avalanche energy strength. This device family is suitable for switching power converter applications such as power factor correction (PFC), flat panel display (FPD) TV power, ATX and electronic lamp ballasts.



Absolute Maximum Ratings T_C = 25°C unless otherwise noted.

Symbol		Parameter		FDP39N20	FDPF39N20 / FDPF39N20TLDTU	Unit
V_{DSS}	Drain-Source Voltage		2	V		
I _D	Drain Current	- Continuous (T _C = 25°C) - Continuous (T _C = 100°C)		39 23.4	39 * 23.4 *	A A
I _{DM}	Drain Current	- Pulsed	(Note 1)	156	156 *	Α
V _{GSS}	Gate-Source voltage			1	V	
E _{AS}	Single Pulsed Avalanche Energy		(Note 2)	3	mJ	
I _{AR}	Avalanche Current		(Note 1)		Α	
E _{AR}	Repetitive Avalanche Energy		(Note 1)	25.1		mJ
dv/dt	Peak Diode Recovery dv/dt		(Note 3)	4.5		V/ns
P _D	Power Dissipation	(T _C = 25°C) - Derate Above 25°C		251 2.0	37 0.29	W W/°C
T _{J,} T _{STG}	Operating and Storage Temperature Range		-55 to +150		°C	
T _L	Maximum Lead Temperature for Soldering, 1/8" from Case for 5 Seconds			300		

^{*} Drain current limited by maximum junction temperature.

Thermal Characteristics

Symbol	Parameter	FDP39N20	FDPF39N20 / FDPF39N20TLDTU	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case, Max.	0.5	3.4	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient, Max.	62.5	62.5	

Package Marking and Ordering Information

Part Number	Top Mark	Package	Packing Method	Reel Size	Tape Width	Quantity
FDP39N20	FDP39N20	TO-220	Tube	N/A	N/A	50 units
FDPF39N20	FDPF39N20	TO-220F	Tube	N/A	N/A	50 units
FDPF39N20TLDTU	FDPF39N20T	TO-220F (L-formed)	Tube	N/A	N/A	50 units

$\textbf{Electrical Characteristics} \quad \textbf{T}_{C} = 25^{\circ} \text{C unless otherwise noted}.$

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
Off Charac	cteristics			•	•	
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} = 0 V, I _D = 250 μA				V
ΔBV _{DSS} / ΔT _J	Breakdown Voltage Temperature Coefficient	I _D = 250 μA, Referenced to 25°C		0.2		V/°C
I _{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 200 \text{ V}, V_{GS} = 0 \text{ V}$ $V_{DS} = 160 \text{ V}, T_{C} = 125^{\circ}\text{C}$			1 10	μA μA
I _{GSSF}	Gate-Body Leakage Current, Forward	V _{GS} = 30 V, V _{DS} = 0 V			100	nA
I _{GSSR}	Gate-Body Leakage Current, Reverse	V _{GS} = -30 V, V _{DS} = 0 V			-100	nA
On Charac	teristics			•		
V _{GS(th)}	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$	3.0		5.0	V
R _{DS(on)}	Static Drain-Source On-Resistance	V _{GS} = 10 V, I _D = 19.5 A		0.056	0.066	Ω
9 _{FS}	Forward Transconductance	V _{DS} = 40 V, I _D = 19.5 A		28.5		S
Dynamic C	Characteristics		1		ı	
C _{iss}	Input Capacitance	V _{DS} = 25 V, V _{GS} = 0 V,		1640	2130	pF
C _{oss}	Output Capacitance	f = 1.0 MHz		400	520	pF
C _{rss}	Reverse Transfer Capacitance			57	85	pF
Switching	Characteristics					
t _{d(on)}	Turn-On Delay Time	V _{DD} = 100 V, I _D = 39 A,		30	70	ns
t _r	Turn-On Rise Time	$V_{GS} = 10 \text{ V}, R_G = 25 \Omega$		160	330	ns
t _{d(off)}	Turn-Off Delay Time		/	150	310	ns
t _f	Turn-Off Fall Time	(Note 4)		150	310	ns
Qg	Total Gate Charge	V _{DS} = 160 V, I _D = 39 A,	/	38	49	nC
Q _{gs}	Gate-Source Charge	V _{GS} = 10 V		11		nC
Q _{gd}	Gate-Drain Charge	(Note 4)		16.5		nC
Drain-Sou	rce Diode Characteristics and Maximum	n Ratings		1		
I _S	Maximum Continuous Drain-Source Diode Forward Current				39	Α
I _{SM}	Maximum Pulsed Drain-Source Diode Forward Current				156	Α
V _{SD}	Drain-Source Diode Forward Voltage	V _{GS} = 0 V, I _S = 39 A			1.4	V
t _{rr}	Reverse Recovery Time	V _{GS} = 0 V, I _S = 39 A,		152		ns
Q _{rr}	Reverse Recovery Charge	dI _F /dt =100 A/μs		1.1		μC

Notes

- 1. Repetitive rating: pulse-width limited by maximum junction temperature.
- 2. L = 0.85 mH, I $_{AS}$ = 39 A, V $_{DD}$ = 50 V, R $_{G}$ = 25 Ω , starting T $_{J}$ = 25°C.
- 3. I_{SD} \leq 39 A, di/dt \leq 200 A/ μ s, V_{DD} \leq BV_{DSS}, starting T_J = 25°C.
- ${\bf 4.} \ {\bf Essentially \ independent \ of \ operating \ temperature \ typical \ characteristics.}$

Typical Performance Characteristics

Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics





Figure 3. On-Resistance Variation vs.
Drain Current and Gate Voltage

Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperatue






Figure 5. Capacitance Characteristics





Figure 6. Gate Charge Characteristics



Typical Performance Characteristics (Continued)

Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 8. On-Resistance Variation vs. Temperature




Figure 9-1. Maximum Safe Operating Area - FDP39N20




Figure 9-2. Maximum Safe Operating Area - FDPF39N20





Figure 10. Maximum Drain Current vs. Case Temperature



Typical Performance Characteristics (Continued)

Figure 11-1. Transient Thermal Response Curve - FDP39N20





Figure 11-2. Transient Thermal Response Curve - FDPF39N20






Figure 12. Gate Charge Test Circuit & Waveform




Figure 13. Resistive Switching Test Circuit & Waveforms




Figure 14. Unclamped Inductive Switching Test Circuit & Waveforms






Figure 15. Peak Diode Recovery dv/dt Test Circuit & Waveforms





ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdt/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exp

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor:

FDPF39N20