





100 V, 20 A power Schottky rectifier







TO-220AB TO-220FPAB

Features

- Negligible switching losses
- · High junction temperature capability
- · Low leakage current
- Good trade off between leakage current and forward voltage drop
- Avalanche rated
- Insulated package: TO-220FPAB
 - Insulating voltage = 2000 V_{RMS} sine
- ECOPACK®2 compliant component for D2PAK on demand



I²PAK



Product status link	
STPS20H100C	

Product summary			
I _{F(AV)}	2 x 10 A		
V_{RRM}	100 V		
T _j (max)	175 °C		
V _F (typ)	0.59 V		

Applications

- · Switching diode
- SMPS
- DC/DC converter
- LED lighting
- Adapter for notebook and game station

Description

Dual center tap Schottky rectifier designed for high frequency miniature switch mode power supplies such as adaptors and on-board DC-DC converters.



1 Characteristics

Table 1. Absolute ratings (limiting values, per diode, at 25 °C, unless otherwise specified)

Symbol		Parameter				
V _{RRM}	Repetitive peak reverse voltage				100	V
I _{F(RMS)}	Forward rms current				30	Α
		TO COOME DODAY 12DAY	T 160 °C	Per diode	10	
	Average forward current δ = 0.5, square wave	TO-220AB, D ² PAK, I ² PAK	1C = 100 C	Per device	20	
I _{F(AV)}		TO 000FDAD	T _C = 145 °C	Per diode	10	Α
		TO-220FPAB	T _C = 125 °C	Per device	20	
I _{FSM}	Surge non repetitive forward current	tp = 10 ms sinusoidal		,	250	Α
P _{ARM}	Repetitive peak avalanche power tp = 10 μ s, T_j = 125 °C				775	W
T _{stg}	Storage temperature range				-65 to + 175	°C
Tj	Maximum operating junction temperature (1)				+ 175	°C

^{1.} $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 2. Thermal resistance parameter

Symbol		Parameter				
		TO-220AB, D ² PAK, I ² PAK	Per diode	1.6		
D.,	S _{th(j-c)} Junction to case	TO-220FPAB	Total	4	°C/W	
r\th(j-c)		TO-220AB, D ² PAK, I ² PAK		0.9	C/VV	
		TO-220FPAB		3.2		
D	Coupling	TO-220AB, D ² PAK, I ² PAK		0.15	°C/W	
T\th(c)	R _{th(c)} Coupling	TO-220FPAB	-	2.5	C/VV	

When the diodes 1 and 2 are used simultaneously:

 $\Delta Tj(diode\ 1) = P(diode\ 1)\ x\ R_{th(j-c)}(Per\ diode) + P(diode\ 2)\ x\ R_{th(c)}$

For more information, please refer to the following application note:

AN5088: Rectifiers thermal management, handling and mounting recommendations

Table 3. Static electrical characteristics (per diode)

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit	
I_ (1)	I _R ⁽¹⁾ Reverse leakage current	T _j = 25 °C	V - V	-		4.5	μA	
IR ^(*)		Reverse leakage current $T_j = 125 ^{\circ}\text{C}$ $V_R = V_{RRM}$	VR - VRRM	-	2	6	mA	
		T _i = 25 °C	I _F = 10 A	-		0.77		
V ₋ (2)	V _F ⁽²⁾ Forward voltage drop		1, - 25 0	I _F = 20 A	-		0.88	V
VF ⁽⁻⁾		T _i = 125 °C	I _F = 10 A	-	0.59	0.64	V	
		1 123 0	I _F = 20 A	-	0.67	0.73		

DS1216 - Rev 10 page 2/18



- 1. Pulse test: t_p = 5 ms, δ < 2%
- 2. Pulse test: $t_p = 380 \ \mu s, \ \delta < 2\%$

To evaluate the conduction losses use the following equation:

$$P = 0.55 \times I_{F(AV)} + 0.009 I_{F}^{2}_{(RMS)}$$

For more information, please refer to the following application notes related to the power losses :

- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses on a power diode

DS1216 - Rev 10 page 3/18




1.1 **Characteristics (curves)**


Figure 1. Average forward power dissipation versus average forward current (per diode) $P_{F(AV)}(W)$ δ = 0.2 6 2 $I_{F(AV)}(A)$ δ=tp/1 0 6 10

Figure 2. Average forward current versus ambient temperature (δ = 0.5, per diode) $I_{F(AV)}(A)$ 12 TO-220AB 10 8 6 2 Tamb(°C) 0

pulse duration (T_i = 125 °C) $\frac{P_{ARM}(t_p)}{P_{ARM}(10 \ \mu s)}$ 0.1 0.01 t。(µs) 0.001 1000




to case versus pulse duration $Z_{th(j-c)}/R_{th(j-c)}$ TO-220FPAB 0.8 0.2 Single pu t_p(s) 0.0 1E-1 1E+0 1E+1 1E-2



DS1216 - Rev 10 page 4/18 Downloaded from Arrow.com.









Figure 9. Thermal resistance junction to ambient versus copper surface under tab (epoxy printed board FR4, e_{Cu} = 35 μ m) (D²PAK)



DS1216 - Rev 10 page 5/18



2 Package information


In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

DS1216 - Rev 10 page 6/18

2.1 D²PAK package information

- Cooling method: by conduction (C)
- Epoxy meets UL 94,V0

Figure 10. D²PAK package outline



DS1216 - Rev 10 page 7/18



Table 4. D²PAK package mechanical data

	Dimensions			
Ref.	. Millimeters		Inch	ies
	Min.	Max.	Min.	Max.
А	4.36	4.60	0.172	0.181
A1	0.00	0.25	0.000	0.010
b	0.70	0.93	0.028	0.037
b2	1.14	1.70	0.045	0.067
С	0.38	0.69	0.015	0.027
c2	1.19	1.36	0.047	0.053
D	8.60	9.35	0.339	0.368
D1	6.90	8.00	0.272	0.311
D2	1.10	1.50	0.043	0.060
E	10.00	10.55	0.394	0.415
E1	8.10	8.90	0.319	0.346
E2	6.85	7.25	0.266	0.282
е	2.54	typ.	0.100	
e1	4.88	5.28	0.190	0.205
Н	15.00	15.85	0.591	0.624
J1	2.49	2.90	0.097	0.112
L	1.90	2.79	0.075	0.110
L1	1.27	1.65	0.049	0.065
L2	1.30	1.78	0.050	0.070
R	0.4	typ.	0.0	15
V2	0°	8°	0°	8°






Figure 11. D²PAK Recommended footprint


DS1216 - Rev 10 page 9/18



2.2 I²PAK package information

- Epoxy meets UL 94,V0
- Cooling method: by conduction (C)

Figure 12. I²PAK package outline



DS1216 - Rev 10 page 10/18



Table 5. I²PAK package mechanical data

	Dimensions				
Ref.	Millimeters		Inches (for re	ference only)	
	Min.	Max.	Min.	Max.	
Α	4.40	4.60	0.173	0.181	
A1	2.40	2.72	0.094	0.107	
b	0.61	0.88	0.024	0.035	
b1	1.14 1.70 0.044		0.067		
С	0.49 0.70 0.019		0.028		
c2	1.23	1.23 1.32 0.048		0.052	
D	8.95	5 9.35 0.352		0.368	
е	2.40	2.70	0.094	0.106	
e1	4.95	5.15	0.195	0.203	
E	10.00	10.40 0.394 0.4		0.409	
L	13.00	14.00 0.512 0.55		0.551	
L1	3.50	50 3.93 0.138		0.155	
L2	1.27	1.40	0.050	0.055	

DS1216 - Rev 10 page 11/18



2.3 TO-220AB package information


Cooling method: by conduction (C)

• Epoxy meets UL 94,V0

• Recommended torque value: 0.55 N·m

• Maximum torque value: 0.7 N·m

Figure 13. TO-220AB package outline



DS1216 - Rev 10 page 12/18



Table 6. TO-220AB package mechanical data

	Dimensions			
Ref.	Millim	eters	Incl	nes
	Min.	Max.	Min.	Max.
А	4.40	4.60	0.173	0.181
b	0.61	0.88	0.240	0.035
b1	1.14	1.55	0.045	0.061
С	0.48	0.70	0.019	0.028
D	15.25	15.75	0.600	0.620
D1	1.27	typ.	0.050 typ.	
E	10.00	10.40	0.394	0.409
е	2.40	2.70	0.094	0.106
e1	4.95	5.15	0.195	0.203
F	1.23	1.32	0.048	0.052
H1	6.20	6.60	0.244	0.260
J1	2.40	2.72	0.094	0.107
L	13.00	14.00	0.512	0.551
L1	3.50	3.93	0.138	0.155
L20	16.40 typ.		0.646 typ.	
L30	28.90 typ.		1.138 typ.	
θР	3.75	3.85	0.148	0.152
Q	2.65	2.95	0.104	0.116

DS1216 - Rev 10 page 13/18



2.4 TO-220FPAB package information


Epoxy meets UL 94,V0

Cooling method: by conduction (C)

• Recommended torque value: 0.55 N·m

Maximum torque value: 0.70 N·m

Figure 14. TO-220FPAB package outline



DS1216 - Rev 10 page 14/18



Table 7. TO-220FPAB package mechanical data

	Dimensions				
Ref.	Millimeters		Inches (for re	eference only)	
	Min. Max.		Min.	Max.	
А	4.40	4.60	0.1739	0.1818	
В	2.50	2.70	0.0988	0.1067	
D	2.50	2.75	0.0988	0.1087	
Е	0.45	0.70	0.0178	0.0277	
F	0.75	1.00	0.0296	0.0395	
F1	1.15	1.70 0.0455		0.0672	
F2	1.15	1.70 0.0455		0.0672	
G	4.95	5.20	0.1957	0.2055	
G1	2.40	2.70 0.0949		0.1067	
Н	10.00	10.40	0.3953	0.4111	
L2	16.00	0 typ.	0.632	24 typ.	
L3	28.60	30.60	1.1304	1.2095	
L4	9.80	10.60	0.3874	0.4190	
L5	2.90	3.60	0.1146	0.1423	
L6	15.90	16.40 0.6285 0.6		0.6482	
L7	9.00	9.30	0.3557	0.3676	
Dia	3.00	3.20 0.1186		0.1265	

DS1216 - Rev 10 page 15/18



3 Ordering information

Table 8. Ordering information

Order code	Marking	Package	Weight	Base qty	Delivery mode
STPS20H100CT	STPS20H100CT	TO-220AB	1.95 g	50	Tube
STPS20H100CFP	STPS20H100CFP	TO-220FPAB	1.90 g	50	Tube
STPS20H100CR	STPS20H100CR	I ² PAK	1.50 g	50	Tube
STPS20H100CG	STPS20H100CG	D ² PAK	1.48 g	50	Tube
STPS20H100CG-TR	STPS20H100CG	D ² PAK	1.48 g	1000	Tape and reel

DS1216 - Rev 10 page 16/18



Revision history

Table 9. Document revision history

Date	Revision	Changes
Jul-2003	4G	Previous release
21-Mar-2007	5	Removed ISOWATT package
10-Sep-2007	6	Reformatted cover page to current standards - no technical changes. Updated dimensions A1, b, b1, c, c2, L, and L1 in Table 8.
22-Sep-2011	7	Updated Table 8.
21-May-2015	8	Updated features, and packages silhouette in cover page. Updated Section 1: "Characteristics" and Section 1.1: "Characteristics (curves)". Updated Section 2.2: "D²PAK package information".
16-Apr-2018	9	Updated I ² PAK package mechanical data.
20-Jan-2020	10	Updated Section 1 Characteristics and Table 8. Ordering information. Added Section Applications.



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics - All rights reserved

DS1216 - Rev 10 page 18/18