Plastic D Ribbon Connectors

Mounting Options and Hardware

Panel Mount Connector	Mating Connector	Table
Rear	No Junction Shell	А
Rear	3359 Series Junction Shell	В
Rear w/ 3359 Junction Shell	3359 Series Junction Shell	С
Front	No Junction Shell	D
Front	3359 Series Junction Shell	Е
Mid-Span	No Junction Shell	D
Mid-Span	3359 Series Junction Shell	Е

		Jack Socket Kit Connector				Jack Screw Kit Connector			
Panel		Threaded Inserts		No Inserts		Threaded Inserts		No Inserts	
Table	Thickness	Kit No.	Spacers	Kit No.	Spacers	Kit No.	Spacers	Kit No.	Spacers
	1/16		2	3341-4	2	3342-6	1	3342-4	1
А	3/32	3341-1L	1		1		1		1
	1/8		0		0		0		0
	1/16	3341-1L	2	3341-4	2	3342-6	0	3342-6	0
В	3/32		1		1		0		0
	1/8		0		0		0		0
	1/16	3341-1L	0		•	3342-6	0	3342-6	0
С	3/32	3341-1S	1	N/A		3342-6	0	3342-6	0
	1/8	3341-1S	0			3343-1	0	3343-1	0
	1/16		•	3341-2	0	3342-2	1	3342-4	1
D	3/32	N	/A		0		0		0
	1/8	1			0		0		0
	1/16				0		0		0
Е	3/32	N	/A	3341-2	0	3342-5	0	3342-5	0
	1/8	1			0		0		0


Notes:

Spacers included with the kits.
 The above table shows the recommended number of spacers to use under the head of the 3M Jack Socket or 3M Jack Screw.


TS-0143-09 Sheet 1 of 4

Plastic D Ribbon Connectors

Mounting Options and Hardware



Plastic D Ribbon Connectors Mounting Options and Hardware



Plastic D Ribbon Connectors Accessories and Assembly Equipment

Plastic Connector

ccessories									
a	Mating Connectors		Junctio	n Shell					
Contact Quantity	Plug	Socket	Plastic	Metal	Strain Relief	Pull-Tab			
14	3572-100X	3573-100X	3485-1800Y	3359-0014Y	3448-60	3490-2			
24	3548-100X	3549-100X	3485-1700Y	3359-0024Y	3448-61	3490-2			
36	3366-100X	3367-100X	3485-2800Y	3359-0036Y	3448-62	3490-3			
50	3564-100X	3565-100X	3485-2500Y	3359-0050Y	3448-63	3490-5			

Options:

X = Mounting Style

Y = "F" for Flat Cable; "R" for Round Cable

Cable Compatibility							
Conductor Type and Sizes:	26 & 28 AWG Stranded, 26, 28 & 30 AWG Solid						
Discrete Wire:	Compatible with all of the above gauges of wire. It is recommended that a strain relief be used.						
Conductor Pitch:	.05μ″ [1.27 μmm]						
Cable Type:	Round conductor flat, high flex, color coded ground plane, jacketed shielded or pleated foil.						

Assembly Equipment

	Flat Ribbon Cable Assembly			Hand Assembly	Discrete Wire Mass Termination 3316 Press		Discrete Single Wire Assembly
3M Part Number	Locator Plate	Platen	Assembly Press	Kit Number	Assembly Nest	Platen	Hand Tool
3572-XXXX	3443-58	3442-1A	3640 or 3335 or 3316* or 3830	N/A	3481-3	3442-1A	3430-1000
3573-XXXX							
3548-XXXX							
3549-XXXX							
3366-XXXX							
3367-XXXX							
3564-XXXX							
**3565-XXXX							
**3582-XXXX							

*Refer to catalog for additional parts to be ordered with the 3316 press for the assembly of flat or discrete wire assemblies. **Remove the bail latches before making the assembly.

> TS-0143-09 Sheet 4 of 4