


- P.C.B. or plug-in mount
- AC, DC, sensitive DC or single bistable coil versions available
- 8 mm, 6 kV (1.2/50 μs) between coil and contacts
- Ambient temperature +85°C
- Sockets and accessories: see 95, 99 and 86 series



\* for 400 V applications, requirements for pollution degree 2 are met.

### 40.31

### 40.51







### 40.52



- 1 pole, 10 A  
- 3.5 mm pinning  
- PCB / for use with 95 series sockets

- 1 pole, 10 A  
- 5 mm pinning  
- PCB / for use with 95 series sockets

- 2 pole, 8 A  
- 5 mm pinning  
- PCB / for use with 95 series sockets




Contact specifications				
Contact configuration		1 CO (SPDT)	1 CO (SPDT)	2 CO (DPDT)
Rated current/Maximum peak current	A	10/20	10/20	8/15
Rated voltage/Maximum switching voltage	V AC	250/400*	250/400*	250/250
Rated load in AC1	VA	2,500	2,500	2,000
Rated load in AC15 (230 VAC)	VA	500	500	400
Single phase motor rating (230 VAC)	kW/HP	0.37/0.6	0.37/0.6	0.3/0.4
Breaking capacity in DC1: 30/110/220V	A	10/0.3/0.12	10/0.3/0.12	8/0.3/0.12
Minimum switching load	mW (V/mA)	300 (5/5)	300 (5/5)	300 (5/5)
Standard contact material		AgNi	AgNi	AgNi
Coil specifications				
Nominal voltage (U <sub>N</sub> )	V AC (50/60 Hz)	6 - 12 - 24 - 48 - 60 - 110 - 120 - 230 - 240		
	V DC	5 - 6 - 7 - 9 - 12 - 14 - 18 - 21 - 24 - 28 - 36 - 48 - 60 - 90 - 110		
Rated power AC/DC/sens. DC	VA (50 Hz)/W	1.2/0.65/0.5	1.2/0.65/0.5	1.2/0.65/0.5
Operating range	AC (50 Hz)	(0.8...1.1)U <sub>N</sub>		
	DC/sens. DC	(0.73...1.5)U <sub>N</sub> /(0.73...1.75)U <sub>N</sub>		
Holding voltage	AC/DC	0.8 U <sub>N</sub> / 0.4 U <sub>N</sub>		0.8 U <sub>N</sub> / 0.4 U <sub>N</sub>
Must drop-out voltage	AC/DC	0.2 U <sub>N</sub> / 0.1 U <sub>N</sub>		0.2 U <sub>N</sub> / 0.1 U <sub>N</sub>
Technical data				
Mechanical life AC/DC	cycles	10 · 10 <sup>6</sup> /20 · 10 <sup>6</sup>		10 · 10 <sup>6</sup> /20 · 10 <sup>6</sup>
Electrical life at rated load AC1	cycles	200 · 10 <sup>3</sup>		100 · 10 <sup>3</sup>
Operate/release time (bounce included)	ms	10/10 - (15/12 sens.)		10/10 - (15/12 sens.)
Insulation according to EN 61810-5		3.6 kV/3		3.6 kV/2
Insulation between coil and contacts (1.2/50μs)	kV	6 (8mm)		6 (8mm)
Dielectric strenght between open contacts	V AC	1,000		1,000
Ambient temperature range	°C	-40...+85		-40...+85
Protection category		IP 50		IP 50

**Approvals:** (according to type)



- P.C.B. or plug-in mount
- AC, DC, sensitive DC or single bistable coil versions available
- 8 mm, 6 kV (1.2/50 μs) between coil and contacts
- Ambient temperature +85°C
- Sockets and accessories: see 95, 99 and 86 series



\* for 400 V applications, requirements for pollution degree 2 are met.

40.61	40.xx.6	
- 1 pole, 16 A - 5 mm pinning - PCB / for use with 95 series sockets	- Bistable version (1 coil) - PCB / for use with 95 series sockets	
	Bistable version (1 coil) types:  40.31.6... 40.51.6... 40.52.6... 40.61.6...  For wiring diagrams see page 16	
<b>Contact specifications</b>		
Contact configuration	1 CO (SPDT)	
Rated current/Maximum peak current      A	16/30	
Rated voltage/Maximum switching voltage V AC	250/400*	
Rated load in AC1                                  VA	4,000	See relays
Rated load in AC15 (230 VAC)                  VA	750	40.31
Single phase motor rating (230 VAC)      kW/HP	0.55/0.8	40.51
Breaking capacity in DC1: 30/110/220V      A	16/0.3/0.12	40.52
Minimum switching load                          mW (V/mA)	500 (10/5)	40.61
Standard contact material	AgCdO	
<b>Coil specifications</b>		
Nominal voltage (U <sub>N</sub> )                              V AC (50/60 Hz)	6 - 12 - 24 - 48 - 60 - 110 - 120 - 230 - 240	5 - 6 - 12 - 24 - 48 - 110
	V DC	**See below
Rated power AC/DC/sens. DC                  VA (50 Hz)/W	1.2/0.65/0.5	1.0/1.0/—
Operating range                                      AC (50 Hz)	(0.8...1.1)U <sub>N</sub>	(0.8...1.1)U <sub>N</sub>
	DC/sens. DC	(0.73...1.5)U <sub>N</sub> /(0.8...1.5)U <sub>N</sub>
Holding voltage                                      AC/DC	0.8 U <sub>N</sub> /0.4 U <sub>N</sub>	—
Must drop-out voltage                              AC/DC	0.2 U <sub>N</sub> /0.1 U <sub>N</sub>	—
<b>Technical data</b>		
Mechanical life AC/DC                              cycles	10 · 10 <sup>5</sup> /20 · 10 <sup>6</sup>	See relays
Electrical life at rated load AC1                  cycles	100 · 10 <sup>3</sup>	40.31
Operate/release time (bounce included)      ms	10/10 - (15/12 sens.)	40.51
Insulation according to EN 61810-5	3.6 kV/3	40.52
Insulation between coil and contacts (1.2/50μs) kV	6 (8mm)	40.61
Dielectric strenght between open contacts    V AC	1,000	
Ambient temperature range                          °C	-40...+85	Min. impulse duration ≥ 20 ms
Protection category	IP 50	
<b>Approvals:</b> (according to type)		

\*\* Nominal voltage (U<sub>N</sub>):  
 5 - 6 - 7 - 9 - 12 - 14 - 18 - 21 -  
 24 - 28 - 36 - 48 - 60 - 90 -  
 110 V DC

## ORDERING INFORMATION

Example: a 40 series P.C.B. relay with 2 CO (DPDT) contacts, with coil rated at 230 V AC.

4 0 . 5 2 . 8 . 2 3 0 . A B C D

**Series**

**Type**

- 3 = P.C.B. - 3.5 mm pinning
- 5 = P.C.B. - 5 mm pinning
- 6 = P.C.B. - 5 mm pinning

**No. of poles**

- 1 = 1 CO (SPDT)  
for: 40.31, 10 A  
40.51, 10 A  
40.61, 16 A
- 2 = 2 CO (DPDT)  
for 40.52, 8 A

**Coil version**

- 6 = AC/DC bistable
- 7 = Sensitive DC
- 8 = AC (50/60 Hz)
- 9 = DC

**Coil voltage**

see coil specifications

**A: Contact material**

- 0 = Standard AgNi  
for: 40.31/51/52  
AgCdO for 40.61
- 2 = AgCdO
- 4 = AgSnO<sub>2</sub>
- 5 = AgNi + Au (5µm)

**B: Contact circuit**

- 0 = Standard
- 3 = Contact NO

**D: Special applications**

- 0 = Standard
- 1 = Sealed version (IP67)
- 3 = High temperature (+125°C) sealed version

**C: Options**

- 0 = Standard

**Only combinations in the same row are possible**

Preferred versions

	coil version	A	B	C	D
40.31/51	AC/DC/sens.DC	0	0	0	0
40.52	AC/DC/sens.DC	0	0	0	0
40.61	AC/DC/sens.DC	0	0	0	0

All versions

	coil version	A	B	C	D
40.31/51	AC/sens.DC	0 - 2 - 4 - 5	0 - 3	0	0 - 1
40.31/51	DC	0 - 2 - 4 - 5	0 - 3	0	0 - 1 - 3
40.52	AC/sens.DC	0 - 2 - 5	0 - 3	0	0 - 1
40.52	DC	0 - 2 - 5	0 - 3	0	0 - 1 - 3
40.61	AC/sens.DC	0 - 4	0 - 3	0	0 - 1
40.61	DC	0 - 4	0 - 3	0	0 - 1 - 3
40.31/51/ 52/61	bistable	0	0	0	0

## TECHNICAL DATA

### INSULATION

INSULATION according to EN 61810-5	insulation rated voltage	V	250
	rated impulse withstand voltage	kV	3.6
	pollution degree		3 (1 CO)    2 (2CO)
	overvoltage category		III

### IMMUNITY


CONDUCTED DISTURBANCE IMMUNITY	BURST (according to EN 61000-4-4) level 4 (4kV)
	SURGE (according to EN 61000-4-5) level 3 (2kV)

### OTHER DATA

VIBRATION RESISTANCE (10...55Hz): NO/NC	g/g	10/4 (1CO)	3/3 (2CO)
POWER LOST IN THE ENVIRONMENT	without contact current	W	
	with rated current	W	0.6
		1.2 (40.31/51)	2 (40.61/52)
RECOMMENDED DISTANCE between RELAY mounted on P.C.B.s	mm	≥5	

## CONTACT SPECIFICATIONS


### F 40



Electrical life vs AC1 load.

- 1** - Type 40.52 (8 A)
- 2** - Type 40.31 - 40.51 (10 A)
- Type 40.61 (16 A)

### H 40



Breaking capacity for DC1 load.

- 1** - Type 40.61
- 2** - Type 40.31 - 40.51
- 3** - Type 40.52
- A** - Load applied to 1 contact
- B** - Load applied to 2 contacts in series

- When switching a resistive load (DC1) having voltage and current values under the curve the expected electrical life is  $\geq 100 \cdot 10^3$  cycles.
- In case of DC13 loads the connection of a diode in parallel with the load will permit the same electrical life as for a DC1 load.

**Note:** the release time of load will be increase.

## COIL SPECIFICATIONS

### DC VERSION DATA (0.65 W standard)

Nominal voltage $U_N$ V	Coil code	Operating range		Resistance R $\Omega$	Rated coil absorption I at $U_N$ mA
		$U_{min}$ V	$U_{max}$ V		
5	<b>9.005</b>	3.65	7.5	38	130
6	<b>9.006</b>	4.4	9	55	109
7	<b>9.007</b>	5.1	10.5	75	93
9	<b>9.009</b>	6.6	13.5	125	72
12	<b>9.012</b>	8.8	18	220	55
14	<b>9.014</b>	10.2	21	300	47
18	<b>9.018</b>	13.1	27	500	36
21	<b>9.021</b>	15.3	31.5	700	30
24	<b>9.024</b>	17.5	36	900	27
28	<b>9.028</b>	20.5	42	1,200	23
36	<b>9.036</b>	26.3	54	2,000	18
48	<b>9.048</b>	35	72	3,500	14
60	<b>9.060</b>	43.8	90	5,500	11
90	<b>9.090</b>	65.7	135	12,500	7.2
110	<b>9.110</b>	80.3	165	18,000	6.1

### DC VERSION DATA (0.5 W sensitive)

Nominal voltage $U_N$ V	Coil code	Operating range		Resistance R $\Omega$	Rated coil absorption I at $U_N$ mA
		$U_{min}^*$ V	$U_{max}^{**}$ V		
5	<b>7.005</b>	3.7	8.8	50	100
6	<b>7.006</b>	4.4	10.5	75	80
7	<b>7.007</b>	5.1	12.2	100	70
9	<b>7.009</b>	6.6	15.8	160	56
12	<b>7.012</b>	8.8	21	300	40
14	<b>7.014</b>	10.2	24.5	400	35
18	<b>7.018</b>	13.2	31.5	650	27.7
21	<b>7.021</b>	15.4	36.9	900	23.3
24	<b>7.024</b>	17.5	42	1,200	20
28	<b>7.028</b>	20.5	49	1,600	17.5
36	<b>7.036</b>	26.3	63	2,600	13.8
48	<b>7.048</b>	35	84	4,800	10
60	<b>7.060</b>	43.8	105	7,200	8.3
90	<b>7.090</b>	65.7	157	16,200	5.5
110	<b>7.110</b>	80.3	192	23,500	4.7

\* $U_{min} = 0.8 U_N$  for 40.61


\*\* $U_{max} = 1.5 U_N$  for 40.61

### AC VERSION DATA


Nominal voltage $U_N$ V	Coil code	Operating range		Resistance R $\Omega$	Rated coil absorption I at $U_N$ (50Hz) mA
		$U_{min}$ V	$U_{max}$ V		
6	<b>8.006</b>	4.8	6.6	21	168
12	<b>8.012</b>	9.6	13.2	80	90
24	<b>8.024</b>	19.2	26.4	320	45
48	<b>8.048</b>	38.4	52.8	1,350	21
60	<b>8.060</b>	48	66	2,100	16.8
110	<b>8.110</b>	88	121	6,900	9.4
120	<b>8.120</b>	96	132	9,000	8.4
230	<b>8.230</b>	184	253	28,000	4.5
240	<b>8.240</b>	192	264	31,500	4.1

## COIL SPECIFICATIONS


### R 40 DC



### R 40 sens. DC



### R 40 AC



Operating range vs ambient temperature.

- 1** - Max coil voltage permitted
- 2** - Min pick-up voltage with coil at ambient temperature

## BISTABLE COIL SPECIFICATIONS


### AC/DC VERSION DATA (bistable)

Nominal voltage $U_N$ V	Coil	Operating range		Resistance $R$ $\Omega$	Rated coil absorption $I$ at $U_N$ mA	DC: Release resistance** $R_{DC}$ $\Omega$
		$U_{min}$ V	$U_{max}$ V			
5	<b>6.005</b>	4	5.5	23	215	37
6	<b>6.006</b>	4.8	6.6	33	165	62
12	<b>6.012</b>	9.6	13.2	130	83	220
24	<b>6.024</b>	19.2	26.4	520	40	910
48	<b>6.048</b>	38.4	52.8	2,100	21	3,600
110	<b>6.110</b>	88	121	11,000	10	16,500

\*\*  $R_{DC}$  = Resistance in DC,  $R_{AC} = 1.3 \times R_{DC}$


### Wiring Diagram for 40 Series bistable coil version

#### AC Operation



On momentary closure of the SET switch the relay is magnetised through the diode and the relay contacts transfer to the set position and remain in this position.  
On momentary closure of the RESET switch the relay is demagnetised through current limiting resistor (R AC) and the contacts return to the reset position.

#### DC Operation



On momentary closure of the SET switch the relay is magnetised and the relay contacts transfer to the set position and remain in this position.  
On momentary closure of the RESET switch the relay is demagnetised through limiting resistor (R DC) and the contacts return to the reset position.

**Notes:** The minimum SET or RESET impulse time is 20 ms. The maximum time can be continuous. In practice, always ensure that the SET and RESET contacts cannot be operated simultaneously.



95.05



Approvals  
(according to type):



Relay type	40.31	40.51, 40.52, 40.61
Clamp terminal socket: panel or 35 mm rail (EN 50022) mount	BLUE 95.03	95.05
	BLACK* 95.03.0	95.05.0
Retaining and release clip (supplied with socket)	095.01	095.01
Identification tag	095.00.4	095.00.4
Modules	99.02	99.02
Timer modules	86.10, 86.20	86.10, 86.20
8-way jumper link for 95.03 and 95.05 sockets	095.18	095.18

- RATED VALUES: 10 A - 250 V  
*with a current >10 A, the contact terminal must be connected in parallel (21 with 11, 24 with 14, 22 with 12)*
- INSULATION:  $\geq 6$  kV (1.2/50 $\mu$ s) between coil and contacts
- PROTECTION CATEGORY: IP 20
- AMBIENT TEMPERATURE: (-40...+70) °C
- TORQUE: 0.5 Nm
- MAX WIRE SIZE:

	solid wire	flexible wire
mm <sup>2</sup>	1x6 / 2x2.5	1x4 / 2x2.5
AWG	1x10 / 2x14	1x12 / 2x14




99.02

99 Series modules for 95.03 and 95.05 sockets		BLUE	BLACK*
Diode	(6...220) V DC	99.02.3.000.00	99.02.3.000.00.0
Diode (inverted polarity)	(6...220) V DC	99.02.2.000.00	99.02.2.000.00.0
LED	(6...24) V DC/AC	99.02.0.024.59	99.02.0.024.59.0
LED	(28...60) V DC/AC	99.02.0.060.59	99.02.0.060.59.0
LED	(110...240) V DC/AC	99.02.0.230.59	99.02.0.230.59.0
LED + Diode	(6...24) V DC	99.02.9.024.99	99.02.9.024.99.0
LED + Diode	(28...60) V DC	99.02.9.060.99	99.02.9.060.99.0
LED + Diode	(110...220) V DC	99.02.9.220.99	99.02.9.220.99.0
LED + Diode (inverted polarity)	(6...24) V DC	99.02.0.024.79	99.02.0.024.79.0
LED + Diode (inverted polarity)	(28...60) V DC	99.02.9.060.79	99.02.9.060.79.0
LED + Diode (inverted polarity)	(110...220) V DC	99.02.9.220.79	99.02.9.220.79.0
LED + Varistor	(6...24) V DC/AC	99.02.0.024.98	99.02.0.024.98.0
LED + Varistor	(28...60) V DC/AC	99.02.0.060.98	99.02.0.060.98.0
LED + Varistor	(110...240) V DC/AC	99.02.0.230.98	99.02.0.230.98.0
RC	(6...24) V DC/AC	99.02.0.024.09	99.02.0.024.09.0
RC	(28...60) V DC/AC	99.02.0.060.09	99.02.0.060.09.0
RC	(110...240) V DC/AC	99.02.0.230.09	99.02.0.230.09.0
No - remanence	(110...240) V AC	99.02.8.230.07	99.02.8.230.07.0



095.18

<b>8-way jumper link</b> for 95.03, and 95.05 sockets	095.18
-------------------------------------------------------	--------




- RATED VALUES: 10 A - 250 V

\* Available on request



Relay type	40.31	40.51, 40.52, 40.61		
Clamp terminal socket: panel or 35 mm rail (EN 50022) mount	BLUE	95.63	95.65	95.75
	BLACK*	95.63.0	95.65.0	95.75.0
Retaining clip (supplied with socket)	095.71	095.71	095.71	
Modules	99.01	—	99.01	
8-way jumper link for 95.63 and 95.75 sockets	095.08	095.08	095.08	






Approvals  
(according to type):



- RATED VALUES: 10 A - 250 V  
with a current > 10 A, the contact terminal must be connected in parallel (21 with 11, 24 with 14, 22 with 12)

- INSULATION:  $\geq 6$  kV (1.2/50 $\mu$ s) between coil and contacts (Types 95.63/75 only)
- PROTECTION CATEGORY: IP 20
- AMBIENT TEMPERATURE: (-40...+70) °C
- TORQUE: 0.5 Nm
- MAX WIRE SIZE:



	solid wire	flexible wire
mm <sup>2</sup>	1x6 / 2x2.5	1x4 / 2x2.5
AWG	1x10 / 2x14	1x12 / 2x14



99 Series modules for 95.63 and 95.75 sockets		BLUE	BLACK*
Diode	(6...220) V DC	99.01.3.000.00	99.01.3.000.00.0
Diode (inverted polarity)	(6...220) V DC	99.01.2.000.00	99.01.2.000.00.0
LED	(6...24) V DC/AC	99.01.0.024.59	99.01.0.024.59.0
LED	(28...60) V DC/AC	99.01.0.060.59	99.01.0.060.59.0
LED	(110...240) V DC/AC	99.01.0.230.59	99.01.0.230.59.0
LED + Diode	(6...24) V DC	99.01.9.024.99	99.01.9.024.99.0
LED + Diode	(28...60) V DC	99.01.9.060.99	99.01.9.060.99.0
LED + Diode	(110...220) V DC	99.01.9.220.99	99.01.9.220.99.0
LED + Diode (inverted polarity)	(6...24) V DC	99.01.0.024.79	99.01.0.024.79.0
LED + Diode (inverted polarity)	(28...60) V DC	99.01.9.060.79	99.01.9.060.79.0
LED + Diode (inverted polarity)	(110...220) V DC	99.01.9.220.79	99.01.9.220.79.0
LED + Varistor	(6...24) V DC/AC	99.01.0.024.98	99.01.0.024.98.0
LED + Varistor	(28...60) V DC/AC	99.01.0.060.98	99.01.0.060.98.0
LED + Varistor	(110...240) V DC/AC	99.01.0.230.98	99.01.0.230.98.0
RC	(6...24) V DC/AC	99.01.0.024.09	99.01.0.024.09.0
RC	(28...60) V DC/AC	99.01.0.060.09	99.01.0.060.09.0
RC	(110...240) V DC/AC	99.01.0.230.09	99.01.0.230.09.0
No - remanence	(110...240) V AC	99.01.8.230.07	99.01.8.230.07.0


\* Available on request



095.08

- RATED VALUES: 10 A - 250 V

<b>8-way jumper link</b> for 95.63, 95.65 and 95.75 sockets	095.08
-------------------------------------------------------------	--------



95.13






95.15

Relay type	40.31	40.51, 40.52, 40.61
<b>P.C.B. socket</b>	BLUE	95.13
	BLACK*	95.13.0
Metal retaining clip	095.51	095.51
Plastic retaining clip	095.52	095.52


Approvals  
(according to type):



- RATED VALUES: 10 A - 250 V
- INSULATION:  $\geq 6$  kV (1.2/50 $\mu$ s) between coil and contacts
- PROTECTION CATEGORY: IP 20
- AMBIENT TEMPERATURE: (-40...+70) °C



95.13



95.15

\* Available on request



- Low-profile, only 15.7 mm high
- DC coil versions
- 8 mm, 6 kV(1.2/50 μs) between coil and contacts
- Ambient temperature +85°C
- Sockets and accessories: see 95 and 99 series

### 41.31

### 41.52








### 41.61



- 1 pole, 12 A  
- low profile, 3.5 mm pinning  
- PCB / for use with 95 series sockets

- 2 pole, 8 A  
- low profile, 5 mm pinning  
- PCB / for use with 95 series sockets

- 1 pole, 16 A  
- low profile, 5 mm pinning  
- PCB / for use with 95 series sockets



\* for 400 V applications, requirements for pollution degree 2 are met.

Contact specifications					
Contact configuration			1 CO (SPDT)	2 CO (DPDT)	1 CO (SPDT)
Rated current/Maximum peak current	A		12/25	8/15	16/30
Rated voltage/Maximum switching voltage	V AC		250/400*	250/400*	250/400*
Rated load in AC1	VA		3,000	2,000	4,000
Rated load in AC15 (230 VAC)	VA		600	400	750
Single phase motor rating (230 VAC)	kW/HP		0.5/0.75	0.3/0.5	0.5/0.75
Breaking capacity in DC1: 30/110/220V	A		12/0.4/0.12	8/0.4/0.12	16/0.4/0.12
Minimum switching load	mW (V/mA)		300 (5/5)	300 (5/5)	300 (5/5)
Standard contact material			AgNi	AgNi	AgNi
Coil specifications					
Nominal voltage (U <sub>N</sub> )	V AC (50/60 Hz)		—	—	—
	V DC		12 - 24 - 48 - 60 - 110	12 - 24 - 48 - 60 - 110	12 - 24 - 48 - 60 - 110
Rated power AC/sens. DC	VA (50 Hz)/W		—/0.4	—/0.4	—/0.4
Operating range	AC (50 Hz)		—	—	—
	DC		(0.7...2.5)U <sub>N</sub>	(0.7...2.5)U <sub>N</sub>	(0.7...2.5)U <sub>N</sub>
Holding voltage	AC/DC		—/0.4U <sub>N</sub>	—/0.4 U <sub>N</sub>	—/0.4 U <sub>N</sub>
Must drop-out voltage	AC/DC		—/0.1U <sub>N</sub>	—/0.1 U <sub>N</sub>	—/0.1 U <sub>N</sub>
Technical data					
Mechanical life AC/DC	cycles		—/30·10 <sup>6</sup>	—/30·10 <sup>6</sup>	—/30·10 <sup>6</sup>
Electrical life at rated load AC1	cycles		150 · 10 <sup>3</sup>	80 · 10 <sup>3</sup>	70 · 10 <sup>3</sup>
Operate/release time (bounce included)	ms		7/8	7/8	7/8
Insulation according to EN 61810-5			3.6kV/3	3.6kV/3	3.6kV/3
Insulation between coil and contacts (1.2/50μs)		kV	6 (8mm)	6 (8mm)	6 (8mm)
Dielectric strenght between open contacts		V AC	1,000	1,000	1,000
Ambient temperature range		°C	−40...+85	−40...+85	−40...+85
Protection category			IP 50	IP 50	IP 50

**Approvals:** (according to type)



## ORDERING INFORMATION

Example: a 41 series low-profile P.C.B. relay with 2 CO (DPDT) contacts, with coil rated 24 V DC.

4

1

.

5

.

2

.

9

.

0

2

4

.

0

0

0

0

**Series** —————

**Type** —————  
 3 = P.C.B. - 3.5 mm pinning  
 5 = P.C.B. - 5 mm pinning  
 6 = P.C.B. - 5 mm pinning

**No. of poles** —————  
 1 = 1 CO (SPDT) for  
     41.31, 12 A  
     41.61, 16A  
 2 = 2 CO (DPDT)  
     for 41.52, 8 A

**Coil version** —————  
 9 = DC

**Coil voltage** —————  
 see coil specifications

**A: Contact material**  
 0 = AgNi Standard

**B: Contact circuit**  
 0 = Standard

**C: Options**  
 0 = Standard

**D: Special applications**  
 0 = Standard

## TECHNICAL DATA

### INSULATION


INSULATION according to EN 61810-5	insulation rated voltage	V	250
	rated impulse withstand voltage	kV	3.6
	pollution degree		3
	overvoltage category		III

### OTHER DATA

VIBRATION RESISTANCE (10...55Hz): NO/NC	g/g	20/5		
POWER LOST IN THE ENVIRONMENT	without contact current	W	0.4	
	with rated current	W	1.7 (41.31)	1.2 (41.52)      1.8 (41.61)
RECOMMENDED DISTANCE between RELAY mounted on P.C.B.s	mm	≥5		

## CONTACT SPECIFICATIONS


### F 41



Contact life vs AC1 load.

- 1** - Type 41.52 (8 A) at 360 cycles/h.
- 2** - Type 41.31 (12 A) at 360 cycles/h.
- Type 41.61 (16 A) at 360 cycles/h.

### H 41



Breaking capacity for DC1 load.

- 1** - type 41.61
- 2** - type 41.31
- 3** - type 41.52
- A** - load applied to 1 contact
- B** - load applied to 2 contacts in series


- When switching a resistive load (DC1) having voltage and current values under the curve the expected electrical life is  $\geq 100 \cdot 10^3$  cycles.
- In case of DC13 loads the connection of a diode in parallel with the load will permit the same electrical life as for a DC1 load.
- Note:** the release time of load will be increase.

## COIL SPECIFICATIONS

### DC VERSION DATA

Nominal voltage $U_N$ V	Coil code	Operating range		Resistance R $\Omega$	Rated coil absorption I at $U_N$ mA
		$U_{min}$ V	$U_{max}$ V		
12	<b>9.012</b>	8.4	30.6	360	33.3
24	<b>9.024</b>	16.8	61.2	1,440	19.7
48	<b>9.048</b>	33.6	122	5,520	8.7
60	<b>9.060</b>	42.0	153	7,340	8.1
110	<b>9.110</b>	77.0	280	26,600	4.1


### R 41/1 DC



**Type 41.52** operating range vs ambient temperature.

- 1** - Max coil voltage permitted
- 2** - Min pick-up voltage with coil at ambient temperature

### R 41/2 DC



**Type 41.31, 41.61** operating range vs ambient temperature.

- 1** - Max coil voltage permitted
- 2** - Min pick-up voltage with coil at ambient temperature



95.05



Approvals  
(according to type):



- RATED VALUES: 10 A - 250 V  
*with a current >10 A, the contact terminal must be connected in parallel (21 with 11, 24 with 14, 22 with 12)*
- INSULATION:  $\geq 6$  kV (1.2/50 $\mu$ s) between coil and contacts
- PROTECTION CATEGORY: IP 20
- AMBIENT TEMPERATURE: (-40...+70) °C
- TORQUE: 0.5 Nm
- MAX WIRE SIZE:

	solid wire	flexible wire
mm <sup>2</sup>	1x6 / 2x2.5	1x4 / 2x2.5
AWG	1x10 / 2x14	1x12 / 2x14

Relay type	41.31	41.52, 41.61
Clamp terminal socket: panel or 35 mm rail (EN 50022) mount	BLUE	95.03
	BLACK*	95.03.0
Identification tag	095.00.4	095.00.4
Modules	99.02	99.02
Timer modules	86.10, 86.20	86.10, 86.20
8-way jumper link for 95.03 and 95.05 sockets	095.18	095.18



99.02


99 Series modules for 95.03 and 95.05 sockets		BLUE	BLACK*
Diode	(6...220) V DC	99.02.3.000.00	99.02.3.000.00.0
Diode (inverted polarity)	(6...220) V DC	99.02.2.000.00	99.02.2.000.00.0
LED	(6...24) V DC/AC	99.02.0.024.59	99.02.0.024.59.0
LED	(28...60) V DC/AC	99.02.0.060.59	99.02.0.060.59.0
LED	(110...240) V DC/AC	99.02.0.230.59	99.02.0.230.59.0
LED + Diode	(6...24) V DC	99.02.9.024.99	99.02.9.024.99.0
LED + Diode	(28...60) V DC	99.02.9.060.99	99.02.9.060.99.0
LED + Diode	(110...220) V DC	99.02.9.220.99	99.02.9.220.99.0
LED + Diode (inverted polarity)	(6...24) V DC	99.02.0.024.79	99.02.0.024.79.0
LED + Diode (inverted polarity)	(28...60) V DC	99.02.9.060.79	99.02.9.060.79.0
LED + Diode (inverted polarity)	(110...220) V DC	99.02.9.220.79	99.02.9.220.79.0
LED + Varistor	(6...24) V DC/AC	99.02.0.024.98	99.02.0.024.98.0
LED + Varistor	(28...60) V DC/AC	99.02.0.060.98	99.02.0.060.98.0
LED + Varistor	(110...240) V DC/AC	99.02.0.230.98	99.02.0.230.98.0
RC	(6...24) V DC/AC	99.02.0.024.09	99.02.0.024.09.0
RC	(28...60) V DC/AC	99.02.0.060.09	99.02.0.060.09.0
RC	(110...240) V DC/AC	99.02.0.230.09	99.02.0.230.09.0
No - remanence	(110...240) V AC	99.02.8.230.07	99.02.8.230.07.0

<b>8-way jumper link for 95.03, and 95.05 sockets</b>	095.18
-------------------------------------------------------	--------



095.18

- RATED VALUES: 10 A - 250 V



\*Available on request






Relay type	41.31	41.52, 41.61	
P.C.B. socket	BLUE	95.13	95.15
	BLACK*	95.13.0	95.15.0
Metal retaining clip	095.41	095.41	
Plastic retaining clip	095.42	095.42	


Approvals  
(according to type):



- RATED VALUES: 10 A - 250 V
- INSULATION:  $\geq 6$  kV (1.2/50 $\mu$ s) between coil and contacts
- PROTECTION CATEGORY: IP 20
- AMBIENT TEMPERATURE: (-40...+70) °C



95.13



95.15