

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild <a href="general-regarding-numbers-n

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



October 2013

GBPC 12, 15, 25, 35 SERIES Bridge Rectifiers (Glass Passivated)

Features

- Integrally molded heat-sink provided very low thermal resistance for maximum heat dissipation.
- Surge Overload Ratings from 300 A to 400 A.
- Isolated voltage from case to lead over 2500 V.
- UL certified, UL #E258596
- Terminals Finish Material Silver (Solderable per MIL-STD-202, Method 208 for the wire type GBPC-W package)
 Nickel for GBPC package.

1

Suffix "W"

• Wire Lead Structure

Suffix "M"

• Terminal Location Face to Face









GBPC-W



Ordering Informations

Part Number	Marking	Package	Packing Method
GBPC12005	GBPC12005		
GBPC1201	GBPC1201		
GBPC1202	GBPC1202		
GBPC1204	GBPC1204		
GBPC1206	GBPC1206		
GBPC1208	GBPC1208		
GBPC1210	GBPC1210		
GBPC15005	GBPC15005		
GBPC1501	GBPC1501		
GBPC1502	GBPC1502		
GBPC1504	GBPC1504		
GBPC1506	GBPC1506		
GBPC1508	GBPC1508		
GBPC1510	GBPC1510	CDDC 41	
GBPC25005	GBPC25005	GBPC 4L	
GBPC2501	GBPC2501		
GBPC2502	GBPC2502		
GBPC2504	GBPC2504		
GBPC2506	GBPC2506		
GBPC2508	GBPC2508		Dulle
GBPC2510	GBPC2510		Bulk
GBPC35005	GBPC35005		
GBPC3501	GBPC3501		
GBPC3502	GBPC3502		
GBPC3504	GBPC3504		
GBPC3506	GBPC3506	1	
GBPC3508	GBPC3508		
GBPC3510	GBPC3510		
GBPC1201W	GBPC1201W		
GBPC1202W	GBPC1202W		
GBPC1204W	GBPC1204W		
GBPC1206W	GBPC1206W		
GBPC1208W	GBPC1208W		
GBPC1210W	GBPC1210W	CPDC W 4I	
GBPC15005W	GBPC15005W	GBPC-W 4L	
GBPC1501W	GBPC1501W		
GBPC1502W	GBPC1502W		
GBPC1504W	GBPC1504W		
GBPC1506W	GBPC1506W		
GBPC1508W	GBPC1508W		

Ordering Informations (continued)

Part Number	Marking	Package	Packing Method
GBPC1510W	GBPC1510W		
GBPC25005W	GBPC25005W		
GBPC2501W	GBPC2501W		
GBPC2502W	GBPC2502W		
GBPC2504W	GBPC2504W		
GBPC2506W	GBPC2506W		
GBPC2508W	GBPC2508W		
GBPC2510W	GBPC2510W	GBPC-W 4L	Bulk
GBPC35005W	GBPC35005W		
GBPC3501W	GBPC3501W		
GBPC3502W	GBPC3502W		
GBPC3504W	GBPC3504W		
GBPC3506W	GBPC3506W		
GBPC3508W	GBPC3508W		
GBPC3510W	GBPC3510W		

Absolute Maximum Ratings(1)

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at $T_A = 25$ °C unless otherwise noted.

Cumbal	Parameter		Value							Unito
Symbol			005	01	02	04	06	08	10	Units
V_{RRM}	Maximum Repetitive Reverse Volt	age	50	100	200	400	600	800	1000	V
V _{RMS}	Maximum RMS Bridge Input Volta	ge	35	70	140	280	420	560	700	V
V_{R}	DC Reverse Voltage (Rated V _R)		50	100	200	400	600	800	1000	V
		GBPC12	12							
	Average Rectified Forward	GBPC15	15					A		
I _{F(AV)}	Current at T _C = 55°C	GBPC25	25							
		GBPC35	35							
I _{FSM}	Non-Repetitive Peak Forward GBPC12, Surge Current 15, 25		300					Α		
	8.3ms Single Half-Sine-Wave GBP0		400					Α		
T _{STG}	Storage Temperature Range		-55 to +150					°C		
TJ	Operating Junction Temperature		-55 to +150					°C		

Note:

1. These ratings are limiting values above which the serviceability of any semiconductor device may by impaired.

Thermal Characteristics

Values are at $T_A = 25^{\circ}C$ unless otherwise noted.

Symbol	Parameter	Value	Units
P _D	Power Dissipation	83.3	W
$R_{\theta JC}$	Thermal Resistance, Junction to Case ⁽²⁾	1.5	°C/W

Note:

2. With Heatsink.

Electrical Characteristics

Values are at $T_A = 25$ °C unless otherwise noted.

Symbol	Parameter	Test Co	Test Conditions Value		Units
		6.0 A	GBPC12		V
V	Forward Voltage Drop, per bridge	7.5 A	GBPC15	1.1 (Max)	
V _F		12.5 A	GBPC25		
		17.5 A	GBPC35		
/1-	Reverse Current, per element at Rated V _R	$T_A = 25^{\circ}C$		25°C 5.0 (Max)	
I _R	Reverse Current, per element at Nated VR	$T_A = 125^{\circ}$	0	500 (Max)	μΑ
l ² t	Rating for Fusing t < 8.35 ms	GBPC12,	15, 25	375	A ² Sec
1 (Rating for Fusing (< 6.55 ms	GBPC35		660	A ² Sec
_	Total Capacitance, per leg	e, per leg GBPC12, 15, 25		180	pF
C _T	$V_R = 4.0 \text{ V}$ f = 1.0 MHz	GBPC35		200	pF

Typical Performance Characteristics




Figure 1. Forward Current Derating Curve




Figure 3. Forward Voltage Characteristics




Figure 2. Non-Repetitive Surge Current





Figure 4. Reverse Current vs. Reverse Voltage

Physical Dimension

GBPC



NOTES:

- A. THIS PACKAGE DOES NOT CONFORM TO ANY STANDARDS.
 B. ALL DIMENSIONS ARE IN MILLIMETERS.
- D. ALL DIMENSIONS ARE IN MILLIMETERS.
 C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.
 D. FAIRCHILDSEMICONDUCTOR
 E. DRAWING FILE NAME: MKT-GBPC04A REV3

Figure 5. 4-TERMINAL, COMBINATION GBPC AND GBPC-W (ACTIVE)

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: http://www.fairchildsemi.com/dwq/GB/GBPC04A.pdf.





TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

FRFET® AX-CAP®,

Global Power ResourceSM BitSiC™ GreenBridge™ Build it Now™ Green FPS™ CorePLUS™

Green FPS™ e-Series™ CorePOWER™

 $CROSSVOLT^{\text{\tiny TM}}$ Gmax™ GTO™ CTL™ IntelliMAX™ Current Transfer Logic™

ISOPLANAR™ DEUXPEED[®] Making Small Speakers Sound Louder Dual Cool™

EcoSPARK® and Better™ EfficientMax™ MegaBuck™

MICROCOUPLER™ ESBC™ MicroFET™ MicroPak™

Fairchild[®] MicroPak2™ Fairchild Semiconductor® MillerDrive™ FACT Quiet Series™ MotionMax™ FACT® FAST® mWSaver[©] OptoHiT™

FastvCore™ **OPTOLOGIC®** FETBench™ OPTOPLANAR®

PowerTrench® PowerXS™

Programmable Active Droop™

QFĔT¹ QS™ Quiet Series™ RapidConfigure™

Saving our world, 1mW/W/kW at a time™

SignalWise™ SmartMax™ SMART START™

Solutions for Your Success™

SPM® STEAL TH™ SuperFET® SuperSOT™-3 SuperSOT™-6 SuperSOT™-8 SupreMOS® SyncFET™

SYSTEM STERNER AL ST TinyBoost®

TinyBuck[®] TinyCalc™ TinyLogic[®] TINYOPTO™ TinyPower™ TinvPWM™ TinyWire™ TranSiC™ TriFault Detect™ TRUECURRENT®*

μSerDes™ UHC Ultra FRFET™ UniFFT™ VCX^{TM} VisualMax™ VoltagePlus™

XS™

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors

PRODUCT STATUS DEFINITIONS

Definition of Terms

Definition of Terms		
Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

Rev 166

^{*} Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdt/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exp

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor:

GBPC2501 GBPC2501W