

Bobbin Type Inductors

muRata PS Murata Power Solutions



FEATURES

- RoHS compliant
- Radial format
- -40°C to 85°C operating temperature
- Up to 13A loc
- 10µH to 22mH
- Low DC resistance
- Fully tinned leads
- PCB mounting hole
- Low temperature dependence
- Backward compatible with Sn/Pb soldering systems
- Custom parts available

DESCRIPTION

The 1400 Series is suitable for many power supply and other general purpose filtering applications. The use of a non-magnetic screw will ensure mechanical stability.



| SELECTION | GUIDE | | | | | | |
|----------------------|----------------|----------------------|----------------|----------|----------|------|--|
| | Inductance, | DC | DC | 0 -1 | £ 1.11= | CDE | Manhanias Dimensiona Fasturia |
| Order Code | (1kHz, 0.1Vac) | Current ¹ | Resistance | u at | f kHz | SRF | Mechanical Dimensions Footprin |
| Order Code | ±10% | Max. | Max. | No | m. | Nom. | a b c d Øe f Øg |
| | μH | A | Ω | Q | f | MHz | mm mm |
| 1410313C | 10 ±15% | 13 | 0.009 | 54 | 50 | 20.7 | 27.0 24.4 14.0 1.30 5.5 23.9 2.6 |
| 1415312C | 15 ±15% | 12 | 0.009 | 42 | 50 | 12.7 | 27.0 24.4 14.0 1.30 5.5 23.9 2.6 |
| 1422311C | 22 ±15% | 11 | 0.014 | 64 | 100 | 9.3 | 27.0 24.4 14.0 1.30 5.5 23.9 2.6 |
| 1433393C | 33 ±15% | 9.3 | 0.017 | 27 | 50 | 9.1 | 27.0 24.4 14.0 1.30 5.5 23.9 2.6 |
| 1447383C | 47 ±15% | 8.3 | 0.019 | 40 | 100 | 6.0 | 27.0 24.4 18.5 1.30 5.5 23.9 2.6 |
| 1447385C | 47 ±15% | 8.5 | 0.021 | 33 | 100 | 6.7 | 26.8 24.4 14.0 1.20 5.5 23.8 2.4 |
| 1468362C | 68 ±15% | 6.2 | 0.032 | 32 | 100 | 5.3 | 26.5 24.4 14.0 1.08 5.5 23.7 2. |
| 1468373C | 68 ±15% | 7.3 | 0.025 | 45 | 100 | 5.3 | 27.0 24.4 18.5 1.30 5.5 23.9 2.6 |
| 1410454C | 100 | 5.4 | 0.046 | 24 | 100 | 4.6 | 26.4 24.4 14.0 1.02 5.5 23.6 2.0 |
| 1410460C | 100 | 6.0 | 0.033 | 37 | 100 | 3.9 | 26.8 24.4 18.5 1.20 5.5 23.8 2.4 |
| 1410478C | 100 | 7.8 | 0.040 | 34 | 50 | 3.3 | 32.4 29.8 21.8 1.30 5.1 29.3 2.6 |
| 1415440C | 150 | 4.0 | 0.069 | 24 | 50 | 3.4 | 26.2 24.4 14.0 0.90 5.5 23.5 1.8 |
| 1415449C | 150 | 4.9 | 0.055 | 34 | 50 | 2.9 | 26.4 24.4 18.5 1.02 5.5 23.6 2.0 |
| 1415465C | 150 | 6.5 | 0.042 | 46 | 100 | 2.4 | 32.2 29.8 21.8 1.20 5.1 29.2 2.4 |
| 1422435C | 220 | 3.5 | 0.096 | 22 | 50 | 2.8 | 26.1 24.4 14.0 0.85 5.5 23.5 1.7 |
| 1422441C | 220 | 4.1 | 0.073 | 33 | 100 | 2.3 | 26.3 24.4 18.5 0.97 5.5 23.6 1.9 |
| 1422455C | 220 | 5.5 | 0.062 | 30 | 50 | 2.2 | 32.1 29.8 21.8 1.14 5.1 29.1 2.2 |
| 1430430C | 300 | 3.0 | 0.140 | 26 | 50 | 2.6 | 25.9 24.4 14.0 0.75 5.5 23.4 1.5 |
| 1430433C | 300 | 3.3 | 0.100 | 37 | 50 | 2.2 | 26.2 24.4 18.5 0.90 5.5 23.5 1.8 |
| 1430450C | 300 | 5.0 | 0.080 | 28 | 50 | 1.7 | 31.8 29.8 21.8 1.02 5.1 29.0 2.0 |
| 1433428C | 330 | 2.8 | 0.150 | 22 | 50 | 2.5 | 25.9 24.4 14.0 0.76 5.5 23.4 1.5 |
| 1433433C | 330 | 3.3 | 0.120 | 29 | 50 | 2.0 | 26.2 24.4 18.5 0.90 5.5 23.5 1.8 |
| 1433445C | 330 | 4.5 | 0.091 | 25 | 50 | 1.6 | 31.8 29.8 21.8 1.02 5.1 29.0 2.0 |
| 1447423C | 470 | 2.3 | 0.250 | 34 | 50 | 2.0 | 25.7 24.4 14.0 0.67 5.5 23.3 1.3 |
| 1447427C | 470 | 2.7 | 0.160 | 25 | 50 | 1.6 | 26.1 24.4 18.5 0.85 5.5 23.5 1.3 |
| 1447440C | 470 | 4.0 | 0.125 | 24 | 50 | 1.4 | 31.7 29.8 21.8 0.97 5.1 29.0 1.9 |
| 1468420C | 680 | 2.0 | 0.300 | 23 | 50 | 1.6 | 25.7 24.4 14.0 0.67 5.5 23.3 1.3 |
| 1468422C | 680 | 2.2 | 0.226 | 28 | 50 | 1.3 | 25.9 24.4 18.5 0.75 5.5 23.4 1.5 |
| 1468431C | 680 | 3.1 | 0.173 | 60 | 10 | 1.0 | 31.6 29.8 21.8 0.90 5.1 28.9 1.8 |
| 1410516C | 1.0mH | 1.6 | 0.460 | 30 | 50 | 1.4 | 25.6 24.4 14.0 0.60 5.5 23.2 1.2 |
| 1410517C | 1.0mH | 1.7 | 0.336 | 35 | 50 | 1.2 | 25.7 24.4 18.5 0.67 5.5 23.3 1.3 |
| 1410524C | 1.0mH | 2.4 | 0.277 | 33 | 50 | 1.0 | 31.4 29.8 21.8 0.79 5.1 28.8 1.5 |
| 1415513C | 1.5mH | 1.3 | 0.680 | 34 | 50 | 1.0 | 25.5 24.4 14.0 0.54 5.5 23.1 1.0 |
| 1415514C | 1.5mH | 1.4 | 0.550 | 47 | 50 | 0.8 | 25.6 24.4 18.5 0.60 5.5 23.2 1.2 |
| 1415517C | 1.5mH | 1.7 | 0.374 | 28 | 50 | 0.7 | 31.3 29.8 21.8 0.75 5.1 28.8 1.9 |
| 1422509C | 2.2mH | 0.9 | 1.000 | 43 | 50 | 0.9 | 25.3 24.4 14.0 0.48 5.5 23.1 0.9 |
| 14225120 | 2.2mH | 1.2 | 0.700 | 33 | 50 | 0.7 | 25.6 24.4 18.5 0.60 5.5 23.2 1.2 |
| 1422514C | 2.2mH | 1.4 | 0.622 | 33 | 50 | 0.6 | 31.1 29.8 21.8 0.67 5.1 28.7 1.3 |
| 14335070 | 3.3mH | 0.7 | 1.428 | 45 | 50 | 0.8 | 25.2 24.4 14.0 0.43 5.5 23.0 0.8 |
| 14335100 | 3.3mH 3.3mH | 1.0 | 1.992 0.930 | 20 | 50 | 0.7 | 25.5 24.4 18.5 0.54 5.5 23.1 1.0 31.0 29.8 21.8 0.60 5.1 28.6 1.2 |
| 1433512C | | | | 20 60 | 50 | 0.5 | |
| 1447506C 1447508C | 4.7mH 4.7mH | 0.6 | 2.200 1.600 | 60 65 | 50 50 | 0.6 | 25.2 24.4 14.0 0.39 5.5 23.0 0.7 25.3 24.4 18.5 0.48 5.5 23.1 0.9 |
| 1447509C | 4.7mH | 0.8 | 1.400 | 57 | 10 | 0.5 | 30.9 29.8 21.8 0.54 5.1 28.5 1.0 |
| 1447509C 1468505C | 4.7111FI | 0.9 | 2.880 | 50 | 50 | 0.5 | 25.2 24.4 14.0 0.39 5.5 23.0 0.7 |
| 1468507C | 6.8mH | 0.5 | 2.300 | 47 | 50 | 0.3 | 25.2 24.4 14.0 0.39 5.5 23.0 0.8 |
| 1468508C | 6.8mH | 0.7 | 2.100 | 30 | 50 | 0.4 | 30.7 29.8 21.8 0.48 5.1 28.5 0.9 |
| 1410604C | 10mH | 0.8 | 4.340 | 51 | 50 | 0.4 | 25.1 24.4 14.0 0.34 5.5 22.9 0.6 |
| 1410604C | 10mH | 0.4 | 3.600 | 48 | 50 | 0.4 | 25.2 24.4 18.5 0.39 5.5 23.0 0.7 |
| 1410605C | 10mH | 0.6 | 2.600 | 48 | 50 | 0.3 | 30.9 29.8 21.8 0.54 5.1 28.5 1.0 |
| 1415604C | 15mH | 0.6 | 5.500 | 61 | 10 | 0.2 | 25.1 24.4 18.5 0.34 5.5 22.9 0.6 |
| 1415605C | 15mH | 0.4 | 3.740 | 55 | 10 | 0.2 | 30.6 29.8 21.8 0.43 5.1 28.4 0.8 |
| 1422604C | 22mH | 0.4 | 6.962 | 30 | 50 | 0.2 | 30.5 29.8 21.8 0.34 5.1 28.3 0.6 |
| 14220040 | 4411111 | 0.4 | 0.302 | 50 | 50 | 0.2 | 00.0 20.0 21.0 0.04 0.1 20.5 0.0 |

¹ Maximum DC current occurs when either the inductance falls to 60% of its nominal value or when its temperature rise reaches 50°C, whichever is sooner.





Bobbin Type Inductors

| SOLDERING INFORMATION ² | |
|------------------------------------|----------------------|
| Peak wave solder temperature | 300°C for 10 seconds |
| Pin finish | Pure tin dip |

| ABSOLUTE MAXIMUM RATINGS | |
|--------------------------------------|----------------|
| Operating free air temperature range | -40°C to 85°C |
| Storage temperature range | -55°C to 125°C |


All specifications typical at T_A=25°C

2 For further information, please visit www.murata-ps.com/rohs

MECHANICAL DIMENSIONS a ±1.50 https://www.acceptages.com/acceptages/accepta

d ±0.05

Package weight: 30-65g Typ.



| PACKAGING DETAILS | |
|------------------------|---------------|
| 21.8mm height products | 15 per carton |
| All other products | 25 per carton |

www.murata.com

All dimensions in mm.

Dot indicates the innermost turn of the winding.

•

muRata Ps Murata Power Solutions

1400 Series

Bobbin Type Inductors

DISCLAIMER

Unless otherwise stated in the datasheet, all products are designed for standard commercial and industrial applications and NOT for safety-critical and/or life-critical applications.

Particularly for safety-critical and/or life-critical applications, i.e. applications that may directly endanger or cause the loss of life, inflict bodily harm and/or loss or severe damage to equipment/property, and severely harm the environment, a prior explicit written approval from Murata is strictly required. Any use of Murata standard products for any safety-critical, life-critical or any related applications without any prior explicit written approval from Murata shall be deemed unauthorised use.

These applications include but are not limited to:

- Aircraft equipment
- Aerospace equipment
- Undersea equipment
- Power plant control equipment
- Medical equipment
- Transportation equipment (automobiles, trains, ships, etc.)
- Traffic signal equipment
- Disaster prevention / crime prevention equipment
- Data Processing equipment

Murata makes no express or implied warranty, representation, or guarantee of suitability, fitness for any particular use/purpose and/or compatibility with any application or device of the buyer, nor does Murata assume any liability whatsoever arising out of unauthorised use of any Murata product for the application of the buyer. The suitability, fitness for any particular use/purpose and/or compatibility of Murata product with any application or device of the buyer remain to be the responsibility and liability of the buyer.

Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm, and take appropriate remedial actions. Buyer will fully indemnify and hold Murata, its affiliated companies, and its representatives harmless against any damages arising out of unauthorised use of any Murata products in any safety-critical and/or life-critical applications.

Remark: Murata in this section refers to Murata Manufacturing Company and its affiliated companies worldwide including, but not limited to, Murata Power Solutions.

This product is subject to the following operating requirements and the Life and Safety Critical Application Sales Policy:

Refer to: https://www.murata.com/en-eu/products/power/requirements

Murata Power Solutions (Milton Keynes). Ltd. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein on timply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are given to change without notice.

© 2021 Murata Power Solutions (Milton Keynes) Ltd.

www.murata.com