

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0530480510**
Status: **Active**
Overview: PicoBlade Connector System
Description: 1.25mm Pitch, PicoBlade PCB Header, Single Row, Right-Angle, Through Hole, Tin (Sn) Plating, Friction Lock, 5 Circuits, Tray, 2.30mm PC Tail Length

Documents:

2D Drawing (DXF)	Product Specification 510211010-PS-000 (PDF)
3D Model (PDF)	Product Specification PS-51021-010-001 (PDF)
2D Drawing DXF (PDF)	Application Specification 510210000-AS-000 (PDF)
3D Model	Packaging Specification SPK-53048-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General


Product Family	PCB Headers
Series	<u>53048</u>
Application	Signal, Wire-to-Board
Current Derating Order No	987651-3691
Overview	<u>PicoBlade Connector System</u>
Product Name	PicoBlade
UPC	800753565920

Physical

Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	3.50mm
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	133.000/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	0.80mm
Packaging Type	Tray
Pitch - Mating Interface	1.25mm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact 1.0A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

53048 Series

Mates With

PicoBlade Housing 51021
PicoBlade
Cable Assembly 15134

Voltage - Maximum

125V

Material Info

Reference - Drawing Numbers

Application Specification

510210000-AS-000

Packaging Specification

SPK-53048-001-001

Product Specification

510211010-PS-000, PS-51021-010-001

Sales Drawing

530480001-SD-000

This document was generated on 12/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[53048-0510](#)