ESD7381

ESD Protection Diode

Micro-Packaged Diodes for ESD Protection

The ESD7381 is designed to protect voltage sensitive components that require ultra-low capacitance from ESD and transient voltage events. Excellent clamping capability, low capacitance, low leakage, and fast response time, make these parts ideal for ESD protection on designs where board space is at a premium. Because of its low capacitance, it is suited for use in high frequency designs such as USB 2.0 high speed and antenna line applications.

Features

• Ultra-Low Capacitance: 0.37 pF

• Low Clamping Voltage

• Small Body Outline Dimensions: 0.60 mm x 0.30 mm

Low Body Height: 0.3 mmStand-off Voltage: 3.3 V

• Low Leakage

Insertion Loss: 0.030 dBmResponse Time is < 1 ns

• Low Dynamic Resistance $< 1 \Omega$

• IEC61000-4-2 Level 4 ESD Protection

• These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

• RF Signal ESD Protection

• RF Switching, PA, and Antenna ESD Protection

• Near Field Communications

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
IEC 61000-4-2 (ESD) Contact Air		±20 ±20	kV
Total Power Dissipation on FR-5 Board (Note 1) @ T _A = 25°C	P_D	250	mW
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	400	°C/W
Junction and Storage Temperature Range	T _J , T _{stg}	-40 to +125	°C
Lead Solder Temperature – Maximum (10 Second Duration)	TL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. $FR-5 = 1.0 \times 0.75 \times 0.62$ in.



ON Semiconductor®

www.onsemi.com





X3DFN2 CASE 152AF



PIN 1

ЕМ

E = Specific Device Code

M = Date Code

ORDERING INFORMATION

Device	Package	Shipping [†]
ESD7381MUT5G	X3DFN2 (Pb-Free)	10000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

See Application Note AND8308/D for further description of survivability specs.


1

ELECTRICAL CHARACTERISTICS

(T_A = 25°C unless otherwise noted)

` ''	,	
Symbol	Parameter	
I _{PP}	Maximum Reverse Peak Pulse Current	
V _C	Clamping Voltage @ I _{PP}	
V_{RWM}	Working Peak Reverse Voltage	
I _R	Maximum Reverse Leakage Current @ V _{RWM}	
V _{BR}	Breakdown Voltage @ I _T	
I _T	Test Current	

^{*}See Application Note AND8308/D for detailed explanations of datasheet parameters.



ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise specified)

Parameter	Symbol	Conditions	Min	Тур	Max	Unit
Reverse Working Voltage	V_{RWM}				3.3	V
Breakdown Voltage (Note 2)	V_{BR}	I _T = 1 mA	5.0			V
Reverse Leakage Current	I _R	V _{RWM} = 3.3 V		< 1.0	50	nA
Clamping Voltage (Note 3)	V _C	I _{PP} = 1 A			8.0	V
Clamping Voltage (Note 3)	V _C	I _{PP} = 3 A			10	V
ESD Clamping Voltage	V _C	Per IEC61000-4-2	See	Figures 1 a	nd 2	
Junction Capacitance	СЈ	$V_R = 0 \text{ V, } f = 1 \text{ Mhz}$ $V_R = 0 \text{ V, } f < 1 \text{ GHz}$		0.37 0.25	0.55 0.55	pF
Dynamic Resistance	R_{DYN}	TLP Pulse		0.32		Ω
Insertion Loss		f = 1 Mhz f = 8.5 GHz		0.030 0.573		dB

- 2. Breakdown voltage is tested from pin 1 to 2 and pin 2 to 1.
- 3. Non-repetitive current pulse at $T_A = 25$ °C, per IEC61000-4-5 waveform.





Figure 1. ESD Clamping Voltage Screenshot Positive 8 kV Contact per IEC61000-4-2


Figure 2. ESD Clamping Voltage Screenshot Negative 8 kV Contact per IEC61000-4-2

ESD7381



FREQUENCY (Hz)
Figure 5. RF Insertion Loss

FREQUENCY
Figure 6. Capacitance over Frequency



IEC 61000-4-2 Spec.

•				
Level	Test Volt- age (kV)	First Peak Current (A)	Current at 30 ns (A)	Current at 60 ns (A)
1	2	7.5	4	2
2	4	15	8	4
3	6	22.5	12	6
4	8	30	16	8




Figure 9. IEC61000-4-2 Spec




Figure 10. Diagram of ESD Test Setup

ESD Voltage Clamping

For sensitive circuit elements it is important to limit the voltage that an IC will be exposed to during an ESD event to as low a voltage as possible. The ESD clamping voltage is the voltage drop across the ESD protection diode during an ESD event per the IEC61000-4-2 waveform. Since the IEC61000-4-2 was written as a pass/fail spec for larger systems such as cell phones or laptop computers it is not clearly defined in the spec how to specify a clamping voltage

at the device level. ON Semiconductor has developed a way to examine the entire voltage waveform across the ESD protection diode over the time domain of an ESD pulse in the form of an oscilloscope screenshot, which can be found on the datasheets for all ESD protection diodes. For more information on how ON Semiconductor creates these screenshots and how to interpret them please refer to AND8307/D.






Figure 11. 8 X 20 µs Pulse Waveform


ESD7381

PACKAGE DIMENSIONS

X3DFN2, 0.62 x 0.32, 0.355P, (0201) CASE 152AF ISSUE A








NOTES

- DIMENSIONING AND TOLERANCING PER
 ASME V14 FM 1994
- ASME Y14.5M, 1994. 2. CONTROLLING DIMENSION: MILLIMETERS.

	MILLIMETERS		
DIM	MIN	MAX	
Α	0.25	0.33	
A 1		0.05	
b	0.22	0.28	
D	0.58	0.66	
Е	0.28	0.36	
е	0.355 BSC		
L2	0.17	0.23	

RECOMMENDED MOUNTING FOOTPRINT*



See Application Note AND8398/D for more mounting details

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns me rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Phone: 81-3-5817-1050

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor: ESD7381MUT5G