



Main

| | |
|-------------------------------|-----------------------------|
| Range of product | OsiSense XU |
| Series name | General purpose single mode |
| Electronic sensor type | Photo-electric sensor |
| Sensor name | XUB |
| Sensor design | Cylindrical M18 |
| Detection system | Diffuse |
| Material | Plastic |
| Line of sight type | Axial |
| Type of output signal | Discrete |
| Supply circuit type | DC |
| Wiring technique | 3-wire |
| Discrete output type | PNP |
| Discrete output function | 1 NO |
| Electrical connection | Cable |
| Cable length | 2 M |
| Product specific application | - |
| Emission | Infrared diffuse |
| [Sn] nominal sensing distance | 0.1 M diffuse |

Complementary

| | |
|---------------------------|---|
| Enclosure material | PBT |
| Lens material | PMMA |
| Maximum sensing distance | 0.15 M diffuse |
| Output type | Solid state |
| Add on output | Without |
| Wire insulation material | PvR |
| Status LED | 1 LED (yellow) for output state |
| [Us] rated supply voltage | 12...24 V DC with reverse polarity protection |
| Supply voltage limits | 10...36 V DC |
| Switching capacity in mA | <= 100 mA (overload and short-circuit protection) |
| Switching frequency | <= 500 Hz |
| Maximum voltage drop | <1.5 V (closed state) |
| Current consumption | 35 mA no-load |
| Maximum delay first up | 15 Ms |
| Maximum delay response | 1 Ms |

| | |
|------------------------|--------------------------------|
| Maximum delay recovery | 1 Ms |
| Setting-up | Without sensitivity adjustment |
| Diameter | 18 Mm |
| Length | 60 Mm |
| Net weight | 0.04 Kg |

Environment

| | |
|---------------------------------------|--|
| Product certifications | CE UL CSA |
| Ambient air temperature for operation | -25...55 °C |
| Ambient air temperature for storage | -40...70 °C |
| Vibration resistance | 7 gn, amplitude = +/- 1.5 mm (f = 10...55 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 30 gn (duration = 11 ms) conforming to IEC 60068-2-27 |
| IP degree of protection | IP67 double insulation conforming to IEC 60529 IP65 double insulation conforming to IEC 60529 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 88 G |
| Package 1 Height | 4.2 Cm |
| Package 1 width | 9.6 Cm |
| Package 1 Length | 13.2 Cm |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 22 |
| Package 2 Weight | 2.515 Kg |
| Package 2 Height | 15 Cm |
| Package 2 width | 30 Cm |
| Package 2 Length | 40 Cm |


Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |

Contractual warranty


| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions



Wiring Schemes

PNP Outputs



BN : Brown
BU : Blue
BK : Black

Detection Curves



1 : White 90%
2 : Grey 18%
Object 10 x 10 cm

Product Life Status : **Commercialised**