

# SPECIFICATION


## 1. SCOPE

This specification is applied to the piezo-element.

## 2. SPECIFICATION

(at 25 °C)

- |                           |   |                      |
|---------------------------|---|----------------------|
| 2.1 Resonant Frequency    | : | 6.0±1.0 KHz          |
| 2.2 Resonant Resistance   | : | 500 Ω max            |
| 2.3 Capacitance           | : | 12000pF±30% at 100Hz |
| 2.4 Input Voltage         | : | 30Vp-p max           |
| 2.5 Operating Temperature | : | -20~+50 °C           |
| 2.6 Storage Temperature   | : | -20~+60 °C           |
| 3. DIMENSION              | : | as per figure        |




TOLERANCES UNLESS NOTED OTHERWISE

.X ±  
.XX ±  
.XXX ±

90° FORMED +2°  
ANGLES -1°

FIRST ANGLE PROJECTION



DRAWN	
DESIGN	
CHECKED	
APPROVED	
DATE	<b>04.04.13</b>
CONTRACT NO.	
AGENCY APPROVAL	

KEPO MODEL NO.

**CBC1560BB**

DWG NO.

**OEM1086**

*KEPO CO., LTD.*

CUSTOMER

**QUARTZ-1LTD**

CUSTOMER NO.

VER	<b>1.0</b>	SCALE	
UNIT	mm	SHEET	

TEL: (+86)574-88370330  
FAX: (+86)574-88370329