



NOTES:

1. CAP FOR ENDP5EF, ENDP6PC AND ENDP6SPC.
2. IP67 RATED WHEN PROPERLY ASSEMBLED.
3. ALL PARTS SHIPPED ASSEMBLED.
4. MAX PANEL THICKNESS OF 0.110 [2.8].
5. MATERIALS:
 SCREW NUT - BLACK, THERMOPLASTIC
 STRAP - BLACK, THERMOPLASTIC RUBBER
 SCREW- STAINLESS STEEL
 GASKET- BLACK, EPDM RUBBER
6. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
					SIZE	WIDTH	MULT	LBS/M	TEMPER	
					UNLESS OTHERWISE SPECIFIED			FINISH		
					1. ALL DIMENSIONS IN INCHES [mm]			MATERIAL		
					- TWO PLACE DECIMALS ±0.02 [0.5]			SPEC No.		
					- THREE PLACE DECIMALS ±0.005 [0.13]			SCALE		
					FIRST USED ON			1:1		
A	28311	08/24/20	PC	TJK	DATE DRAWN	BY	CHKD	APVD	Switchcraft®	
REV	ECO NUMBER	DATE	BY	APVD	7/9/20	FM	FM	TJK		
REVISIONS					DO NOT SCALE DRAWING					SHEET 1 OF 1
					NAME WATERPROOF SCREW CAP, THREADED					
					PART No. ENDPCAP					REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[ENDPCAP](#)