1D23A Series Class D Inductor






Features

- Small Footprint
- · Shielded Design for low EMI
- Ferrite Material Designed for Audio Applications


Applications

• Class D Audio Amplifiers

Front View




Side View



Schematic







units: mm

Electrical Specifications

| Part No. | Ls ¹ | DCR | l _{sat} ⁵ | l _{DC} ⁴ |
|------------|-----------------|--------------|--------------------|-------------------|
| | (uH +/-20%) | (mOhms Max.) | (Adc) | (Adc) |
| 1D23A-100M | 10 | 9.6 | 37.8 | 9.4 |
| 1D23A-150M | 15 | 9.6 | 23.5 | 9.4 |
| 1D23A-220M | 22 | 9.6 | 18.5 | 9.4 |
| 1D23A-330M | 33 | 9.6 | 10.4 | 9.4 |

Notes:

- 1. Tested at 100kHz, 1Vrms series.
- 2. Electrical specifications at 25°C.
- 3. Operating range: -40 $^{\circ}\text{C}$ to +130 $^{\circ}\text{C}$. This is a combination of ambient plus temperature rise.
- 4. DC current through winding to cause a 40°C temperature rise at 25°C ambient.
- 5. DC current through the winding to cause a 10% drop in inductance
- 6. All products are RoHS-compliant.
- 7. Meets UL 94V-0



Specifications subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ICE Components:

1D23A-100M 1D23A-150M 1D23A-220M 1D23A-330M