


DETAIL "A"
CHAMFER
SCALE=10:1



NET IMPEDANCE (Z)			
Frequency	300 MHz	500 MHz	1 GHz
Nominal (REF)	64 Ω	74 Ω	85 Ω
Minimum	- Ω	59 Ω	- Ω



AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture

FERRITE CORE DIMENSIONS (SPEC) MM [Inches]:

A	9.52 [.375]	±	0.20 [.008]
B	5.08 [.200]	±	0.15 [.006]
C	10.00 [.394]	±	0.20 [.008]

WEIGHT/1000 2.50 kgs [5.52 Lbs]

NOTES: UNLESS OTHERWISE SPECIFIED

1. COSMETIC SPECIFICATION REFER TO WI-QA-038.

SCALE DRAWING 1:1

HFB095051-100

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.		Laird	
D	CHANGE THE CHAMFER ,ADD NOTE	08/28/14	QIU	PROJECT/PART NUMBER:		REV	DRAWN BY:
C	UPDATE FORMAT CHG CURVE & Z SPECS	03/25/03	JRK	HFB095051-100		D	JRK
B	CHANGE CHAMFER DETAIL FROM .021 CORRECT P/N IN SCALE DRAWING CHG TEST FIXTURE	09/05/02	JRK	DATE:	08/19/02	SCALE:	4:1
A	ORIGINAL DRAFT	08/19/02	JRK	CAD #	HFB095051-100-D	TOOL #	B0375
REV	DESCRIPTION	DATE	INT			MATERIAL: HF	