



PRODUCT NUMBER  
SEE TABLE



mat'l. code	surface	tolerance	projection	product family
ISO 1302	ISO 406	ISO 1101	INCH/MM	CARD CONN

tr	ecn	no	dr	date	tolerances unless otherwise specified	inches	mm	scale	title
NOTES	1 & 2							4:1	VERTICAL CARD CONNECTOR
F	V11848	JCS		7/2/91					CARD CONN
G	V23245	MRC		10/13/92					
H	V70789	MDR		8/14/97	0 ±.2				
J	V94468	MDR		1/7/00	dr	J.SURENER			
K	M05-0216	ERE		10/11/05	engr	M.HAHN			
L	M05-0210	MHT		6/03/06	chr	M.HAHN			
M	M07-0143	ERE		03/03/07	pppd	M.HAHN			

sheet	revision	M	M	M	M	M	M	M	M
1									
2									
3									
4									
5									
6									



type Product Customer Drawing  
sheet no 66951  
sheet 1 of 4 size A3

PRODUCT NUMBER  
SEE TABLE

NOTES:  
 ① HOUSING MATERIAL: FILLED POLYESTER, FLAME RETARDANT PER UL 94V-0.  
 COLOR: BLACK.

② TERMINAL MATERIAL:  
 BODY: BRASS  
 SPRING: BeCu, HEAT TREATED  
 BODY PLATING: 30u" / .76u Au OVER 50u" / 1.27u Ni IN CONTACT AREA.  
 100u" / 2.54u Sn (NOTE 9) OVER 50u" / 1.27u Ni ON SOLDER TAIL.  
 SPRING PLATING: GOLD FLASH

3. MARKED FCI PART NUMBER & DATE CODE LEGIBLE ON TUBE LABEL.
4. APPLICATION INFORMATION.  
 A. RECOMMENDED MOUNTING HOLE PATTERN IS SHOWN IN FIG. #1.  
 B. ALL MATING PINS TO BE .025 / .64 SQUARE ON TRUE CENTER OF GIVEN TERMINAL SPACINGS, WITHIN .015 / .38 DIAMETER.  
 C. SUGGESTED MATING PIN LENGTH, .210 ± .020 / 5.33 ± .51.
- ⑤ STAND-OFF CONFIGURATION:  
 BUMP OR RIB AT MANUFACTURERS' OPTION.
- ⑥ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ⑦ THESE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
8. THIS PART WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
- ⑨ "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."




FIG.1  
SCALE 5/1

mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406	ISO 1101	CARD CONN
lit ecn no dr	tolerance unless otherwise specified			title
M	angles	XXX.X/XXX.X	INCH/MM	VERTICAL CARD CONNECTOR
	in ecd	XXX.X/XXX.X	scale 4:1	100/2.54 CTR. SINGLE. ROW
	dr	J.SHREINER 12/11/90		dwg no
	engr	M.HAHN 12/11/90		66951
	chr	M.HAHN 12/11/90		sheet 2 of 4 size
	opppd	M.HAHN 12/11/90		A3
sheet	revision			type
index	sheet			Product Customer Drawing

1 2 3 4 5 6

PRODUCT NO	NO. OF POS	DIM A	DIM B	DESC P/N ON -8XX SERIES ONLY	LEAD FREE OPTION
66951-Y01	UNASSIGNED				
-Y02	1X2	.100/2.54	.200/5.08	WWWWW-02	NOTE 6,7
-Y03	1X3	.200/5.08	.300/7.62	WWWWW-03	
-Y04	1X4	.300/7.62	.400/10.16	WWWWW-04	
-Y05	1X5	.400/10.16	.500/12.70	WWWWW-05	
-Y06	1X6	.500/12.70	.600/15.24	WWWWW-06	
-Y07	1X7	.600/15.24	.700/17.78	WWWWW-07	
-Y08	1X8	.700/17.78	.800/20.32	WWWWW-08	
-Y09	1X9	.800/20.32	.900/22.86	WWWWW-09	
-Y10	1X10	.900/22.86	1.000/25.40	WWWWW-10	
-Y11	1X11	1.000/25.40	1.100/27.94	WWWWW-11	
-Y12	1X12	1.100/27.94	1.200/30.48	WWWWW-12	
-Y13	1X13	1.200/30.48	1.300/33.02	WWWWW-13	
-Y14	1X14	1.300/33.02	1.400/35.56	WWWWW-14	
-Y15	1X15	1.400/35.56	1.500/38.10	WWWWW-15	
-Y16	1X16	1.500/38.10	1.600/40.64	WWWWW-16	
-Y17	1X17	1.600/40.64	1.700/43.18	WWWWW-17	
-Y18	1X18	1.700/43.18	1.800/45.72	WWWWW-18	
-Y19	1X19	1.800/45.72	1.900/48.26	WWWWW-19	
-Y20	1X20	1.900/48.26	2.000/50.80	WWWWW-20	
-Y21	1X21	2.000/50.80	2.100/53.34	WWWWW-21	
-Y22	1X22	2.100/53.34	2.200/55.88	WWWWW-22	
-Y23	1X23	2.200/55.88	2.300/58.42	WWWWW-23	
-Y24	1X24	2.300/58.42	2.400/60.96	WWWWW-24	
66951-Y25	1X25	2.400/60.96	2.500/63.50	WWWWW-25	

DBS

NOTE 6,7

PRODUCT NO	NO. OF POS	DIM A	DIM B	DESC P/N ON -8XX SERIES ONLY	LEAD FREE OPTION
66951-Y01	UNASSIGNED				

mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406		CARD CONN
itr	ecn	no	dr	date
M				
angles		in		ecr
0° ±2'		XXXX.0/XXX.3		XXXX.000/XXXX.001
dr	J.SURENER	12/11/90	scale 4:1	
enr	M.HAHN	12/11/90	title	
chr	M.HAHN	12/11/90	VERTICAL CARD CONNECTOR	
pppd	M.HAHN	12/11/90	100/2.54 CTR. SINGLE. ROW	
sheet	revision	dwg no		sheet 3 of 4 size
index	sheet	66951		A3
		type		Product Customer Drawing

form: A3 1 2 3 4 5 6

PRODUCT NO	NO. OF POS	DIM A	DIM B	DESC P/N ON -8XX SERIES ONLY	LEAD FREE OPTION
66951-Y26	1X26	2.500/63.50	2.600/66.04	WWWWW-26	NOTE 6,7
-Y27	1X27	2.600/66.04	2.700/68.58	WWWWW-27	
-Y28	1X28	2.700/68.58	2.800/71.12	WWWWW-28	
-Y29	1X29	2.800/71.12	2.900/73.66	WWWWW-29	
-Y30	1X30	2.900/73.66	3.000/76.20	WWWWW-30	
-Y31	1X31	3.000/76.20	3.100/78.74	WWWWW-31	
-Y32	1X32	3.100/78.74	3.200/81.28	WWWWW-32	
-Y33	1X33	3.200/81.28	3.300/83.82	WWWWW-33	
-Y34	1X34	3.300/83.82	3.400/86.36	WWWWW-34	
-Y35	1X35	3.400/86.36	3.500/88.90	WWWWW-35	
66951-Y36	1X36	3.500/88.90	3.600/91.44	WWWWW-36	NOTE 6,7

mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406		CARD CONN
itr ecn no/dr	tolerances unless otherwise specified		INCH/MM	title
M	angles	xxxx.0/xx.x.3	scale 4:1	VERTICAL CARD CONNECTOR
	in edr	xxxx.000/xxx.xx.13		100/2.54 CTR. SINGLE. ROW
	dr	J.SURENER 12/11/90		dwg no
	enr	M.HAHN 12/11/90		66951
	chr	M.HAHN 12/11/90		sheet 4 of 4 size
	pppd	M.HAHN 12/11/90		A3
sheet	revision			type
index	sheet			Product Customer Drawing