

Specification Sheet

Part Number: 156-03943

Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

Two-piece assembly allows the mount to slide along the strap, ensuring proper orientation.

Cable tie is outside serrated to reduce bundle chafing.

Low profile cable tie helps bundle wires neatly to accommodate wire harnesses with smaller diameters.

Product Image

Low profile head won't snag on surrounding parts and wires.

2-Pc Low Profile Cable Tie/EC5A Edge Clip, 7.7"L, 1 - 3mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/bg

Article Number	156-03943
Type	LPT50REC5A
Color	Black (BK)
Quantity Per	bag

Product Description	HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place. EC5A orientation. The low profile cable tie features a compact, contoured head that uses less space in confined areas and reduces protrusions that might otherwise interfere with or damage adjacent wire insulation and hoses. The outside serration provides a smooth inside surface to further minimize indentation or damage to soft bundles while offering high tensile strength and low insertion force. The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature extremes. Edge clips are widely used for attaching cables and wires within automotive, trucking, heavy equipment, solar panel, wind power and white goods equipment manufacturing.
Short Description	2-Pc Low Profile Cable Tie/EC5A Edge Clip, 7.7"L, 1 - 3mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/bg
Global Part Name	LPT50REC5A-PA66HS/PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	7.7
Length L (Metric)	194.6
Fixation Method	EdgeClip, sideways, assembled, 2 piece
Identification Plate Position	none
Releasable Closure	No

Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.24
Bundle Diameter Min (Metric)	6.0
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	0.05
Height H (Metric)	1.20
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.08
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HIRHSUV PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C) -40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-03943](#)