


1N5817~1N5819



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.


Single phase, half wave, 60 Hz, resistive or inductive load.

PARAMETER	SYMBOL	1N5817	1N5818	1N5819	UNITS
Maximum Recurrent Peak Reverse Voltage	V _{rrm}	20 30 40			V
Maximum RMS Voltage	V _{rms}	14 21 28			V
Maximum DC Blocking Voltage	V _{DC}	20	30	40	V
Maximum Average Forward Current 0.375"(9.5mm) lead length (See Figure1)	I _{F(AV)}	1			A
Peak Forward Surge Current : 8.3ms single half sine-wave superimposed on rated load	I _{fsm}	25			А
Maximum Forward Voltage at 1A DC Maximum Forward Voltage at 3A DC	V _F	0.47 0.75	0.55 0.875	0.6 0.9	V
Maximum DC Reverse Current at Rated DC Blocking $T_j=25^{\circ}C$ Voltage $T_j=100^{\circ}C$	I _R	0.2 10		mA	
Typical Thermal Resistance	R _{eja}	80		°C / W	
Operating Junction and Storage Temperature Range	T _J ,T _{stg}	-55 to +125 -55 to +150		°C	



1N5817~1N5819

RATING AND CHARACTERISTIC CURVES







1N5817~1N5819

Part No_packing code_Version

1N5817_AY_00001
1N5817_AY_10001
1N5817_B0_00001
1N5817_B0_10001
1N5817_R2_00001
1N5817_R2_10001

For example :


RB500V-40_R2_00001



Serial number Version code means HF Packing size code means 13" Packing type means T/R

Packing Code XX			Version Code XXXXX			
Packing type	1 st Code	Packing size code	2 nd Code	HF or RoHS	1 st Code	2 nd ~5 th Code
Tape and Ammunition Box (T/B)	A	N/A	0	HF	0	serial number
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number
Bulk Packing (B/P)	В	13"	2			
Tube Packing (T/P)	т	26mm	X			
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y			
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U			
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D			





Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panjit:

<u>1N5819_F0_000A1</u> <u>1N5819_R2_00001</u> <u>1N5819_AY_000A4</u> <u>1N5819_F0_100A1</u> <u>1N5819_AY_100A4</u> <u>1N5819_R2_10001</u> <u>1N5819_AY_100A1</u> <u>1N5819_B0_00001</u> <u>1N5819_B0_10001</u> <u>1N5819_AY_00001</u> <u>1N5819_AY_10001</u>