


RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

100E Series Porcelain High RF Power Multilayer Capacitors



GENERAL DESCRIPTION

KYOCERA AVX, the industry leader, offers new improved ESR/ESL performance for the 100 E Series RF Capacitors. This high Q multilayer capacitor is ultra-stable under high RF current and voltage applications. High density porcelain construction provides a rugged, hermetic package. KYOCERA AVX offers an encapsulation option for applications requiring extended protection against arc-over and corona.

FUNCTIONAL APPLICATIONS

- Bypass
- Impedance Matching
- Coupling
- DC Blocking
- Tuning

CIRCUIT APPLICATIONS

- HF/RF Power Amplifiers
- Plasma Chambers
- Transmitters
- Medical (MRI coils)
- Antenna Tuning

ENVIRONMENTAL CHARACTERISTICS

Thermal Shock	Mil-STD-202, Method 107, Condition A
Moisture Resistance	Mil-STD-202, Method 106
Low Voltage Humidity	Mil-STD-202, Method 103, condition A, with 1.5 VDC applied while subjected to an environment of 85°C with 85% relative humidity for 240 hours
Life Test	MIL-STD-202, Method 108, for 2000 hours, at 125°C. Voltage applied. 200% of WVDC for capacitors rated at 500 volts DC or less. 120% of WVDC for capacitors rated at 1250 volts DC or less. 100% of WVDC for capacitors rated above 1250 volts DC
Termination Styles	Available in various surface mount and leaded styles. See Mechanical Configurations
Terminal Strength	Terminations for chips and pellets withstand a pull of 10 lbs. min., 25 lbs. typical, for 5 seconds in direction perpendicular to the termination surface of the capacitor.

FEATURES

- Case E Size (.380" x .380")
- Capacitance Range 1pF to 5100pF
- Extended WVDC up to 7200 VDC
- Low ESR/ESL
- High Q
- High RF Power
- Ultra-Stable Performance
- High RF Current/Voltage
- Available with Encapsulation Option*

* For leaded styles only

PACKAGING OPTIONS



Tape & Reel



Tray
(96 pcs)



ELECTRICAL SPECIFICATIONS

Temperature Coefficient (TCC)	90 ± 30 PPM/°C
Capacitance Range	1 pF to 5100 pF
Operating Temperature	-55°C to +125°C*
Quality Factor	Greater than 10,000 (1 pF to 1000 pF) @ 1 MHz. Greater than 10,000 (1100 pF to 5100 pF) @ 1 KHz.
Insulation Resistance (IR)	1 pF to 5100 pF 10 ⁵ Megohms min. @ 25°C at 500 VDC 10 ⁴ Megohms min. @ 125°C at 500 VDC
Working Voltage (WVDC)	See Capacitance Values table
Dielectric Withstanding Voltage (DWV)	250% of WVDC for capacitors rated at 500 volts DC or less for 5 seconds. 150% of WVDC for capacitors rated at 1250 volts DC or less for 5 seconds. 120% of WVDC for capacitors rated above 1250 Volts DC for 5 seconds
Aging Effects	None
Piezoelectric Effects	None
Capacitance Drift	± (0.02% or 0.02 pF), whichever is greater
Retrace	Less than ±(0.02% or 0.02 pF), whichever is greater.

RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

100E Series Porcelain High RF Power Multilayer Capacitors




CAPACITANCE VALUES

Cap. Code	Cap. (pF)	Tol.	Rated WVDC		Cap. Code	Cap. (pF)	Tol.	Rated WVDC		Cap. Code	Cap. (pF)	Tol.	Rated WVDC		CAP. CODE	CAP. (pF)	TOL.	RATED WVDC																		
			STD.	EXT.				STD.	EXT.				STD.	EXT.				STD.	EXT.																	
1R0	1.0	B, C, D	3600	7200	5R6	5.6	B, C, D	3600	7200	470	47	F, G, J, K, M	3600	TAGE	391	390	F, G, J, K, M	3600	N/A																	
1R1	1.1				6R2	6.2				510	51				431	430																				
1R2	1.2				6R8	6.8				560	56				471	470																				
1R3	1.3				7R5	7.5				620	62				511	510																				
1R4	1.4				8R2	8.2				680	68				561	560																				
1R5	1.5				9R1	9.1				750	75				621	620																				
1R6	1.6				EXTENDED VOLTAGE	100				10	820				82	EXTENDED VOLTAGE				910	91	7200	EXTENDED VOLTAGE	821	820	EXT.	102	1000	500	N/A						
1R7	1.7																														110	11	121	120	112	1100
1R8	1.8																														120	12	131	130	122	1200
1R8	1.9																														130	13	151	150	152	1500
2R0	2.0	150	15	161			160	182	1800																											
2R1	2.1	160	16	181			180	222	2200																											
2R2	2.2	180	18	201			200	272	2700																											
2R3	2.4	200	20	221			220	302	3000																											
2R4	2.7	220	22	241			240	332	3300																											
3R0	3.0	240	24	271			270	392	3900																											
3R0	3.3	270	27	301	300	472	4700																													
3R0	3.6	300	30	331	330	512	5100																													
3R0	3.9	330	33	361	360																															
4R3	4.3	360	36																																	
4R7	4.7	390	39																																	
5R1	5.1	430	43																																	

VRMS = 0.707 X WVDC

• SPECIAL VALUES, TOLERANCES, MATCHING, AND CAPACITOR ASSEMBLIES ARE AVAILABLE. • KYOCERA AVX CUSTOM POWER CAPACITOR ASSEMBLY CATALOG, LISTS ASSEMBLY OPTIONS. • DIFFERENT WORKING VOLTAGES ARE AVAILABLE • ENCAPSULATION OPTION AVAILABLE. PLEASE CONSULT FACTORY.

HOW TO ORDER



The above part number refers to a 100 E Series (case size E) 390 pF capacitor, K tolerance (±10%), 3600 WVDC, with W termination (Tin / Lead, Solder Plated over Nickel Barrier), laser marking and Tape and Reel packaging.

RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

100E Series Porcelain High RF Power Multilayer Capacitors



MECHANICAL CONFIGURATION

Series & Case Size	Term. Code	Case Size & Type	Outline W/T is a Termination Surface	Body Dimensions inches (mm)			Lead and Termination Dimensions and Material		Pkg Type & Qty	Pkg Code		
				Length (L)	Width (W)	Thickness (T)	Overlap (Y)	Materials				
100E	W	E Solder Plate		.380+.015-.010 (9.65+0.38-0.25)	.380 ±.010 (9.65 ±0.25)	.170 (4.32) max.	.040 (1.02) max.	Tin/Lead, Solder Plated over Nickel Barrier Termination	T&R, 250 pcs Tray, 24 or 96 pcs	T J24 J96		
100E	P	E Pellet		.380+.040-.010 (9.65+1.02-0.25)				Heavy Tin/Lead Coated, over Nickel Barrier Termination	T&R, 250 pcs Tray, 24 or 96 pcs	T J24 J96		
100E	T	E Solderable Nickel		.380+.015-.010 (9.65+0.38-0.25)				RoHS Compliant Tin Plated over Nickel Barrier Termination	T&R, 250 pcs Tray, 24 or 96 pcs	T J24 J96		
100E	MS	E Microstrip		.380+.035-.010 (9.65+0.89-0.25)			N/A	N/A	High Purity Silver Leads L _L = .750 (19.05) min W _L = .350 ±.010 (8.89 ±0.25) T _L = .010 ±.005 (0.25 ±0.13) Leads are Attached with High Temperature Solder.	Tray, 16 or 32 pcs	J16 J32	
100E	AR	E Axial Ribbon							Silver-plated Copper Leads Dia. = .032 ±.002 (.813 ±.051) L _L = 2.25 (57.2) min.	Tray, 16 or 32 pcs	J16 J32	
100E	AW	E Non-Mag Axial Wire								Silver-plated Copper Leads Dia. = .032 ±.002 (.813 ±.051) L _L = 1.0 (25.4) min.	Box, 20 pcs	B20
100E	RW	E Non-Mag Radial Wire									Tray, 16 or 64 pcs	J16 J64

Custom lead styles and lengths are available; consult factory. All leads are high purity silver attached with high temperature solder and are **RoHS** compliant.

RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

100E Series Porcelain High RF Power Multilayer Capacitors



MECHANICAL CONFIGURATION

Series & Case Size	Term. Code	Case Size & Type	Outline W/T is a Termination Surface	Body Dimensions inches (mm)			Lead and Termination Dimensions and Material		Pkg Type & Qty	Pkg Code	
				Length (L)	Width (W)	Thickness (T)	Overlap (Y)	Materials			
100E	WN	Non-Mag Solder Plate		.380±.015 -.010 (9.65±0.38-0.25)	.380 ±.010 (9.65 ±0.25)	.170 (4.32) max.	.040 (1.02) max.	Tin/Lead, Solder Plated over Non-Magnetic Barrier Termination	T&R, 250 pcs Tray, 24 or 96 pcs	T J24 J96	
100E	PN	Non-Mag Pellet		.380±.040 -.010 (9.65±1.02-0.25)				Heavy Tin/Lead Coated, over Non-Magnetic Barrier Termination	T&R, 250 pcs Tray, 24 or 96 pcs	T J24 J96	
100E	TN	Non-Mag Solderable Barrier		.380±.015 -.010 (9.65±0.38-0.25)				RoHS Compliant Tin Plated over Non-Magnetic Barrier Termination	T&R, 250 pcs Tray, 24 or 96 pcs	T J24 J96	
100E	MN	Non-Mag Microstrip		.380±.035 -.010 (9.65±0.89-0.25)			N/A	N/A	High Purity Silver Leads $L_L = .750$ (19.05) min $W_L = .350 \pm .010$ (8.89 ±0.25) $T_L = .010 \pm .005$ (0.25 ±0.13) Leads are Attached with High Temperature Solder.	Tray, 16 or 32 pcs	J16 J32
100E	AN	Non-Mag Axial Ribbon							Tray, 16 or 32 pcs	J16 J32	
100E	BN	Non-Mag Axial Wire							Box, 20 pcs	B20	
100E	RN	Non-Mag Radial Wire							Tray, 16 or 64 pcs	J16 J64	

Custom lead styles and lengths are available; consult factory. All leads are high purity silver attached with high temperature solder and are **RoHS** compliant.

RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

100E Series Porcelain High RF Power Multilayer Capacitors



SUGGESTED MOUNTING PAD DIMENSIONS





Horizontal
Electrode Orientation

Vertical
Electrode Orientation

Mount Type	Case E				
	Pad Size	A Min.	B Min.	C Min.	D Min.
Vertical Mount	Normal	.185	.050	.325	.425
	High Density	.165	.030	.325	.385
Horizontal Mount	Normal	.405	.050	.325	.425
	High Density	.385	.030	.325	.385

Dimensions are in inches.

PERFORMANCE DATA



RF/Microwave Capacitors


RF/Microwave Multilayer Capacitors (MLC)

100E Series Porcelain High RF Power Multilayer Capacitors




PERFORMANCE DATA


SERIES RESONANCE VS. CAPACITANCE
AVX SERIES 100, CASE E




CAPACITANCE CHANGE VS. TEMPERATURE
AVX SERIES 100, CASE E




CURRENT RATING VS. CAPACITANCE
AVX SERIES 100, CASE E



CURRENT RATING VS. CAPACITANCE
AVX Series 100, CASE E



CURRENT RATING VS. CAPACITANCE
AVX SERIES 100, CASE E, EXTENDED VOLTAGE



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kyocera AVX:

[100E8R2BT3600X](#) [100E9R1BT7200X](#) [100E4R7BT7200X](#) [100E2R7BT7200X](#) [100E1R6BT7200X](#)
[100E1R8BT7200X](#) [100E1R8BT7200XT](#) [100E1R0BT7200X](#) [100E1R5BW7200XT](#) [100E9R1BMN3600X](#)
[100E2R2BW7200XT](#) [100E8R2DBN3600X](#) [100E8R0BMS3600X](#) [100E8R2BT3600XT](#) [100E8R2BW3600XT](#)
[100E820KBN3600X](#) [100E7R5BAW3600X](#) [100E6R2BT3600XT](#) [100E6R2BMN3600X](#) [100E680GBN3600X](#)
[100E680KBN3600X](#) [100E5R2BMN3600X](#) [100E5R6BAR3600X](#) [100E5R6BTN3600X](#) [100E5R0BMS3600X](#)
[100E5R1BT3600X](#) [100E511GBN2500X](#) [100E4R7BAR7200X](#) [100E4R7BMS3600X](#) [100E4R0BMS3600X](#)
[100E3R3BAN3600X](#) [100E3R3BT7200X](#) [100E391KBN3600X](#) [100E3R0BMN3600X](#) [100E391GBN3600X](#)
[100E331KBN3600X](#) [100E330GBN3600X](#) [100E330KBN3600X](#) [100E2R4BMN3600X](#) [100E2R5BMS3600X](#)
[100E2R2BT3600X](#) [100E2R2BT7200X](#) [100E2R2BW3600X](#) [100E2R2BW7200X](#) [100E2R2BAR7200X](#)
[100E2R0BMN3600X](#) [100E2R0BMS3600X](#) [100E221KBN3600X](#) [100E220KBN3600X](#) [100E201GBN3600X](#)
[100E1R3BW3600X](#) [100E1R4BW3600X](#) [100E1R5BMS3600X](#) [100E1R5BW3600X](#) [100E1R2BMN3600X](#)
[100E1R2BMS3600X](#) [100E1R2DBN3600X](#) [100E1R0BAR3600X](#) [100E1R0BAR7200XC](#) [100E1R0BMS3600X](#)
[100E101KBN3600X](#) [100E101GBN3600X](#) [100E2R7BMS3600X](#) [100E9R1BAW3600X](#) [100E9R1BW3600X](#)
[100E8R2BW3600X](#) [100E8R2BWN3600X](#) [100E8R2BAR3600X](#) [100E8R2BAW3600X](#) [100E8R2BMN3600X](#)
[100E8R2BMS3600X](#) [100E8R2BP3600X](#) [100E8R2BTN3600X](#) [100E8R2BAN3600X](#) [100E7R5BT3600X](#)
[100E7R5BW3600X](#) [100E7R5BAN3600X](#) [100E7R5BMN3600X](#) [100E7R5BP3600X](#) [100E6R8BT3600X](#)
[100E6R8BTN3600X](#) [100E6R8BW3600X](#) [100E6R8BW3600XT](#) [100E6R8BWN3600X](#) [100E6R8BAN3600X](#)
[100E6R8BAR3600X](#) [100E6R8BMN3600X](#) [100E6R8BMS3600X](#) [100E6R8BP3600X](#) [100E6R2BMS3600X](#)
[100E6R2BT3600X](#) [100E6R2BW3600X](#) [100E680JBN3600X](#) [100E5R6DBN3600X](#) [100E5R6BT3600X](#)
[100E5R6BT3600XT](#) [100E5R6BW3600X](#) [100E5R6BW3600XT](#) [100E5R6BWN3600X](#) [100E5R6BAN3600X](#)