

NPN 50mA 120V High Voltage Amplifier transistors

Parameter	Value
$V_{\sf CEO}$	120V
I _C	50mA


Features

- 1) High Breakdown Voltage (V_{CEO}=120V).
- 2) Complementary PNP Types: 2SA1579 (UMT3) / 2SA1514K (SMT3)
- 3) Complex transistors :


IMX8 (SMT6)

4) Lead Free/RoHS Compliant.

Outline



•Inner circuit



Applications

High Voltage Amplifier

Packaging specifications

Part No.	Package	Package size (mm)	Taping code	Reel size (mm)	Tape width (mm)	Basic ordering unit (pcs)	Marking
2SC4102	UMT3	2021	T106	180	8	3,000	Tx ^{*1}
2SC3906K	SMT3	2928	T146	180	8	3,000	Tx ^{*1}

^{*1} x:h_{FE} rank

●Absolute maximum ratings (Ta = 25°C)

Parameter		Symbol	Values	Unit
Collector-base voltage		V _{CBO}	120	V
Collector-emitter voltage	ector-emitter voltage V _{CEO}		120	V
Emitter-base voltage		V_{EBO}	5	V
		I _C	50	mA
Collector current	Collector current		100	mA
Power dissipation 2SC4102 2SC3906K		P _D *2	200	mW
Junction temperature		T _j	150	°C
Range of storage temperature		T _{stg}	-55 to +150	°C

●Electrical characteristics(Ta = 25°C)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Collector-emitter breakdown voltage	BV _{CEO}	I _C = 1mA	120	ı	-	V
Collector-base breakdown voltage	BV _{CBO}	I _C = 50μA	120	ı	-	V
Emitter-base breakdown voltage	BV _{EBO}	I _E = 50μA	5	ı	-	V
Collector cut-off current	I _{CBO}	V _{CB} = 100V	-	ı	0.5	μΑ
Emitter cut-off current	I _{EBO}	V _{EB} = 4V	-	-	0.5	μА
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C = 10 \text{mA}, I_B = 1 \text{mA}$	-	ı	0.5	V
DC current gain	h _{FE}	$V_{CE} = 6V$, $I_C = 2mA$	180	ı	560	-
Transition frequency	f _T	$V_{CE} = 12V$, $I_E = -2mA$ $f=100MH_Z$	ı	140	ı	MHz
Output capacitance	Cob	$V_{CB} = 12V$, $I_E = 0mA$, $f = 1MHz$	-	2.5	-	pF

^{*1} P_W=100ms Single Pulse


●h_{FE} rank categories

Rank	R	S
h _{FE}	180 to 390	270 to 560

^{*2} Each terminal mounted on a reference footprint


●Electrical characteristic curves(Ta = 25°C)

Fig.1 Ground Emitter Propagation Characteristics



BASE TO EMITTER VOLTAGE : $V_{BE}[V]$

Fig.2 Typical Output Characteristics



COLECTOR TO EMITTE VOLTAGE : $V_{CE}[V]$

Fig.3 DC Current Gain vs. Collector Current(I)





Fig.4 DC Current Gain vs. Collector Current(II)





COLLECTOR CURRENT : I_C [mA]

100

●Electrical characteristic curves(Ta = 25°C)

Fig.6 Collector-Emitter Saturation Voltage Fig.5 Collector-Emitter Saturation Voltage vs. Collector Current (II) vs. Collector Current (I) Ta=25°C COLLECTOR-EMITTER SATURATION VOLTAGE : V_{CE(sat)} [V] SATURATION VOLTAGE: V_{CE(sat)} [V] $I_{\rm C}/I_{\rm B} = 50/1$ 20/1 Ta=100°C 10/1 25°C -40°C 0.1 0.1 COLLECTOR-EMITTER 0.01 0.01 0.1 10 0.1 10 COLLECTOR CURRENT : I_C [mA] COLLECTOR CURRENT : I_C [mA]






●Electrical characteristic curves(Ta = 25°C)


Fig.9 Emitter input capacitance vs. **Emitter-Base Voltage** Collector output capacitance vs. Collector-Base Voltage 100 COLLECTOR OUTPUT CAPACITANCE: Cob [pF] EMITTER INPUT CAPACITANCE: Cib [pF] Ta=25°C f=1MHz I_C=0A I_E=0A C_{ib} 10 0.1 10 100 COLLECTOR - BASE VOLTAGE : V_{CB} [V] EMITTER - BASE VOLTAGE : V_{EB} [V]

Fig.10 Safe Operating Area



COLLECTOR TO EMITTER VOLTAGE: V_{CE}[V]


Fig.11 Safe Operating Area



COLLECTOR TO EMITTER VOLTAGE : $V_{CE}[V]$

●Dimensions (Unit:mm)

UMT3



Pattern of terminal position areas [Not a recommended pattern of soldering pads]


DIM	MILIM	ETERS	INC	HES
DIM	MIN	MAX	MIN	MAX
Α	0.80	1.00	0.031	0.039
A1	0.00	0.10	0.000	0.004
A3	0.3	25	0.0	10
b	0.15	0.30	0.006	0.012
С	0.10	0.20	0.004	0.008
D	1.90	2.10	0.075	0.083
Е	1.15	1.35	0.045	0.053
е	0.0	65	0.026	
HE	2.00	2.20	0.079	0.087
L1	0.20	0.50	0.008	0.020
Lp	0.25	0.55	0.010	0.022
Q	0.10	0.30	0.004	0.012
Х	_	0.10	_	0.004

DIM MILIMETER		ETERS	INC	HES
DIIVI	MIN	MAX	MIN	MAX
b2	-	0.50	ı	0.020
e1	1.55		0.0	161
l1	-	0.65	-	0.026

Dimension in mm / inches

●Dimensions (Unit : mm)





Pattern of terminal position areas [Not a recommended pattern of soldering pads]

DIM	MILIMETERS		INC	HES
DIM	MIN	MAX	MIN	MAX
Α	1.00	1.30	0.039	0.051
A1	0.00	0.10	0.000	0.004
A3	0.2	25	0.0	10
b	0.35	0.50	0.014	0.020
С	0.09	0.25	0.004	0.010
D	2.80	3.00	0.110	0.118
E	1.50	1.80	0.059	0.071
е	0.9	95	0.0	37
HE	2.60	3.00	0.102	0.118
L1	0.30	0.60	0.012	0.024
Lp	0.40	0.70	0.016	0.028
Q	0.20	0.30	0.008	0.012
Х	_	0.10	_	0.004
У	_	0.10	_	0.004

DIM	MILIM	ETERS	S INCHES	
DIN	MIN	MAX	MIN	MAX
b2	_	0.60	-	0.024
e1	2.10		0.0	83
l1	_	0.90	_	0.035

Dimension in mm / inches

Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications:
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
- 7) The Products specified in this document are not designed to be radiation tolerant.
- 8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative: transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 9) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 11) ROHM has used reasonable care to ensur the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ROHM Semiconductor:

2SC3906KT146R 2SC3906KT146S 2SC4102T106R 2SC4102T106S