

SES® automatic stripping pliers of precision



SES®

SES-4010

| | |
|-------------------------|---|
| Material: | Zamak (zinc alloy) PVC insulated handles |
| Material blades: | special tool steel |
| Sections: | 0,15 to 10 mm² |
| Weight: | 360 g |
| Length: | 180 mm |

STANDARD



- For a precision work, with blades adapted to each size of cable.
- Flexible stripped cables stay round, ideal for the mounting of terminals or end sleeves.
- Synchronized opening and closing of the pliers with a single pressure of the handles.
- Automatic device of withhold of the jaws, avoiding the graining of the stripped filaments, before release of the thrust.

| type | tool with blade art. no. | | spare blade art. no. | | diameter mm | section mm ² |
|---|-----------------------------|---|-------------------------|---|---|---|
| ex: 4010-E: tool SES-4010 fitted with blade E | | | | | | |
| 4010-E* | 0401 0002 000 | 1 | 0401 0128 000 | 1 | 0,8 - 1 - 1,2 - 1,4 - 1,8 - 2,3 - 2,8 | 0,35 - 0,5 - 0,75 - 1 - 1,5 - 2,5 - 4 |
| 4010-L | 0401 0003 000 | 1 | 0401 0228 000 | 1 | 0,5 - 0,6 - 0,7 - 0,8 - 1 - 1,2 - 1,4 | 0,15 - 0,22 - 0,35 - 0,5 - 0,75 - 1 |
| 4010-R | 0401 0005 000 | 1 | 0401 0928 000 | 1 | 0,5 - 0,6 - 0,7 - 0,8 - 1 - 1,2 - 1,4 - 1,8 - 2,3 | 0,15 - 0,22 - 0,35 - 0,5 - 0,75 - 1 - 1,5 - 2,5 |
| 4010-P | 0401 0009 000 | 1 | 0401 0728 000 | 1 | 0,8 - 1 - 1,2 - 1,4 - 1,8 | 0,5 - 0,75 - 1 - 1,5 |
| 4010-T | 0401 0008 000 | 1 | 0401 0628 000 | 1 | 1,4 - 1,8 - 2,8 - 3,4 | 1,5 - 2,5 - 4 - 6 |
| 4010-S | 0401 0001 000 | 1 | 0401 0028 000 | 1 | 2,3 - 2,8 - 3,4 | 2,5 - 4 - 6 |
| 4010-F | 0401 0006 000 | 1 | 0401 0428 000 | 1 | 1,4 | 1,5 - 0,75x8 |
| 4010-C | 0401 0007 000 | 1 | 0401 0528 000 | 1 | 2,8 | 4 - 0,5x8 |
| 4010-Z | 0401 0120 000 | 1 | 0401 0220 000 | 1 | 1 - 1,2 - 1,8 - 3,2 | 1 - 2,5 - 6 |
| 4010-Y | 0401 0121 000 | 1 | 0401 0221 000 | 1 | 1 - 1,2 - 3,2 - 4,7 | 1 - 6 |
| 4010-H | 0401 0129 000 | 1 | 0401 0929 000 | 1 | 0,7 - 0,8 - 1 - 1,2 - 1,4 - 1,8 - 2,3 - 2,8 | 0,5 - 0,75 - 1 - 2,5 - 4 - 6 |
| 4010-K | 0401 0122 000 | 1 | 0401 0222 000 | 1 | 1 - 1,2 - 1,8 - 2,8 - 3,2 - 3,4 | 1 - 1,5 - 2,5 - 4 - 6 |
| 4010-B | 0401 0123 000 | 1 | 0401 0223 000 | 1 | 1,8 - 2,3 - 3,2 - 4 | 2,5 - 4 - 6 - 10 |
| 4010-US | 0401 0124 000 | 1 | 0401 0224 000 | 1 | 1 - 1,2 - 1,4 - 1,8 - 2,3 - 3,2 | 0,75 - 1 - 1,5 - 2,5 - 4 - 6 |

* popular model

Special blades

Special blades can be manufactured to strip wire sizes not covered by standard blades.

Please state number and diameters of cutting sections per blade (minimum cross section 0,75 mm²)

| number of strippers | art. no. |
|------------------------|---------------|
| 1 | 0415 0001 000 |
| 2 | 0415 0002 000 |
| 3 | 0415 0003 000 |
| 4 | 0415 0004 000 |
| 5 | 0415 0005 000 |
| 6 | 0415 0006 000 |

