anasonic

Automation Controls Catalog



mm inch





Recommended LED forward current 2 mA, High Sensitivity (Low current-consumption) Miniature SOP4-pin Type

FEATURES

1. High sensitivity (Low currentconsumption)

HS type PhotoMOS need less than half LED forward current of other types. This contributes to energy-saving working of equipment and longer operating life for battery.

Sensitivity comparison between HS type and GU type

In case of load voltage 60V type, SOP4-pin

		•			
			HS type (AQY232S)	GU type (AQY212S)	
-	LED operate current	Typical	0.35 mA	0.9 mA	
		Maximum	0.5 mA	3 mA	
	Recomme forward cu	ended LED Irrent	2 mA	5 mA	

2. Small package (SOP4-pin) 3. 60 V, 350 V and 400 V load voltage types available



TYPICAL APPLICATIONS

Ideal for battery-powered devices that need to lengthen operating life. Also recommended for powereconomizing of testing equipment that uses many relays.

1. Security equipment

• Crime-preventing system: Surveillance

camera, burglar alarm

• Disaster-preventing system: Fire alarm, heat/smoke sensor

- 2. Measuring instruments
- 3. Meters (watt-hour, gas, etc.)
- 4. Telecommunication equipment
- 5. Industrial equipment
- 6. Battery operating equipment

	Output rating*				Part No.	Packing quantity				
	Lood	Lood	Package	Tube packing style	Tape and reel	packing style		Tape and reel		
	voltage	current			Picked from the 1/2-pin side	Picked from the 3/4-pin side	Tube			
	60V	500mA	SOP4-pin	AQY232S	AQY232SX	AQY232SZ	1 tube contains:			
AC/DC dual use	350V	120mA		AQY230S	AQY230SX	AQY230SZ	100 pcs.	1,000 pcs.		
	400V	100mA		AQY234S	AQY234SX	AQY234SZ	2,000 pcs.			

Note: For space reasons, the three initial letters of the part number "AQY", the surface mount terminal indicator "S" and the packing style indicator "X" or "Z" are not marked on the device. (Ex. the label for product number AQY232SX is 232.) * Indicate the peak AC and DC values.

Ratings and packages other than those given above are available by special order. Please contact our sales office in your area.

RATING

TVDEC

1. Absolute maximum ratings	(Ambient temperature: 25°C 77°F))
-----------------------------	----------------------------------	---

	3 (,			
Item		Symbol	AQY232S	AQY230S	AQY234S	Remarks
	LED forward current	IF	50 mA			
Innut	LED reverse voltage	VR	5 V			
input	Peak forward current	IFP	1 A			f = 100 Hz, Duty factor = 0.1%
	Power dissipation	Pin	75 mW			
	Load voltage (peak AC)	VL	60 V	350 V	400 V	
Output	Continuous load current	١L	0.5 A	0.12 A	0.1 A	Peak AC, DC
Oulpul	Peak load current	Ipeak	1.5 A	0.3 A	0.24 A	100ms (1 shot), V∟ = DC
	Power dissipation	Pout	300 mW			
Total power dissipation			350 mW			
I/O isolation voltage			1,500 Vrms			
Ambient	Operating	Topr	−40 to +85°C −40 to +185°F		(Non-icing at low temperatures)	
temperature	Storage	Tstg	-40 to +100°C -40 to +212°F			

HS SOP 1 Form A (AQY23OS)

2. Electrical c	haracteristics (Ambient ter	nperature: 28	5°C / /°F)				-	
Item				AQY232S	AQY230S	AQY234S	Condition	
	I ED oporato current	Typical	le .		$\Delta I_{\text{F}}/\Delta t \ge 100 \ \mu\text{A/s}$ I_ = Max.			
		Maximum	IFON					
Input		Minimum	le "		$\Delta I_F / \Delta t \ge 100 \ \mu A/s$ IL = Max.			
input		Typical	Теоп					
	LED dropout voltage	Typical	Ve	1.2	– I⊧ = 50 mA			
		Maximum	VF	1.5 V				
	On resistance	Typical	Ron	0.85 Ω	19 Ω	27 Ω	$I_F = 2 \text{ mA}$	
Output		Maximum		2.5 Ω	25 Ω	35 Ω	Within 1 s	
	Off state leakage current	Maximum	Leak	1 μΑ			I⊧ = 0 mA V∟ = Max.	
	Turn on time*	Typical	-	1.5 ms	1.2 ms	0.8 ms	I⊧ = 2 mA	
		Maximum	Ion	5 ms			I∟ = Max.	
	Turn off time*	Typical	-	0.15 ms	0.1 ms	0.1 ms	I⊧ = 2 mA	
Iranster characteristics		Maximum	loff	2 ms			l∟ = Max.	
characteristics		Typical	0	0.8 pF			f = 1 MHz V _B = 0 V	
		Maximum	Ciso	1.5 pF				
	Initial I/O isolation resistance	Minimum	Riso	1,000 ΜΩ			500 V DC	

*Turn on/Turn off time



3. Recommended operating conditions (Ambient temperature: 25°C 77°F)

rease use under recommended operating conditions to obtain expected characteristics								
Ite	Symbol	Min.	Max.	Unit				
LED	lF	2	30	mA				
101/0206	Load voltage (Peak AC)	V∟	—	48	V			
AQ12323	Continuous load current	l.	—	0.5	А			
10/0208	Load voltage (Peak AC)	V∟	—	280	V			
AQ12303	Continuous load current	l.	—	0.12	А			
10/0240	Load voltage (Peak AC)	VL	—	320	V			
AQ 1 2345	Continuous load current	l.	_	0.1	A			

■ These products are not designed for automotive use.

If you are considering to use these products for automotive applications, please contact your local Panasonic Corporation technical representative.

REFERENCE DATA

1. Load current vs. ambient temperature characteristics

Allowable ambient temperature: -40 to +85°C -40 to +185°F



2. On resistance vs. ambient temperature characteristics

Measured portion: between terminals 3 and 4; LED current: 2 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)



3. Turn on time vs. ambient temperature characteristics

LED current: 2 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)



Panasonic Corporation Electromechanical Control Business Division industrial.panasonic.com/ac/e/

HS SOP 1 Form A (AQY23OS)

4. Turn off time vs. ambient temperature characteristics

LED current: 2 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)



7. LED dropout voltage vs. ambient temperature characteristics Sample: All types; LED current: 2 to 50 mA



9. Off state leakage current vs. load voltage characteristics

Measured portion: between terminals 3 and 4: Ambient temperature: 25°C 77°F



12. Output capacitance vs. applied voltage characteristics

Measured portion: between terminals 3 and 4; Frequency: 1 MHz (30 mVrms); Ambient temperature: 25°C 7



5. LED operate current vs. ambient temperature characteristics



8-(1). Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 3 and 4: Ambient temperature: 25°C 77°F



10. Turn on time vs. LED forward current characteristics

Measured portion: between terminals 3 and 4: Load voltage: Max. (DC); Continuous load current: Max. (DC); Ambient temperature: 25°C 77°F



6. LED turn off current vs. ambient temperature characteristics

Sample: All types; Load voltage: Max. (DC); Continuous load current: Max. (DC)



8-(2). Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 3 and 4; Ambient temperature: 25°C 77°F



11. Turn off time vs. LED forward current characteristics

Measured portion: between terminals 3 and 4: Load voltage: Max. (DC); Continuous load current: Max. (DC); Ambient temperature: 25°C 77°F



Sample: All types; Load voltage: Max. (DC); Continuous load current: Max. (DC)

"PhotoMOS", "PhotoMOS" and "PHOTOMOS" are registered trademarks of Panasonic Corporation. *Recognized in Japan, the United States, all member states of European Union and other countries.

Please contact

Panasonic Corporation Electromechanical Control Business Division

Electromechanical Control Business Division ■ 1006, Oaza Kadoma, Kadoma-shi, Osaka 571-8506, Japan industrial.panasonic.com/ac/e/



©Panasonic Corporation 2017

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic: AQY232S AQY232SX AQY232SZ