


150 V power Schottky rectifier



Features

- · High junction temperature capability
- Low leakage current
- · High voltage capabilities
- Good trade off between leakage current and forward voltage drop
- · Low thermal resistance
- · High frequency operation
- ECOPACK®2 compliant for TO-220AB and TO-247, on demand for D²PAK

Applications

- · Switching diode
- SMPS
- DC/DC converter
- Telecom power

Description

This dual center tab Schottky rectifier is suited for high frequency switched mode power supplies.

Packaged in TO-247, TO-220AB and D^2PAK , this STPS40150C is optimized for use to enhance the reliability of the application.

Product status				
STPS40150C				
Product summary				
I _{F(AV)} 2 x 20 A				
V _{RRM}	150 V			
T _{j(max.)}	175 °C			
V _{F(typ.)}	0.69 V			



1 Characteristics

Table 1. Absolute ratings (limiting values, per diode at 25 °C, unless otherwise specified)

Symbol	Parameter	Value	Unit			
V_{RRM}	Repetitive peak reverse voltage	150	V			
I _{F(RMS)}	Forward rms current			60	Α	
	Average feminard average \$ = 0.5 according to	T _C = 150 °C	Per diode	20	_	
^I F(AV)	$I_{F(AV)}$ Average forward current, δ = 0.5, square wave	T _C = 145 °C	Per device	40	Α	
I _{FSM}	Surge non repetitive forward current $t_p = 10 \text{ ms sinusoidal}$			250	Α	
P _{ARM}	Repetitive peak avalanche power $t_p = 10 \mu s, T_j = 125 ^{\circ}C$			1015	W	
T _{stg}	Storage temperature range	-65 to +175	°C			
Tj	Maximum operating junction temperature ⁽¹⁾				°C	

^{1.} $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 2. Thermal resistance parameters

Symbol	Parameter -		Value	Unit
Symbol			Max.	Oille
D.,	lunation to coop	Per diode	1.20	°C/W
R _{th(j-c)}	Junction to case Total		0.85	C/VV
R _{th(c)}	Coupling		0.50	°C/W

When the diodes 1 and 2 are used simultaneously:

 $\Delta T_{i \text{ (diode1)}} = P_{\text{(diode1)}} x R_{\text{th(i-c)}} \text{ (per diode)} + P_{\text{(diode2)}} x R_{\text{th(c)}}$

Table 3. Static electrical characteristics (per diode)

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
L (1)	Povorco logicado gurrent	T _j = 25 °C	$V_R = V_{RRM}$	-	2	8	μA
'R`	I _R ⁽¹⁾ Reverse leakage current	T _j = 125 °C		-	2	11	mA
	V _F ⁽²⁾ Forward voltage drop	T _j = 25 °C	I _F = 20 A	-		0.92	
V ₋ (2)		T _j = 125 °C		-	0.69	0.75	V
VF * /		T _j = 25 °C	I _F = 40 A	-		1.00	V
	T _j = 125 °C	1F - 40 A	-	0.79	0.86		

- 1. Pulse test: $t_p = 5$ ms, $\delta < 2\%$
- 2. Pulse test: t_p =380 μ s, δ < 2%

To evaluate the conduction losses, use the following equation: P = 0.64 x $I_{F(AV)}$ + 0.0055 x I_{F} 2 (RMS)

For more information, please refer to the following application notes related to the power losses :

- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses on a power diode

DS3262 - Rev 2 page 2/15



1.1 Characteristics (curves)

Figure 1. Average forward power dissipation versus average forward current (per diode) $P_{F(AV)}(W)$ 18 20

Figure 2. Average forward current versus ambient temperature (δ = 0.5, per diode) $I_{F(AV)}(A)$ Rth(i-a)=15°C/W δ=tp/

Figure 3. Normalized avalanche power derating versus pulse duration (T_j = 125 °C)




Figure 4. Relative variation of thermal impedance junction to case versus pulse duration




Figure 5. Reverse leakage current versus reverse voltage applied (typical values, per diode)





Figure 6. Junction capacitance versus reverse voltage applied (typical values, per diode)



DS3262 - Rev 2 page 3/15



Figure 7. Forward voltage drop versus forward current (per diode)





Figure 8. Thermal resistance junction to ambient versus copper surface under tab



page 5/15



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

2.1 D²PAK package information

- Epoxy meets UL94, V0
- Cooling method: by conduction (C)

D3202 - Rev 2






Figure 9. D²PAK package outline

Note: This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

DS3262 - Rev 2 page 6/15



Table 4. D²PAK package mechanical data

	Dimensions				
Ref.	Millim	neters	Inc	hes	
	Min.	Max.	Min.	Max.	
А	4.36	4.60	0.172	0.181	
A1	0.00	0.25	0.000	0.010	
b	0.70	0.93	0.028	0.037	
b2	1.14	1.70	0.045	0.067	
С	0.38	0.69	0.015	0.027	
c2	1.19	1.36	0.047	0.053	
D	8.60	9.35	0.339	0.368	
D1	6.90	8.00	0.272	0.311	
D2	1.10	1.50	0.043	0.060	
E	10.00	10.55	0.394	0.415	
E1	8.10	8.90	0.319	0.346	
E2	6.85	7.25	0.266	0.282	
е	2.54	typ.	0.100		
e1	4.88	5.28	0.190	0.205	
Н	15.00	15.85	0.591	0.624	
J1	2.49	2.90	0.097	0.112	
L	1.90	2.79	0.075	0.110	
L1	1.27	1.65	0.049	0.065	
L2	1.30	1.78	0.050	0.070	
R	0.4	typ.	0.0	15	
V2	0°	8°	0°	8°	






Figure 10. D²PAK recommended footprint (dimensions in mm)

DS3262 - Rev 2 page 8/15



2.2 TO-247 package information


• Epoxy meets UL94, V0

Cooling method: by conduction (C)

• Recommended torque value: 0.8 N·m

Maximum torque value: 1.0 N·m

Figure 11. TO-247 package outline



DS3262 - Rev 2 page 9/15



Table 5. TO-247 package mechanical data

			Dimer	nsions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	4.85		5.15	0.191		0.203
A1	2.20		2.60	0.086		0.102
b	1.00		1.40	0.039		0.055
b1	2.00		2.40	0.078		0.094
b2	3.00		3.40	0.118		0.133
С	0.40		0.80	0.015		0.031
D	19.85		20.15	0.781		0.793
E	15.45		15.75	0.608		0.620
е	5.30	5.45	5.60	0.209	0.215	0.220
L	14.20		14.80	0.559		0.582
L1	3.70		4.30	0.145		0.169
L2		18.50			0.728	
ØP	3.55		3.65	0.139		0.143
ØR	4.50		5.50	0.177		0.217
S	5.30	5.50	5.70	0.209	0.216	0.224

^{1.} Inches dimensions given for reference only

DS3262 - Rev 2 page 10/15



2.3 TO-220AB package information

Epoxy meets UL 94,V0

Cooling method: by conduction (C)
Recommended torque value: 0.55 N·m

Maximum torque value: 0.70 N⋅m

Figure 12. TO-220AB package outline




Table 6. TO-220AB package mechanical data

Dimensions						
Ref.	Millimeters		Ref. Millimeters		Incl	nes
	Min.	Max.	Min.	Max.		
А	4.40	4.60	0.173	0.181		
b	0.61	0.88	0.240	0.035		
b1	1.14	1.55	0.045	0.061		

DS3262 - Rev 2 page 11/15



	Dimensions				
Ref.	Millimeters		Inc	hes	
	Min.	Max.	Min.	Max.	
С	0.48	0.70	0.019	0.028	
D	15.25	15.75	0.600	0.620	
D1	1.27	typ.	0.050	O typ.	
E	10.00	10.40	0.394	0.409	
е	2.40	2.70	0.094	0.106	
e1	4.95	5.15	0.195	0.203	
F	1.23	1.32	0.048	0.052	
H1	6.20	6.60	0.244	0.260	
J1	2.40	2.72	0.094	0.107	
L	13.00	14.00	0.512	0.551	
L1	3.50	3.93	0.138	0.155	
L20	16.40 typ. 0.646 typ.		6 typ.		
L30	28.90 typ.		1.138	8 typ.	
θР	3.75	3.85	0.148	0.152	
Q	2.65	2.95	0.104	0.116	



3 Ordering information

Table 7. Order code

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPS40150CT	STPS40150CT	TO-220AB	1.95 g	50	Tube
STPS40150CW	STPS40150CW	TO-247	4.36 g	30	Tube
STPS40150CG	STPS40150CG	D²PAK	1.38 g	50	Tube
STPS40150CG-TR	STPS40150CG	D²PAK	1.38 g	1000	Tape and reel



Revision history

Table 8. Document revision history

Date	Revision	Changes
07-Sep-2006	1	First issue.
01-Jun-2018	2	Updated P_{ARM} value and removed "Normalized avalanche power derating" curves. Removed I^2PAK package information.

DS3262 - Rev 2 page 14/15



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics - All rights reserved

DS3262 - Rev 2 page 15/15